


PL-Q 2-PIN & 4-PIN Quadrant

PL-Q lamps are compact fluorescent lamps consisting of three double-bent parallel fluorescent tubes.



Product ID	C max.	C1 max.	D max.	D1 max.	E max.	F max.	U max.
16W	141	51	15	27.5	138	41	40
28W	207	77	24	33	205	41	49
38W	207	77	24	33	205	41	49

Dimensions in mm

MASTER PL-Q 2 PIN & 4 PIN

Shortcode	Wattage (W)	Cap Base	Luminous Flux Lamp (lm)	Average Lifetime (hrs)	Colour Rendering Index (Ra)	Colour Temp (K)	Min Order Quantity	Carton Qty
PLQ16W8272P	16	GR8	1050	10000	82	2700	1	10
PLQ16W8352P	16	GR8	1050	10000	82	3500	1	10
PLQ28W8274P	28	GR10Q	2050	13000	82	2700	1	10
PLQ28W8354P	28	GR10Q	2050	13000	82	3500	1	10
PLQ38W8354P	38	GR10Q	2850	13000	82	3500	1	10