


PL-S 2-PIN

PL-S lamps are compact, single ended fluorescent lamps, with two parallel tubes. They have either a 2-pin or 4-pin base incorporating a special instant starter and capacitor.



Product ID	A max.	B max.	C max.	D max.	D1 max.
5W 2P	67	83	105	28	13
7W 2P	97	113	135.0	28	13
9W 2P	129	145	167.0	28	13
11W 2P	198	214	235.8	28	13

Dimensions in mm

PL-S 2-PIN

Shortcode	Wattage (W)	Cap Base	Luminous Flux Lamp (lm)	Average Lifetime (hrs)	Colour Temp (K)	Min Order Quantity	Carton Qty
PLS5W8402P	5	G23	250	10000	4000	1	50
PLS7W8272P	7	G23	400	10000	2700	25	25
PLS7W8402P	7	G23	400	10000	4000	1	25
PLS9W8272P	9	G23	600	10000	2700	1	25
PLS9W8402P	9	G23	600	10000	4000	1	25
PLS11W8272P	11	G23	900	10000	2700	25	25
PLS11W8402P	11	G23	900	10000	4000	1	25