


# Plusline Pro – Compact / Small / Large

These high performance, general purpose, linear halogen lamps give perfect colour rendition. These lamps feature two arc prevention fuses built-in for added safety. The burning position is universal on the compact and small types. Used mainly for outdoor floodlighting applications.



Product ID	Description	Overall Length B nom.	Diameter Length C max.	Overall Length D max.
1000W	LARGE	185.7	189.1	11
1500W	LARGE	250.7	254.1	11

Dimensions in mm

## Plusline - Compact / Small / Large

Shortcode	Wattage (W)	Cap Base	Voltage	Bulb Shape	Luminous Flux Lamp (lm)	Average Lifetime (hrs)	Colour Temperature (K)	Unit	Carton Quantity	Trade Price
100PLUS	100	R7	240V	R7	1550	2000	2900	PCE	10	\$17.35
150PLUS	150	R7	240V	R7	2400	2000	2900	PCE	12	\$17.35
200PLUS	200	R7	240V	R7	3000	2000	2900	PCE	10	\$17.35
300PLUS	300	R7	240V	R7	5000	2000	2900	PCE	10	\$17.35
500PLUS	500	R7	240V	R7	9660	2000	2900	PCE	12	\$17.35
1000PLUS	1000	R7	240V	R7	21500	2000	2900	PCE	10	\$17.35
1500PLUS	1500	R7	240V	R7	33000	2000	2900	PCE	10	\$17.35