


Reflector Standard Floodline

Reflector lamps based on advanced spotlighting technology. Used for display lighting in shops, hotels, restaurants and homes.



Product ID	Overall Length C max.	Diameter D max.
R80 B22	113	80
R80 E27	114.5	80

Dimensions in mm

Reflector Standard Floodline

Shortcode	Wattage (W)	Cap Base	Voltage	Bulb Shape	Luminous Intensity (cd)	Average Lifetime (hrs)	Colour Temperature (K)	Unit	Carton Quantity	Trade Price
60ESFLOOD	60	E27	240V	R80	270	1000	2700	PCE	6	\$3.77
75ESFLOOD	75	E27	240V	R80	360	1000	2700	PCE	6	\$3.77
100ESFLOOD	100	E27	240V	R80	530	1000	2700	PCE	6	\$3.77