


Reflector Ring Mirror

Reflector lamps based on advanced spotlighting technology. Used for display lighting in shops, hotels, restaurants and homes.



Product ID	Overall Length Diameter	
	C max.	D max.
R39 E14	67	39
NR50 E14	86	50
NR63 E27	104.5	63

Dimensions in mm

Reflector Ring Mirror

Shortcode	Wattage (W)	Cap Base	Voltage	Bulb Shape	Luminous Intensity (cd)	Average Lifetime (hrs)	Colour Temperature (K)	Unit	Carton Quantity	Trade Price
30R39SPOT	30	E14	240V	R39	160	1000	2700	PCE	12	\$3.43
40R50SPOT	40	E14	240V	R50	400	1000	2700	PCE	10	\$3.43
60R63SPOT	60	E27	240V	R63	1050	1000	2700	PCE	8	\$3.43