


SON-H

High Pressure Sodium lamp with opalized outer bulb retrofit for High Pressure Mercury lamps. An instant and cost-effective upgrade of light level and reduction of energy use when replacing HPL lamps.



Product ID	C max.	D max.
110W	156	71
220W	227	91

Dimensions in mm

SON-H

Shortcode	Description	Wattage (W)	Cap Base	Voltage	Colour Rendering Index (Ra)	Luminous Flux (lm)	Average Lifetime (hrs)	Colour Temp (K)	Min Order Qty	Carton Qty
SONH110	SON H 110W I E27 1CT/24	110W	E27	107	25	9600	28000	2000	24	24
SONH220	SON H 220W E40 SLV/12	220W	E40	120	25	19000	26000	2000	12	12