


# SON-T

High Pressure Sodium lamps with clear tubular outer bulb.



| Product ID | C max. | D max. | L nom. | O nom. |
|------------|--------|--------|--------|--------|
| 150W       | 209    | 47     | 132    | 58     |
| 250W       | 255    | 47     | 158    | 66     |
| 400W       | 286    | 47     | 175    | 82     |
| 1000W      | 390    | 66     | 240    | 145    |

Dimensions in mm

## SON-T

| Shortcode | Description             | Wattage (W) | Cap Base | Luminous Flux (lm) | Average Lifetime (hrs) | Colour Rendering Index (Ra) | Colour Temp (K) | Min Order Qty | Carton Qty |
|-----------|-------------------------|-------------|----------|--------------------|------------------------|-----------------------------|-----------------|---------------|------------|
| SONT150   | SON-T 150W E E40 SLV/12 | 150         | E40      | 15000              | 28000                  | 25                          | 2000            | 1             | 12         |
| SONT250   | SON-T 250W E E40 SLV/12 | 250         | E40      | 28000              | 28000                  | 25                          | 2000            | 1             | 12         |
| SONT400   | SON-T 400W E E40 SLV/12 | 400         | E40      | 48000              | 28000                  | 25                          | 2000            | 1             | 12         |
| SONT1000  | SON-T 1000W E E40 SLV/4 | 1000        | E40      | 130000             | 20000                  | 25                          | 2000            | 1             | 4          |