


SON-T PIA

High Pressure Sodium lamp with clear tubular outer bulb, high lumen output that is maintained over life and Unique Philips Integrated Antenna (PIA) concept enabling long and reliable lifetime. Robust construction with few welding points is highly vibration- and shock-resistant, further reducing early failures and extending lamp life.



Product ID	C max.	D max.	L nom.	O nom.
150W	209	47	132	58
250W	255	47	158	66
400W	286	47	175	82
1000W	390	66	240	145

Dimensions in mm

SON-T PIA

Shortcode	Description	Wattage (W)	Cap Base	Voltage	Colour Rendering Index (Ra)	Luminous Flux (lm)	Average Lifetime (hrs)	Colour Temp (K)	Min Order Qty	Carton Qty
SONT50PLUS	SON-T PIA PLUS 50W E E27 SLV/12	50	E27	91	25	4400	30000	2000	1	12
SONT70PLUS	MST SON-T PIA Plus 70W E27 1SL/12	70	E27	93	25	6600	28000	2000	1	12
SONT100PLUS	MST SON-T PIA Plus 100W E40 1SL/12	100	E40	100	25	10700	28000	2000	1	12
SONT150PLUS	MST SON-T PIA Plus 150W E40 1SL/12	150	E40	100	25	18000	32000	2000	1	12
SONT250PLUS	MST SON-T PIA Plus 250W E40 1SL/12	250	E40	100	25	33000	36000	2000	1	12
SONT400PLUS	SON-T PIA PLUS 400W E E40 SLV/12	400	E40	100	25	55800	36000	2000	1	12
SONT600PLUS	SON-T PIA PLUS 600W E40 SLV/12	600	E40	115	25	90000	30000	2000	1	12