


# Sodium Lamps

High pressure sodium vapour lamps have a sintered aluminium oxide discharge tube enclosed in an internally coated outer bulb. They offer a long, reliable lifetime and have excellent lumen maintenance. SON lamps require control gear to operate and have a universal burning position.



Product ID	C max.	D max.
50W, 70W	156	71
150W, 250W	226	91
400W	290	122

Dimensions in mm

## SODIUM LIGHT

Shortcode	Description	Wattage (W)	Cap Base	Voltage	Colour Rendering Index (Ra)	Luminous Flux (lm)	Average Lifetime (hrs)	Colour Temp (K)	Min Order Qty	Carton Qty	Trade Price
SON50	SON 50W E E27 CO CRP/24	50	E27	85	25	3500	28000	2000	1	24	\$60.00
SON50I	SON 50W I E27 CRP/24	50	E27	85	25	3500	28000	2000	1	24	\$66.00
SON70	SON 70W E E27 CO ICT/24	70	E27	90	25	5600	28000	2000	1	24	\$60.00
SON70I	SON 70W/220 I E27 ICT/24	70	E27	90	25	5600	28000	2000	1	24	\$66.00
SON100PLUS	SON PLUS 100W E E40 SLV/12	100	E40	100	25	9700	36000	2000	1	12	\$72.00
SON150	SON 150W E E40 CO SLV/12	150	E40	100	25	13750	28000	2000	1	12	\$80.00
SON250	SON 250W E E40 CO SLV/12	250	E40	100	25	27000	28000	2000	1	12	\$84.00
SON400	SON 400W E E40 CO SLV/12	400	E40	105	25	48000	28000	2000	1	12	\$88.00