


TL-D Standard Colours

Low-wattage standard colour tubes with shorter length and moderate colour rendering.



| Product ID | A max. | B max. | C max. | D max. |
|------------|--------|--------|--------|--------|
| 10W | 331.5 | 338.6 | 345.7 | 28 |
| 15W | 437.4 | 444.5 | 451.6 | 28 |

Dimensions in mm

TL-D STANDARD COLOURS

| Shortcode | Wattage (W) | Cap Base | Luminous Flux Lamp (lm) | Average Lifetime (hrs) | Colour Rendering Index (Ra) | Min Order Quantity | Carton Quantity |
|-----------|-------------|----------|-------------------------|------------------------|-----------------------------|--------------------|-----------------|
| TLD10W33 | 10 | G13 | 520 | 10000 | 60 | 25 | 25 |
| TLD15W33 | 15 | G13 | 960 | 10000 | 63 | 9 | 9 |