


TL-E Circular Super 80

A range of simple, yet decorative shaped circular fluorescent lamps. To provide non-directional light in decorative or functional fittings.



Product ID	D max.	E max.	I max.
22W	30.9	215.9	157.5
32W	30.9	304.8	246.1
40W	30.9	406.4	347.7

Dimensions in mm

TL-E Circular Super 80

Shortcode	Wattage (W)	Cap Base	Luminous Flux Lamp (lm)	Average Lifetime (hrs)	Colour Rendering Index (Ra)	Colour Temperature (K)	Min Order Quantity	Carton Quantity
TLE22W840	22	G10q	1285	9000	85	4000	20	20
TLE22W865	22	G10q	1250	9000	85	6500	20	20
TLE32W840	32	G10q	2130	9000	85	4000	20	20
TLE32W865	32	G10q	2130	9000	85	6500	20	20
TLE40W865	40	G10q	3100	9000	85	6500	20	20