


TL Miniature

Miniature tubes with 16mm diameter. Suited to orientation or compact lighting applications, and where space is limited.



Product ID	A max.	B max.	C max.	D max.
6W TL	212.1	219.2	226.3	16
8W TL	288.3	295.4	302.5	16
13W TL	516.9	524	531.1	16

Dimensions in mm

TL Miniature

Shortcode	Wattage (W)	Cap Base	Luminous Flux Lamp (lm)	Average Lifetime (hrs)	Colour Rendering Index (Ra)	Colour Temperature (K)	Min Order Quantity	Carton Quantity
TL6W33	6	G5	260	10,000	60	4100	10	10
TL8W33	8	G5	410	5,000	60	4100	25	250
TL13W33	13	G5	930	8,000	60	4100	25	250