


# TL-X XL Instant Start

Instant start safety lamps specifically designed for use in potentially explosive atmospheres. Internal ignition switch and nickel single pin caps. Must be used with explosion-proof ballasts in flameproof or increased safety fittings.



Product ID	A max.	B max.	C max.	D max.
20W	574	592.5	611	40.5
40W	1183.5	1202	1220.5	40.5
65W	1484.1	1502.6	1521.1	40.5

Dimensions in mm

## TL-X XL Instant Start

Shortcode	Wattage (W)	Cap Base	Luminous Flux Lamp (lm)	Average Lifetime (hrs)	Colour Temperature (K)	Min Order Quantity	Carton Quantity
TLXXL20W33	20	FA6	1100	26000	4100	25	25
TLXXL40W33	40	FA6	2350	26000	4100	25	25
TLXXL65W33	65	FA6	4400	26000	4100	25	25