




## CoreLine Waterproof

CoreLine Waterproof LED is a direct replacement for traditional fluorescent waterproof luminaires, in terms of light performance, installation flexibility and length. With similar look and feel to traditional battens, this diffused luminaire will save up to 50% in energy, and will last 50,000 hours, hence reducing maintenance costs.



### Features and Benefits

- Up to 50% lower energy consumption compared to TL-D.
- Reliable LED technology – maintenance free.
- Direct substitute to conventional waterproofs in light performance, installation flexibility & length.
- Substitute available for 2X18W/1X36W/2X36W/1X58W/2X58W TL-D.
- Sleek design to create traditional look and feel.
- Wide-beam light distribution.
- Diffuser with optical element ensures visual comfort.
- Ceiling-mounted bracket and suspension hooks included; installation can be made vandal-proof by additional screw fixation of mounting brackets.
- EL3 Emergency option compliant to AS/NZS 2293.
- Central cable entry and through wiring possible.



Model	W (mm)	H (mm)	L (mm)
2ft	87	82	661
4ft	87	82	1223
5ft	87	82	1504

Dimensions in mm (Nominal)

### CORELINE WATERPROOF BATTEN

Family Name	CoreLine Waterproof Batten	Installation	Surface Mounted, Suspension Hook
Model	WT120C - Standalone version	IP rating	IP65
Lumen/ Watt	6000lm/ 57W 4000lm/ 41W 3400lm/ 29W 2200lm/ 23W 1800lm/ 19W	IK Rating	IK08
CCT	4000K	Weight	1500mm - 1.82kg 1200mm - 1.53kg 600mm - 1kg
Colour Rendering Index (CRI)	≥80	Colour of housing	Light Grey
Lifetime (L70)	50,000hrs	Application	Industry, F&B, Parking, Semi Outdoor, Under Canopy
Unified Glare Ratio (UGR)	23	Accessories (Included)	Mounting bracket (2pcs), suspension hook (2pcs), anti-vandal screws (2pcs), grommet (2pcs), cable gland (2pcs)
Optics	Symmetrical wide beam		
Driver	Philips titanium driver		
Dimmable	PSU fixed output		