



Core Range LED Batten

The Core Range LED batten combines the technology of the successful Greenperform batten range with the addition of 58W replacement models.

Using between 20 – 60W of power, there is up to 60% energy savings when compared to traditional Philips TL-D Fluorescent lamps. The Core Range has been developed for the New Zealand 58W market and provides both the contractor and end user with a wider range of options for general lighting needs.




Features and Benefits

- Designed for the NZ market.
- Choice of models for greater flexibility.
- Energy savings of up to 45% compared to Philips 2x 58W battens.
- Long lifetime - Up to 40,000 hrs @L70.

Applications

- Industry
- Corridors
- Supermarkets
- Storerooms
- Commercial



Dimension	A	B	C	D
2000/4000 lumen	57mm	58mm	1170mm	828+/-20mm
6000 lumen	57mm	58mm	1420mm	1126+/-20mm

Dimensions in mm (Nominal)

CORE RANGE LED BATTEN

Family Name	Core Range LED Battens
Lumen/Watt	2000 lm @ 4 FT 4000 lm @ 4 FT 6000 lm @ 5 FT
Temperature (CCT)	NW 4000/ CW 6500
Index (CRI)	≥80
Lifetime (L70)	40,000hrs
PF	>90
Input voltage	220-240V 50/60 HZ

Optics	Clear/Frost
Dimmable	NA
Installation	Surfaced (clips in pack) Standalone/Trunkable
Colour of Housing	White
Application	General/Commercial lighting