



## Coreline Wallmount

The elegant design looks good across a variety of applications, including hallways, stairways and garages. The homogenous soft lighting effect is easy on the eye – and it's easy on energy too. In fact, the Coreline Wallmount is up to 55% more energy efficient than traditional luminaires with PL-C lamps.

Installation is simplicity itself with just two luminaire parts to handle.

Flexibility is a big benefit with the Coreline Wall Mounted. The range provides all your application requirements, with a variety of light levels, built in controls, and IP65 and IK10 certification. Emergency option available.



---

### Features and Benefits


- Up to 55% energy savings compared to other luminaires with PL-C lamps.
- The unobtrusive styling is perfect for a variety of applications.
- Homogenous soft lighting effect.
- Up to 50,000 hours @L70 lifetime makes this a true fit and forget solution.
- Available in white or dark grey housings.

### Applications

- Residential
- Offices and stairways
- Hospitality
- Garages

---

### WL120V



### WL121V

