





Pacific LED Waterproof

Pacific LED Waterproof batten is a high performance luminaire, replacing traditional fluorescent fittings. With comparable lumen outputs, Pacific LED will save up to 50% energy, and lasts 50,000 hours. Further savings can be achieved through DALI dimming, and comes in a variety of lengths and beam angles. There is also a chemical resistance option, and multiple wiring options.



Features and Benefits

- Point-to-point replacement of high performance TL-D waterproof luminaires up to 2 x 58W.
- Energy savings up to 50%, dimmable (DALI) for even more savings.
- Significant lower maintenance cost due to high system lifetime.
- Multiple Beam angles, lengths, and wiring connections.
- Easy to install and maintain.
- Suitable for use in freezers down to minus 30°C.



Model	W (mm)	H (mm)	L (mm)
2ft	96	96	721
4ft	96	96	1342
5ft	96	96	1642

Dimensions in mm (Nominal)

PACIFIC LED WATERPROOF BATTEN			
Family Name	Pacific LED G3	Installation	Surface Mounted
Model	WT460C - Standalone Version WT461C - Chemical Resistance Version	IP rating	IP66
Lumen/ Watt	6400lm/ 64W 4200lm/ 39W 3500lm/ 28W 2300lm/ 24W	IK Rating	IK08
CCT	4000K	Weight	1500mm - 3.9kg 1200mm - 3.4kg 600mm - 1.7kg
Colour Rendering Index (CRI)	≥80	Colour of housing	Clear with light grey
Flex and Plug	No	Application	Industry, F&B, Parking, Semi Outdoor, Under Canopy, Freezers
Lifetime (L70)	50,000hrs	Accessories	Flexible ceiling bracket, Suspension Hooks, Ceiling clips, Cable glands, End cap 3 or 5 pole connector, Polycarbonate tube
Unified Glare Ratio (UGR)	22		
Optics	NB, WB, VWB		
Driver	Philips Xitanium Driver		
Dimmable	PSD (DALI), PSU (Fixed)		