



SmartBright LED Troffer

When you need to provide energy efficient and reliable LED lighting on a budget, the range of SmartBright LED Troffers is the perfect solution.

The unobtrusive, elegant design blends seamlessly into any commercial décor. The SmartBright Troffer can be used in a range of indoor applications, including offices and administration areas.



Features

- Up to 90 lm/W system efficacy with significant energy savings that gives up to 50% energy saving when compared to a conventional Philips traditional TL8 or TL5 system.
- CRI 80 provides good colour consistency that's easy on the eye.
- Entry level LED pricing makes this the perfect fit when budgets are tight and TCO is short.
- The simple design is suitable for offices and a variety of commercial applications. The traditional 1200 x 600, 600 x 600 and 1200 x 300mm sizes suit most Tee-rail ceiling grids.

- 25,000hrs @ L70
- 4600, 2200 lumens
- 4000K
- T-Rail ceilings
- CRI \geq 80

Applications

- Offices
- Education
- General commercial applications
- Accessory - Seismic Restraint Kit available on request. PHSEKIT

Product ID	W (mm)	H (mm)
RC0888 LED23S/840 PSU W60L60 PLS	597	597
RC0888 LED23S/840 PSU W30L120 PLS	1197	297
RC0888 LED46S/840 PSU W60L120 PLS	1197	597

Dimensions in mm (Nominal)
