


HID PrimaVision Xtreme for CPO

Compact, robust, outdoor, one-piece, electronic ballasts for CosmoPolis White (CPO-TW) lamps. Offering an energy-saving street and road light solution with extremely long life, and suitable for withstanding outdoor environments (storms, lightning strikes, etc.).



Product ID	A1	A2	B1	B2	C1	D1
HIDPVC1	150	135.9	65	46.8	65	5
HIDPVQ	150	133.6	90	70	40	4.5

Dimensions in mm

HID DynaVision DALI Xtreme for CPO

Shortcode	Description	Wattage (W)	Voltage	Min Order Quantity	Carton Qty
HIDPVXT45CPOC1	HID-PV Xt 45 CPO C1 208-277V	45	208-277	12	12
HIDPVXT60CPOC1	HID-PV Xt 60 CPO C1 208-277V	60	208-277	12	12
HIDPVXT90CPOC1	HID-PV Xt 90 CPO C1 208-277V	90	208-277	12	12
HIDPVXT140CPOC1	HID-PV Xt 140 CPO C1 208-277V	140	208-277	12	12
HIDPVXT45CPOQ	HID-PV Xt 45 CPO Q 208-277V	45	208-277	12	12
HIDPVXT60CPOQ	HID-PV Xt 60 CPO Q 208-277V	60	208-277	12	12
HIDPVXT90CPOQ	HID-PV Xt 90 CPO Q 208-277V	90	208-277	12	12
HIDPVXT140CPOQ	HID-PV Xt 140 CPO Q 208-277V	140	208-277	12	12