



MASTER LEDspot Mains Voltage GU10

The perfect replacement for mains voltage halogen spots. Delivering a warm, halogen-like accent beam, MASTER LEDspot MV is a perfect fit for spot lighting. MASTER LEDspot MV delivers huge energy savings and minimizes maintenance cost without any compromise on brightness.



Product ID	Overall Length C max.	Diameter D max.
5.5W	55.0	50.0
5.3W	55.0	50.0

Dimensions in mm

LEDspot Mains Voltage GU10

Shortcode	Wattage (W)	Cap Base	Voltage	Luminous Intensity (cd)	Luminous Flux (lm)	Average Lifetime (hrs)	Colour Temp (K)	Beam Angle °	Min Order Quantity	Carton Qty	Trade Price
MAS5.5WGU1082725D	5.5	GU10	220-240	1100	370	40000	2700	25	10	10	\$41.17
MAS5.5WGU1082740D	5.5	GU10	220-240	800	370	40000	2700	40	1	10	\$41.17
MAS5.5WGU1083025D	5.5	GU10	220-240	1200	400	40000	3000	25	1	10	\$41.17
MAS5.5WGU1083040D	5.5	GU10	220-240	850	400	40000	3000	40	1	10	\$41.17
MAS5.5WGU1084025D	5.5	GU10	220-240	1200	415	40000	4000	25	1	10	\$41.17
MAS5.5WGU1084040D	5.5	GU10	220-240	850	415	40000	4000	40	1	10	\$41.17
LEDGU1083036D	5.3	GU10	220-240	950	385	25000	3000	36	1	10	\$19.17

Dimming compatibility for Master LED GU10 5.5W

5.5W GU10

Brand	Model	Type	Load	Lamps
Clipsal	32E450LM	Leading	450W	1-2
Clipsal	KB31RD400	Trailing	400W	1-3
KIWI	K400U	Universal	400W	1-7

5.3W GU10

Brand	Model	Type	Load	Lamps
Clipsal	32E2CFLDM	Leading	300W	1-8
Clipsal	32E450LM	Leading	450W	1-8
Clipsal	32E450TM	Trailing	450W	1-8
Clipsal	32E450UDM	Universal	450W	1-8
HPM	400T	Trailing	400W	1-8
HPM	400L	Leading	400W	1-8
PDL	654MWh	Trailing	450W	1-8
PDL	624TMWH	Trailing	450W	6-8