



# Security lighting

# QHF560 Security Floodlight



QHF560



## QHF560

A compact flexible security light which can be mounted on walls or under eaves. The QHF560 consists of two weatherproof lampholders and seals end on adjustable PIR detector.

### Materials and finish

- Die-cast aluminium with powder coat black finish.

### Installation and mounting

Mounting bracket allows ceiling or wall mounting.

### Classifications

- IP44
- IEC 598

### Main applications

- Security Lighting
- Car Parks

### Features

- Adjustable PIR movement-activated sensor. With a 12 metre area of coverage at 110°
- Time adjustment control from 5 seconds to 12 mins
- Twilight adjustment
- Manual override

IP 44

Order Code	Description	Lamp Required
QHF560	Secipar light c/w sensor	2x120W PAR38 reflector (not included)
QHF560W	White Twin-PAR Security c/w sensor	2x120W PAR38 reflector (not included)
QHF560B	Black Twin-PAR Security c/w sensor	2x120W PAR38 reflector (not included)

Note: Some items are indent products.  
Please contact your local sales office for availability.