

Ordering guide

Example: 2FGG42B840-4-D-UNV-DIM

Width	Family	Ceiling Type	Air Function	Lumens	Color	Length	Center Diffuser	Voltage	Driver	Options
<input type="text"/>	<input type="text" value="FG"/>	<input type="text" value="G"/>	<input type="text"/>	<input type="text"/>	<input type="text"/>	<input type="text"/>	<input type="text"/>	<input type="text"/>	<input type="text"/>	<input type="text"/>
1 1' 2 2'	FG FluxGrid	G Grid	Blank Static H Air return	1x4 & 2x2 Standard Configurations 30L 3000lm Std 38L 3800lm Std 45L 4500lm Std 2x4 Standard Configurations 38L 3800lm Std 43L 4300lm Std 48L 4800lm Std 54L 5400lm Std 74L 7400lm Std Base Configurations 41B 4100lm (1x4) 38B 3800lm (2x2) 42B 4200lm (2x4)	830 80 CRI, 3000K 835 ¹ 80 CRI, 3500K 840 ¹ 80 CRI, 4000K 850 80 CRI, 5000K	2 2' 4 4'	D ¹ Diffuse (ribbed) DS ¹ Diffuse (smooth)	UNV ¹ Universal voltage 120-277V 120 ² 120V 277 ² 277V 347 347V	DIM ¹ 0-10V dimming SDIM ² 40% Step dimming XDIM ³ MarkX phase dimming L3D ⁴ Lutron Hi-lume A 1% dimming LDE Lutron LDE5 5% dimming DALI DALI	F1 3/8" flex, 3 wire 18 gauge 6' F2 3/8" flex, 4 wire 18 gauge 6' F1/D 3/8" twin flex, 3 wire 18 gauge 6' for dimmable luminaires F2/5W 3/8" single flex, 5 wire 18 gauge 6' for dimmable luminaires. F2/6W 3/8" single flex, 6 wire 18 gauge 6' for dimmable and EMLED luminaires. GLR Fusing, fast blow EMLED ^{1,5} Integral emergency battery pack DAYOCC ⁶ Integral daylighting and occupancy, Phillips EasySense SNS102 CHIC Chicago Plenum rated

Footnotes:

1. Base configurations available only with noted options.
2. Consult factory for SDIM on 2x4 74L package.
3. XDIM option is voltage specific. Specify 120V or 277V. Consult factory for availability on 2x4 74L package.
4. Available up to 4300lm.
5. Philips Bodine BSL310, 1100lm nominal delivered.
6. Specify DIM driver option only with DAYOCC controls option

