

Dostępne produkty

| EAN | Nazwa |
|---|--------------------------------------|
| Batten BN060C Belka LEDtube | |
| 8718696070079 | BN060C 1xTLED16/840 L1200 |
| 8718696070093 | BN060C 2xTLED16/840 L1200 |
| Downlight DN060B Oprawa typu downlight | |
| 8710163306629 | DN060B LED8S/830 PSU WH |
| 8710163306643 | DN060B LED8S/840 PSU WH |
| 8710163306612 | DN060B LED18S/830 PSU WH |
| 8710163306636 | DN060B LED18S/840 PSU WH |
| Recessed RC060B Oprawa do wbudowania | |
| 8718696069585 | RC060B LED32S/840 PSU W60L60 |
| 8718696069592 | RC060B LED32S/830 PSU W60L60 |
| 8718696069608 | RC060B LED32S/840 PSU W30L120 |
| 8718696069615 | RC060B LED32S/830 PSU W30L120 |
| Surface Mounted SM060C Oprawa nasufitowa | |
| 8718696069622 | SM060C LED32S/840 PSU W20L120 |
| 8718696069639 | SM060C LED32S/830 PSU W20L120 |
| Waterproof WT060C Oprawa hermetyczna | |
| 8718699380090 | WT060C LED18S/840 PSU L650 |
| 8718699380106 | WT060C LED18S/840 PSU TW1 L675 |
| 8718699380113 | WT060C LED36S/840 PSU L1250 |
| 8718699380120 | WT060C LED36S/840 PSU TW1 L1275 |
| 8718699380137 | WT060C LED56S/840 PSU L1550 |
| 8718699380144 | WT060C LED56S/840 PSU TW1 L1575 |
| Panel RC065B Oprawa do wbudowania | |
| 8718696073285 | RC065B LED32S/840 PSU W60L60 NOC |
| Clearaccent RS060B Spot LED zintegrowany | |
| 8718696072677 | RS060B LED5-36-/830 PSR II WH |
| 8718696072684 | RS060B LED5-36-/840 PSR II WH |
| 8718696072691 | RS061B LED5-36-/830 PSR II WH |
| 8718696072707 | RS061B LED5-36-/840 PSR II WH |
| Zadora LED Spot LED GU10 | |
| 8718696070116 | RS049B LED-40-3.5W-2700-GU10 WH 35W |
| 8718696070123 | RS049B LED-40-4.3W-2700-GU10 WH 50W |
| 8718696070147 | RS049B LED-40-4.3W-2700-GU10 ALU 50W |
| 8718696070130 | RS049B LED-40-4.3W-4000-GU10 WH 50W |
| Pentura Mini LED Belka LED | |
| 8718696072431 | BN132C LED12S/840 PSU L1200 |
| 8718696072448 | BN132C LED12S/830 PSU L1200 |
| 8718696072455 | BN132C LED9S/840 PSU L900 |
| 8718696072462 | BN132C LED9S/830 PSU L900 |
| 8718696072479 | BN132C LED6S/840 PSU L600 |
| 8718696072486 | BN132C LED6S/830 PSU L600 |
| 8718696072493 | BN132C LED3S/840 PSU L300 |
| 8718696072509 | BN132C LED3S/830 PSU L300 |
| 8718696072516 | BN133C LED6S/840 PSU L600 |
| 8718696072523 | BN133C LED6S/830 PSU L600 |
| Akcesoria montażowe | |
| 8718696073346 | RC125Z SME-2 WH |
| 8718696073339 | RC125Z SMB-PLC |
| 8718696073308 | RC125Z SMB W60L60 |
| 8718696073353 | RC125Z SC |