

The top image shows three Philips LEDtube lamps on a wooden surface. Two are upright, one is lying on its side. The lamps are white with blue accents and have 'PHILIPS LEDtube' printed on them. One of the upright lamps has 'EMANS' and 'High Output' printed on its base. A fourth lamp is lying on its side in the foreground, partially obscured.

PHILIPS

LEDlamps

LEDtube High Output

O LEDtube certo para alto fluxo luminoso com a melhor relação lm/W

Seja qual for a sua aplicação de iluminação, o portefólio Philips MASTER LEDtube tem o LEDtube certo para si.




Com um alto fluxo luminoso de 2100lm até 3100lm, os nossos LEDtubes High Output oferecem qualidade de luz brilhante com a melhor relação lumens por watt. Um simples mudança disponível em dois comprimentos e temperaturas de cor, com a opção de casquilhos rotativos.

A escolha acertada para supermercados, DIY e aplicações industriais.



Dados de produto

MASTER LEDtube High Output



Tipo de produto	LED	Tradicional	Casquilho rotativo	Fluxo luminoso	Operação	Ângulo abertura	IRC	Temperatura de cor	EOC 1 pcs (C)
MASTER LEDtube	Potência	Equivalente		Lumen		°		K	
1200mm ROT	20 W	36 W	Sim	1900 lm	EM & 230V	160°	83	3000	871869642198700
1200mm ROT	20 W	36 W	Sim	2100 lm	EM & 230V	160°	83	4000	871869642200700
1200mm ROT	20 W	36 W	Sim	2100 lm	EM & 230V	160°	83	6500	871869642202100
1500mm ROT	23 W	58 W	Sim	2900 lm	EM & 230V	160°	83	3000	871829178956700
1500mm ROT	23 W	58 W	Sim	3100 lm	EM & 230V	160°	83	4000	871829178958100
1500mm ROT	23 W	58 W	Sim	3100 lm	EM & 230V	160°	83	6500	871829178960400
1200mm ROT InstantFit	18 W	36 W	Sim	2100 lm	HF	160°	83	4000	871869647125800
1200mm ROT InstantFit	18 W	36 W	Sim	2100 lm	HF	160°	83	6500	871869647127200
1500mm ROT InstantFit	25 W	58 W	Sim	3100 lm	HF	160°	83	4000	871869640886500
1500mm ROT InstantFit	25 W	58 W	Sim	3100 lm	HF	160°	83	6500	871869640888900

