

TL Rapid Start Standard Colours



The TL RS (Rapid Start) lamp (tube diameter 38 mm) has an external silicin coating. It is suitable for situations where high humidity requires fast and stable ignition but color rendering is not important. Rapid Start lamps can be ignited without a starter

General Characteristics		
System Description	Rapid Start	Rapid Start
Cap-Base	G13 [Medium Bi-Pin Fluorescent]	G13 [Medium Bi-Pin Fluorescent]
Base information	Silver Base	Silver Base
Bulb	T12 [38 mm]	T12 [38 mm]
Life to 50% failures	9000 hr	20000 hr
Rated Avg. Life [3 hr Start]	9000 hr	20000 hr
Life with 3h/day use [years]	4 yrs	7 yrs
Light Technical Characteristics		
Color Code	54-765	54-765
Color Rendering Index	73Ra8	73Ra8
Color Designation (text)	Daylight	Daylight
Color Temperature	6500 K	6500 K
Initial lumen/Lumonos Flux Lamp EM	1075 lm	2600 lm
Design Means Lumens	960 Lm	2250lm
Chromaticity Coordinate X	313	313
Chromaticity Coordinate Y	337	337
Electrical Characteristics		
Lamp Wattage EM	20W	40W
Lamp Voltage	60V	101V
Lamp Current EM	380mA	430mA
Dimmable	Yes	Yes
Environmental Characteristics		
Mercury (Hg)Content	1,7mg	4,4mg
Product Dimensions		
Base Face to base Face A	589.8 mm	1199.4 mm
Insertion Length B	594mm (min), 596.9mm(max)	1204.0mm (min), 1206.5mm(max)
Overall Length C	604mm(max)	1213.6mm(max)
Nominal Length [inch]	24	48
Product data		
Full Product name	TL RS 20W/54-765 30PK	TL RS 40W/54-765 30PK
Short Product name	TL RS 20W/54-765	TL RS 40W/54-765
Pcs per Sku	1	1
SKUs/Case	30	30
Bar code on pack	46677226472	46677226480
Bar code on case	50046677226478	50046677226485
Logistic code	927883005411	927888005406
net weight	0.125kg	0.235kg

