



PHILIPS

Lighting

Octubre 2017

Catálogo lámparas LED
de consumo

Índice

| | |
|--|----|
| Gama Estandar y Globo | 4 |
| Estandar | 6 |
| - Cristal No regulable | 6 |
| - Mate No regulable..... | 8 |
| - WarmGlow..... | 14 |
| Globo | 16 |
| - No regulable..... | 16 |
| | |
| Gama Velas y Esféricas | 18 |
| - Cristal No regulable | 20 |
| - Mate No regulable..... | 21 |
| - Warmglow | 24 |
| - Colores..... | 25 |
| | |
| Gama Spot | 27 |
| GU10 | 28 |
| - No regulable..... | 28 |
| - Warmglow | 32 |
| - Regulable | 33 |
| GU5.3 | 34 |
| - No regulable..... | 34 |
| - Regulable | 35 |
| - Warmglow | 36 |
| | |
| Gama Reflectoras | 37 |
| - Mate No regulable..... | 38 |
| - Filamento regulable | 39 |
| - Mate Regulable | 40 |
| | |
| Gama Cápsulas | 41 |
| - G4/G9 No regulable | 42 |
| - G4/G9 Regulable..... | 43 |
| | |
| Gama Lineales | 44 |
| - R7S No regulable | 45 |
| - R7S Regulable..... | 46 |
| | |
| Gama Especiales | 47 |
| - T25 No regulable..... | 48 |
| - GX53 No regulable..... | 49 |
| | |
| Gama Iluminación Inteligente | 50 |
| - SceneSwitch..... | 51 |
| - Sensor Luz Diurna | 51 |
| - Estandar SceneSwitch..... | 52 |
| - Vela SceneSwitch..... | 53 |
| - Spot SceneSwitch..... | 54 |
| | |
| Gama Tubos | 55 |
| - Tubos..... | 56 |
| - Lineal..... | 57 |
| - PLC | 58 |
| | |
| Gama Filamento | 59 |
| Estandar | 60 |
| - Filamento Clara No Regulable..... | 60 |
| - Filamento Clara Warmglow..... | 62 |
| Estandar y Globo | 63 |
| - Filamento Clara Regulable..... | 63 |
| - Filamento Ambar Regulable..... | 64 |
| Vela y Esférica | 65 |
| - Filamento Clara Regulable..... | 65 |
| - Filamento Ambar Regulable..... | 66 |
| | |
| Gama Vintage | 67 |
| Estandar | 68 |
| - Filamento Espiral Gigante No regulable | 68 |
| Estandar, Globo y Vela | 69 |
| - Filamento Espiral No regulable..... | 69 |
| | |
| Gama Promocional | 70 |
| | |
| Attralux | 74 |





Gama Estándar y Globo



Cristal no regulable
40W/60W



Cristal no regulable
75W/100W



Mate no regulable
40W



Mate no regulable
60W



Mate no regulable
75W



Mate no regulable
100W



Mate no regulable
120W



Mate no regulable
150W



Clara regulable
Warmglow



Mate regulable
Warmglow



LED Globo

Gama Estandar No Regulable Cristal 40w/60w



2700K



4000 -
6500K



E27



15,000 H



EEL



EEL



300°
Ángulo del Haz



CRI

| Descripción | LED | Equivalencia | Temp. Color | Lumen | Eficacia | Pack | EAN1 | GPC | PVPR |
|--|-----|--------------|-------------|-------|----------|------|---------|--------------|------|
| | W | W | K | lm | lm/W | | 8718696 | | € |
| LED classic 40W A60 E27 WW FR ND SRT4 | 4,5 | 40 | 2700 | 470 | 104 | 4 | 576571 | 929001242958 | 3,99 |
| LED classic 40W A60 E27 CW FR ND 1BC/6 | 4,5 | 40 | 4000 | 470 | 104 | 6 | 705490 | 929001323601 | 3,99 |
| LED classic 40W A60 E27 CDL FR ND 1BC/6 | 4,5 | 40 | 4000 | 470 | 104 | 6 | 740705 | 929001372501 | 3,99 |
| LED classic 60W A60 E27 WW FR ND RF1BC/6 | 7 | 60 | 2700 | 806 | 115 | 6 | 576632 | 929001243017 | 4,99 |
| LED classic 60W A60 E27 CW FR ND 1BC/6 | 7 | 60 | 4000 | 806 | 115 | 6 | 703335 | 929001323501 | 4,99 |
| LED classic 60W A60 E27 CDL FR ND 1BC/6 | 7 | 60 | 6500 | 806 | 115 | 6 | 740729 | 929001372601 | 4,99 |

Gama Estandar No Regulable Cristal 75w/100w



2700K



4000 -
6500K



E27



15,000 H



EEL



300°
Ángulo del Haz



CRI

| Descripción | LED | Equivalencia | Temp. Color | Lumen | Eficacia | Pack | EAN1 | GPC | PVPR |
|--|------|--------------|-------------|-------|----------|------|---------|--------------|------|
| | W | W | K | lm | lm/W | | 8718696 | | € |
| LED classic 75W A60 E27 WW FR ND RF1BC/6 | 8,5 | 75 | 2700 | 1055 | 124 | 6 | 705537 | 929001286317 | 6,99 |
| LED classic 75W A60 E27 CW FR ND 1BC/6 | 8,5 | 75 | 4000 | 1055 | 124 | 6 | 705599 | 929001323401 | 6,99 |
| LED classic 75W A60 E27 CDL FR ND 1BC/6 | 8,6 | 75 | 6500 | 1055 | 123 | 6 | 740668 | 929001372701 | 6,99 |
| LED classic 100W A67 WW FR ND SRT4 | 11,5 | 100 | 2700 | 1521 | 132 | 4 | 739105 | 929001802717 | 8,99 |
| LED classic 100W A67 CW FR ND 1BC/6 | 11,5 | 100 | 4000 | 1521 | 132 | 6 | 739228 | 929001802801 | 8,99 |
| LED classic 100W A67 CDL FR ND 1BC/6 | 11,5 | 100 | 6500 | 1521 | 132 | 6 | 739242 | 929001802901 | 8,99 |

Gama Estandar No Regulable

Mate 40w



2700K



4000 -
6500K



E27



15,000 H



EEL



200°
Ángulo del Haz



CRI

| Descripción | LED | Equivalencia | Temp. Color | Lumen | Eficacia | Pack | EAN1 | GPC | PVPR |
|--|-----|--------------|-------------|-------|----------|------|---------|--------------|------|
| | W | W | K | lm | lm/W | | 8718696 | | € |
| LED 40W A60 E27 WW 230V FR ND RF 1BC/6 | 5,5 | 40 | 2700 | 470 | 85 | 6 | 577097 | 929001234217 | 4,99 |
| LED 40W A60 E27 CW 230V FR ND 1BC/6 | 5 | 40 | 4000 | 470 | 94 | 6 | 577271 | 929001234658 | 4,99 |
| LED 40W A60 E27 CDL 230V FR ND 1BC/6 | 5 | 40 | 6500 | 470 | 94 | 6 | 577356 | 929001304631 | 4,99 |

Gama Estandar No Regulable

Mate 60w



2700K



4000 -
6500K



E27



15,000 H



EEL



200°
Ángulo del Haz



CRI

| Descripción | LED | Equivalencia | Temp. Color | Lumen | Eficacia | Pack | EAN1 | GPC | PVPR |
|---|-----|--------------|-------------|-------|----------|------|---------|--------------|------|
| | W | W | K | lm | lm/W | | 8718696 | | € |
| LED 60W A60 E27 WW 230V FR ND RF 1BC/6 | 8 | 60 | 2700 | 806 | 101 | 6 | 577073 | 929001234317 | 5,99 |
| LED 60W E27 CW A60 FR ND RF 1BC/6 | 7,5 | 60 | 4000 | 806 | 107 | 6 | 577257 | 929001234717 | 5,99 |
| LED 60W A60 E27 CDL 230V FR ND RF 1BC/6 | 7,5 | 60 | 6500 | 806 | 107 | 6 | 577332 | 929001304877 | 5,99 |

Gama Estandar No Regulable

Mate 75w



2700K



4000 -
6500K



E27



15,000 H



EEL



200°
Ángulo del Haz



CRI

| Descripción | LED | Equivalencia | Temp. Color | Lumen | Eficacia | Pack | EAN1 | GPC | PVPR |
|--|-----|--------------|-------------|-------|----------|------|---------|--------------|------|
| | W | W | K | lm | lm/W | | 8718696 | | € |
| LED 75W A60 E27 CDL 230V FR ND 1BC/6 | 10 | 75 | 6500 | 1055 | 106 | 6 | 510506 | 929001163858 | 7,99 |
| LED 75W A60 E27 WW 230V FR ND RF 1BC/6 | 11 | 75 | 2700 | 1055 | 96 | 6 | 577059 | 929001234417 | 7,99 |
| LED 75W A60 E27 CW 230V FR ND RF 1BC/6 | 10 | 75 | 4000 | 1055 | 106 | 6 | 510162 | 929001234858 | 7,99 |

Gama Estandar No Regulable

Mate 100w



2700K



4000 -
6500K



E27



15,000 H



EEL



200°
Ángulo del Haz



CRI

| Descripción | LED | Equivalencia | Temp. Color | Lumen | Eficacia | Pack | EAN1 | GPC | PVPR |
|---|------|--------------|-------------|-------|----------|------|---------|--------------|------|
| | W | W | K | lm | lm/W | | 8718696 | | € |
| LED 100W A60 E27 WW 230V FR ND RF 1BC/6 | 13 | 100 | 2700 | 1521 | 117 | 6 | 577035 | 929001234517 | 9,99 |
| LED 100W A60 E27 CW 230V FR ND 1BC/6 | 12,5 | 100 | 4000 | 1521 | 117 | 6 | 577219 | 929001312401 | 9,99 |
| LED 100W A60 E27 CDL 230V FR ND 1BC/6 | 12,5 | 100 | 6500 | 1521 | 117 | 6 | 577295 | 929001312501 | 9,99 |

Gama Estandar No Regulable

Mate 120w



2700K



4000 -
6500K



E27



15,000 H



EEL



150°
Ángulo del haz



CRI

| Descripción | LED | Equivalencia | Temp. Color | Lumen | Eficacia | Pack | EAN1 | GPC | PVPR |
|---|------|--------------|-------------|-------|----------|------|---------|--------------|-------|
| | W | W | K | lm | lm/W | | 8718696 | | € |
| LED Bulb 120W E27 WW 230V A67 FR 1BC/6 | 18,5 | 120 | 2700 | 2000 | 108 | 6 | 701614 | 929001313201 | 11,99 |
| LED Bulb 120W E27 CW 230V A67 FR 1BC/6 | 18 | 120 | 4000 | 2000 | 111 | 6 | 701638 | 929001313301 | 11,99 |
| LED Bulb 120W E27 CDL 230V A67 FR 1BC/6 | 18 | 120 | 6500 | 2000 | 111 | 6 | 701652 | 929001313401 | 11,99 |

Gama Estandar No Regulable

Mate 150w



2700K



4000 -
6500K



E27



15,000 H



EEL



CRI

| Descripción | LED | Equivalencia | Temp. Color | Lumen | Eficacia | Pack | EAN1 | GPC | PVPR |
|---|------|--------------|-------------|-------|----------|------|---------|--------------|-------|
| | W | W | K | lm | lm/W | | 8718696 | | € |
| LED Bulb 150W E27 WW 230V A67 FR 1BC/6 | 22.5 | 150 | 2700 | 2500 | 111 | 6 | 770290 | 929001817301 | 13,99 |
| LED Bulb 150W E27 CW 230V A67 FR 1BC/6 | 20 | 150 | 4000 | 2500 | 125 | 6 | 770313 | 929001817401 | 13,99 |
| LED Bulb 150W E27 CDL 230V A67 FR 1BC/6 | 20 | 150 | 6500 | 2500 | 125 | 6 | 770337 | 929001817501 | 13,99 |

Gama Estandar Regulable WarmGlow

Regulable en intensidad y Temperatura de color



2200 -
2700K



E27



15,000 H



EEL



150°
Ángulo del Haz



CRI

| Descripción | LED | Equivalencia | Temp. Color | Lumen | Eficacia | Pack | EAN1 | GPC | PVPR |
|------------------------------------|-----|--------------|-------------|-------|----------|------|---------|--------------|------|
| | W | W | K | lm | lm/W | | 8718696 | | € |
| LED 40W A60 E27 WW CL WGD RF 1BC/6 | 6 | 40 | 2200-2700 | 470 | 78 | 6 | 481202 | 929001150817 | 7,99 |
| LED 60W A60 E27 WW CL WGD RF 1BC/6 | 8,5 | 60 | 2200-2700 | 806 | 95 | 6 | 572177 | 929001150917 | 8,99 |

Gama Estandar Regulable WarmGlow

Regulable en intensidad y Temperatura de color



2200 -
2700K



E27



15,000 H



EEL



150°
Ángulo del Haz



CRI

| Descripción | LED | Equivalencia | Temp. Color | Lumen | Eficacia | Pack | EAN1 | GPC | PVPR |
|------------------------------------|------|--------------|-------------|-------|----------|------|---------|--------------|-------|
| | W | W | K | lm | lm/W | | 8718696 | | € |
| LED 40W A60 E27 WW FR WGD RF 1BC/6 | 5,5 | 40 | 2200-2700 | 470 | 85 | 6 | 577011 | 929001352477 | 5,99 |
| LED 60W A60 E27 WW FR WGD 1BC/6 | 8,5 | 60 | 2200-2700 | 806 | 95 | 6 | 576991 | 929001352577 | 7,99 |
| LED 75W A60 E27 WW FR WGD SRT4 | 11 | 75 | 2200-2700 | 1055 | 96 | 4 | 706954 | 929001352701 | 9,99 |
| LED 100W A67 E27 WW FR WGD SRT4 | 13,5 | 100 | 2200-2700 | 1521 | 113 | 4 | 706978 | 929001352801 | 11,99 |

Gama Globo



NON-DIMMABLE



2700 -
3000K



6500K



E27



15,000 H



EEL



150°



200°



CRI

Ángulo del Haz Ángulo del Haz

| Descripción | LED | Equivalencia | Temp. Color | Lumen | Eficacia | Pack | EAN1 | GPC | PVPR |
|--|------|--------------|-------------|-------|----------|------|---------|--------------|-------|
| | W | W | K | lm | lm/W | | 8718696 | | € |
| LED Globe 60W G93 E27 WW FR ND RF 1CT/4 | 9,5 | 60 | 2700 | 806 | 85 | 4 | 580639 | 929001229201 | 9,99 |
| LED Globe 60W G93 E27 CDL FR ND 1CT/6 | 8,5 | 60 | 6500 | 806 | 95 | 6 | 742976 | 929001229301 | 9,99 |
| LED Globe 75W G120 E27 CDL FR ND 1CT/6 | 10,5 | 75 | 6500 | 1055 | 100 | 6 | 742990 | 929001229701 | 12,99 |
| LED Globe 100W G93 E27 WW FR ND 1CT/4 | 15 | 100 | 2700 | 1521 | 101 | 4 | 580615 | 929001229401 | 13,99 |
| LED Globe 100W G93 E27 CDL FR ND 1CT/6 | 13,5 | 100 | 6500 | 1521 | 113 | 6 | 743010 | 929001229501 | 13,99 |
| LED Globe 120W G120 E27 WW 230V ND 1CT/4 | 18 | 120 | 2700 | 2000 | 111 | 4 | 567593 | 929001229801 | 17,99 |
| LED Globe 120W G120 E27 WH 230V ND 1CT/4 | 17 | 120 | 3000 | 2000 | 118 | 4 | 567616 | 929001229901 | 17,99 |



A woman with voluminous curly hair is laughing joyfully, looking towards the right. She is wearing a white blouse with small black polka dots. Above her is a modern chandelier with multiple lit light bulbs and white curved arms. The background features a brick wall and a window with white blinds. A green plant is visible in the lower right corner.

Gama Velas y Esféricas



Cristal no regulable



Mate no regulable
25W



Mate no regulable
40W



Mate no regulable
60W



Clara
Regulable Warmglow



Especial
Colores

Gama Velas y Esfericas No Regulable Cristal 25w/40w



NON-DIMMABLE



2700K



E14



E27



15,000 H



EEL



CRI

| Descripción | LED | Equivalencia | Temp. Color | Lumen | Eficacia | Pack | EAN1 | GPC | PVPR |
|--|-----|--------------|-------------|-------|----------|------|---------|--------------|------|
| | W | W | K | lm | lm/W | | 8718696 | | € |
| LED classic 25W B35 E14 WW FR ND RF1BC/6 | 2,2 | 25 | 2700 | 250 | 114 | 6 | 706237 | 929001345217 | 3,99 |
| LED classic 25W P45 E14 WW FR ND RF1BC/6 | 2,2 | 25 | 2700 | 250 | 114 | 6 | 706275 | 929001345417 | 3,99 |
| LED classic 25W P45 E27 WW FR ND RF1BC/6 | 2,2 | 25 | 2700 | 250 | 114 | 6 | 706312 | 929001345617 | 3,99 |
| LED classic 25W BA35 E14 WW FR ND SRT4 | 2,2 | 25 | 2700 | 250 | 114 | 4 | 706350 | 929001345801 | 3,99 |
| LED classic 40W B35 E14 WW FR ND RF1BC/6 | 4,3 | 40 | 2700 | 470 | 109 | 6 | 706251 | 929001345317 | 5,99 |
| LED classic 40W P45 E14 WW FR ND RF1BC/6 | 4,3 | 40 | 2700 | 470 | 109 | 6 | 706299 | 929001345517 | 5,99 |
| LED classic 40W P45 E27 WW FR ND RF1BC/6 | 4,3 | 40 | 2700 | 470 | 109 | 6 | 706336 | 929001345717 | 5,99 |

Gama Velas y Esfericas No Regulable Mate 25W



NON-DIMMABLE



2700K



4000K



E14



E27



15,000 H



EEL



CRI

| Descripción | LED | Equivalencia | Temp. Color | Lumen | Eficacia | Pack | EAN1 | GPC | PVPR |
|-----------------------------------|-----|--------------|-------------|-------|----------|------|---------|--------------|------|
| | W | W | K | lm | lm/W | | 8718696 | | € |
| LED 25W B35 E14 WW FR ND RF 1BC/6 | 4 | 25 | 2700 | 250 | 63 | 6 | 474914 | 929001157417 | 3,99 |
| LED 25W P45 E14 WW FR ND RF 1BC/6 | 4 | 25 | 2700 | 250 | 63 | 6 | 474945 | 929001157517 | 3,99 |
| LED 25W P45 E27 WW FR ND RF 1BC/6 | 4 | 25 | 2700 | 250 | 63 | 6 | 474969 | 929001157617 | 3,99 |
| LED 25W B35 E14 CW FR ND 1BC/6 | 3,5 | 25 | 4000 | 290 | 83 | 6 | 543467 | 929001205658 | 3,99 |
| LED 25W P45 E14 CW FR ND 1BC/6 | 3,5 | 25 | 4000 | 290 | 83 | 6 | 543504 | 929001205758 | 3,99 |

Gama Velas y Esfericas No Regulable Mate 40W



NON-DIMMABLE



2700K



4000 -
6500K



E14



E27



15,000 H



EEL



CRI

| Descripción | LED | Equivalencia | Temp. Color | Lumen | Eficacia | Pack | EAN1 | GPC | PVPR |
|------------------------------------|-----|--------------|-------------|-------|----------|------|---------|--------------|------|
| | W | W | K | lm | lm/W | | 8718696 | | € |
| LED 40W B35 E14 WW FR ND RF 1BC/6 | 5,5 | 40 | 2700 | 470 | 85 | 6 | 474983 | 929001157717 | 5,99 |
| LED 40W P45 E14 WW FR ND RF 1BC/6 | 5,5 | 40 | 2700 | 470 | 85 | 6 | 475003 | 929001157817 | 5,99 |
| LED 40W P45 E27 WW FR ND RF 1BC/6 | 5,5 | 40 | 2700 | 470 | 85 | 6 | 505786 | 929001175417 | 5,99 |
| LED 40W P45 E14 CW FR ND RF 1BC/6 | 5,5 | 40 | 4000 | 520 | 95 | 6 | 543580 | 929001205917 | 5,99 |
| LED 40W B35 E14 CW FR ND RF 1BC/6 | 5,5 | 40 | 4000 | 520 | 95 | 6 | 543542 | 929001325401 | 5,99 |
| LED 40W P45 E14 CDL FR ND RF 1BC/6 | 5,5 | 40 | 6500 | 520 | 95 | 6 | 746752 | 929001394601 | 5,99 |
| LED 40W B35 E14 CDL FR ND RF 1BC/6 | 5,5 | 40 | 6500 | 520 | 95 | 6 | 746738 | 929001394501 | 5,99 |

Gama Velas y Esfericas No Regulable Mate 60W



NON-DIMMABLE



2700K



4000 -
6500K



E14



E27



15,000 H



EEL



CRI

| Descripción | LED | Equivalencia | Temp. Color | Lumen | Eficacia | Pack | EAN1 | GPC | PVPR |
|------------------------------------|-----|--------------|-------------|-------|----------|------|---------|--------------|------|
| | W | W | K | lm | lm/W | | 8718696 | | € |
| LED 60W B35 E14 WW FR ND 1BC/6 | 7 | 60 | 2700 | 806 | 119 | 6 | 702871 | 929001325101 | 7,99 |
| LED 60W P45 E14 WW FR ND 1BC/6 | 7 | 60 | 2700 | 806 | 119 | 6 | 702895 | 929001325201 | 7,99 |
| LED 60W P45 E27 WW FR ND 1BC/6 | 7 | 60 | 2700 | 830 | 119 | 6 | 702918 | 929001325301 | 7,99 |
| LED 60W P45 E14 CW FR ND 1BC/6 | 7 | 60 | 4000 | 830 | 119 | 6 | 702956 | 929001325501 | 7,99 |
| LED 60W B35 E14 CW FR ND 1BC/6 | 7 | 60 | 4000 | 830 | 119 | 6 | 702932 | 929001325401 | 7,99 |
| LED 60W P45 E27 CW FR ND 1BC/6 | 7 | 60 | 6500 | 830 | 119 | 6 | 702970 | 929001325601 | 7,99 |
| LED 60W P48 E14 CDL FR ND RF 1BC/6 | 7 | 60 | 6500 | 830 | 119 | 6 | 746790 | 929001394801 | 7,99 |
| LED 60W B38 E14 CDL FR ND RF 1BC/6 | 7 | 60 | 6500 | 830 | 119 | 6 | 746776 | 929001394701 | 7,99 |

Gama Velas y Esfericas regulables Warmglow Claras



Regulable en intensidad y temperatura de color



2200 - 2700K



E14



E27



15,000 H



EEL




CRI

| Descripción | LED | Equivalencia | Temp. Color | Lumen | Eficacia | Pack | EAN1 | GPC | PVPR |
|-------------------------------------|-----|--------------|-------------|-------|----------|------|--------------|--------------|-------|
| | W | W | K | lm | lm/W | | S 8718696 | | € |
| LED 25W B38 E14 WW CL WGD SRT4 | 4 | 25 | 2200-2700 | 250 | 63 | 4 | 453667 | 929001139858 | 6,99 |
| LED 25W E14 WW BA38 CL WGD RF 1BC/6 | 4 | 25 | 2200-2700 | 250 | 63 | 6 | 453742 | 929001139917 | 6,99 |
| LED 40W P48 E27 WW CL WGD SRT4 | 6 | 40 | 2200-2700 | 470 | 78 | 4 | 700617 | 929001140730 | 7,99 |
| LED 40W B38 E14 WW CL WGD SRT4 | 6 | 40 | 2200-2700 | 470 | 78 | 4 | 453483 | 929001140458 | 7,99 |
| LED 40W BA38 E14 WW CL WGD RF 1BC/6 | 6 | 40 | 2200-2700 | 470 | 78 | 6 | 581032 | 929001140517 | 7,99 |
| LED 40W P48 E14 WW CL WGD SRT4 | 6 | 40 | 2200-2700 | 470 | 78 | 4 | 453568 | 929001140658 | 7,99 |
| LED 60W B40 E14 WW CL WGD RF 1BC/6 | 8 | 60 | 2200-2700 | 806 | 101 | 6 | 555972 | 929001211717 | 10,99 |
| LED 60W P50 E14 WW CL WGD RF 1BC/6 | 8 | 60 | 2200-2700 | 806 | 101 | 6 | 580653 | 929001211917 | 10,99 |

Gama Esféricas de colores



| Descripción | LED | Equivalencia | Temp. Color | Lumen | Eficacia | Pack | EAN1 | GPC | PVPR |
|---------------------------------|-----|--------------|-------------|-------|----------|------|---------|--------------|------|
| | W | W | K | lm | lm/W | | 8718696 | | € |
| LED colored P45 E27 RED 1SR4 | 3,1 | NA | rojo | - | - | 4 | 748589 | 929001393901 | 4,99 |
| LED colored P45 E27 YELLOW 1SR4 | 3,1 | NA | amarillo | - | - | 4 | 748602 | 929001394001 | 4,99 |
| LED colored P45 E27 BLUE 1SR4 | 3,1 | NA | azul | - | - | 4 | 748626 | 929001394101 | 4,99 |
| LED colored P45 E27 GREEN 1SR4 | 3,1 | NA | verde | - | - | 4 | 748640 | 929001394201 | 4,99 |



Gama Spot



GU10 No regulable
35W



GU10 No regulable
50W



GU10 No regulable
65W



GU10 No regulable
120D



GU10 Regulable
Warmglow



GU10 Regulable



MR16 No regulable



MR16 Regulable
35W



MR16 Regulable
50W

Gama Spots No Regulable GU10 Cristal 35W



NON-DIMMABLE



4000K



2700 -
3000K



GU10



15,000 H



EEL



36°
Ángulo del Haz



CRI

| Descripción | LED | Equivalencia | Temp. Color | Lumen | Eficacia | Intensidad del haz | Ángulo del Haz | Pack | EAN1 | GPC | PVPR |
|---|-----|--------------|-------------|-------|----------|--------------------|----------------|------|---------|--------------|------|
| | W | W | K | lm | lm/W | | | | 8718696 | | € |
| LED classic 35W GU10 WW 36D ND SRT4 | 3.5 | 35 | 2700 | 255 | 72,9 | 545 | 36 | 4 | 562666 | 929001217858 | 4,99 |
| LED classic 35W GU10 WH 36D ND RF 1BC/6 | 3.5 | 35 | 3000 | 265 | 75,7 | 565 | 36 | 6 | 562680 | 929001217917 | 4,99 |
| LED classic 35W GU10 CW 36D ND 1BC/6 | 3.5 | 35 | 4000 | 275 | 78,6 | 590 | 36 | 6 | 562703 | 929001218058 | 4,99 |

Gama Spots No Regulable GU10 Cristal 50W



4000 -
6500K



2700K



GU10



15,000 H



EEL



36°



60°



CRI

Ángulo del Haz Ángulo del Haz

| Descripción | LED | Equivalencia | Temp. Color | Lumen | Eficacia | Intensidad del haz | Ángulo del Haz | Pack | EAN1 | GPC | PVPR |
|--|-----|--------------|-------------|-------|----------|--------------------|----------------|------|---------|--------------|------|
| | W | W | K | lm | lm/W | | | | 8718696 | | € |
| LEDClassic 50W GU10 CW 36D RF ND 1BC/6 | 4.6 | 50 | 4000 | 390 | 84,8 | 770 | 36 | 6 | 562741 | 929001218217 | 5,99 |
| LEDClassic 50W GU10 CW 230V 60D ND 1BC/6 | 4.6 | 50 | 4000 | 390 | 84,8 | 450 | 60 | 6 | 562802 | 929001218558 | 5,99 |
| LED classic 50W GU10 WW 36D ND SRT4 | 4.6 | 50 | 2700 | 355 | 77,2 | 700 | 36 | 4 | 582572 | 929001215258 | 5,99 |
| LED classic 50W GU10 WH 36D ND SRT4 | 4.6 | 50 | 3000 | 355 | 77,2 | 700 | 36 | 4 | 562727 | 929001218158 | 5,99 |
| LED classic 50W GU10 CDL 36D ND 1BC/6 | 4.6 | 50 | 6500 | 390 | 84,8 | 770 | 36 | 6 | 562765 | 929001218358 | 5,99 |

Gama Spots No Regulable GU10 Cristal 65W



| Descripción | LED | Equivalencia | Temp. Color | Lumen | Eficacia | Intensidad del haz | Ángulo del Haz | Pack | EAN1 | GPC | PVPR |
|--|-----|--------------|-------------|-------|----------|--------------------|----------------|------|---------|--------------|------|
| | W | W | K | lm | lm/W | | | | 8718696 | | € |
| LEDClassic 65W GU10 WH 36D RF ND 1BC/6 | 5 | 65 | 3000 | 460 | 92,0 | 800 | 36 | 6 | 733431 | 929001381277 | 7,99 |
| LEDClassic 65W GU10 CW 36D ND 1BC/6 | 5 | 65 | 4000 | 485 | 97,0 | 800 | 36 | 6 | 732670 | 929001381301 | 7,99 |

Gama Spots No Regulable GU10 Cristal con ángulo de apertura 120D



NON-DIMMABLE



4000K



GU10



15,000 H



EEL



120°
Ángulo del Haz



CRI

| Descripción | LED | Equivalencia | Temp. Color | Lumen | Eficacia | Intensidad del haz | Ángulo del Haz | Pack | EAN1 | GPC | PVPR |
|--|-----|--------------|-------------|-------|----------|--------------------|----------------|------|---------|--------------|------|
| | W | W | K | lm | lm/W | | | | 8718696 | | € |
| LEDClassic 550lm GU10 CW 120D ND 1BC/6 | 5 | / | 4000 | 550 | 84,8 | / | 120 | 6 | 750377 | 929001297301 | 4,99 |

Gama Spots Regulable WarmGlow

35W/50W



Regulable en intensidad y temperatura de color



2200 -
2700K



GU10



15,000 H



EEL



36°
Ángulo del Haz



CRI

| Descripción | LED | Equivalencia | Temp. Color | Lumen | Eficacia | Intensidad del haz | Ángulo del Haz | Pack | EAN1 | GPC | PVPR |
|-------------------------------------|-----|--------------|-------------|-------|----------|--------------------|----------------|------|---------|--------------|------|
| | W | W | K | lm | lm/W | | | | 8718696 | | € |
| LEDClassic 35W GU10 WW 36D WGD SRT4 | 4 | 35 | 2200-2700 | 250 | 62.5 | 540 | 36 | 4 | 582534 | 929001363858 | 7,99 |
| LEDClassic 50W GU10 WW 36D WGD SRT4 | 5 | 50 | 2200-2700 | 350 | 70 | 710 | 36 | 4 | 562864 | 929001364101 | 8,99 |

Gama Spots Regulable GU10 35W/50W/80W



DIMMABLE



4000K



2700K



GU10



15,000 H
25,000 H



EEL



36°
Ángulo del Haz



CRI

| Descripción | LED | Equivalencia | Temp. Color | Lumen | Eficacia | Intensidad del haz | Ángulo del Haz | Pack | EAN1 | GPC | PVPR |
|--------------------------------------|-----|--------------|-------------|-------|----------|--------------------|----------------|------|---------|--------------|------|
| | W | W | K | lm | lm/W | | | | 8718696 | | € |
| LEDClassic 35W GU10 CW 36D D 1BC/6 | 4 | 35 | 4000 | 270 | 67,5 | 540 | 36 | 6 | 721476 | 929001364001 | 6,99 |
| LEDClassic 50W GU10 CW 36D DIM 1BC/6 | 5 | 50 | 4000 | 380 | 76,0 | 710 | 36 | 6 | 562888 | 929001364301 | 7,99 |
| LED 80W GU10 CW 36D D 1BC/6 | 7 | 80 | 4000 | 610 | 87,1 | 1200 | 36 | 6 | 708156 | 929001349501 | 9,99 |
| LED 80W GU10 WW 36D D 1BC/6 | 7 | 80 | 2700 | 575 | 82,1 | 1200 | 36 | 6 | 711224 | 929001353301 | 9,99 |

Gama Spots No Regulable GU5.3 Cristal 20W/35W/50W



4000K



2700K



G5.3



15,000 H



EEL



EEL



36°

Ángulo del Haz



CRI

| Descripción | LED | Equivalencia | Temp. Color | Lumen | Eficacia | Intensidad del haz | Ángulo del Haz | Pack | EAN1 | GPC | PVPR |
|---------------------------------|-----|--------------|-------------|-------|----------|--------------------|----------------|------|---------|--------------|------|
| | W | W | K | lm | lm/W | | | | 8718696 | | € |
| LED 20W MR16 WW 36D ND RF 1BC/6 | 3 | 20 | 2700 | 230 | 76,7 | 600 | 36 | 6 | 710470 | 929001344001 | 5,99 |
| LED 35W MR16 WW 36D ND SRT4 | 5 | 35 | 2700 | 345 | 69,0 | 650 | 36 | 4 | 710494 | 929001344301 | 6,99 |
| LED 35W MR16 CW 36D ND RF 1BC/6 | 5 | 35 | 4000 | 390 | 78,0 | 650 | 36 | 6 | 710531 | 929001344501 | 6,99 |
| LED 50W MR16 WW 36D ND SRT4 | 8 | 50 | 2700 | 621 | 77,6 | 1100 | 36 | 4 | 710555 | 929001344901 | 8,99 |
| LED 50W MR16 CW 36D ND 1SRT4 | 8 | 50 | 4000 | 630 | 78,8 | 1100 | 36 | 4 | 710593 | 929001345101 | 8,99 |

Gama Spots Regulable GU5.3 Cristal 35W



DIMMABLE



4000K



2700K



G5.3



15,000 H



EEL



EEL



36°



60°



CRI

Ángulo del Haz Ángulo del Haz

| Descripción | LED | Equivalencia | Temp. Color | Lumen | Eficacia | Intensidad del haz | Ángulo del Haz | Pack | EAN1 | GPC | PVPR |
|--------------------------------|-----|--------------|-------------|-------|----------|--------------------|----------------|------|---------|--------------|------|
| | W | W | K | lm | lm/W | | | | 8718696 | | € |
| LED 35W MR16 WW 36D D RF 1BC/6 | 5 | 35 | 2700 | 380 | 76,0 | 980 | 36 | 6 | 708477 | 929001327177 | 9,99 |
| LED 35W MR16 WW 60D D RF 1BC/6 | 5 | 35 | 2700 | 360 | 72,0 | 330 | 60 | 6 | 708514 | 929001327401 | 9,99 |
| LED 35W MR16 CW 36D D RF 1BC/6 | 5 | 35 | 4000 | 410 | 82,0 | 1000 | 36 | 6 | 708491 | 929001327301 | 9,99 |

Gama Spot Regulable WarmGlow GU5.3 50W



Regulable en intensidad y temperatura de color



4000K



2700K



G5.3



15,000 H



EEL



EEL



36°
Ángulo del Haz



60°
Ángulo del Haz



CRI

| Descripción | LED | Equivalencia | Temp. Color | Lumen | Eficacia | Intensidad del haz | Ángulo del Haz | Pack | EAN1 | GPC | PVPR |
|--------------------------------|-----|--------------|-------------|-------|----------|--------------------|----------------|------|---------|--------------|-------|
| | W | W | K | lm | lm/W | | | | 8718696 | | € |
| LED 50W MR16 WW 36D D 1SRT4 | 7 | 50 | 2700 | 621 | 88,7 | 1600 | 36 | 4 | 708644 | 929001327758 | 12,99 |
| LED 50W MR16 WW 60D D RF 1BC/6 | 7 | 50 | 2700 | 621 | 88,7 | 800 | 60 | 6 | 708576 | 929001328001 | 12,99 |

Gama Reflectoras



Mate
No regulable



Filamento
No regulable



Mate
Regulable

Gama Reflectoras No Regulable Mate



2700K



E14



E27



15,000 H



EEL



CRI

| Descripción | LED | Equivalencia | Temp. Color | Lumen | Eficacia | Intensidad del haz | Ángulo del Haz | Pack | EAN1 | GPC | PVPR |
|---|-----|--------------|-------------|-------|----------|--------------------|----------------|------|---------|--------------|-------|
| | W | W | K | lm | lm/W | | | | 8718696 | | € |
| LED 25W E14 WW 230V R50 36D ND SRT4 | 1.7 | 25 | 2700 | 135 | 79,4 | 310 | 36 | 4 | 578438 | 929001235858 | 4,99 |
| LED 30W E14 WW 230V R39 36D ND SRT4 | 2.2 | 28 | 2700 | 150 | 68,2 | 250 | 36 | 4 | 578377 | 929001235558 | 5,99 |
| LED 40W E14 WW 230V R50 36D ND RF 1BC/6 | 2.9 | 40 | 2700 | 230 | 79,3 | 530 | 36 | 6 | 578452 | 929001235917 | 5,99 |
| LED 40W E27 WW 230V R63 36D ND SRT4 | 2.7 | 40 | 2700 | 210 | 77,8 | 450 | 36 | 4 | 578551 | 929001233658 | 8,99 |
| LED 60W E27 827WW 230V R80 40D ND RF | 3.7 | 60 | 2700 | 370 | 100,0 | 850 | 40 | 4 | 578391 | 929001235677 | 9,99 |
| LED 100W E27 827WW 230V R80 40D ND RF | 7 | 100 | 2700 | 667 | 95,3 | 1500 | 40 | 4 | 578414 | 929001235777 | 11,99 |

Gama Reflectoras No Regulable Filamento



2700K



E14



E27



15,000 H



EEL



EEL



CRI

| Descripción | LED | Equivalencia | Temp. Color | Lumen | Eficacia | Intensidad del haz | Angulo del Haz | Pack | EAN1 | GPC | PVPR |
|------------------------------------|-----|--------------|-------------|-------|----------|--------------------|----------------|------|---------|--------------|-------|
| | W | W | K | lm | lm/W | | | | 8718696 | | € |
| LED Classic 28W R50 E14 WW ND SRT4 | 3.8 | 28 | 2700 | 330 | 86,8 | / | <120 | 4 | 714447 | 929001316101 | 6,99 |
| LED Classic 28W R63 E27 WW ND SRT4 | 3.2 | 28 | 2700 | 330 | 103,1 | / | <120 | 4 | 714461 | 929001316201 | 9,99 |
| LED Classic 42W R63 E27 WW ND SRT4 | 4.5 | 42 | 2700 | 505 | 112,2 | / | <120 | 4 | 714485 | 929001316301 | 10,99 |
| LED Classic 42W R80 E27 WW ND SRT4 | 5 | 42 | 2700 | 505 | 101,0 | / | <120 | 4 | 714423 | 929001316401 | 12,99 |

Gama Reflectoras Regulable Mate 60W



DIMMABLE



2700K



E14



E27



15,000 H



EEL



CRI

| Descripción | LED | Equivalencia | Temp. Color | Lumen | Eficacia | Intensidad del haz | Ángulo del Haz | Pack | EAN1 | GPC | PVPR |
|--|-----|--------------|-------------|-------|----------|--------------------|----------------|------|---------|--------------|------|
| | W | W | K | lm | lm/W | | | | 8718291 | | € |
| LED 60W E27 WW 230V R63 36D DIM RF 1BC/6 | 5.7 | 60 | 2700 | 345 | 60,5 | 600 | 36 | 6 | 785415 | 92900114417 | 9.99 |
| | | | | | | | | | 8718696 | | |
| LED 60W E14 WW 230V R50 36D DIM SRT4 | 5 | 60 | 2700 | 320 | 64,0 | 735 | 36 | 4 | 578476 | 929001236058 | 7.99 |

Gama Cápsulas



No regulable
G4



Regulables
G4 y G9

Gama Cápsulas No Regulables G4/G9



NON-DIMMABLE



2700 -
3000K



G4



G9



15,000 H



EEL



CRI

| Descripción | LED | Equivalencia | Temp. Color | Lumen | Eficacia | Intensidad del haz | Ángulo del Haz | Pack | EAN1 | GPC | PVPR |
|-------------------------------|-----|--------------|-------------|-------|----------|--------------------|----------------|------|---------|--------------|------|
| | W | W | K | lm | lm/W | | | | 8718696 | | € |
| LED 10W G4 WH 12V ND 1BC/6 | 1.2 | 10 | 3000 | 105 | 87.5 | / | / | 6 | 422304 | 92900118758 | 5,99 |
| LED 20W G4 WH 12V ND RF 1BC/6 | 2 | 20 | 3000 | 200 | 97.5 | / | / | 6 | 419182 | 929001131817 | 6,99 |
| LED 25W G9 WW ND RF 1BC/6 | 1.9 | 25 | 2700 | 204 | 107.4 | N.A | N.A | 6 | 734469 | 929001323877 | 7,99 |
| LED 35W G9 WH ND 1BC/6 | 2.8 | 35 | 3000 | 315 | 112.5 | N.A | N.A | 6 | 726365 | 929001357801 | 8,99 |

Gama Cápsulas Regulables G4/G9



DIMMABLE



2700K



G4



G9



15,000 H



EEL



CRI

| Descripción | LED | Equivalencia | Temp. Color | Lumen | Eficacia | Intensidad del haz | Ángulo del Haz | Pack | EAN1 | GPC | PVPR |
|----------------------------|-----|--------------|-------------|-------|----------|--------------------|----------------|------|---------|--------------|------|
| | W | W | K | lm | lm/W | | | | 8718696 | | € |
| LED 20W G4 WW 12V Dim SRT4 | 2 | 20 | 2700 | 200 | 100 | / | / | 4 | 578636 | 929001235358 | 7,99 |
| LED 25W G9 WW 230V Dim/4 | 2.3 | 25 | 2700 | 215 | 93 | / | / | 4 | 578674 | 929001232058 | 8,99 |

Gama Lineales



No regulable
R7S



Regulables
R7S

Gama Lineales No Regulable R7S 60W



3000K



4000K



R7S



15,000 H



EEL



CRI

| Descripción | LED | Equivalencia | Temp. Color | Lumen | Eficacia | Intensidad del haz | Ángulo del Haz | Pack | EAN1 | GPC | PVPR |
|------------------------------|-----|--------------|-------------|-------|----------|--------------------|----------------|------|---------|--------------|-------|
| | W | W | K | lm | lm/W | | | | 8718696 | | € |
| LED 60W R7S 78mm WH ND SRT4 | 7.5 | 60 | 3000 | 950 | 126,7 | NA | / | 4 | 713402 | 929001339001 | 16,99 |
| LED 60W R7S 78mm CW ND 1BC/6 | 7.5 | 60 | 4000 | 1000 | 133,3 | NA | / | 6 | 713440 | 929001339101 | 16,99 |
| LED 60W R7S 118mm WH ND SRT4 | 6.5 | 60 | 3000 | 806 | 124 | / | / | 4 | 522516 | 929001186158 | 12,99 |

Gama Lineales Regulable R7S 100W/120W



DIMMABLE



3000K



4000K



R7S



15,000 H



EEL



EEL



CRI

| Descripción | LED | Equivalencia | Temp. Color | Lumen | Eficacia | Intensidad del haz | Ángulo del Haz | Pack | EAN1 | GPC | PVPR |
|-------------------------------|-----|--------------|-------------|-------|----------|--------------------|----------------|------|---------|--------------|-------|
| | W | W | K | lm | lm/W | | | | 8718696 | | € |
| LED 100W R7S 118mm CW D 1BC/6 | 14 | 100 | 4000 | 1800 | 128,6 | / | / | 6 | 578759 | 929001243858 | 19,99 |
| LED 100W R7S 118mm WH D SRT4 | 14 | 100 | 3000 | 1600 | 114,3 | / | / | 4 | 578735 | 929001243758 | 19,99 |
| LED 120W R7S 118mm WH D SRT4 | 14 | 120 | 3000 | 2000 | 142,9 | / | / | 4 | 713464 | 929001353601 | 23,99 |
| LED 120W R7S 118mm CW D 1BC/6 | 14 | 120 | 4000 | 2000 | 142,9 | / | / | 6 | 713488 | 929001353701 | 23,99 |

Gama Especiales



No regulables
T25



No regulables
GX53

Gama Especiales Frigorífico

No regulable T25



2700K



E14



15,000 H



EEL



EEL



CRI

| Descripción | LED | Equivalencia | Temp. Color | Lumen | Eficacia | Pack | EAN1 | GPC | PVPR |
|-----------------------------------|-----|--------------|-------------|-------|----------|------|---------|--------------|------|
| | W | W | K | lm | lm/W | | 8718696 | | € |
| LED 15W T25 E14 WW FR ND RF 1BC/6 | 1,7 | 15 | 2700 | 150 | 88 | 6 | 703113 | 929001325777 | 6,99 |
| LED 25W T25 E14 WW FR ND SRT4 | 3,2 | 25 | 2700 | 250 | 78 | 4 | 703137 | 929001325801 | 7,99 |

Gama Especiales No Regulable GX53



NON-DIMMABLE



2700K



4000K



GX53



15,000 H



EEL



CRI

| Descripción | LED | Equivalencia | Temp. Color | Lumen | Eficacia | Intensidad del haz | Ángulo del Haz | Pack | EAN1 | GPC | PVPR |
|--------------------------|-----|--------------|-------------|-------|----------|--------------------|----------------|------|---------|--------------|------|
| | W | W | K | lm | lm/W | | | | 8718696 | | € |
| LED 40W GX53 CW ND IBC/6 | 5.5 | 40 | 4000 | 560 | 101,8 | / | / | 6 | 724552 | 929001264401 | 6,99 |
| LED 40W GX53 WW ND SRT4 | 5.5 | 40 | 2700 | 500 | 90,9 | / | / | 4 | 724576 | 929001264501 | 6,99 |

Gama Iluminación Inteligente

SceneSwitch permite cambiar la temperatura de color de la bombilla solamente utilizando el interruptor de la luz



SceneSwitch
Sensor de Luz Diurna



Estandar
SceneSwitch



Vela
SceneSwitch



Spot GU10
SceneSwitch

Gama Estandar SceneSwitch y Gama Sensor de Luz Diurna 60w



SceneSwitch



NON-DIMMABLE



2700 -
4000



2500 -
2200



E27



15,000 H



EEL



EEL



150°
Ángulo del Haz




200°
Ángulo del Haz



CRI

| Descripción | LED | Equivalencia | Temp. Color | Lumen | Eficacia | Pack | EAN1 | GPC | PVPR |
|--|-----------|--------------|----------------|-------------|----------|------|---------|--------------|-------|
| SCENESWITCH | W | W | K | lm | lm/W | | 8718696 | | € |
| LED SSW 60W A60 E27 WW FR ND RF 1BC/6 | 8/5/02 | 60 | 2200/2500/2700 | 806-320-80 | 101 | 6 | 588840 | 929001236517 | 9,99 |
| LED SSW 60W A60 E27 WW-CW FR ND 1SRT4 | 9,5 | 60 | 2700/4000 | 806 | 85 | 4 | 598375 | 929001264158 | 9,99 |
| LEDClassic SSW 60W A60 E27 WW CL ND 1SRT | 1,6-3-7,5 | 16-30-60 | 2200-2500-2700 | 150-320-806 | 107 | 4 | 743096 | 929001383801 | 10,99 |
| LUZ DIURNA | | | | | | | | | |
| LED D2D 60W A60 E27 CW FR ND 1BC/6 | 6,5 | 60 | 4000 | 806 | 124 | 6 | 739426 | 929001383701 | 14,99 |
| LED D2D 60W A60 E27 WW FR ND SRT4 | 7,5 | 60 | 2700 | 806 | 107 | 4 | 739402 | 929001383601 | 14,99 |

Gama Estandar SceneSwitch 100w



2700 - 4000K



2200 - 2500 - 2700K



E27



15,000 H



EEL



150°
Ángulo del Haz



250°
Ángulo del Haz



CRI

| Descripción | LED | Equivalencia | Temp. Color | Lumen | Eficacia | Pack | EAN1 | GPC | PVPR |
|--|----------|--------------|----------------|--------------|----------|------|---------|--------------|-------|
| | W | W | K | lm | lm/W | | 8718696 | | € |
| LED SSW 100W A67 E27 WW FR ND 1BC/6 | 14-7-3,5 | 100 | 2200-2500-2700 | 1521-600-150 | 108 | 6 | 706794 | 929001336601 | 13,99 |
| LED SSW 100W A67 E27 WW-CW FR ND 1BC/6 | 14 | 100 | 2700-4000 | 1521 | 108 | 6 | 706831 | 929001336801 | 13,99 |

Gama Vela SceneSwitch 40w



2200 - 2500
- 2700K



E14



15,000 H



EEL



EEL



CRI

| Descripción | LED | Equivalencia | Temp. Color | Lumen | Eficacia | Pack | EAN1 | GPC | PVPR |
|---------------------------------------|---------|--------------|----------------|------------|----------|------|---------|--------------|------|
| | W | W | K | lm | lm/W | | 8718696 | | € |
| LED SSW 40W B38 E14 WW CL ND RF 1BC/6 | 5,5/4/2 | 40 | 2200/2500/2700 | 470/190/50 | | 6 | 598474 | 929001260817 | 8,99 |

Gama Spot SceneSwitch GU10



SceneSwitch



NON-DIMMABLE



2200 - 2500
- 2700K



GU10



15,000 H



EEL



36°
Ángulo del Haz

| Descripción | LED | Equivalencia | Temp. Color | Lumen | Eficacia | Intensidad y ángulo del haz | Pack | EAN1 | GPC | PVPR |
|-------------------------------------|-----------|--------------|----------------|-------|----------|-----------------------------|------|---------|--------------|------|
| | W | W | K | lm | lm/W | | | 8718696 | | € |
| LED SSW 50W GU10 WW 36D RF ND 1BC/6 | 1.5/3.5/5 | 5/20/50 | 2200-2500-2700 | 345 | 69 | 600 36 | 6 | 710937 | 929001346001 | 9.99 |

Gama Tubos



Tubos

Lineales

PLC

Tubos



4000 -
6500K



G13



15,000 H



EEL



CRI

| Descripción | LED | Equivalencia | Temp. Color | Lumen | Eficacia | Intensidad del haz | Ángulo del Haz | Pack | EAN1 | GPC | PVPR |
|--------------------------------------|-----|--------------|-------------|-------|----------|--------------------|----------------|------|---------|--------------|-------|
| | W | W | K | lm | lm/W | | | | 8718696 | | € |
| LED T8 600mm 8W G13 CW ND 1CT/4 G | 8 | 18 | 4000 | 800 | 100 | N/A | 160 | 4 | 662274 | 929001276201 | 10,99 |
| LED T8 600mm 8W G13 CDL ND 1CT/4 G | 8 | 18 | 6500 | 800 | 100 | N/A | 160 | 4 | 662298 | 929001276301 | 10,99 |
| LED T8 1200mm 16W G13 CW ND 1CT/4 G | 16 | 36 | 4000 | 1600 | 100 | N/A | 160 | 4 | 662236 | 929001276001 | 14,99 |
| LED T8 1200mm 16W G13 CDL ND 1CT/4 G | 16 | 36 | 6500 | 1600 | 100 | N/A | 160 | 4 | 662250 | 929001276101 | 14,99 |
| LED T8 1500mm 20W G13 CW ND 1CT/4 C | 20 | 58 | 4000 | 2000 | 100 | N/A | 160 | 4 | 710975 | 929001338101 | 18,99 |
| LED T8 1500mm 20W G13 CDL ND 1CT/4 C | 20 | 58 | 6500 | 2000 | 100 | N/A | 160 | 4 | 711019 | 929001338201 | 18,99 |

Lineales



2700K



S14d



S14s



S19



15,000 H



EEL




CRI



CRI

| Descripción | LED | Equivalencia | Temp. Color | Lumen | Eficacia | Intensidad del haz | Angulo del Haz | Pack | EAN1 | GPC | PVPR |
|---------------------------------|-----|--------------|-------------|-------|----------|--------------------|----------------|------|---------|--------------|-------|
| | W | W | K | lm | lm/W | | | | 8718696 | | € |
| LED 3W 300mm S14D WW ND 1CT/4 | 3 | | 2700 | 250 | 83 | N/A | 160 | 4 | 586051 | 929001249301 | 13,99 |
| LED 3W 300mm S14S WW ND 1CT/4 | 3 | | 2700 | 250 | 83 | N/A | 160 | 4 | 789482 | 92900116330 | 13,99 |
| LED 4.5W 500mm S14D WW ND 1CT/4 | 4.5 | | 2700 | 375 | 83 | N/A | 160 | 4 | 586075 | 929001249401 | 15,99 |
| LED 4.5W 500mm S14S WW ND 1CT/4 | 4.5 | | 2700 | 375 | 83 | N/A | 160 | 4 | 789505 | 92900116430 | 15,99 |
| LED 6.5W 310mm S19 WW ND 1CT/4 | 6.5 | | 2700 | 480 | 74 | N/A | 160 | 4 | 419854 | 929001126730 | 17,99 |

PLC



| Descripción | LED | Equivalencia | Temp. Color | Lumen | Eficacia | Intensidad del haz | Ángulo del Haz | Pack | EAN1 | GPC | PVPR |
|----------------------------|-----|--------------|-------------|-------|----------|--------------------|----------------|------|---------|--------------|-------|
| | W | W | K | lm | lm/W | | | | 8718696 | | € |
| LED PLC 6.5W 840 2P G24d-2 | 6.5 | 18 | 4000 | 700 | 108 | / | / | 10 | 733738 | 929001201501 | 10,99 |
| LED PLC 8.5W 840 2P G24d-3 | 8.5 | 26 | 4000 | 1000 | 118 | / | / | 10 | 733714 | 929001201301 | 12,99 |



Gama Filamento

Gama Estandar No Regulable Filamento Clara 40W/60W



NON-DIMMABLE



4000 -
6500K



E27



15,000 H



EEL



CRI

| Descripción | LED | Equivalencia | Temp. Color | Lumen | Eficacia | Pack | EAN1 | GPC | PVPR |
|---|-----|--------------|-------------|-------|----------|------|---------|--------------|------|
| | W | W | K | lm | lm/W | | 8718696 | | € |
| LED classic 40W A60 E27 CW CL ND 1BC/6 | 4 | 40w | 4000k | 540 | | 6 | 766743 | 929001814901 | 5,99 |
| LED classic 40W A60 E27 CDL CL ND 1BC/6 | 4 | 40w | 6500k | 540 | | 6 | 766767 | 929001815101 | 5,99 |
| LED classic 60W A60 E27 CDL CL ND 1BC/6 | 7 | 60W | 6500k | 850 | | 6 | 766804 | 929001815201 | 6,99 |
| LED classic 60W A60 E27 CWCL ND 1BC/6 | 7 | 60W | 4000K | 850 | | 6 | 766781 | 929001815001 | 6,99 |

Gama Estandar No Regulable Filamento Clara 75W/100W



NON-DIMMABLE



2700K



4000K



E27



15,000 H



EEL



CRI

| Descripción | LED | Equivalencia | Temp. Color | Lumen | Eficacia | Pack | EAN1 | GPC | PVPR |
|---|-----|--------------|-------------|-------|----------|------|---------|--------------|-------|
| | W | W | K | lm | lm/W | | 8718696 | | € |
| LED classic 75W A60 E27 CW CL ND 1BC/6 | 8 | 75 | 4000 | 1055 | 132 | 6 | 742471 | 929001384101 | 8,99 |
| LED classic 100W A67 E27 CW CL ND 1BC/6 | 11 | 100 | 4000 | 1521 | 138 | 6 | 742518 | 929001384501 | 11,99 |

Gama Estandar Regulable WarmGlow Filamento Clara 40W/60W

Regulable en intensidad y temperatura de color



2200 -
2700K



E27



15,000 H



EEL



CRI

| Descripción | LED | Equivalencia | Temp. Color | Lumen | Eficacia | Pack | EAN1 | GPC | PVPR |
|---|-----|--------------|-------------|-------|----------|------|---------|--------------|-------|
| | W | W | K | lm | lm/W | | 8718696 | | € |
| LED classic 40W A60 E27 WW CL WGD SRT4 | 5,5 | 40 | 2200-2700 | 470 | 85 | 4 | 709283 | 929001333601 | 7,99 |
| LED classic 60W A60 E27 WW CL WGD SRT4 | 8 | 60 | 2200-2700 | 806 | 101 | 4 | 709320 | 929001333801 | 8,99 |
| LED classic 60W ST64 E27 WW CL WGD SRT4 | 8 | 60 | 2200-2700 | 806 | 101 | 4 | 709368 | 929001334001 | 10,99 |

Gama Estandar y Globo Regulable Filamento Clara 40W/60W



DIMMABLE



2700K



E27



15,000 H



EEL



EEL



300°
Ángulo del Haz



CRI

| Descripción | LED | Equivalencia | Temp. Color | Lumen | Eficacia | Pack | EAN1 | GPC | PVPR |
|---------------------------------------|-----|--------------|-------------|-------|----------|------|---------|--------------|-------|
| | W | W | K | lm | lm/W | | 8718696 | | € |
| LED classic 40W A60 E27 WW CL D SRT4 | 5,5 | 40 | 2700 | 470 | 85 | 4 | 709023 | 929001331001 | 6,99 |
| LED classic 60W A60 E27 WW CL D SRT4 | 8 | 60 | 2700 | 806 | 101 | 4 | 709061 | 929001331201 | 7,99 |
| LED classic 60W ST64 E27 WW CL D SRT4 | 7 | 60 | 2700 | 806 | 115 | 4 | 751046 | 929001228658 | 9,99 |
| LEDclassic 60W G93 E27 WW CL D | 7 | 60 | 2700 | 806 | 115 | 4 | 575413 | 929001229001 | 11,99 |

Gama Estandar y Globo Regulable Filamento Ambar



DIMMABLE



2000K



E27



15,000 H



EEL



CRI

| Descripción | LED | Equivalencia | Temp. Color | Lumen | Eficacia | Pack | EAN1 | GPC | PVPR |
|--|-----|--------------|-------------|-------|----------|------|---------|--------------|-------|
| | W | W | K | lm | lm/W | | 8718696 | | € |
| LED classic 48W A60 E27 FL GOLD D SRT4 | 7,5 | 48 | 2000 | 610 | 81 | 4 | 709146 | 929001332901 | 8,99 |
| LED classic 50W ST64 E27 2000K GOLD D RF | 7 | 50 | 2000 | 630 | 90 | 6 | 575390 | 929001228917 | 15,99 |
| LEDclassic 50W G120 E27 2000K GOLD D | 7 | 50 | 2000 | 630 | 90 | 4 | 575437 | 929001229101 | 15,99 |

Gama Velas y Esfericas Regulable Filamento Clara 25W/40W



DIMMABLE



2700K



E14



E27



15,000 H



EEL



EEL



CRI

| Descripción | LED | Equivalencia | Temp. Color | Lumen | Eficacia | Pack | EAN1 | GPC | PVPR |
|---------------------------------------|-----|--------------|-------------|-------|----------|------|---------|--------------|------|
| | W | W | K | lm | lm/W | | 8718696 | | € |
| LED classic 25W B35 E14 WW CL D SRT4 | 2,7 | 25 | 2700 | 250 | 93 | 4 | 709986 | 929001332001 | 6,99 |
| LED classic 25W P45 E14 WW CL D SRT4 | 2,7 | 25 | 2700 | 250 | 93 | 4 | 710043 | 929001332301 | 6,99 |
| LED classic 25W P45 E27 WW CL D SRT4 | 2,7 | 25 | 2700 | 250 | 93 | 4 | 710067 | 929001332401 | 6,99 |
| LED classic 40W B35 E14 WW CL D SRT4 | 5 | 40 | 2700 | 470 | 94 | 4 | 710005 | 929001332101 | 7,99 |
| LED classic 40W P45 E14 WW CL D SRT4 | 5 | 40 | 2700 | 470 | 94 | 4 | 710081 | 929001332501 | 7,99 |
| LED classic 40W P45 E27 WW CL D SRT4 | 5 | 40 | 2700 | 470 | 94 | 4 | 710104 | 929001332601 | 7,99 |
| LED classic 40W BA35 E14 WW CL D SRT4 | 5 | 40 | 2700 | 470 | 94 | 4 | 710142 | 929001332801 | 7,99 |

Gama Velas y Esfericas Regulable Filamento Ambar 35W



DIMMABLE



2500K



E14



E27



15,000 H



EEL



CRI

| Descripción | LED | Equivalencia | Temp. Color | Lumen | Eficacia | Pack | EAN1 | GPC | PVPR |
|--|-----|--------------|-------------|-------|----------|------|---------|--------------|------|
| | W | W | K | lm | lm/W | | 8718696 | | € |
| LED classic 35W P45 E27 GOLD D 1SR T4 | 5 | 35 | 2500 | 410 | 82 | 4 | 750803 | 929001395501 | 9,99 |
| LED classic 35W B35 E14 GOLD D 1SR T4 | 5 | 35 | 2500 | 410 | 82 | 4 | 750742 | 929001395201 | 9,99 |
| LED classic 35W P45 E14 GOLD D 1SR T4 | 5 | 35 | 2500 | 410 | 82 | 4 | 750766 | 929001395301 | 9,99 |
| LED classic 35W BA35 E14 GOLD D 1SR T4 | 5 | 35 | 2500 | 410 | 82 | 4 | 750780 | 929001395401 | 9,99 |



Gama Vintage

Gama Estandar Vintage No Regulable

Filamento Espiral Gigante



NON-DIMMABLE

Disponible a finales de octubre



2000K



E27



15,000 H




EEL



CRI

| Descripción | LED | Equivalencia | Temp. Color | Lumen | Eficacia | Pack | EAN1 | GPC | PVPR |
|--|-----|--------------|-------------|-------|----------|------|---------|--------------|-------|
| LED BULB FILAMENTO | W | W | K | lm | lm/W | | 8718696 | | € |
| LED classic-giant 25W E27 A160 GOLD ND | 5 | 25 | 2000 | 300 | | 2 | 768068 | 929001817101 | 44,99 |
| LED classic-giant 25W E27 G200 GOLD ND | 5 | 25 | 2000 | 300 | | 2 | 768082 | 929001817201 | 44,99 |
| CORDONES | | | | | | | 8718686 | | |
| Vintage Cord Pendant Gold | | | | | | | 167779 | 915005623401 | 15,99 |
| Vintage Cord Pendant Black | | | | | | | 167762 | 915005623301 | 15,99 |

Gama Estandar, Globo y Vela Vintage No Regulable Filamento Espiral



2000K

E14

E27

15,000 H

EEL

CRI

| Descripción | LED | Equivalencia | Temp. Color | Lumen | Eficacia | Pack | EAN1 | GPC | PVPR |
|--|-----|--------------|-------------|-------|----------|------|---------|--------------|-------|
| | W | W | K | lm | lm/W | | 8718696 | | € |
| LED classic SP 14W A60 E27 GOLD ND 1SRT4 | 2.3 | 14 | 2000 | 125 | | 4 | 743034 | 929001391901 | 12,99 |
| LED classic SP 25W ST64 E27 GOLD ND1SRT4 | 5 | 25 | 2000 | 250 | | 4 | 743058 | 929001392001 | 12,99 |
| LED classic SP 25W G93 E27 GOLD ND 1PF/4 | 5 | 25 | 2000 | 250 | | 4 | 743072 | 929001392101 | 22,99 |
| LED classic 14W B35 E14 SP GOLD NDSRT4 | 2.3 | 14 | 2000 | 125 | | 4 | 767450 | 929001814501 | 9,99 |




Gama Promocional

| | Descripción | 8718696 | Nueva Outer box | Potencia lámpara (W) | Potencia Reemp. (W) | Temp. Color (K) | Vida útil (h) | Regulable | Lúmenes (lm) | Switch Cycle (times) | EEL | PVP € |
|--------|--|---------|-----------------|----------------------|---------------------|-----------------|---------------|-----------|--------------|----------------------|-----|-------|
| | BOMBILLAS ESTANDAR | | | | | | | | | | | |
| pack 2 | LED 40W A60 E27 WW 230V FR ND w2BC/6 | 576854 | 6 | 5.5 | 40 | 2700 | 15000 | Non-Dim | 470 | 50000 | A+ | 7.99 |
| pack 2 | LED 40W A60 E27 CW 230V FR ND 2BC/6 | 576892 | 6 | 5 | 40 | 4000 | 15000 | Non-Dim | 470 | 50000 | A+ | 7.99 |
| pack 3 | LED 40W A60 E27 WW 230V FR ND 3BC/6 | 586259 | 6 | 5.5 | 40 | 2700 | 15000 | Non-Dim | 470 | 50000 | A+ | 10.99 |
| pack 3 | LEDClassic 40W A60 E27 WW CL ND 3BC/6 | 587515 | 6 | 4.0 | 40 | 2700 | 15000 | Non-Dim | 470 | 50000 | A+ | 12.99 |
| pack 2 | LEDClassic 40W A60 E27 WW CL ND 2BC/6 | 587454 | 6 | 4 | 40 | 2700 | 15000 | Non-Dim | 470 | 50000 | A+ | 9.99 |
| pack 2 | LEDClassic 40W A60 E27 WW FR ND 2BC/10 | 422328 | 10 | 4 | 40 | 2700 | 15000 | Non-Dim | 470 | 50000 | A+ | 5.99 |
| pack 2 | LEDClassic 40W A60 E27 WW FR ND 2BC/10 | 422328 | 10 | 4.5 | 40 | 2700 | 15000 | Non-Dim | 470 | 50000 | A+ | 5.99 |
| pack 2 | LEDClassic 40W A60 E27 CW FR ND 2BC/10 | 740521 | 10 | 4.5 | 40 | 4000 | 15000 | Non-Dim | 470 | 50000 | A | 5.99 |
| pack 2 | LED classic 40W A60 E27 CDL FR ND 2BC/10 | 740545 | 10 | 4.5 | 40 | 6500 | 15000 | Non-Dim | 470 | 30000 | A++ | 5.99 |
| pack 2 | LED 60W A60 E27 WW 230V FR ND 2BC/6 | 576830 | 6 | 8 | 60 | 2700 | 15000 | Non-Dim | 806 | 50000 | A+ | 8.99 |
| pack 2 | LED 60W A60 E27 CW 230V FR ND 2BC/6 | 576878 | 6 | 7.5 | 60 | 4000 | 15000 | Non-Dim | 806 | 50000 | A+ | 8.99 |
| pack 3 | LED 60W A60 E27 WW 230V FR ND 3BC/6 | 586235 | 6 | 8 | 60 | 2700 | 15000 | Non-Dim | 806 | 50000 | A+ | 12.99 |
| pack 3 | LED 60W A60 E27 CW 230V FR ND 3BC/6 | 764596 | 6 | 7.5 | 60 | 4000 | 15000 | Non-Dim | 806 | 50000 | A+ | 12.99 |
| pack 2 | LEDClassic 60W A60 E27 WW CL ND 2BC/6 | 587478 | 6 | 6 | 60 | 2700 | 15000 | Non-Dim | 806 | 50000 | A+ | 10.99 |
| pack 3 | LEDClassic 60W A60 E27 WW CL ND 3BC/6 | 587539 | 6 | 6 | 60 | 2700 | 15000 | Non-Dim | 806 | 50000 | A+ | 14.99 |
| pack 2 | LEDClassic 60W A60 E27 WW ND 2BC/10 | 472224 | 10 | 7 | 60 | 2700 | 15000 | Non-Dim | 806 | 50000 | A+ | 6.99 |
| pack 2 | LEDClassic 60W A60 E27 CW ND 2BC/10 | 740569 | 10 | 7 | 60 | 4000 | 15000 | Non-Dim | 806 | 50000 | A | 6.99 |
| pack 2 | LED 75W A60 E27 WW 230V FR ND 2BC/6 | 586112 | 6 | 11 | 75 | 2700 | 15000 | Non-Dim | 1055 | 50000 | A+ | 10.99 |
| pack 3 | LED 75W A60 E27 WW 230V FR ND 3BC/6 | 739082 | 6 | 11.0 | 75 | 2700 | 15000 | Non-Dim | 0 | 50000 | A+ | 14.99 |
| pack 3 | LED 75W A60 E27 CW 230V FR ND 3BC/6 | 739068 | 6 | 11.0 | 75 | 4000 | 15000 | Non-Dim | 0 | 50000 | A+ | 14.99 |
| pack 2 | LED classic 75W A60 E27 WW FR ND 2BC/10 | 703830 | 10 | 8.5 | 75 | 2700 | 15000 | Non-Dim | 1055 | 50000 | A | 10.99 |

| | Descripción | 8718696 | Nueva Outer box | Potencia lámpara (W) | Potencia Reemp. (W) | Temp. Color (K) | Vida útil (h) | Regulable | Lúmenes (lm) | Switch Cycle (times) | EEL | PVP |
|--------|--|---------|-----------------|----------------------|---------------------|-----------------|---------------|-----------|--------------|----------------------|-----|-------|
| pack 2 | LED classic 75W A60 E27 CW FR ND 2BC/10 | 703854 | 10 | 8.5 | 75 | 4000 | 15000 | Non-Dim | 1055 | 50000 | A | 10.99 |
| pack 2 | LED classic 75W A60 E27 CDL FR ND 2BC/10 | 740507 | 10 | 8.5 | 75 | 6500 | 15000 | Non-Dim | 1055 | 50000 | A | 10.99 |
| pack 2 | LED 100W A60 E27 WW 230V FR ND 2BC/6 | 586099 | 6 | 13 | 100 | 2700 | 15000 | Non-Dim | 1521 | 50000 | A+ | 15.99 |
| pack 2 | LED 100W A60 E27 CW 230V FR ND 2BC/6 | 789865 | 6 | 13.0 | 100 | 4000 | 15000 | Non-Dim | 1521 | 50000 | A+ | 15.99 |
| pack 3 | LED 100W A60 E27 WW 230V FR ND 3BC/6 | 657782 | 6 | 13 | 100 | 2700 | 15000 | Non-Dim | 1521 | 50000 | A+ | 19.99 |
| pack 2 | LED classic 100W A67 WW FR ND 2BC/10 | 739327 | 10 | 11.5 | 100 | 2700 | 15000 | Non-Dim | 1521 | 20000 | A++ | 14.99 |
| pack 2 | LED classic 100W A67 CW FR ND 2BC/10 | 739341 | 10 | 11.5 | 100 | 4000 | 15000 | Non-Dim | 1521 | 20000 | A++ | 14.99 |
| pack 2 | LED classic 100W A67 CDL FR ND 2BC/10 | 739365 | 10 | 11.5 | 100 | 6500 | 15000 | Non-Dim | 1521 | 20000 | A++ | 14.99 |
| | BOMBILLAS VELA Y ESFÉRICA | | | | | | | | | | | |
| pack 2 | LED 25W B35 E14 WW FR ND 2BC/6 | 475201 | 6 | 4 | 25 | 2700 | 15000 | Non-Dim | 250 | 50000 | A+ | 5.99 |
| pack 3 | LED 25W B35 E14 WW FR ND 3BC/6 | 586624 | 6 | 4 | 25 | 2700 | 15000 | Non-Dim | 250 | 50000 | A+ | 7.99 |
| pack 2 | LEDClassic 25W B35 E14 WW CL ND 2BC/6 | 587553 | 6 | 2 | 25 | 2700 | 15000 | Non-Dim | 250 | 50000 | A+ | 7.99 |
| pack 2 | LED 40W B35 E14 WW FR ND 2BC/6 | 485460 | 6 | 5.5 | 40 | 2700 | 15000 | Non-Dim | 470 | 50000 | A+ | 8.99 |
| pack 3 | LED 40W B35 E14 WW FR ND 3BC/6 | 646120 | 6 | 5.5 | 40 | 2700 | 15000 | Non-Dim | 470 | 50000 | A+ | 9.99 |
| pack 3 | LED 40W P45 E27 CW FR ND 3BC/6 | 764572 | 6 | 5.5 | 40 | 2700 | 15000 | Non-Dim | 470 | 50000 | A+ | 9.99 |
| pack 2 | LED 40W P45 E14 WW FR ND 2BC/6 | 586648 | 6 | 5.5 | 40 | 2700 | 15000 | Non-Dim | 470 | 50000 | A+ | 7.99 |
| | CÁPSULAS | | | | | | | | | | | |
| pack 2 | LED 10W G4 WH 12V ND 2BC/6 | 585979 | 6 | 1.2 | 10 | 3000 | 15000 | Non-Dim | 105 | 200000 | A++ | 9.99 |
| pack 2 | LED 10W G4 WW 12V ND 2pk/6 | 578216 | 6 | 1.2 | 10 | 2700 | 15000 | Non-Dim | 120 | 50000 | A+ | 9.99 |
| pack 2 | LED 20W G4 WW 12V ND 2pk/6 | 578254 | 6 | 2 | 20 | 2700 | 15000 | Non-Dim | 200 | 50000 | A+ | 10.99 |
| pack 2 | LED 20W G4 WH 12V ND 2BC/6 | 585993 | 6 | 2 | 20 | 3000 | 15000 | Non-Dim | 200 | 200000 | A++ | 10.99 |
| pack 2 | LED 25W G9 WW ND 2BC/6 | 726914 | 6 | 1.9 | 25 | 2700 | 15000 | Non-Dim | 204 | 50000 | A | 11.99 |

| | Descripción | 8718696 | Nueva Outer box | Potencia lámpara (W) | Potencia Reemp. (W) | Temp. Color (K) | Vida útil (h) | Regulable | Lúmenes (lm) | Switch Cycle (times) | EEL | PVP |
|--------|--|---------|-----------------------|----------------------------|---------------------------|--------------------|---------------------|-----------|-----------------|----------------------------|-----|-------|
| | SPOTS GU10 | | | | | | | | | | | |
| pack 2 | LEDclassic Classic 35W GU10 WW 230V 36D ND 2BC/6 | 582633 | 6 | 3.5 | 35 | 2700 | 15000 | Non-Dim | / | 50000 | A+ | 7.99 |
| pack 2 | LEDClassic 35W GU10 WH 230V 36D ND 2BC/6 | 582671 | 6 | 3.5 | 35 | 3000 | 15000 | Non-Dim | / | 50000 | A+ | 7.99 |
| pack 3 | LEDClassic 35W GU10 WW 230V 36D ND 3BC/8 | 582350 | 8 | 3.5 | 35 | 2700 | 15000 | Non-Dim | / | 50000 | A+ | 12.99 |
| pack 3 | LEDClassic 35W GU10 CW 230V 36D ND 3BC/8 | 582374 | 8 | 3.5 | 35 | 4000 | 15000 | Non-Dim | / | 50000 | A+ | 12.99 |
| pack 3 | LED 35W GU10 WW 230V 36D 3BC/8 | 599723 | 8 | 3.5 | 35 | 2700 | 15000 | Non-Dim | 275 | 50000 | A+ | 12.99 |
| pack 3 | LED 35W GU10 WH 230V 36D 3BC/8 | 599747 | 8 | 3.5 | 35 | 3000 | 15000 | Non-Dim | 275 | 50000 | A+ | 12.99 |
| pack 3 | LED 35W GU10 CW 230V 36D 3BC/8 | 599761 | 8 | 3.5 | 35 | 4000 | 15000 | Non-Dim | 300 | 50000 | A+ | 12.99 |
| pack 2 | LEDClassic 50W GU10 WW 230V 36D ND 2BC/6 | 582695 | 6 | 4.6 | 50 | 2700 | 15000 | Non-Dim | / | 50000 | A+ | 8.99 |
| pack 2 | LEDClassic 50W GU10 WH 230V 36D ND 2BC/6 | 582718 | 6 | 4.6 | 50 | 3000 | 15000 | Non-Dim | / | 50000 | A+ | 8.99 |
| pack 2 | LEDClassic 50W GU10 CW 230V 36D ND 2BC/6 | 591468 | 6 | 4.6 | 50 | 4000 | 15000 | Non-Dim | / | 50000 | A+ | 8.99 |
| pack 2 | LEDClassic 50W GU10 WW 36D WGD 2BC/6 | 721698 | 6 | 5 | 50 | 2200-2700 | 15000 | Dim | 395 | 30000 | A++ | 12.99 |
| pack 3 | LED 50W GU10 CW 230V 60D 3BC/8 | 599860 | 8 | 5 | 50 | 4000 | 15000 | Non-Dim | 415 | 50000 | A+ | 9.99 |
| pack 3 | LEDClassic 50W GU10 WW 230V 36D ND 3BC/8 | 582411 | 8 | 4.6 | 50 | 2700 | 15000 | Non-Dim | / | 50000 | A+ | 11.99 |
| pack 3 | LEDClassic 50W GU10 CW 230V 36D ND 3BC/8 | 582435 | 8 | 4.6 | 50 | 4000 | 15000 | Non-Dim | / | 50000 | A+ | 11.99 |
| pack 3 | LEDClassic 50W GU10 WW 36D WGD 3BC/8 | 582336 | 8 | 5 | 50 | 2200-2700 | 15000 | Dim | 395 | 30000 | A++ | 11.99 |
| pack 3 | LEDClassic 400lm GU10 CW 120D ND 3BC/8 | 686843 | 8 | 4.5 | / | 4000 | 15000 | Non-Dim | 440 | 50000 | A | 9.99 |



Gama Attralux

Gama Estandar No Regulable Mate y Filamento 40W



NON-DIMMABLE



2700 -
4000K



E27



15,000 H



EEL



EEL



CRI

| Descripción | Potencia | Equivalencia | Temp. Color | Lumen | Ciclos | IRC | Pack | Dimensiones (AxL) | EAN1 | 12NC | PVPR |
|--|----------|--------------|-------------|-------|--------|-----|------|-------------------|---------|--------------|------|
| | W | | | | | | | | 8710619 | | € |
| ATR LEDclear 40W E27 WW A60 ND 1BC/6 | 4 | 40 | 2700 | 470 | 15000 | 80 | 6 | 60x104 | 392503 | 929001262001 | 3,99 |
| ATR LED 40W A60 E27 WW FR ND 1BC/6 SRP | 6 | 40 | 2700 | 470 | 15000 | 80 | 6 | 60x108 | 390394 | 929001252101 | 2,99 |
| ATR LED 40W A60 E27 CW FR ND 1BC/6 SRP | 6 | 40 | 4000 | 500 | 15000 | 80 | 6 | 60x108 | 390417 | 929001252201 | 2,99 |

Gama Estandar No Regulable

Mate 60W



2700 -
4000K



E27



15,000 H



EEL



EEL



CRI

| Descripción | Potencia | Equivalencia | Temp. Color | Lumen | Ciclos | IRC | Pack | Dimensiones (AxL) | EAN1 | 12NC | PVPR |
|---|----------|--------------|-------------|-------|--------|-----|------|-------------------|---------|--------------|------|
| | W | | | | | | | | 8710619 | | € |
| ATR LED 60W A60 E27 WW FR ND 1BC/6 G3 | 8.5 | 60 | 2700 | 806 | 15000 | 80 | 1 | 60x112 | 390479 | 929001313501 | 3,99 |
| ATR LED 60W A60 E27 CW FR ND 1BC/6 G3 | 8.5 | 60 | 4000 | 806 | 15000 | 80 | 1 | 60x112 | 390493 | 929001365201 | 3,99 |
| ATR LED clear 60W A60 E27 WW CK ND 1BC/6 G3 | 8.5 | 60 | 2700 | 806 | 15000 | 80 | 1 | 60x112 | 392480 | 929001387311 | 4,99 |

Gama Estandar No Regulable

Mate 75W



2700 -
4000K



E27



15,000 H



EEL



CRI

| Descripción | Potencia | Equivalencia | Temp. Color | Lumen | Ciclos | IRC | Pack | Dimensiones (AxL) | EAN1 | 12NC | PVPR |
|--|----------|--------------|-------------|-------|--------|-----|------|-------------------|---------|--------------|------|
| | W | | | | | | | | 8710619 | | € |
| ATR LED 75W A60 E27 WW FR ND RF 1BC G3 | 10.5 | 75 | 2700 | 1055 | 15000 | 80 | 1 | 60x120 | 390592 | 929001365577 | 5,99 |
| ATR LED 75W A60 E27 CW FR ND RF 1BC G3 | 10 | 75 | 4000 | 1055 | 15000 | 80 | 1 | 60x120 | 390615 | 929001365677 | 5,99 |

Gama Estandar No Regulable

Mate 100W



2700 -
4000K



E27



15.000 H



EEL



CRI

| Descripción | Potencia | Equivalencia | Temp. Color | Lumen | Ciclos | IRC | Pack | Dimensiones (AxL) | EAN1 | 12NC | PVPR |
|---|----------|--------------|-------------|-------|--------|-----|------|-------------------|---------|--------------|------|
| | W | | | | | | | | 8710619 | | € |
| ATR LED 100W A67 E27 CW FR ND 1BC/6 G3 | 14 | 100 | 4000 | 1521 | 15000 | 80 | 1 | 65x120 | 390233 | 929001365801 | 6,99 |
| ATR LED 100W A67 E27 WW FR ND 1BC/6 SRP | 14 | 100 | 2700 | 1521 | 50000 | 80 | 6 | 65x120 | 390196 | 929001252901 | 6,99 |

Gama Especiales

Mate T25



2700K



E14



15,000 H



EEL



CRI

| Descripción | Potencia | Equivalencia | Temp. Color | Lumen | Ciclos | IRC | Pack | Dimensiones (AxL) | EAN1 | 12NC | PVPR |
|-------------------------------------|----------|--------------|-------------|-------|--------|-------|------|-------------------|---------|--------------|------|
| | W | | | | | | | | 8710619 | | € |
| ATR LED 15W E14 WW T25 ND 1BC/8 SRP | 1.8 | 15 | 2700 | 140 | 80 | 15000 | 8 | 25x59 | 365941 | 929001169551 | 4,99 |

Gama Velas No Regulable

Mate 25W/40W



2700K



E14



15,000 H



EEL



CRI

| Descripción | Potencia | Equivalencia | Temp. Color | Lumen | IRC | Ciclos | Pack | Dimensiones (AxL) | EAN1 | 12NC | PVPR |
|--|----------|--------------|-------------|-------|-----|--------|------|-------------------|---------|--------------|------|
| | W | | | | | | | | 8710619 | | € |
| ATR LED 25W B35 E14 WW FR ND 1BC/6 SRP | 3.2 | 25 | 2700 | 250 | 80 | 15000 | 6 | 35x106 | 390677 | 929001253001 | 2,99 |
| ATR LED 40W B35 E14 WW FR ND 1BC/6 SRP | 5.5 | 40 | 2700 | 470 | 80 | 15000 | 6 | 35x106 | 390776 | 929001253601 | 4,59 |

Gama Velas No Regulable Clara y Filamento 25W



NON-DIMMABLE



2700K



E14



15,000 H



EEL



EEL



CRI

| Descripción | Potencia | Equivalencia | Temp. Color | Lumen | IRC | Ciclos | Pack | Dimensiones (AxL) | EAN1 | 12NC | PVPR |
|--|----------|--------------|-------------|-------|-----|--------|------|-------------------|---------|--------------|------|
| | W | | | | | | | | 8710619 | | € |
| ATR LED 25W B35 E14 WW CL ND 1BC/6 SRP | 3.2 | 25 | 2700 | 250 | 80 | 15000 | 6 | 35x106 | 390691 | 929001253101 | 2,99 |
| ATR LEDclear 25W E14 WW B35 ND 1BC/6 | 2.1 | 25 | 2700 | 250 | 80 | 15000 | 6 | 35x97 | 392589 | 929001261601 | 3,99 |

Gama Esfericas No Regulable Mate 25W/40W



NON-DIMMABLE



2700K



E27



E14



15,000 H



EEL



CRI

| Descripción | Potencia | Equivalencia | Pack | Dimensiones (AxL) | Temp. Color | Lumen output | IRC | Ciclos | EAN1 | 12NC | PVPR |
|---|----------|--------------|------|-------------------|-------------|--------------|-----|--------|---------|--------------|------|
| | W | | | | | | | | 8710619 | | € |
| ATR LED 25W P45 E14 WW FR ND 1BC/6 SRP | 3.2 | 25 | 6 | 45x90 | 2700 | 250 | 80 | 15000 | 390851 | 929001253201 | 2,99 |
| ATR LED 25W P45 E27 WW FR ND 1BC/6 SRP | 3.2 | 25 | 6 | 45x90 | 2700 | 250 | 80 | 15000 | 390837 | 929001253301 | 2,99 |
| ATR LED 40W P45 E14 WW P45 FR ND RF 1BC | 5.5 | 40 | 6 | 45x90 | 2700 | 470 | 80 | 15000 | 391018 | 929001253777 | 4,59 |
| ATR LED 40W P45 E27 WW FR RF ND 1BC | 5.5 | 40 | 6 | 45x90 | 2700 | 470 | 80 | 15000 | 391032 | 929001253877 | 4,59 |

Gama Esfericas No Regulable Clara y Filamento 25W/40W



2700K



E14



E27



15,000 H



EEL



EEL



CRI

| Descripción | Potencia | Equivalencia | Temp. Color | Lumen | IRC | Ciclos | Pack | Dimensiones (AxL) | EAN1 | 12NC | PVPR |
|--|----------|--------------|-------------|-------|-----|--------|------|-------------------|---------|--------------|------|
| | W | | | | | | | | 8710619 | | € |
| ATR LED 25W P45 E14 WW CL ND 1BC/6 SRP | 3.2 | 25 | 2700 | 250 | 80 | 15000 | 6 | 45x90 | 390875 | 929001253401 | 2,99 |
| ATR LED 25W P45 E27 WW CL ND 1BC/6 SRP | 3.2 | 25 | 2700 | 250 | 80 | 15000 | 6 | 45x90 | 390899 | 929001253577 | 2,99 |
| ATR LEDclear 40W E14 WW P45 ND 1BC/6 | 4 | 40 | 2700 | 470 | 80 | 15000 | 6 | 45x80 | 392527 | 929001261701 | 5,59 |

Gama Spot No Regulable GU10 35W



2700 -
4000K



GU10



15,000 H



EEL



CRI

| Descripción | Potencia | Equivalencia | Temp. Color | Lumen | IRC | Ciclos | Pack | Dimensiones (AxL) | EAN1 | 12NC | PVPR |
|----------------------------------|----------|--------------|-------------|-------|-----|--------|------|-------------------|---------|--------------|------|
| | W | | | | | | | | 8710619 | | € |
| ATR LED 35W GU10 WW 36D ND 1BC/6 | 3 | 35 | 2700 | 230 | 80 | 15000 | 6 | 50x54 | 391391 | 929001250301 | 2,99 |

Gama Spot No Regulable GU10 50W



4000K



2700K



GU10



15.000 H



EEL



CRI

| Descripción | Potencia | Equivalencia | Temp. Color | Lumen | IRC | Ciclos | Pack | Dimensiones (AxL) | EAN1 | 12NC | PVPR |
|----------------------------------|----------|--------------|-------------|-------|-----|--------|------|-------------------|---------|--------------|------|
| | W | | | | | | | | 8710619 | | € |
| ATR LED 50W GU10 WW 36D ND 1BC/6 | 4.7 | 50 | 2700 | 345 | 80 | 15000 | 6 | 50x54 | 391490 | 929001250401 | 3,99 |
| ATR LED 50W GU10 CW 36D ND 1BC/6 | 4.7 | 50 | 4000 | 380 | 80 | 15000 | 6 | 50x54 | 391551 | 929001247001 | 3,99 |

Gama Spot No Regulable MR16

35W/50W



NON-DIMMABLE



2700K



4000K



G5.3



15.000 H



EEL



CRI

| Descripción | Potencia | Equivalencia | Temp. Color | Lumen | IRC | Ciclos | Pack | Dimensiones (AxL) | EAN1 | 12NC | PVPR |
|---------------------------------------|----------|--------------|-------------|-------|-----|--------|------|-------------------|---------|--------------|------|
| | W | | | | | | | | 8710619 | | € |
| ATR LED 35W GU5,3 WW 12V 36D ND 1BC/6 | 4,5 | 35 | 2700 | 345 | 80 | 15000 | 6 | 50x46 | 391810 | 929001210901 | 4,99 |
| ATR LED 50W GU5,3 CW 12V 36D ND 1BC/6 | 8 | 50 | 4000 | 630 | 80 | 15000 | 6 | 50x46 | 391919 | 929001246001 | 4,99 |

Gama Cápsulas No Regulable G4-G9



2700K



G4



G9



15,000 H



EEL



CRI

| Descripción | Potencia | Equivalencia | Temp. Color | Lumen | IRC | Ciclos | Pack | Dimensiones (AxL) | EAN1 | 12NC | PVPR |
|--------------------------------|----------|--------------|-------------|-------|-----|--------|------|-------------------|---------|--------------|------|
| | W | | | | | | | | 8710619 | | € |
| ATR LED 25W G9 WW ND RF 1BC/8 | 2.8 | 25 | 2700 | 250 | 80 | 15000 | 8 | 17x52 | 365989 | 929001169780 | 5,99 |
| ATR LED 20W G4 WW 12V ND 1BC/8 | 1.8 | 20 | 2700 | 250 | 80 | 15000 | 8 | 17x52 | 391315 | 929001199701 | 4,99 |

Gama Reflectoras Regulables y No Regulables R50-R63



DIMMABLE



2700K



E14



E27



15,000 H



EEL



CRI

| Descripción | Potencia | Equivalencia | Temp. Color | Lumen | IRC | Ciclos | Pack | Dimensiones (AxL) | EAN1 | 12NC | PVPR |
|---|----------|--------------|-------------|-------|-----|--------|------|-------------------|---------|--------------|------|
| | W | | | | | | | | 8710619 | | € |
| ATR LED 40W E14 WW R50 36D DIM 1BC/6 SRP | 3.5 | 40 | 2700 | 255 | 80 | 15000 | 6 | 50x86 | 391971 | 929001250801 | 6,99 |
| ATR LED 40W E14 WW R50 36D ND1BC/6 SRT - NO REGULABLE | 2.9 | 40 | 2700 | 230 | 80 | 50000 | 6 | 51x81 | 392015 | 929001235921 | 5,99 |



© Philips Lighting España
Calle María de Portugal, 1, Madrid

www.lighting.philips.es