

TUBOS LED DE MAZDA PARA UNA ILUMINACIÓN MÁS BRILLANTE

A⁺

EEL label

80

CRI



220-240Vac



25,000h



50,000x



nondimmable

Tipo de producto	Tipo de lámpara	LED	Entrada Actual	Frecuencia	Dimensión	12 NC	EOC
		W	mA	Hz	mm		
MZD LEDtube 600mm 8W 840	LEDtube	8	38	50/60	604h / 27,80ø	929001855632	71745500
MZD LEDtube 600mm 8W 865	LEDtube	8	38	50/60	604h / 27,80ø	929001855732	71747900
MZD LEDtube 1200mm 14.5W 840	LEDtube	14.5	70	50/60	1213,60h / 27,80ø	929001855832	71741700
MZD LEDtube 1200mm 14.5W 865	LEDtube	14.5	70	50/60	1213,60h / 27,80ø	929001855932	71743100
MZD LEDtube 1500mm 20W 840	LEDtube	20	96	50/60	1514,20h / 27,80ø	929001855432	71737000
MZD LEDtube 1500mm 20W 865	LEDtube	20	96	50/60	1514,20h / 27,80ø	929001855532	71739400
MZD LED PLC 7.5W 840 2P G24d1CT/10	PLC	7.5	70	50/60	115h / 37,20ø	929001879032	16298300
MZD LED PLC 7.5W 865 2P G24d1CT/10	PLC	7.5	70	50/60	115h / 37,20ø	929001879132	16300300
MZD LED PLC 840 2P G24d1CT/10	PLC	9	80	50/60	115h / 37,20ø	929001879332	16302700
MZD LED PLC 9W 865 2P G24d1CT/10	PLC	9	80	50/60	115h / 37,20ø	929001879432	16304100