

The Philips logo is displayed in a white rounded rectangle on a blue background. The word "PHILIPS" is written in a bold, blue, sans-serif font.

LEDtube
compatibility list
Professional Q2 2018



Table of content

MASTER LEDtube HF T5

- MASTER LEDtube HF InstantFit T5 HO - 1200 mm 2
- MASTER LEDtube HF InstantFit T5 HO - 1500 mm 3
- MASTER LEDtube HF InstantFit T5 UO - 1500 mm 4
- MASTER LEDtube HF InstantFit HE T5 - 600mm 5
- MASTER LEDtube HF InstantFit HE T5 - 1200mm 6
- MASTER LEDtube HF InstantFit HE T5 - 1500mm 7

MASTER LEDtube HF T8

- MASTER LEDtube HF InstantFit T8 - 600mm 8
- MASTER LEDtube HF InstantFit T8 - 1200 mm 9
- MASTER LEDtube HF InstantFit T8 - 1500 mm 11
- MASTER LEDtube Universal T8 - 1200 mm 13
- MASTER LEDtube Universal T8 - 1500 mm 15

CorePro LEDtube HF T8

- CorePro LEDtube HF InstantFit T8 - 600mm 17
- CorePro LEDtube HF InstantFit T8 - 1200mm 18
- CorePro LEDtube HF InstantFit T8 - 1500mm 20
- CorePro LEDtube Universal HO - 1200mm 22
- CorePro LEDtube Universal HO - 1500mm 24

MASTER LEDtube HF InstantFit T5 HO - 1200 mm



Ballast Compatibility

KEY

	Ballast is compatible
	Ballast is compatible, light output may differ >10% compared to specifications
	Ballast is compatible and conditional released for dimming
	Ballast is not compatible
	Ballast LEDtube combination not tested

This document is for information purposes and must be treated as recommendation. Philips attempted to provide best results, results are generated in lab controlled environment and may differ from actual application conditions



MAS LEDtube HF 1200mm HO 26W 8x T5
Model number: 9290013383 9290013384 9290013385
AC (50 Hz) on HF Ballast Compatible

	Ballast type	10nc / Ref. no.	Lamps on ballast
PHILIPS	HF-E 1/2 54 TL5 II	9137 130 408	1
	HF-E 1/2 54 TL5 II	9137 130 408	2
	HF-P 154 TL5 HO EII 220-240	9137 006 133	1
	HF-P 154/155 TL5 HO/PL-L III IDC	9137 130 282	1
	HF-P 254/255 TL5 HO/PL-L III IDC	9137 130 283	2
	HF-P Xt 254 TL5 EII 220-240	9137 006 300	2
	HF-R 154 TL5 220-240	9137 001 291	1
	HF-R 254 TL5 EII	9137 006 089	2
	HF-R DALI 154 TL5 220-240	9137 001 335	1
	HF-R Es 154 TL5	9137 006 618	1
	HF-R Es 254 TL5	9137 006 619	2
	HF-R TD 154 TL5 EII 220-240	9137 006 064	1
	HF-S 154 TL5 II	9137 130 336	1
	HF-S 254 TL5 II	9137 130 337	2
OSRAM	QT-FIT 5/8 1x54-58		1
	QT-FIT 5/8 2x54-58		2
	QTP-OPTIMAL 1x54-58		1
	QTP-OPTIMAL 2x54-58		2
HELVAR	EL1x54iDim		1
	EL1x54sc		1
	EL1x54ngn5		1
	EL1x54s		1
	EL2x54iDim		2
	EL2x54sc		2
TRIDONIC ATCO	PC 1/54 T5 INDUSTRY	89800458	1
	PC 1x54 T5 PRO lp	22185155	1
	PC 1x54 T5 TOP lp	22185165	1
	PC 2/54 T5 INDUSTRY	89800459	1
	PC 2x54 T5 PRO lp	22185156	2
	PC 2x54 T5 TOP lp	22185166	2
	PCA 1x54 T5 BASIC lp	22185088	1
	PCA 2x54 T5 BASIC lp	22185089	2
VOSSLOH-SCHWABE	ELXc 254.865	188618	2
BAG-HUECO	BCS54.1FX-11/220-240	10077585	1
	BCD54.1F-01/220-240/1-10V	10097248	1
	BCS54.2FX-11/220-240	10077586	2
Others	Direct mains		

	* / Dim
	* / Dim
	Dim
	.
	.
	.
	.
	.
	.
	.
	.
	.
	.

General note Philips Master LEDtube HF InstantFit T5 HO

General notes: Refer to the product reference number in the header of the columns to use this product-ballast compatibility list. Please note that Philips LEDtubes InstantFit T5 are only tested with HF ballast on AC operation. The performance of Philips LEDtubes InstantFit T5 on HF ballasts with DC operation is not tested and is therefore not guaranteed. Philips LEDtubes InstantFit T5 range is designed to work on HF ballasts only. This document is for information purposes only and must be treated as recommendation. Philips will not accept claims for any damage caused by not implementing the recommendations in this document. Philips does not accept any responsibility, warranty or liability when using Philips LEDtubes with ballasts not mentioned in this list, or when using successor models of the tested ballasts. Although Philips aims to provide the most accurate information and test results from controlled experiments the results may vary in different applications. This document focuses on the behaviour of above mentioned Philips LEDtube. Please also check and follow the instructions of HF ballast manufacturers for installation instructions.

Always check the latest update of the compatibility list on www.philips.com/ledtube

Dimming a LEDtube: Ballast types indicated in this list with DIM are conditional released by Philips to offer dimming functionality. Please note that the dimming curve of the LEDtube might differ from the curve of a fluorescent lamp. All other Philips LED tubes are not developed for dimming therefore the performance cannot be guaranteed in a dimming application. In case of usage of a non dimmable product in a dimmable application, warranty does not apply.

MASTER LEDtube HF InstantFit T5 UO - 1500 mm



Ballast Compatibility

KEY

	Ballast is compatible
	Ballast is compatible, light output may differ >10% compared to specifications
Dim	Ballast is compatible and conditional released for dimming
	Ballast is not compatible
	Ballast LEDtube combination not tested

This document is for information purposes and must be treated as recommendation. Philips attempted to provide best results, results are generated in lab controlled environment and may differ from actual application conditions



	Ballast type	10nc / Ref. no.	Lamps on ballast
PHILIPS	HF-P 2 80 TL5/PL-L III IDC	9137 130 343	2
	HF-P I 80 TL5/PL-L III IDC	9137 130 342	1
	HF-P Xt 180 TL5 EII 220-240	9137 006 301	1
	HF-P Xt 280 TL5 EII 220-240	9137 006 302	2
	HF-R 180 TL5/PLL EII	9137 006 090	1
	HF-R 280 TL5/PLL EII 220-240	9137 006 091	2
	HF-R TD 180 TL5/PLL 220-240	9137 006 066	1
	HF-R TD 280 TL5/PL-L EII	9137 006 096	2
	HF-S 2 80 TL5/PL-L II	9137 130 423	2
OSRAM	QT-FQ 1x80/230-240		1
	QT-FQ 2x80		2
	QTP5 1x80		1
HELVAR	EL1x80iDim		1
	EL1x80sc		1
	EL2x80iDim		2
TRIDONIC-ATCO	PC 1/80 T5 INDUSTRY	89800460	1
	PC 1x80 T5 PRO Ip	22185209	1
	PC 2/80 T5 INDUSTRY	89800461	2
	PC 2x80 T5 PRO Ip	22185210	2
	PCA 1x80 T5 BASIC Ip	22185084	1
	PCA 2x80 T5 BASIC Ip	22185085	2
	PCA 2x80 T5 ECO Ip	22185098	2
	PCA 2x80 T5 EXCEL one4all Ip	22185107	2
VOSSLOH-SCHWABE	ELXc 180.866	188144	1
	ELXc 280.538	188619	2
BAG-HUECO	BCS80.1FX-11/220-240	10077587	1
	BCS80.2FX-11/220-240	10095407	2
Others	Direct mains		

MAS LEDtube HF 1500mm UO 36W 8xx T5
Model number: 9290013461 9290013462 9290013463
AC (50 Hz) on HF Ballast Compatible
* / Dim
* / Dim

General note Philips Master LEDtube HF InstantFit T5 UO

General notes: Refer to the product reference number in the header of the columns to use this product-ballast compatibility list. Please note that Philips LEDtubes InstantFit T5 are only tested with HF ballast on AC operation. The performance of Philips LEDtubes InstantFit T5 on HF ballasts with DC operation is not tested and is therefore not guaranteed. Philips LEDtubes InstantFit T5 range is designed to work on HF ballasts only. This document is for information purposes only and must be treated as recommendation. Philips will not accept claims for any damage caused by not implementing the recommendations in this document. Philips does not accept any responsibility, warranty or liability when using Philips LEDtubes with ballasts not mentioned in this list, or when using successor models of the tested ballasts. Although Philips aims to provide the most accurate information and test results from controlled experiments the results may vary in different applications. This document focuses on the behaviour of above mentioned Philips LEDtube. Please also check and follow the instructions of HF ballast manufacturers for installation instructions.

Always check the latest update of the compatibility list on www.philips.com/ledtube

Dimming a LEDtube: Ballast types indicated in this list with DIM are conditional released by Philips to offer dimming functionality. Please note that the dimming curve of the LEDtube might differ from the curve of a fluorescent lamp. All other Philips LED tubes are not developed for dimming therefore the performance cannot be guaranteed in a dimming application. In case of usage of a non dimmable product in a dimmable application, warranty does not apply.



MASTER LEDtube HF InstantFit HE T5 - 1200mm




Ballast Compatibility

KEY

	Ballast is compatible
*	Ballast is compatible, light output may differ >10% compared to specifications
Dim	Ballast is compatible and conditional released for dimming
	Ballast is not compatible
	Ballast LEDtube combination not tested

This document is for information purposes and must be treated as recommendation. Philips attempted to provide best results, results are generated in lab controlled environment and may differ from actual application conditions



	Ballast type	12nc	Lamps on ballast
PHILIPS	EB-C 128 TL5	9137131964	1
	EB-C 228 TL5	9137131971	2
	EB-Ci 1-2 14-28W	9137130432	1
	EB-Ci 1-2 14-28W	9137130432	2
	HF-P 1 14-35 TL5 HE III IDC	9137130310	1
	HF-P 2 14-35 TL5 HE III IDC	9137130311	2
	HF-S 2 14-35 TL5 HE II	9137130421	2
	HF-R Es 114-35 TL5	9137006616	1
	HF-R Es 214-35 TL5	9137006617	2
	HF-R T 228 TL5 220-240	9137001863	2
OSRAM	QT-FIT5 1x14-35		1
	QT-FIT5 2x14-35		2
	QTP5 1x14-35		1
	QTP5 2x14-35		2
	EZ-T5 1x28/220		1
	EZP5 1x28/220-230		1
	EZP5 2x28/220-230		2
HELVAR	EL1x14-35ngn5		1
TRIDONIC-ATCO	PC 1x14-35 T5 TOP Ip	22185157	1
	PC 2x14-28 T5 TOP Ip	22185158	2
	PC 1x14-35 T5 PRO Ip	22185147	1
	PC 2x14-35 T5 PRO Ip	22185148	2
VOSSLOH-SCHWABE	ELXc 135.220	188921	1
BAG-HUECO	BCS35.1FX-11/220-240	10077579	1
Others	Direct mains		

MAS LEDtube HF 1200mm HE 16.5W 8xx T5
Model number: 9290013910 9290013911 9290013912
AC (50 Hz) on HF Ballast Compatible
*
*
*
Dim
Dim
Dim
*
*
*
(1)

(1) Tridonic PC 1x14-35 T5 PRO Ip 22185147 versions released / luminaires installed after 2014: compatible
Tridonic PC 1x14-35 T5 PRO Ip 22185147 versions released / luminaires installed until 2014: not compatible

General note Philips Master LEDtube HF InstantFit HE T5

General notes: Refer to the product reference number in the header of the columns to use this product-ballast compatibility list. Please note that Philips LEDtubes InstantFit T5 are only tested with HF ballast on AC operation. The performance of Philips LEDtubes InstantFit T5 on HF ballasts with DC operation is not tested and is therefore not guaranteed. Philips LEDtubes InstantFit T5 range is designed to work on HF ballasts only. This document is for information purposes only and must be treated as recommendation. Philips will not accept claims for any damage caused by not implementing the recommendations in this document. Philips does not accept any responsibility, warranty or liability when using Philips LEDtubes with ballasts not mentioned in this list, or when using successor models of the tested ballasts. Although Philips aims to provide the most accurate information and test results from controlled experiments the results may vary in different applications. This document focuses on the behaviour of above mentioned Philips LEDtube. Please also check and follow the instructions of HF ballast manufacturers for installation instructions.

Always check the latest update of the compatibility list on www.philips.com/ledtube

Dimming a LEDtube: Ballast types indicated in this list with DIM are conditional released by Philips to offer dimming functionality. Please note that the dimming curve of the LEDtube might differ from the curve of a fluorescent lamp. All other Philips LED tubes are not developed for dimming therefore the performance cannot be guaranteed in a dimming application. In case of usage of a non dimmable product in a dimmable application, warranty does not apply.

MASTER LEDtube HF InstantFit HE T5 - 1500mm



Ballast Compatibility

KEY

	Ballast is compatible
	Ballast is compatible, light output may differ >10% compared to specifications
	Ballast is compatible and conditional released for dimming
	Ballast is not compatible
	Ballast LEDtube combination not tested

This document is for information purposes and must be treated as recommendation. Philips attempted to provide best results, results are generated in lab controlled environment and may differ from actual application conditions



	Ballast type	12nc	Lamps on ballast
PHILIPS	HF-P 1 14-35 TL5 HE III IDC	9137130310	1
	HF-P 2 14-35 TL5 HE III IDC	9137130311	2
	HF-S 2 14-35 TL5 HE II	9137130421	2
	HF-R Es 114-35 TL5	9137006616	1
	HF-R Es 214-35 TL5	9137006617	2
OSRAM	QT-FIT5 1x14-35		1
	QT-FIT5 2x14-35		2
	QTP5 1x14-35		1
	QTP5 2x14-35		2
HELVAR	EL1x14-35ngn5		1
TRIDONIC ATCO	PC 1x14-35 T5 TOP Ip	22185157	1
	PC 2x35 T5 TOP Ip	28000047	2
	PC 1x14-35 T5 PRO	22185147	1
	PC 2x14-35 T5 PRO Ip	22185148	2
VOSSLOH-SCHWABE	ELXc 135.220	188921	1
BAG-HUECO	BCS35.1FX-11/220-240	10077579	1
Others	Direct mains		

<p>MAS LEDtube HF 1500mm HE 20W 8x T5</p>	
<p>Model number: 9290013913 9290013914 9290013915</p>	
<p>AC (50 Hz) on HF Ballast Compatible</p>	

(1) Tridonic PC 1x14-35 T5 PRO Ip 22185147 versions released / luminaires installed after 2014: compatible
 Tridonic PC 1x14-35 T5 PRO Ip 22185147 versions released / luminaires installed until 2014: not compatible

General note Philips Master LEDtube HF InstantFit HE T5

General notes: Refer to the product reference number in the header of the columns to use this product-ballast compatibility list. Please note that Philips LEDtubes InstantFit T5 are only tested with HF ballast on AC operation. The performance of Philips LEDtubes InstantFit T5 on HF ballasts with DC operation is not tested and is therefore not guaranteed. Philips LEDtubes InstantFit T5 range is designed to work on HF ballasts only. This document is for information purposes only and must be treated as recommendation. Philips will not accept claims for any damage caused by not implementing the recommendations in this document. Philips does not accept any responsibility, warranty or liability when using Philips LEDtubes with ballasts not mentioned in this list, or when using successor models of the tested ballasts. Although Philips aims to provide the most accurate information and test results from controlled experiments the results may vary in different applications. This document focuses on the behaviour of above mentioned Philips LEDtube. Please also check and follow the instructions of HF ballast manufacturers for installation instructions.

Always check the latest update of the compatibility list on www.philips.com/ledtube

Dimming a LEDtube: Ballast types indicated in this list with DIM are conditional released by Philips to offer dimming functionality. Please note that the dimming curve of the LEDtube might differ from the curve of a fluorescent lamp. All other Philips LED tubes are not developed for dimming therefore the performance cannot be guaranteed in a dimming application. In case of usage of a non dimmable product in a dimmable application, warranty does not apply.



MASTER LEDtube HF InstantFit T8 - 1200 mm



Ballast Compatibility

KEY

	Ballast is compatible
	Ballast is compatible, light output may differ >10% compared to specifications
	Dim
	Ballast is compatible and conditional released for dimming
	Ballast is not compatible
	Ballast LEDtube combination not tested

This document is for information purposes and must be treated as recommendation. Philips attempted to provide best results, results are generated in lab controlled environment and may differ from actual application conditions



	Ballast type	10nc / Ref. no.	Lamps on ballast	MASTER LEDtube HF 1200mm 16.5W 833 T8 MEAT	MASTER LEDtube 1200mm HF HO, InstantFit T8 2100 lm	MASTER LEDtube 1200mm HF UO, InstantFit T8 2500 lm
				Model number: 9290012263	Model number: 9290012843A 9290012841A 9290012842A	Model number: 9290013002A 9290013000A 9290013001A
				AC (50 Hz) on HF Ballast Compatible	AC (50 Hz) on HF Ballast Compatible	AC (50 Hz) on HF Ballast Compatible
PHILIPS	EB-C 136 TL-D 220-240	9137131992	1			
	HF-B 136 TLD 220-240	9137001122	1			
	HF-B 136 TLD EII 220-240	9137001926	1			
	HF-B 236 TL-D 220-240	9137001124	2			
	HF-B 236 TLD EII 220-240	9137001928	2			
	HF-E 136 TL-D II	9137130410	1			
	HF-E 236 TL-D	9137130391	2			
	HF-E 236 TL-D II	9137130411	2			
	HF-K 136 TLD 220-240	9137001477	1			
	HF-P 136 TL-D III IDC	9137130315	1			
	HF-P 236 TL-D III IDC	9137130316	2			
	HF-P 336 TL-D III IDC	9137130317	3			
	HF-P Xt 136 TLD EII 220-240	9137006177	1			
	HF-P XT 236 TLD EII 220-240	9137006178	2			
	HF-P 136 TLD EII 220-240	9137001911	1			
	HF-P 236 TLD 230-240	9137001112	2			
	HF-Pi 1 14/21/24/39 TL5 EII 220-240	9137006240	1			
	HF-R 136 TL-D EII	9137006092	1			
	HF-R 236 TL-D EII	9137006093	2			
	HF-R 136 TL-D 220-240V 50/60Hz	9137001117	1			
	HF-Ri TD 1 14/21/24/39TL5 E+	9137006983	1			
	HF-Ri TD 2 14/21/24/39TL5 E+	9137006984	2			
HF-S 136 TL-D II	9137130321	1				
HF-S 236 TL-D II	9137130324	2				
HF-S 336 TL-D II	9137130327	3				
HF-P 118/136 TL-D III	9137130315	1				
HF-S 118/136 TL-D II	9137130321	1				
HF-P 218/236 TL-D III	9137130316	2				
HF-S 218/236 TL-D II	9137130324	2				
OSRAM	QT-FIT8 1x36		1			
	QT-FIT8 2x36		2			
	QTP8 1x36		1			
	QTP8 2x36		2			
	QTP-OPTIMAL 1x18-40		1			
	QTP-OPTIMAL 2x18-40		2			
	QT-FIT 5/8 2x18-39		2			
HELVAR	EL1x36/40/18S		1			
	EL1x36HF		1			
	EL1x36ngn		1			
	EL2x36/40s		2			
	EL2x36ngn		2			

MASTER LEDtube HF InstantFit T8 - 1200 mm



Ballast Compatibility

KEY

	Ballast is compatible
	Ballast is compatible, light output may differ >10% compared to specifications
	Ballast is compatible and conditional released for dimming
	Ballast is not compatible
	Ballast LEDtube combination not tested

This document is for information purposes and must be treated as recommendation. Philips attempted to provide best results, results are generated in lab controlled environment and may differ from actual application conditions



			MASTER LEDtube HF 1200mm 16.5W 833 T8 MEAT	MASTER LEDtube 1200mm HF HO, InstantFit T8 2100 lm	MASTER LEDtube 1200mm HF UO, InstantFit T8 2500 lm
			Model number: 9290012263	Model number: 9290012843A 9290012841A 9290012842A	Model number: 9290013002A 9290013000A 9290013001A
			AC (50 Hz) on HF Ballast Compatible	AC (50 Hz) on HF Ballast Compatible	AC (50 Hz) on HF Ballast Compatible
Ballast type	10nc / Ref. no.	Lamps on ballast			
TRIDONIC ATCO	PC 1/36 T8 INDUSTRY	86458035	1		
	PC 1/36 T8 PRO	22176217	1		
	PC 1x36 T8 PRO lp	22185214	1		
	PC2/36 T8 INDUSTRY	86458036	2		
	PC2x36 T8 PRO sl	22185217	2		
	PC 2x36 T8 TOP sl	22185226	2		
	PC 1x36 T8 TOP sl	22185223	1		
	PC1/36 T8 PRO sc	89800008	1		
	PC 1/36 T8 PRO	22176108	1		
	PC 3/36 T8 PRO	22176231	3		
VOSSLÖH-SCHWABE	ELXc 136.207	188708	1		
	ELXc 236.202	188316	2		
	ELXc 236.208	188705	2		
	ELXe 238.527	188137	2		
	ELXe 238.527	188137	1		
BAG-HUECO	BCS36.1FX-11/220-240	10077590	1		
	BCS36.2FX-11/220-240	10077591	2		
	D36.2-23021 E	166132	2		
	D 58.1-23021 E	166072	1		
	ECS36.2SR-01/220-240	167032	2		
Trilux	D36.2-23021 E		2		
	D58.1-23021E		1		
	DD58.1-23031E		1		
Others	EM ballast		1		
	Direct Mains		1		

General note Philips Master LEDtube HF InstantFit T8

General notes: Refer to the product reference number in the header of the columns to use this product-ballast compatibility list.

Please note that Philips LEDtubes InstantFit T8 are only tested with HF ballast on AC operation. The performance of Philips LEDtubes InstantFit T8 on HF ballasts with DC operation is not tested and is therefore not guaranteed. Philips LED tube InstantFit range is designed to work on HF ballasts only. For EM ballasts or direct mains connection, please contact a Philips sales representative for more information on our EM/Mains compatible range. This document is for information purposes only and must be treated as recommendation. Philips will not accept claims for any damage caused by not implementing the recommendations in this document. Philips does not accept any responsibility, warranty or liability when using Philips LEDtubes with ballasts not mentioned in this list, or when using successor models of the tested ballasts. Although Philips aims to provide the most accurate information and test results from controlled experiments the results may vary in different applications. This document focuses on the behaviour of above mentioned Philips LEDtube. Please also check and follow the instructions of HF ballast manufacturers for installation instructions.

Always check the latest update of the compatibility list on www.philips.com/ledtube

Dimming a LEDtube: Ballast types indicated in this list with DIM are conditional released by Philips to offer dimming functionality. Please note that the dimming curve of the LEDtube might differ from the curve of a fluorescent lamp. All other Philips LED tubes are not developed for dimming therefore the performance cannot be guaranteed in a dimming application. In case of usage of a non dimmable product in a dimmable application, warranty does not apply.

MASTER LEDtube HF InstantFit T8 - 1500 mm



Ballast Compatibility

KEY

	Ballast is compatible
	Ballast is compatible, light output may differ >10% compared to specifications
Dim	Ballast is compatible and conditional released for dimming
	Ballast is not compatible
	Ballast LEDtube combination not tested

This document is for information purposes and must be treated as recommendation. Philips attempted to provide best results, results are generated in lab controlled environment and may differ from actual application conditions



	Ballast type	10nc / Ref. no.	Lamps on ballast	MASTER LEDtube 1500mm HF HO, Instant Fit T8 3100 lm		MASTER LEDtube 1500mm HF UO, Instant Fit T8 3700 lm	
				Model number: 9290012846A 9290012844A 9290012845A	Model number: 9290013005A 9290013003A 9290013004A	AC (50 Hz) on HF Ballast Compatible	AC (50 Hz) on HF Ballast Compatible
PHILIPS	EI 158 TL-D 220-240	9137 006 075	1				
	HF-B 158 TLD 220-240	9137 001 123	1				
	HF-B 158 TLD EII 220-240	9137 001 927	1				
	HF-B 258 TLD 220-240	9137 001 125	2				
	HF-B 258 TL-D EII 220-240	9137 001 929	2				
	HF-E 158 TL-D	9137 130 389	1				
	HF-E 1/2 58 TL-D II	9137 130 409	2				
	HF-E 1/2 58 TL-D II	9137 130 409	1				
	HF-P 154/155 TL5 HO/PL-L III IDC	9137 130 282	1				
	HF-P 158 TLD EII 220-240	9137 001 912	1				
	HF-P 158 TL-D III IDC	9137 130 318	1				
	HF-P 258 TLD EII 220-240	9137 001 916	2				
	HF-P 258 TL-D III IDC	9137 130 319	2				
	HF-P Xt 158 TLD EII 220-240	9137 006 179	1				
	HF-P Xt 258 TL-D EII 220-240	9137 006 180	2				
	HF-P 158 TLD 220-240	9137 001 185	1				
	HF-P 258 TLD 220-240	9137 001 110	2				
	HF-R 258 TLD 220-240	9137 001 119	2				
	HF-R 158 TLD EII	9137 006 094	1				
	HF-R 258 TLD EII	9137 006 095	2				
	HF-RITD 1 28/35/49/54TL5 E+	9137006956	1				
	HF-RITD 2 28/35/49/54TL5 E+	9137006958	2				
	HF-S 158		1				
	HF-S 158 TL-D II	9137 130 322	1				
HF-S 258 TL-D II	9137 130 325	2					
HF-S 258 TL-D II HT	9137 006 899	2					
HF-S 158 TLD 220-240	9137 006 319	1					
EB-P 258 TLD ICC 220-240	9137 130 210	2					
HF-P 258 TLD 220-240	9137001206	2					
OSRAM	QT Deluxe HF 1x58 230-240 DIM		1				
	QT Deluxe HF 2x58 230-240 Dim		2				
	QT-FIT8 1x58 - 70		1				
	QT-FIT8 2x58 - 70		2				
	QTP8 1x58		1				
	QTP8 2x58		2				
	QTP-OPTIMAL 1x54-58		1				
	QTP-OPTIMAL 2x54-58		2				
	QT 1X58 DIM		1				
	QT-FIT 5/8 1x54-58		1				
	QT-FIT 5/8 2x54-58		2				
QT-FIT8 2x58		2					
HELVAR	EL1x58ngn		1				
	EL1x58s		1				
	EL2x58es		2				
	EL2x58HF		2				
	EL2x58ngn		2				
	EL2x58s		2				
TRIDONIC ATCO	PC 1/58 T8 INDUSTRY	86 458 037	1				
	PC 1/58 T8 PRO	22 176 094	1				
	PC 1x58 T8 PRO lp	22 185 215	1				
	PC 2/58 T8 INDUSTRY	86 458 038	2				
	PC 2x58 E011		2				
	PC 2x58 E011 IDC	22 083 174	2				
	PC 2x58 T8 PRO sl	22 185 218	2				
	PC 1x58 T8 TOP sl	22 185 224	1				
	PC 2x58 T8 TOP sl	22 185 227	2				
	PCA 1/58 excel one4all	22 085 286	1				
	PCA 2x58 EXCEL One4all lp	28 000 040	2				

MASTER LEDtube HF InstantFit T8 - 1500 mm



Ballast Compatibility

KEY

	Ballast is compatible
	Ballast is compatible, light output may differ >10% compared to specifications
	Ballast is compatible and conditional released for dimming
	Ballast is not compatible
	Ballast LEDtube combination not tested

This document is for information purposes and must be treated as recommendation. Philips attempted to provide best results, results are generated in lab controlled environment and may differ from actual application conditions



			MASTER LEDtube 1500mm HF HO, Instant Fit T8 3100 lm	MASTER LEDtube 1500mm HF UO, Instant Fit T8 3700 lm
			Model number: 9290012846A 9290012844A 9290012845A	Model number: 9290013005A 9290013003A 9290013004A
			AC (50 Hz) on HF Ballast Compatible	AC (50 Hz) on HF Ballast Compatible
Ballast type	10nc / Ref. no.	Lamps on ballast		
VOSSLOH-SCHWABE	ELXc 158.201	188315	1	
	ELXc 158.209	188706	1	
	ELXc 158.218	188870	1	
	ELXc 258.203	188317	2	
	ELXc 258.210	188707	2	
	ELXc 258.219	188871	2	
	ELXe 258.222	188130	2	
	ELXe 158.524	188024	1	
BAG-HUECO	BCD58.1F-01/220-240/1-10V	1009 7145	1	
	BCS58.1FX-11/220-240	1007 7592	1	
	BCS58.2FX-11/220-240	1007 7593	2	
	BCS58.2SX-01/220-240	1005 1003	2	
	D 58.1-23021 E	166 072	1	
	D 58.2-23021 E	166 082	2	
	SCS58.2SR-11/220-240	166 272	2	
Trilux	D58.1-23021E		1	
	DD58.1-23031E		1	
May + Christie	MCU 158		1	
	MCU 258		2	
Others	Direct mains			
	Electro Magnetic Ballast			

General note Philips Master LEDtube HF InstantFit T8

General notes: Refer to the product reference number in the header of the columns to use this product-ballast compatibility list. Please note that Philips LEDtubes InstantFit T8 are only tested with HF ballast on AC operation. The performance of Philips LEDtubes InstantFit T8 on HF ballasts with DC operation is not tested and is therefore not guaranteed. Philips LED tube InstantFit range is designed to work on HF ballasts only. For EM ballasts or direct mains connection, please contact a Philips sales representative for more information on our EM/Mains compatible range. This document is for information purposes only and must be treated as recommendation. Philips will not accept claims for any damage caused by not implementing the recommendations in this document. Philips does not accept any responsibility, warranty or liability when using Philips LEDtubes with ballasts not mentioned in this list, or when using successor models of the tested ballasts. Although Philips aims to provide the most accurate information and test results from controlled experiments the results may vary in different applications. This document focuses on the behaviour of above mentioned Philips LEDtube. Please also check and follow the instructions of HF ballast manufacturers for installation instructions.

Always check the latest update of the compatibility list on www.philips.com/ledtube

Dimming a LEDtube: Ballast types indicated in this list with DIM are conditional released by Philips to offer dimming functionality. Please note that the dimming curve of the LEDtube might differ from the curve of a fluorescent lamp. All other Philips LED tubes are not developed for dimming therefore the performance cannot be guaranteed in a dimming application. In case of usage of a non dimmable product in a dimmable application, warranty does not apply.

MASTER LEDtube Universal T8 - 1200 mm



Ballast Compatibility

KEY

	Ballast is compatible
*	Ballast is compatible, light output may differ >10% compared to specifications
	Ballast is not compatible
	Ballast LEDtube combination not tested

This document is for information purposes and must be treated as recommendation. Philips attempted to provide best results, results are generated in lab controlled environment and may differ from actual application conditions



			MASTER LEDtube 1200mm Universal, Instant Fit 2500lm
			Model number: 9290013361 9290013362 9290013360
			AC (50Hz) on HF Ballast Compatible
Ballast type	10nc	Lamps on ballast	
PHILIPS	EB-C 136 TL-D 220-240	9137 131 992	1
	EB-S 236 TL-D 220-230	9137 130 216	2
	HF-B 136 TLD 220-240	9137 001 122	1
	HF-B 136 TLD EII 220-240	9137 001 926	1
	HF-B 236 TL-D 220-240	9137 001 124	2
	HF-B 236 TLD EII 220-240	9137 001 928	2
	HF-E 136 TL-D II	9137 130 410	1
	HF-E 236 TL-D	9137 130 391	2
	HF-E 236 TL-D II	9137 130 411	2
	HF-K 136 TLD 220-240	9137 001 477	1
	HF-P 136 TL-D III IDC	9137 130 315	1
	HF-P 236 TL-D III IDC	9137 130 316	2
	HF-P 336 TL-D III IDC	9137 130 317	3
	HF-P Xt 136 TLD EII 220-240	9137 006 177	1
	HF-P XT 236 TLD EII 220-240	9137 006 178	2
	HF-P 136 TLD EII 220-240	9137 001 911	1
	HF-P 236 TLD 230-240	9137 001 112	2
	HF-Pi 1 14/21/24/28/39 TL5 EII 220-240	9137 006 240	1
	HF-R 136 TL-D EII	9137 006 092	1
	HF-R 236 TL-D EII	9137 006 093	2
	HF-R 136 TL-D 220-240V 50/60Hz	9137 001 117	1
	HF-Ri TD 1 14/21/24/39TL5 E+	9137 006 983	1
	HF-Ri TD 2 14/21/24/39TL5 E+	9137 006 984	2
	HF-S 136 TL-D II	9137 130 321	1
	HF-S 236 TL-D II	9137 130 324	2
	HF-S 336 TL-D II	9137 130 327	3
	HF-P 118/136 TL-D III	9137 130 315	1
	HF-S 118/136 TL-D II	9137 130 321	1
HF-P 218/236 TL-D III	9137 130 316	2	
HF-S 218/236 TL-D II	9137 130 324	2	
OSRAM	QT-FIT8 1x36		1
	QT-FIT8 2x36		2
	QTP8 1x36		1
	QTP8 2x36		2
	QTP-OPTIMAL 1x18-40		1
	QTP-OPTIMAL 2x18-40		2
	QT-FIT 5/8 2x18-39		2
HELVAR	EL1x36/40/18S		1
	EL1x36HF		1
	EL1x36ngn		1
	EL2x36/40s		2
	EL2x36ngn		2
TRIDONIC	PC 1/36 T8 INDUSTRY	86458035	1
	PC 1/36 T8 PRO	22176217	1
	PC 1x36 T8 PRO Ip	22185214	1
	PC2/36 T8 INDUSTRY	86458036	2
	PC2x36 T8 PRO sl	22185217	2
	PC 2x36 T8 TOP sl	22185226	2
	PC 1x36 T8 TOP sl	22185223	1
	PC1/36 T8 PRO sc	89800008	1
	PC 1/36 T8 PRO	22176108	1
	PC 3/36 T8 PRO	22176231	3

MASTER LEDtube Universal T8 - 1200 mm



Ballast Compatibility

KEY

	Ballast is compatible
	Ballast is compatible, light output may differ >10% compared to specifications
	Ballast is not compatible
	Ballast LEDtube combination not tested

This document is for information purposes and must be treated as recommendation. Philips attempted to provide best results, results are generated in lab controlled environment and may differ from actual application conditions



	Ballast type	10nc	Lamps on ballast
VOSSLOH-SCHWABE	ELXc 136.207	188708	1
	ELXc 236.202	188316	2
	ELXc 236.208	188705	2
	ELXe 238.527	188137	2
	ELXe 238.527	188137	1
BAG-HUECO	BCS36.1FX-11/220-240	10077590	1
	BCS36.2FX-11/220-240	10077591	2
	D36.2-23021 E	166132	2
	D 58.1-23021 E	166072	1
	ECS36.2SR-01/220-240	167032	2
Trilux	D36.2-23021 E		2
	D58.1-23021E		1
	DD58.1-23031E		1
Others	EM ballast		1
	Direct Mains (only one single side supply)		1

MASTER LEDtube 1200mm Universal, Instant Fit 2500lm
Model number: 9290013361 9290013362 9290013360
AC (50Hz) on HF Ballast Compatible

General note Philips Master LEDtube Universal T8

General notes: Philips LEDtubes Universal T8 are designed to work on HF ballasts, or EM ballast, or direct mains connection.

For HF ballast connection: Refer to the product reference number in the header of the columns to use this product-ballast compatibility list.

Please note that Philips LEDtubes Universal T8 are only tested with HF ballast on AC operation. The performance of Philips LEDtubes Universal T8 on HF ballasts with DC operation is not tested and is therefore not guaranteed. This document is for information purposes only and must be treated as recommendation. Philips will not accept claims for any damage caused by not implementing the recommendations in this document. Philips does not accept any responsibility, warranty or liability when using Philips LEDtubes with HF ballasts not mentioned in this list, or when using successor models of the tested ballasts. Although Philips aims to provide the most accurate information and test results from controlled experiments the results may vary in different applications. This document focuses on the behaviour of above mentioned Philips LEDtube. Please also check and follow the instructions of HF ballast manufacturers for installation instructions.

Always check the latest update of the compatibility list on www.philips.com/ledtube

Dimming a LEDtube: Philips MASTER LEDtubes Universal T8 are not developed for dimming therefore the performance cannot be guaranteed in a dimming application. In case of usage of a non-dimmable product in a dimmable application, warranty does not apply.

For EM ballasts or direct mains connection: Please refer to the installation guide.

MASTER LEDtube Universal T8 - 1500 mm



Ballast Compatibility

KEY

	Ballast is compatible
	Ballast is compatible, light output may differ >10% compared to specifications
	Ballast is not compatible
	Ballast LEDtube combination not tested

This document is for information purposes and must be treated as recommendation. Philips attempted to provide best results, results are generated in lab controlled environment and may differ from actual application conditions



MASTER LEDtube 1500mm Universal, Instant Fit 3700lm
Model number:
 9290013364
 9290013365
 9290013363

	Ballast type	10nc / Ref. no.	Lamps on ballast	AC (50Hz) on HF Ballast Compatible	
PHILIPS	EI 158 TL-D 220-240	9137 006 075	1	*	
	HF-B 158 TLD 220-240	9137 001 123	1		
	HF-B 158 TLD EII 220-240	9137 001 927	1	*	
	HF-B 258 TLD 220-240	9137 001 125	2		
	HF-B 258 TL-D EII 220-240	9137 001 929	2	*	
	HF-E 158 TL-D	9137 130 389	1		
	HF-E 1/2 58 TL-D II	9137 130 409	2		
	HF-E 1/2 58 TL-D II	9137 130 409	1	*	
	HF-P 154/155 TL5 HO/PL-L III IDC	9137 130 282	1		
	HF-P 158 TLD EII 220-240	9137 001 912	1	*	
	HF-P 158 TL-D III IDC	9137 130 318	1		
	HF-P 258 TLD EII 220-240	9137 001 916	2		
	HF-P 258 TL-D III IDC	9137 130 319	2		
	HF-P Xt 158 TLD EII 220-240	9137 006 179	1	*	
	HF-P Xt 258 TL-D EII 220-240	9137 006 180	2		
	HF-P 158 TLD 220-240	9137 001 185	1		
	HF-P 258 TLD 220-240	9137 001 110	2		
	HF-R 158 TLD 220-240	9137 001 118	1		
	HF-R 258 TLD 220-240	9137 001 119	2		
	HF-R 158 TLD EII	9137 006 094	1		
	HF-R 258 TLD EII	9137 006 095	2		
	HF-R TD 258 TLD EII 220-240	9137 006 070	2		
	HF-RITD 1 28/35/49/54TL5 E+	9137 006 956	1		
	HF-RITD 2 28/35/49/54TL5 E+	9137 006 958	2		
	HF-S 158		1		
	HF-S 158 TL-D II	9137 130 322	1	*	
	HF-S 158 TL-D II 220-240V 50/60Hz	9137 130 322	1		
	HF-S 258 TL-D II	9137 130 325	2	*	
	HF-S 258 TL-D II HT	9137 006 899	2		
	HF-S 158 TLD 220-240	9137 006 319	1		
	EB-P 258 TLD ICC 220-240	9137 130 210	2	*	
	OSRAM	QT Deluxe HF 1x58 230-240 DIM		1	
		QT Deluxe HF 2x58 230-240 Dim		2	
QT-FIT8 1x58 - 70			1		
QT-FIT8 2x58 - 70			2		
QTP8 1x58			1		
QTP8 2x58			2	*	
QTP-OPTIMAL 1x54-58			1		
QTP-OPTIMAL 2x54-58			2		
QT 1X58 DIM			1		
QT-FIT 5/8 1x54-58			1	*	
QT-FIT 5/8 2x54-58		2			
HELVAR	EL1x58ngn		1		
	EL1x58s		1		
	EL2x58es		2		
	EL2x58HF		2		
	EL2x58ngn		2		
	EL2x58s		2		
TRIDONIC	PC 1/58 T8 INDUSTRY	86 458 037	1	*	
	PC 1/58 T8 PRO	22 176 094	1	*	
	PC 1x58 T8 PRO lp	22 185 215	1		
	PC 2/58 T8 INDUSTRY	86 458 038	2		
	PC 2x58 E011		2	*	
	PC 2x58 E011 IDC	22 083 174	2		
	PC 2x58 T8 PRO sl	22 185 218	2		
	PC 1x58 T8 TOP sl	22 185 224	1		
	PC 2x58 T8 TOP sl	22 185 227	2		
	PCA 1/58 excel one4all	22 085 286	1		
	PCA 2x58 EXCEL One4all lp	28 000 040	2		



MASTER LEDtube Universal T8 - 1500 mm



Ballast Compatibility

KEY

	Ballast is compatible
	Ballast is compatible, light output may differ >10% compared to specifications
	Ballast is not compatible
	Ballast LEDtube combination not tested

This document is for information purposes and must be treated as recommendation. Philips attempted to provide best results, results are generated in lab controlled environment and may differ from actual application conditions



MASTER LEDtube 1500mm Universal,
Instant Fit
3700lm

Model number:
9290013364
9290013365
9290013363

AC (50Hz) on HF Ballast Compatible

Ballast type	10nc	Lamps on ballast	
VOSSLOH-SCHWABE	ELXc 158.201	188315	1
	ELXc 158.209	188706	1
	ELXc 158.218	188870	1
	ELXc 258.203	188317	2
	ELXc 258.210	188707	2
	ELXc 258.219	188871	2
	ELXe 258.222	188130	2
	ELXe 258.222	188130	1
	ELXe 158.524	188024	1
BAG-HUECO	BCD58.1F-01/220-240/1-10V	1009 7145	1
	BCS58.1FX-11/220-240	1007 7592	1
	BCS58.2FX-11/220-240	1007 7593	2
	BCS58.2SX-01/220-240	1005 1003	2
	BCS58.1SR-01/220-240		1
	D 58.1-23021 E	166 072	1
	D 58.2-23021 E	166 082	2
	SCS58.2SR-11/220-240	166 272	2
Trilux	D58.1-23021E		1
	DD58.1-23031E		1
	DD58.2-23021E		2
May + Christie	MCU 158		1
	MCU 258		2
Others	Direct Mains (only one single side supply)		
	Electro Magnetic Ballast		

	*
	*
	*
	*
	*
	*
	*
	*
	*
	*
	*
	*
	*
	*
	*
	*
	*

General note Philips Master LEDtube Universal T8

General notes: Philips LEDtubes Universal T8 are designed to work on HF ballasts, or EM ballast, or direct mains connection.

For HF ballast connection: Refer to the product reference number in the header of the columns to use this product-ballast compatibility list. Please note that Philips LEDtubes Universal T8 are only tested with HF ballast on AC operation. The performance of Philips LEDtubes Universal T8 on HF ballasts with DC operation is not tested and is therefore not guaranteed. This document is for information purposes only and must be treated as recommendation. Philips will not accept claims for any damage caused by not implementing the recommendations in this document. Philips does not accept any responsibility, warranty or liability when using Philips LEDtubes with HF ballasts not mentioned in this list, or when using successor models of the tested ballasts. Although Philips aims to provide the most accurate information and test results from controlled experiments the results may vary in different applications. This document focuses on the behaviour of above mentioned Philips LEDtube. Please also check and follow the instructions of HF ballast manufacturers for installation instructions.

Always check the latest update of the compatibility list on www.philips.com/ledtube

Dimming a LEDtube: Philips MASTER LEDtubes Universal T8 are not developed for dimming therefore the performance cannot be guaranteed in a dimming application. In case of usage of a non-dimmable product in a dimmable application, warranty does not apply.

For EM ballasts or direct mains connection: Please refer to the installation guide.

CorePro LEDtube HF InstantFit T8 - 1200mm



Ballast Compatibility

KEY

Ballast is compatible
• Ballast is compatible, light output may differ >10% compared to specifications
Ballast is not compatible

This document is for information purposes and must be treated as recommendation. Philips attempted to provide best results, results are generated in lab controlled environment and may differ from actual application conditions



**Corepro LEDtube HF,
Instant Fit 1200mm T8
1600lm**

**Model number:
9290012499
9290011365**

	Ballast type	10nc / Ref. no.	Lamps on ballast	AC (50Hz) on HF Ballast Compatible
PHILIPS	EB-C 136 TL-D 220-240	9137 131 992	1	
	EB-S 236 TL-D 220-230	9137 130 216	2	
	HF-B 136 TLD 220-240	9137 001 122	1	
	HF-B 136 TLD EII 220-240	9137 001 926	1	
	HF-B 236 TL-D 220-240	9137 001 124	2	
	HF-B 236 TLD EII 220-240	9137 001 928	2	
	HF-E 136 TL-D II	9137 130 410	1	
	HF-E 236 TL-D	9137 130 391	2	
	HF-E 236 TL-D II	9137 130 411	2	
	HF-K 136 TLD 220-240	9137 001 477	1	
	HF-P 136 TL-D III IDC	9137 130 315	1	
	HF-P 236 TL-D III IDC	9137 130 316	2	
	HF-P 336 TL-D III IDC	9137 130 317	3	
	HF-P Xt 136 TLD EII 220-240	9137 006 177	1	
	HF-P XT 236 TLD EII 220-240	9137 006 178	2	
	HF-P 136 TLD EII 220-240	9137 001 911	1	
	HF-P 236 TLD 230-240	9137 001 112	2	
	HF-Pi 1 14/21/24/28/39 TL5 EII 220-240	9137 006 240	1	
	HF-R 136 TL-D EII 220-240V 50/60Hz	9137 006 092	1	
	HF-R 236 TL-D EII 220-240V 50/60Hz	9137 006 093	2	
	HF-R 136 TL-D 220-240V 50/60Hz	9137 001 117	1	
	HF-R 236 TL-D 220-240V 50/60Hz	9137 001 120	2	
	HF-S 136 TL-D II	9137 130 321	1	
HF-S 236 TL-D II	9137 130 324	2		
HF-S 336 TL-D II	9137 130 327	3		
HF-P 118/136 TL-D III	9137 130 315	1		
HF-S 118/136 TL-D II	9137 130 321	1		
HF-P 218/236 TL-D III	9137 130 316	2		
HF-S 218/236 TL-D II	9137 130 324	2		
OSRAM	QT-FIT8 1x36		1	
	QT-FIT8 2x36		2	
	QTP8 1x36		1	
	QTP8 2x36		2	
	QTP-OPTIMAL 1x18-40		1	
	QTP-OPTIMAL 2x18-40		2	
	QT-FIT 5/8 2x18-39		2	
HELVAR	EL1x36/40/18S		1	
	EL1x36HF		1	
	EL1x36ngn		1	
	EL2x36/40s		2	
	EL2x36ngn		2	
TRIDONIC	PC 1/36 T8 INDUSTRY	86458035	1	
	PC 1/36 T8 PRO	22176217	1	
	PC 1x36 T8 PRO lp	22185214	1	
	PC2/36 T8 INDUSTRY	86458036	2	
	PC2x36 T8 PRO sl	22185217	2	
	PC 2x36 T8 TOP sl	22185226	2	
	PC 1x36 T8 TOP sl	22185223	1	
	PC1/36 T8 PRO sc	89800008	1	
	PC 1/36 T8 PRO	22176108	1	
	PC 3/36 T8 PRO	22176231	3	

CorePro LEDtube HF InstantFit T8 - 1200mm



Ballast Compatibility

KEY

	Ballast is compatible
•	Ballast is compatible, light output may differ >10% compared to specifications
	Ballast is not compatible

This document is for information purposes and must be treated as recommendation. Philips attempted to provide best results, results are generated in lab controlled environment and may differ from actual application conditions



	Ballast type	10nc / Ref. no.	Lamps on ballast
VOSSLOH-SCHWABE	ELXc 136.207	188708	1
	ELXc 236.202	188316	2
	ELXc 236.208	188705	2
	ELXe 238.527	188137	2
BAG-HUECO	BCS36.1FX-11/220-240	10077590	1
	BCS36.2FX-11/220-240	10077591	2
	D36.2-23021 E	166132	2
	D 58.1-23021 E	166072	1
	ECS36.2SR-01/220-240	167032	2
Trilux	D58.1-23021E		1
	DD58.1-23031E		1
Others	EM ballast		1
	Direct Mains		1

Corepro LEDtube HF, Instant Fit 1200mm T8 1600lm
Model number: 9290012499 9290011365
AC (50Hz) on HF Ballast Compatible

General note Philips CorePro LEDtube HF InstantFit T8

General notes: Refer to the product reference number in the header of the columns to use this product-ballast compatibility list. Please note that Philips LEDtubes are only tested with HF ballast on AC operation. The performance of Philips LEDtubes on HF ballasts with DC operation is not tested and is therefore not guaranteed. Philips LED tube InstantFit range is designed to work on HF ballasts only. For EM ballasts or direct mains connection, please contact a Philips sales representative for more information on our EM/Mains compatible range. This document is for information purposes only and must be treated as recommendation. Philips will not accept claims for any damage caused by not implementing the recommendations in this document. Philips does not accept any responsibility, warranty or liability when using Philips LEDtubes with ballasts not mentioned in this list, or when using successor models of the tested ballasts. Although Philips aims to provide the most accurate information and test results from controlled experiments the results may vary in different applications. This document focuses on the behaviour of above mentioned Philips LEDtube. Please also check and follow the instructions of HF ballast manufacturers for installation instructions.

Always check the latest update of the compatibility list on www.philips.com/ledtube

Dimming a LEDtube: Philips CorePro LEDtubes HF InstantFit T8 are not developed for dimming therefore the performance cannot be guaranteed in a dimming application. In case of usage of a non-dimmable product in a dimmable application, warranty does not apply.

CorePro LEDtube HF InstantFit T8 - 1500mm



Ballast Compatibility

KEY

	Ballast is compatible	This document is for information purposes and must be treated as recommendation. Philips attempted to provide best results, results are generated in lab controlled environment and may differ from actual application conditions
•	Ballast is compatible, light output may differ >10% compared to specifications	
	Ballast is not compatible	



Corepro LEDtube HF, Instant Fit 1500mm T8 2000lm
Model number: 9290012497 9290012498

		AC (50Hz) on HF Ballast Compatible	
PHILIPS	Ballast type	10nc / Ref. no.	
	Lamps on ballast		
	EI 158 TL-D 220-240	9137 006 075	1
	HF-B 158 TLD 220-240	9137 001 123	1
	HF-B 158 TLD EII 220-240	9137 001 927	1
	HF-B 258 TLD 220-240	9137 001 125	2
	HF-B 258 TL-D EII 220-240	9137 001 929	2
	HF-E 158 TL-D	9137 130 389	1
	HF-E 1/2 58 TL-D II	9137 130 409	2
	HF-E 1/2 58 TL-D II	9137 130 409	1
	HF-P 158 TLD EII 220-240	9137 001 912	1
	HF-P 158 TL-D III IDC	9137 130 318	1
	HF-P 258 TLD EII 220-240	9137 001 916	2
	HF-P 258 TL-D III IDC	9137 130 319	2
	HF-P Xt 158 TLD EII 220-240	9137 006 179	1
	HF-P Xt 258 TL-D EII 220-240	9137 006 180	2
	HF-P 258 TLD 220-240	9137 001 110	2
	HF-S 158		1
	HF-S 158 TL-D II	9137 130 322	1
	HF-S 258 TL-D II	9137 130 325	2
HF-S 258 TL-D II HT	9137 006 899	2	
HF-S 158 TLD 220-240	9137 006 319	1	
EB-P 258 TLD ICC 220-240		2	
OSRAM	QT-FIT8 1x58-70		1
	QT-FIT8 2x58-70		2
	QTP8 1x58		1
	QTP8 2x58		2
	QTP-OPTIMAL 1x54-58		1
	QTP-OPTIMAL 2x54-58		2
	QT-FIT 5/8 1x54-58		1
	QT-FIT 5/8 2x54-58		2
HELVAR	EL1x58ngn		1
	EL1x58s		1
	EL2x58es		2
	EL2x58HF		2
	EL2x58ngn		2
	EL2x58s		2
TRIDONIC	PC 1/58 T8 INDUSTRY	86 458 037	1
	PC 1/58 T8 PRO	22 176 094	1
	PC 1x58 T8 PRO lp	22 185 215	1
	PC 2/58 T8 INDUSTRY	86 458 038	2
	PC 2x58 E011		2
	PC 2x58 E011 IDC	22 083 174	2
	PC 2x58 T8 PRO sl	22 185 218	2
	PC 1x58 T8 TOP sl	22 185 224	1
	PC 2x58 T8 TOP sl	22 185 227	2
	PCA 1/58 excel one4all	22 085 286	1
	PCA 2x58 EXCEL One4all lp	28 000 040	2

CorePro LEDtube HF InstantFit T8 - 1500mm



Ballast Compatibility

KEY

	Ballast is compatible
•	Ballast is compatible, light output may differ >10% compared to specifications
	Ballast is not compatible

This document is for information purposes and must be treated as recommendation. Philips attempted to provide best results, results are generated in lab controlled environment and may differ from actual application conditions



	Ballast type	10nc / Ref. no.	Lamps on ballast
VOSSLOH-SCHWABE	ELXc 158.201	188315	1
	ELXc 158.209	188706	1
	ELXc 158.218	188870	1
	ELXc 258.203	188317	2
	ELXc 258.210	188707	2
	ELXc 258.219	188871	2
	ELXe 258.222	188130	2
	ELXe 258.222	188130	1
	ELXe 158.524	188024	1
BAG-HUECO	BCS58.1FX-11/220-240	1007 7592	1
	BCS58.2FX-11/220-240	1007 7593	2
	BCS58.2SX-01/220-240	1005 1003	2
	D 58.1-23021 E	166 072	1
	D 58.2-23021 E	166 082	2
	SCS58.2SR-11/220-240	166 272	2
Trilux	D58.1-23021E		1
	DD58.1-23031E		1
May + Christie	MCU 158		1
	MCU 258		2
Others	Direct mains		
	Electro Magnetic Ballast		

Corepro LEDtube HF, Instant Fit 1500mm T8 2000lm
Model number: 9290012497 9290012498
AC (50Hz) on HF Ballast Compatible
•
•
•
•
•
•
•
•
•
•
•
•
•
•
•
•
•
•

General note Philips CorePro LEDtube HF InstantFit T8

General notes: Refer to the product reference number in the header of the columns to use this product-ballast compatibility list. Please note that Philips LEDtubes are only tested with HF ballast on AC operation. The performance of Philips LEDtubes on HF ballasts with DC operation is not tested and is therefore not guaranteed. Philips LED tube InstantFit range is designed to work on HF ballasts only. For EM ballasts or direct mains connection, please contact a Philips sales representative for more information on our EM/Mains compatible range. This document is for information purposes only and must be treated as recommendation. Philips will not accept claims for any damage caused by not implementing the recommendations in this document. Philips does not accept any responsibility, warranty or liability when using Philips LEDtubes with ballasts not mentioned in this list, or when using successor models of the tested ballasts. Although Philips aims to provide the most accurate information and test results from controlled experiments the results may vary in different applications. This document focuses on the behaviour of above mentioned Philips LEDtube. Please also check and follow the instructions of HF ballast manufacturers for installation instructions.

Always check the latest update of the compatibility list on www.philips.com/ledtube

Dimming a LEDtube: Philips CorePro LEDtubes HF InstantFit T8 are not developed for dimming therefore the performance cannot be guaranteed in a dimming application. In case of usage of a non-dimmable product in a dimmable application, warranty does not apply.

CorePro LEDtube Universal HO - 1200mm



Ballast Compatibility

KEY

	Ballast is compatible
•	Ballast is compatible, light output may differ >10% compared to specifications
	Ballast is not compatible

This document is for information purposes and must be treated as recommendation. Philips attempted to provide best results, results are generated in lab controlled environment and may differ from actual application conditions



Corepro LEDtube UN, 1200mm HO 18W8xx T8
Model number: 9290018692 9290018693 9290018694

	Ballast type	10nc / Ref. no.	Lamps on ballast
VOSSLOH-SCHWABE	ELXc 136.207	188708	1
	ELXc 236.202	188316	2
	ELXc 236.208	188705	2
	ELXe 238.527	188137	2
	ELXe 238.527	188137	1
BAG-HUECO	BCS36.1FX-11/220-240	10077590	1
	BCS36.2FX-11/220-240	10077591	2
	D36.2-23021 E	166132	2
	D 58.1-23021 E	166072	1
	ECS36.2SR-01/220-240	167032	2
Trilux	D36.2-23021 E		2
	D58.1-23021E		1
	DD58.1-23031E		1
Others	EM ballast		1
	Direct Mains (only one single side supply)		1

AC (50Hz) on HF Ballast Compatible
•
•

General note Philips CorePro LEDtube Universal HO

General notes: Philips LEDtubes Universal T8 are designed to work on HF ballasts, or EM ballast, or direct mains connection.

For HF ballast connection: Refer to the product reference number in the header of the columns to use this product-ballast compatibility list.

Please note that Philips LEDtubes Universal T8 are only tested with HF ballast on AC operation. The performance of Philips LEDtubes Universal T8 on HF ballasts with DC operation is not tested and is therefore not guaranteed. This document is for information purposes only and must be treated as recommendation. Philips will not accept claims for any damage caused by not implementing the recommendations in this document. Philips does not accept any responsibility, warranty or liability when using Philips LEDtubes with HF ballasts not mentioned in this list, or when using successor models of the tested ballasts. Although Philips aims to provide the most accurate information and test results from controlled experiments the results may vary in different applications. This document focuses on the behaviour of above mentioned Philips LEDtube. Please also check and follow the instructions of HF ballast manufacturers for installation instructions.

Always check the latest update of the compatibility list on www.philips.com/ledtube

Dimming a LEDtube: Philips CorePro LEDtubes Universal HO are not developed for dimming therefore the performance cannot be guaranteed in a dimming application. In case of usage of a non-dimmable product in a dimmable application, warranty does not apply.

For EM ballasts or direct mains connection: Please refer to the installation guide.

CorePro LEDtube Universal HO - 1500mm

Ballast Compatibility



KEY

	Ballast is compatible
*	Ballast is compatible, light output may differ >10% compared to specifications
	Ballast is not compatible

This document is for information purposes and must be treated as recommendation. Philips attempted to provide best results, results are generated in lab controlled environment and may differ from actual application conditions



Corepro LEDtube UN,
1500mm HO
18W8xx T8

Model number:
9290018695
9290018696
9290018697

AC (50Hz) on HF Ballast Compatible

	Ballast type	10nc / Ref. no.	Lamps on ballast	
PHILIPS	EI 158 TL-D 220-240	9137 006 075	1	
	HF-B 158 TLD 220-240	9137 001 123	1	
	HF-B 158 TLD EII 220-240	9137 001 927	1	
	HF-B 258 TLD 220-240	9137 001 125	2	
	HF-B 258 TL-D EII 220-240	9137 001 929	2	*
	HF-E 158 TL-D	9137 130 389	1	
	HF-E 1/2 58 TL-D II	9137 130 409	2	*
	HF-E 1/2 58 TL-D II	9137 130 409	1	*
	HF-P 154/155 TL5 HO/PL-L III IDC	9137 130 282	1	
	HF-P 158 TLD EII 220-240	9137 001 912	1	
	HF-P 158 TL-D III IDC	9137 130 318	1	
	HF-P 258 TLD EII 220-240	9137 001 916	2	
	HF-P 258 TL-D III IDC	9137 130 319	2	
	HF-P Xt 158 TLD EII 220-240	9137 006 179	1	
	HF-P Xt 258 TL-D EII 220-240	9137 006 180	2	*
	HF-P 158 TLD 220-240	9137 001 185	1	
	HF-P 258 TLD 230-240	9137 001 110	2	*
	HF-R 158 TLD 220-240	9137 001 118	1	
	HF-R 258 TLD 220-240	9137 001 119	2	
	HF-R 158 TLD EII	9137 006 094	1	
	HF-R 258 TLD EII	9137 006 095	2	
	HF-R TD 258 TLD EII 220-240	9137 006 070	2	
	HF-RITD 1 28/35/49/54TL5 E+	9137006956	1	
	HF-RITD 2 28/35/49/54TL5 E+	9137006958	2	
	HF-S 158		1	*
	HF-S 158 TL-D II	9137 130 322	1	
	HF-S 258 TL-D II	9137 130 325	2	
	HF-S 258 TL-D II HT	9137 006 899	2	
	HF-S 158 TLD 220-240	9137 006 319	1	
	EB-P 258 TLD ICC 220-240	9137 130 210	2	
	HF-P 258 TLD 220-240	9137001206	2	
	OSRAM	QT Deluxe HF 1x58 230-240 DIM		1
QT Deluxe HF 2x58 230-240 Dim			2	
QT-FIT8 1x58-70			1	
QT-FIT8 2x58-70			2	
QTP8 1x58			1	
QTP8 2x58			2	*
QTP-OPTIMAL 1x54-58			1	
QTP-OPTIMAL 2x54-58			2	
QT 1X58 DIM			1	
QT-FIT 5/8 1x54-58			1	
QT-FIT 5/8 2x54-58			2	
QT-FIT8 2x54-58		2		
HELVAR	EL1x58ngn		1	
	EL1x58s		1	
	EL2x58es		2	
	EL2x58HF		2	
	EL2x58ngn		2	
	EL2x58s		2	
TRIDONIC	PC 1/58 T8 INDUSTRY	86 458 037	1	
	PC 1/58 T8 PRO	22 176 094	1	*
	PC 1x58 T8 PRO Ip	22 185 215	1	
	PC 2/58 T8 INDUSTRY	86 458 038	2	
	PC 2x58 E011		2	
	PC 2x58 E011 IDC	22 083 174	2	
	PC 2x58 T8 PRO sl	22 185 218	2	
	PC 1x58 T8 TOP sl	22185224	1	
	PC 2x58 T8 TOP sl	22185227	2	
	PCA 1/58 excel one4all	22 085 286	1	
	PCA 2x58 EXCEL One4all Ip	28 000 040	2	



© Philips Lighting Holding B.V. 2018. All rights reserved. Philips reserves the right to make changes in specifications and/or to discontinue any product at any time without notice or obligation and will not be liable for any consequences resulting from the use of this publication.

05/2018
Data subject to change.

www.philips.com/LEDtube