

Philips  
Cordless phone answer  
machine

SE8881B



## All calls from one device

The 8000 series provides ultimate convenience and a superior sound experience. You can make and receive landline and mobile phone calls from one device!

### Experience superior sound quality

- MySound: Personal Sound Profiles
- Handset speakerphone - Talk handsfree

### Benefit from pure convenience

- 6.1 cm (2.4") High Resolution TFT color display
- Make and receive landline and cellphone calls from your home
- Connects two mobile phones to your home phone via Bluetooth
- 200 name landline phonebook 500 name mobile phonebook
- charges I-phone and mobilephones

### Never miss a call or a message

- Direct access answering machine on base and via handset
- Up to 60 minutes recording time

### Save Energy

- EcoMode: reduced transmission power between handset and base
- Low power consumption: < 0.65 W in stand-by mode

**PHILIPS**  
sense and simplicity

# Highlights

## MySound



Sound perception is subjective and everyone has their individual listening preference, therefore MySound provides you with three distinctly different profiles in your choice of sound to give you the ultimate listening experience: Clear - for making the voices very crisp and clear Soft - for a more friendly and soft voice Warm - for making the voice sound welcoming and warm.

## Handset speakerphone



Handsfree mode uses a built-in loud speaker to amplify the voice of the caller, allowing you to speak and listen during a call without holding the phone to your ear. This is especially useful if you want to share the call with others or simply multitask.

## All calls from your home phone

You can now make and receive landline and mobile phone calls from your home phone. This product can connect up to two mobile phones to your home phone via Bluetooth connection for ultimate convenience. You can also synchronize your mobile phonebook to landline phone and to your computer.

## Low power consumption: < 0.65 W



Philips phones are energy efficient and are designed to be respectful to the environment. Now the power consumed in stand-by mode is less than < 0.65 W.

## Up to 60 min. recording time



Up to 60 minutes recording time

## Answering machine

Access all your messages directly from the base and the handset.

## make and receive landline and

Make and receive landline and cellphone calls from your home


## 6.1cm (2.4") TFT color display



Bigger, clearer and much sharper resolution displays allow you to effortlessly read the

characters on larger screens. This telephone has a 6 cm (2.4") TFT high-resolution display with an icon menu

## 200 name landline phonebook 50



200 name landline phonebook 500 name mobile phonebook

## charges I-phone and mobilephon

charges I-phone and mobilephones

## EcoMode: reduced transmission



Since the base station recognizes when the handset is docked on its base, an intelligent embedded system ensures transmitted power is permanently controlled and optimised according to the distance between handset and base unit. It means power emission is automatically reduced by up to 93% when the handset is near its base. When used in Eco Mode, you'll also enjoy a 60% manual reduction of emitted power.

# Specifications

## Sound

- Sound Profile: Mysound
- Noise reduction
- Volume control on handset
- Ringtones on handset: 10 polyphonic HQ + 5 standard
- Speakerphone

## Picture/Display

- Display size: 2.4"
- Display Type: TFT Color
- Backlight: Yes
- Backlight color: White

## Answering Machine

- Plug & Play answering machine
- Recording time capacity: Up to 60 minutes
- Message counter on base
- Answering machine control: base & handset
- Loud speaker on base

## Bluetooth

- Connects up to 2 mobilephones
- Access mobilephone contacts
- Back-up mobilephone contacts

## Convenience

- Mobilephone charger: Micro USB
- Room monitoring
- Date / Time display
- Alarm Clock
- Up to 22 hrs talk time
- Up to 300 hrs standby time
- Event light on the handset
- Base Station keys: Paging key
- Battery charge indication
- Charge time: 8 hours
- Signal strength indication

- Call Management: Call Waiting, Caller ID, Microphone mute, Missed Calls, Received Calls
- Illuminated keypad
- Keypad lock
- Key tone on/off
- Auto Registration
- Multi base capability: 1
- Multi handset capability: Up to 4

## Memory Capacity

- Phonebook: 200 names and numbers + 500 entries per cellular phone
- Phonebook: 50 entries
- Redial List Capacity: 20
- VIP Caller Identification

## Power

- Battery capacity: 750 mAh
- Battery type: AAA NiMH Rechargeable
- Mains power: AC 100-240V~50/60Hz
- Power Consumption: < 0.7 W

## Security

- Transmission encryption : Yes

## Network Features

- Compatible: GAP

## SAR Value

- Philips handsets: < 0.1 W/kg

## Eco Design

- EcoMode: automatic and manual

## Dimensions

- Base dimensions: TBD (H x D x W)
- Handset dimensions: TBD (H x D x W)



Issue date 2011-08-18

Version: 3.8.8

12 NC: 8670 000 69672  
EAN: 87 12581 57199 3

© 2011 Koninklijke Philips Electronics N.V.  
All Rights reserved.

Specifications are subject to change without notice.  
Trademarks are the property of Koninklijke Philips  
Electronics N.V. or their respective owners.

[www.philips.com](http://www.philips.com)