

PHILIPS

Home Lighting



Home lighting

collection 2015





“ฟิลิปส์ โฮม लाइटติ้ง” ศูนย์รวมโคมไฟตกต่างหลากหลายรุ่น หลายดีไซน์
อินเทรนด์ คลสิกทุกสไตล์ เวอร์คทุกฟังก์ชั่น ช่วยเปิดไอเดีย มุมมอง
และแรงบันดาลใจใหม่ๆ เพื่อเอาใจคนรักการแต่งบ้าน



Philips Home Lighting App

บริการจำลองภาพ “จับโคมไฟแต่งห้องจริง”

ฟรี! บริการให้คำปรึกษา ในการเลือกโคมไฟให้เหมาะกับห้องต่างๆ ที่ Philips Home Lighting เพียงคุณเตรียมรูปถ่าย
ห้องจริงของบ้านคุณ ให้พนักงานช่วยแมตช์โคมไฟฟิลิปส์ดีไซน์ที่คุณชื่นชอบ นำไปจัดวางในรูปถ่ายในรูปแบบ 3D เพื่อให้
คุณตัดสินใจเลือกโคมไฟฟิลิปส์ดีไซน์ “ใช่ที่สุด” ผ่าน Philips Home Lighting App

หรือคุณสามารถดาวน์โหลด Philips Home Lighting App
จากทั้ง App Store และ Google Play เพื่อมีกษเอนต์แมตช์
โคมไฟฟิลิปส์รุ่นต่างๆ ให้ลงตัวกับทุกสไตล์ห้องที่คุณต้องการ
ในรูปแบบ 3D ด้วยตัวคุณเอง





Contents

LIFE STYLE COLLECTION

4 Modern Living

myLiving

04 *Ledino*

13 General range

myGarden

14 *Ledino*

16 General range

18 Contemporary Chic

myLiving

18 General range

myGarden

30 General range

38 Vibrant Expressions

myLiving

38 **Kidsplace**

42 General range

52 *Linea*

55 *LivingColors*

56 *Accents*

58 Heritage Refined

myLiving

58 General range

myGarden

63 General range

68 Timeless Classics

myLiving

68 General range

UTILITY COLLECTION

70 *myBathroom*

72 Modern Living

74 Contemporary Chic



MAINSTREAM COLLECTION

80 Mainstream *Ceiling*

86 Mainstream *Spot*

91 Mainstream *Wall*

92 Mainstream *Desk*


LIFESTYLE COLLECTION



Modern Living



Contemporary Chic



Vibrant Expressions



Heritage Refined



Timeless Classics



Light for every style.


You've built a home, and lovingly furnished it to make it your own. A lush sofa set to lounge in comfort, an elegant dining table for family meals and sleek cupboards to hold your possessions. However no home is complete until the lights are turned on to bathe everything in a welcoming glow.

For the proud homeowner, Philips offers the Home Lighting Lifestyle Collection. Modern Living, Contemporary Chic, Vibrant Expressions, Heritage Refined and Timeless Classics describe the stylistic genres that span the home decor spectrum, and there is bound to be one that's just right for your home. Light up your living today.



Modern *Living*

I choose my lighting for its **functionality** and **light effect**.
I prefer **uncomplicated, pure shapes** in **neutral**
and **primary colors**.





















myLiving



myGarden

myLiving - Ledino

COMMERCIAL CODE	37368/48	37367/48
12 NC		
		
 Application	Suspension light	Wall light
 Color	Aluminum	Aluminum
 Material	Aluminum	Aluminum
 Lamp base & wattage	LED 7.5W X 3 included 2100K - 2700K warm white light	LED 7.5W X 1 included 2100K - 2700K warm white light
 Dimensions (L X W X H) mm	984 X 104 X 2500	92 X 92 X 306
 Extra Feature	Adjustable height, dimtone*	Dimtone*, on-base switch
 Price (Baht)	25,400	9,100

COMMERCIAL CODE	69054/48	69092/29, 69092/31
12 NC		
		
 Application	Suspension light	Suspension light
 Color	Aluminum	White
 Material	Aluminum, glass	Aluminum
 Lamp base & wattage	LED 7.5W X 3 included, 2500K-3450K tunable with white light	LED 7.5W x 4 included, 2700K warm white light
 Dimensions (L X W X H) mm	940 X 90 X 2500	901 X 106 X 1480
 Extra Feature	Adjustable height, dimmable*	Adjustable height, dimmable*
 Price (Baht)	12,700	16,200

*Dimmable / dimtone with separately available commercial trailing-edge dimmers.

myLiving - Ledino

COMMERCIAL CODE

12 NC

69088/11, 69088/14



Application

Ceiling light



Color

Chrome



Material

Aluminum



Lamp base & wattage

LED 7.5W x 2 included, 2700K warm white light
4000K cool white light

Dimensions (L X W X H) mm

490 X 170 X 40



Extra Feature


Dimmable*



Price (Baht)

8,700

69089/29, 69089/31



Wall light

White

Aluminum

LED 7.5W x 2 included, 2700K
warm white light

127 X 55 X 195

On-base switch

6,700

COMMERCIAL CODE

12 NC

69089/11, 69089/14



Application

Wall light



Color

Chrome



Material

Aluminum



Lamp base & wattage

LED 7.5W X 2 included, 2700K
warm white light

Dimensions (L X W X H) mm

127 X 55 X 195




Extra Feature

On-base switch



Price (Baht)

7,300



Spot light

White

Aluminum

LED 7.5W X 4 included, 2700K
warm white light







409 X 218 X 230












Dimmable*

14,500

*Dimmable / dimtone with separately available commercial trailing-edge dimmers.

myLiving - Ledino

COMMERCIAL CODE	69068/29, 69068/31	69084/87, 69084/99
12 NC		
		
		
 Application	Ceiling light	Spot light
 Color	White	Gray
 Material	Aluminum	Aluminum
 Lamp base & wattage	LED 7.5W included, 2700K warm white light	LED 7.5W X 4 included, 2700K warm white light 4000K cool white light
 Dimensions (L X W X H) mm	127 X 127 X 55	903 X 58 X 190
 Extra Feature	Dimmable*	Dimmable*
 Price (Baht)	6,200	15,000

COMMERCIAL CODE	69082/87, 69082/99	69080/99, 69080/87
12 NC		
		
		
 Application	Spot light	Wall light
 Color	Gray	Gray
 Material	Aluminum	Aluminum
 Lamp base & wattage	LED 7.5W X 2 included, 2700K warm white light	LED 7.5W included, 2700K warm white light
 Dimensions (L X W X H) mm	503 X 58 X 190	132 X 102 X 136
 Extra Feature	Dimmable*	Dimmable*, on-base switch
 Price (Baht)	8,600	4,400

*Dimmable / dimtone with separately available commercial trailing-edge dimmers.

myLiving - Ledino

COMMERCIAL CODE

12 NC

69074/29, 69074/31

69072/29, 69072/31



Application

Spot light

Spot light

Color

White

White

Material

Aluminum

Aluminum

Lamp base & wattage

LED 7.5W X 4 included, 2700K warm white light
4000K cool white lightLED 7.5W X 2 included, 2700K warm white light
4000K cool white light

Dimensions (L X W X H) mm

284 X 284 X 75

315 X 133 X 73

Extra Feature

Dimmable*

Dimmable*

Price (Baht)

15,600

8,900

COMMERCIAL CODE

12 NC

69070/29, 69070/31

69078/11, 69078/48



Application

Wall light

Recessed spot light

Color

White

Gray

Material

Aluminum

Aluminum

Lamp base & wattage

LED 7.5W included, 2700K warm white light

LED 7.5W included, 2700K warm white light

Dimensions (L X W X H) mm

168 X 130 X 72

110 X 110 X 49

Extra Feature

Dimmable*, on-base switch

Dimmable*










Price (Baht)










4,400

5,300

*Dimmable / dimtone with separately available commercial trailing-edge dimmers.










myLiving - Ledino










COMMERCIAL CODE	69096/48	69085/29, 69085/31
12 NC		
		
 Application	Recessed spot light	Wall light
 Color	Aluminum	White
 Material	Aluminum	Aluminum
 Lamp base & wattage	LED 7.5W included, 2700K warm white light	LED 2.5W X 2 included, 2700K warm white light
 Dimensions (L X W X H) mm	120 X 120 X 80	131 X 131 X 65
 Extra Feature	Dimmable*	On-base switch
 Price (Baht)	4,500	4,500

COMMERCIAL CODE	69085/99, 69085/87	69087/29, 69087/31
12 NC		
		
 Application	Wall light	Wall light
 Color	Gray	White
 Material	Aluminum	Aluminum
 Lamp base & wattage	LED 2.5W X 2 included, 2700K warm white light	LED 2.5W X 2 included, 2700K warm white light
 Dimensions (L X W X H) mm	131 X 131 X 65	74 X 70 X 120
 Extra Feature	On-base switch	On-base switch
 Price (Baht)		

*Dimmable / dimtone with separately available commercial trailing-edge dimmers.

myLiving - Ledino

COMMERCIAL CODE	69087/99, 69087/87	69086/90
12 NC		
		
 Application	Wall light	Wall light
 Color	Gray	Black
 Material	Aluminum	Aluminum
 Lamp base & wattage	LED 2.5W X 2 included, 2700K warm white light	LED 2.5W X 2 included, 2700K warm white light
 Dimensions (L X W X H) mm	74 X 70 X 120	95 X 90 X 95
 Extra Feature	On-base switch	On-base switch
 Price (Baht)	4,300	4,500

COMMERCIAL CODE	69064/99, 69064/87	69064/90, 69064/30
12 NC		
		
 Application	Wall light	Wall light
 Color	Gray	Black
 Material	Aluminum	Aluminum
 Lamp base & wattage	LED 2.5W included, 2700K warm white light 4000K cool white light	LED 2.5W included, 2700K warm white light 4000K cool white light
 Dimensions (L X W X H) mm	120 X 120 X 506	120 X 120 X 506
 Extra Feature	On-base switch	On-base switch
 Price (Baht)	3,500	3,500












myLiving - Ledino












COMMERCIAL CODE	56240/31 Star	56242/31 Star
12 NC		
		
		
 Application	Wall light	Ceiling / Wall light
 Color	White	White
 Material	Aluminum	Aluminum
 Lamp base & wattage	LED 4W, 2700K warm white light	LED 4W X 2, 2700K warm white light
 Dimensions (L X W X H) mm	118 X 82 X 60	198 X 82 X 60
 Extra Feature	Adjustable head	Adjustable head
 Price (Baht)	1,300	2,200

COMMERCIAL CODE	56244/31 Star	53154/48
12 NC		
		
		
 Application	Ceiling / Wall light	Ceiling light
 Color	White	Aluminum
 Material	Aluminum	Aluminum
 Lamp base & wattage	LED 4W X 4, 2700K warm white light	LED 7.5W X 4, 4000K cool white light
 Dimensions (L X W X H) mm	560 X 82 X 60	567 X 125 X 115
 Extra Feature	Adjustable head	Adjustable head, dimmable*
 Price (Baht)	3,700	17,800

*Dimmable / dimtone with separately available commercial trailing-edge dimmers.

myLiving

COMMERCIAL CODE	53150/48	37246/11
12 NC		
		
		
 Application	Wall light	Ceiling light
 Color	Aluminum	Chrome
 Material	Aluminum	Aluminum, glass
 Lamp base & wattage	LED 7.5W, 4000K included	LED 2.5W X 9 included
 Dimensions (L X W X H) mm	150 X 125 X 115	281 X 281 X 70
 Extra Feature	Adjustable head, on-base switch, dimmable*	Dimmable*
 Price (Baht)	7,300	16,700

COMMERCIAL CODE	37241/11	32157/31
12 NC		
		
		
 Application	Suspension light	Ceiling light
 Color	Chrome	White
 Material	Aluminum, glass	Aluminum
 Lamp base & wattage	LED 2.5W X 8 ,4000K cool white light	LED 2.5W X 9 ,4000K cool white light
 Dimensions (L X W X H) mm	1160 X 81 X 1320	230 X 230 X 36
 Extra Feature	Adjustable height, dimmable*	Dimmable*
 Price (Baht)	22,300	12,800

*Dimmable / dimtone with separately available commercial trailing-edge dimmers.

myLiving

COMMERCIAL CODE
12 NC

33257/31



myGarden - Ledino

16816/87



Application	Wall light
Color	White
Material	Aluminum
Lamp base & wattage	LED 2.5W X 2 ,4000K cool white light
Dimensions (L X W X H) mm	148 X 94 X 128
Extra Feature	On-base switch
Price (Baht)	4,800

Application	Wall light
Color	White
Material	Aluminum
Lamp base & wattage	LED 2.5W X 2 ,4000K cool white light
Dimensions (L X W X H) mm	148 X 94 X 128
Extra Feature	On-base switch
Price (Baht)	4,800

Application	Wall light
Color	Gray
Material	Aluminum
Lamp base & wattage	LED 7.5W included 2700K warm white light
Dimensions (L X W X H) mm	134 X 68 X 235
Extra Feature	Dimmable*, water resistant IP44 rating
Price (Baht)	6,400

myGarden - Ledino

COMMERCIAL CODE
12 NC

16816/93



16817/87














Application	Wall light
Color	Black
Material	Aluminum
Lamp base & wattage	LED 7.5W included 2700K warm white light
Dimensions (L X W X H) mm	134 X 68 X 235
Extra Feature	Dimmable*,water resistant IP44 rating
Price (Baht)	6,400












Application	Wall light
Color	Black
Material	Aluminum
Lamp base & wattage	LED 7.5W included 2700K warm white light
Dimensions (L X W X H) mm	134 X 68 X 235
Extra Feature	Dimmable*,water resistant IP44 rating
Price (Baht)	6,400

Application	Post light
Color	Gray
Material	Aluminum
Lamp base & wattage	LED 7.5W included 2700K warm white light
Dimensions (L X W X H) mm	129 X 60 X 600
Extra Feature	Dimmable*,water resistant IP44 rating
Price (Baht)	10,300

*Dimmable / dimtone with separately available commercial trailing-edge dimmers.










myGarden - Ledino










COMMERCIAL CODE	16817/93	16825/87
12 NC		
		
		
 Application	Post light	Wall light
 Color	Black	Gray
 Material	Aluminum	Aluminum
 Lamp base & wattage	LED 7.5W included 2700K warm white light	LED 7.5W included 2700K warm white light
 Dimensions (L X W X H) mm	129 X 60 X 600	160 X 236 X 42
 Extra Feature	Dimmable*, water resistant IP44 rating	Dimmable*, water resistant IP44 rating
 Price (Baht)	10,300	8,000

COMMERCIAL CODE	16800/93	16801/93
12 NC		
		
		
 Application	Wall light	Post light
 Color	Anthracite	Anthracite
 Material	Aluminum	Aluminum
 Lamp base & wattage	LED 7.5W included 2700K warm white light	LED 7.5W included 2700K warm white light
 Dimensions (L X W X H) mm	128 X 178 X 241	127 X 164 X 395
 Extra Feature	Dimmable*, water resistant IP44 rating	Dimmable*, water resistant IP44 rating
 Price (Baht)	5,600	6,800

*Dimmable / dimtone with separately available commercial trailing-edge dimmers.










myGarden - Ledino




COMMERCIAL CODE	16802/93	16815/47
12 NC		
		
 Application	Post light	Wall light
 Color	Anthracite	Inox
 Material	Aluminum	Aluminum
 Lamp base & wattage	LED 7.5W included 2700K warm white light	LED 5W included 2700K warm white light
 Dimensions (L X W X H) mm	127 X 164 X 790	136 X 58 X 185
 Extra Feature	Dimmable*, water resistant IP44 rating	Water resistant IP44 rating
 Price (Baht)	7,800	7,600

COMMERCIAL CODE	16809/47	16806/87
12 NC		
		
 Application	Wall light	Wall light
 Color	Inox	Gray
 Material	Aluminum	Aluminum
 Lamp base & wattage	LED 15W included 2700K warm white light	LED 7.5W included 2700K warm white light
 Dimensions (L X W X H) mm	283 X 48 X 180	186 X 179 X 99
 Extra Feature	Dimmable*, water resistant IP44 rating	Dimmable*, water resistant IP44 rating
 Price (Baht)	10,600	5,700

*Dimmable / dimtone with separately available commercial trailing-edge dimmers.

myGarden

COMMERCIAL CODE	16343/47	16344/47
12 NC		
		
 Application	Wall light	Pedestal light
 Color	Aluminium	Aluminium
 Material	Stainless steel, synthetics	Stainless steel, synthetics
 Lamp base & wattage	Essential E27, 14W not included	Essential E27, 14W not included
 Dimensions (L X W X H) mm	100 X 100 X 350	100 X 100 X 393
 Extra Feature	Water resistant IP44 rating	Water resistant IP44 rating
 Price (Baht)	1,500	2,200

COMMERCIAL CODE	16345/47	16904/87
12 NC		
		
 Application	Pedestal light	Wall light
 Color	Aluminium	Gray
 Material	Stainless steel, synthetics	Aluminum, synthetics
 Lamp base & wattage	Essential E27, 14W not included	2G7, PLS-4P 11W included
 Dimensions (L X W X H) mm	100 X 100 X 790	81 X 164 X 278
 Extra Feature	Water resistant IP44 rating	Water resistant IP44 rating
 Price (Baht)	2,400	3,600

myGarden

COMMERCIAL CODE

12 NC

17515/87

16412/47



Application

Wall light

Wall light

Color

Gray

Inox

Material

Aluminum, glass

Stainless steel

Lamp base & wattage

Essential E27, 23W X 2 not included

E27, CFLi 20W not included

Dimensions (L X W X H) mm

166 X 98 X 402

102 X 125 X 180

Extra Feature

Water resistant IP44 rating, adjustable head

Water resistant IP44 rating

Price (Baht)

3,800

1,900

COMMERCIAL CODE

12 NC

16414/47



Application

Post light

Color

Inox

Material

Stainless steel

Lamp base & wattage

E27, CFLi 20W not included

Dimensions (L X W X H) mm

100 X 100 X 400

Extra Feature

Water resistant IP44 rating

Price (Baht)

2,500



CONTEMPORARY *Chic*

I like, **diffused**, **indirect** light that is **friendly** and **gentle**. Light that creates soft shadows.





















myLiving












myGarden










myLiving

COMMERCIAL CODE	45615/17 Vase	45618/17 Bowl
12 NC		
		
 Application	Ceiling light	Ceiling Light
 Color	Chrome	Chrome
 Material	Metal	Metal
 Lamp base & wattage	Tornado E27, 15W X 6 not included	Tornado E27, 15W X 6 not included
 Dimensions (L X W X H) mm	771 X 771 X 275	724 X 724 X 215
 Extra Feature	-	-
 Price (Baht)	5,000	5,500

COMMERCIAL CODE	41750/31 Cocoon	40695/17
12 NC		
		
 Application	Suspension Light	Suspension light
 Color	Matt Chrome	Smoke
 Material	Metal	Glass
 Lamp base & wattage	Ambience globe E27, 18W not included	Ambience Globe E27, 18W not included
 Dimensions (L X W X H) mm	420 X 300 X 1450	238 X 238 X 1500
 Extra Feature	-	Adjustable height
 Price (Baht)	7,000	6,000

myLiving

COMMERCIAL CODE	40695/11	53143/31
12 NC		
		
 Application	Suspension light	Ceiling light
 Color	Clear	White
 Material	Glass	Metal, synthetics
 Lamp base & wattage	Ambiance Globe E27, 18W not included	LED 7.5W X 3 included, 4000K cool white light
 Dimensions (L X W X H) mm	238 X 238 X 1500	527 X 118 X 111
 Extra Feature	Adjustable height	Dimmable*
 Price (Baht)	6,000	12,300

COMMERCIAL CODE	53142/31	53140/31
12 NC		
		
 Application	Ceiling light	Wall light
 Color	White	White
 Material	Metal, synthetics	Metal, synthetics
 Lamp base & wattage	LED 7.5W X 2 included, 4000K cool white light	LED 7.5W included, 4000K cool white light
 Dimensions (L X W X H) mm	304 X 118 X 111	201 X 118 X 112
 Extra Feature	Dimmable*	On-base switch, dimmable*
 Price (Baht)	11,000	7,300

*Dimmable / dimtone with separately available commercial trailing-edge dimmers.

myLiving

COMMERCIAL CODE	40194/17(QPG310)	34104/48
12 NC		
Application	Suspension light	Wall light
Color	White	Aluminum
Material	Glass, metal	Glass, metal
Lamp base & wattage	Tornado E27, 24W X 3 not included	Tornado E14, 12W not included
Dimensions (L X W X H) mm	945 X 210 X 1500	300 X 72 X 120
Extra Feature	Adjustable height	-
Price (Baht)	6,700	2,600

COMMERCIAL CODE	52174/17(FCG323)	52178/17(FCG324)
12 NC		
Application	Spot light	Spot light
Color	Matt chrome	Matt chrome
Material	Glass, metal	Glass, metal
Lamp base & wattage	Tornado E14, 8W X 4 not included	Tornado E14, 8W X 4 not included
Dimensions (L X W X H) mm	260 X 260 X 120	1330 X 130 X 190
Extra Feature	-	-
Price (Baht)	5,100	6,000

myLiving

COMMERCIAL CODE	52173/17(FCG309)	52172/17(FCG308)
12 NC		












Application	Spot light	Spot light
Color	Matt chrome	Matt chrome
Material	Glass, metal	Glass, metal
Lamp base & wattage	Tornado E14, 8W X 3 not included	Tornado E14, 8W X 2 not included
Dimensions (L X W X H) mm	400 X 110 X 110	260 X 110 X 110
Extra Feature	-	-
Price (Baht)	3,900	2,600










COMMERCIAL CODE	52170/17(FCG307)	52171/17(FWG305)
12 NC		



Application	Wall light	Wall light
Color	Matt chrome	Matt chrome
Material	Glass, metal	Glass, metal
Lamp base & wattage	Tornado E14, 8W not included	Tornado E14, 8W not included
Dimensions (L X W X H) mm	120 X 90 X 90	90 X 420 X 90
Extra Feature	On-base switch	On-line switch
Price (Baht)	1,400	1,900










myLiving

COMMERCIAL CODE	30082/11(QCG300)	33200/38(FWG301)
12 NC		
		
 Application	Ceiling/ Wall light	Wall light
 Color	White, chrome	Beige
 Material	Glass, synthetics	Glass, fabric
 Lamp base & wattage	Tornado E27, 24W not included	Essential E27, 23W not included
 Dimensions (L X W X H) mm	300 X 300 X 100	315 X 111 X 168
 Extra Feature	-	-
 Price (Baht)	1,000	2,000










COMMERCIAL CODE	72894/31(QCG304)	30088/67(QCG319)
12 NC		
		
 Application	Ceiling light	Ceiling/ Wall light
 Color	White	White
 Material	Glass, synthetics	Glass
 Lamp base & wattage	Tornado E27, 15W not included	Tornado E27, 24W not included
 Dimensions (L X W X H) mm	150 X 150 X 175	300 X 300 X 100
 Extra Feature	-	-
 Price (Baht)	600	800







myLiving

COMMERCIAL CODE	30012/17(TCG702)	30010/17(TCG701)
12 NC		
		
 Application	Ceiling/ Wall light	Ceiling/ Wall light
 Color	Nickel	White
 Material	Glass, metal	Glass, metal
 Lamp base & wattage	Tornado E27, 24W not included	Tornado E27, 24W not included
 Dimensions (L X W X H) mm	360 X 360 X 96	290 X 290 X 95
 Extra Feature	-	-
 Price (Baht)	1,600	900










COMMERCIAL CODE	30200/87(QCG305)	30200/86(QCG305)
12 NC		
		
 Application	Ceiling/ Wall light	Ceiling/ Wall light
 Color	Gray	Brown
 Material	Glass, metal	Glass, metal
 Lamp base & wattage	Essential E27, 18W X 2 not included	Essential E27, 18W X 2 not included
 Dimensions (L X W X H) mm	400 X 400 X 86	400 X 400 X 86
 Extra Feature	-	-
 Price (Baht)	3,400	3,400










myLiving

COMMERCIAL CODE	33067/48(FWG300)	33067/17(FWG300)
12 NC		
		
 Application	Wall light	Wall light
 Color	Aluminum	Matt chrome
 Material	Metal, glass	Metal, glass
 Lamp base & wattage	Essential E27, 23W not included	Essential E27, 23W not included
 Dimensions (L X W X H) mm	270 X 78 X 78	270 X 78 X 78
 Extra Feature	-	-
 Price (Baht)	1,600	1,600






COMMERCIAL CODE	33206/31(QWG311)	33206/93(QWG311)
12 NC		
		
 Application	Wall light	Wall light
 Color	White	Anthracite
 Material	Metal, glass	Metal, glass
 Lamp base & wattage	Essential E27, 23W not included	Essential E27, 23W not included
 Dimensions (L X W X H) mm	401 X 103 X 90	401 X 103 X 90
 Extra Feature	-	-
 Price (Baht)	2,400	2,400










myLiving

COMMERCIAL CODE	80813/67(QWG302)	80815/67(QWG301)
12 NC		
		
 Application	Wall light	Wall light
 Color	White	White
 Material	Glass, metal	Glass
 Lamp base & wattage	Tornado E27, 20W not included	Tornado E27, 20W not included
 Dimensions (L X W X H) mm	260 X 90 X 260	265 X 88 X 260
 Extra Feature	-	-
 Price (Baht)	1,200	1,000

COMMERCIAL CODE	36061/17(QPG302)	36062/17(QWG305)
12 NC		
		
 Application	Suspension light	Wall light
 Color	Matt chrome	Matt chrome
 Material	Glass, metal	Glass, metal
 Lamp base & wattage	Tornado E27, 24W X 3 not included	Tornado E27, 24W not included
 Dimensions (L X W X H) mm	637 X 115 X 1300	280 X 115 X 225
 Extra Feature	Adjustable height	-
 Price (Baht)	3,900	2,000

myLiving

COMMERCIAL CODE	36866/48(QPG301)	36865/48(QPG300)
12 NC		
		
 Application	Suspension light	Suspension light
 Color	Aluminum	Aluminum
 Material	Metal	Metal
 Lamp base & wattage	Tornado E14, 12W X 3 not included	Tornado E27, 24W not included
 Dimensions (L X W X H) mm	980 X 191.3 X 1500	330.8 X 330.8 X 1500
 Extra Feature	Adjustable height	Adjustable height
 Price (Baht)	6,700	3,700

COMMERCIAL CODE	36867/48(QFG300)	52161/06(FWG306)
12 NC		
		
 Application	Floor light	Wall light
 Color	Aluminum	Bronze
 Material	Metal	Glass, metal
 Lamp base & wattage	Tornado E27, 24W not included	Tornado E14, 12W not included
 Dimensions (L X W X H) mm	331 X 331 X 1670	82 X 320 X 280
 Extra Feature	Foot switch	On-line switch
 Price (Baht)	6,000	1,000


myLiving

COMMERCIAL CODE	52163/17(FCG312)	52162/17(FCG311)
12 NC		














Application	Spot light	Spot light
Color	Matt chrome	Matt chrome
Material	Glass, metal	Glass, metal
Lamp base & wattage	Tornado E14, 12W X 3 not included	Tornado E14, 12W X 2 not included
Dimensions (L X W X H) mm	680 X 95 X 117	335 X 95 X 117
Extra Feature	-	-
Price (Baht)	3,100	2,100










COMMERCIAL CODE	52160/17(FCG310)	52160/06(FCG310)
12 NC		



Application	Spot light	Spot light
Color	Matt chrome	Bronze
Material	Glass, metal	Glass, metal
Lamp base & wattage	Tornado E14, 12W not included	Tornado E14, 12W not included
Dimensions (L X W X H) mm	80 X 80 X 90	80 X 80 X 90
Extra Feature	On-base switch	On-base switch
Price (Baht)	1,100	1,100










myLiving










COMMERCIAL CODE	40902/48 Ayr	53235/31 Dyna spot
12 NC		
	 	 
 Application	Suspension light	Wall / ceiling light
 Color	Aluminum	White
 Material	Steel	Synthetics
 Lamp base & wattage	LED 25W included 2700K warm white light	LED 4W included 2700K warm white light
 Dimensions (L X W X H) mm	400 X 400 X 1500	96 X 96 X 119
 Extra Feature	Adjustable height, dimmable*	Adjustable head
 Price (Baht)	10,900	800

COMMERCIAL CODE	53235/99 Dyna spot
12 NC	
	 
 Application	Wall / ceiling light
 Color	Grey
 Material	Synthetics
 Lamp base & wattage	LED 4W included 2700K warm white light
 Dimensions (L X W X H) mm	96 X 96 X 119
 Extra Feature	Adjustable head
 Price (Baht)	800










*Dimmable / dimtone with separately available commercial trailing-edge dimmers.










myGarden

COMMERCIAL CODE	16917/87	16917/93
12 NC		
		
 Application	Wall light	Wall light
 Color	Gray	Anthracite
 Material	Aluminum, synthetics	Aluminum, synthetics
 Lamp base & wattage	Tornado E27, 24W not included	Tornado E27, 24W not included
 Dimensions (L X W X H) mm	127 X 108 X 315	127 X 108 X 315
 Extra Feature	Water resistant IP44 rating	Water resistant IP44 rating
 Price (Baht)	2,300	2,300

COMMERCIAL CODE	16926/87	16926/93
12 NC		
		
 Application	Wall light	Wall light
 Color	Gray	Anthracite
 Material	Aluminum, synthetics	Aluminum, synthetics
 Lamp base & wattage	Essential E27, 23W not included	Essential E27, 23W not included
 Dimensions (L X W X H) mm	235 X 137 X 85	235 X 137 X 85
 Extra Feature	Water resistant IP44 rating	Water resistant IP44 rating
 Price (Baht)	2,100	2,100










myGarden

COMMERCIAL CODE	16927/87	32010/87(ECB300)
12 NC		
		
 Application	Wall light	Ceiling / Wall light
 Color	Gray	Gray
 Material	Aluminum, synthetics	Metal, glass
 Lamp base & wattage	Essential E27, 23W X 2 not included	Tornado E27, 20W not included
 Dimensions (L X W X H) mm	440 X 137 X 85	315 X 315 X 100
 Extra Feature	Water resistant IP44 rating	Water resistant IP44 rating
 Price (Baht)	3,400	1,500










COMMERCIAL CODE	01726/93(EWS300)	01726/31(EWS300)
12 NC		
		
 Application	Wall light	Wall light
 Color	Anthracite	White
 Material	Stainless steel, synthetics	Stainless steel, synthetics
 Lamp base & wattage	Tornado E27, 20W not included	Tornado E27, 20W not included
 Dimensions (L X W X H) mm	235 X 95 X 260	235 X 95 X 260
 Extra Feature	Water resistant IP44 rating	Water resistant IP44 rating
 Price (Baht)	1,200	1,200










myGarden

COMMERCIAL CODE	17086/47(EWS300)	17105/93
12 NC		
		
 Application	Wall light	Wall light
 Color	Inox	Anthracite
 Material	Stainless steel, synthetics	Aluminum, synthetics
 Lamp base & wattage	Tornado E27, 20W not included	Essential E27, 23W not included
 Dimensions (L X W X H) mm	235 X 95 X 260	290 X 130 X 113
 Extra Feature	Water resistant IP44 rating	Water resistant IP44 rating
 Price (Baht)	1,500	1,800










COMMERCIAL CODE	17105/87	17130/93(EWP300)
12 NC		
		
 Application	Wall light	Wall light
 Color	Gray	Anthracite
 Material	Aluminum, synthetics	Aluminum, synthetics
 Lamp base & wattage	Essential E27, 23W not included	Essential E27, 23W not included
 Dimensions (L X W X H) mm	290 X 130 X 113	356 X 93 X 75
 Extra Feature	Water resistant IP44 rating	Water resistant IP44 rating
 Price (Baht)	1,800	1,500










myGarden

COMMERCIAL CODE	17130/87(EWP300)	16212/87
12 NC		
		
 Application	Wall light	Wall light
 Color	Light gray	Gray
 Material	Aluminum, synthetics	Aluminum, synthetics
 Lamp base & wattage	Essential E27, 23W not included	Essential E27, 23W not included
 Dimensions (L X W X H) mm	356 X 93 X 75	150 X 255 X 171
 Extra Feature	Water resistant IP44 rating	Water resistant IP44 rating
 Price (Baht)	1,500	1,800










COMMERCIAL CODE	16212/93	71797/31(EWC300)
12 NC		
		
 Application	Wall light	Wall light
 Color	Anthracite	White
 Material	Aluminum, synthetics	Synthetics
 Lamp base & wattage	Essential E27, 23W not included	Tornado E27, 24W not included
 Dimensions (L X W X H) mm	150 X 255 X 171	205 X 255 X 255
 Extra Feature	Water resistant IP44 rating	Water resistant IP44 rating
 Price (Baht)	1,800	900

myGarden

COMMERCIAL CODE	71797/93(EWC300)	17173/47
12 NC		
		
 Application	Wall light	Wall light
 Color	Black	Inox
 Material	Synthetics	Stainless steel, glass
 Lamp base & wattage	Tornado E27, 24W not included	Tornado E14, 12W not included
 Dimensions (L X W X H) mm	205 X 255 X 255	176 X 93 X 200
 Extra Feature	Water resistant IP44 rating	Water resistant IP44 rating
 Price (Baht)	900	1,800










COMMERCIAL CODE	17173/30	17014/31
12 NC		
		
 Application	Wall light	Wall light
 Color	Black	White
 Material	Stainless steel, glass	Synthetics, metal
 Lamp base & wattage	Tornado E14, 12W not included	Essential E27, 23W not included
 Dimensions (L X W X H) mm	176 X 93 X 200	235 X 95 X 260
 Extra Feature	Water resistant IP44 rating	Water resistant IP44 rating, motion & daylight sensor
 Price (Baht)	1,800	1,800










myGarden

COMMERCIAL CODE	17014/47	17014/93
12 NC		
		
 Application	Wall light	Wall light
 Color	Inox	Anthracite
 Material	Synthetics, metal	Synthetics, metal
 Lamp base & wattage	Essential E27, 23W not included	Essential E27, 23W not included
 Dimensions (L X W X H) mm	235 X 95 X 260	235 X 95 X 260
 Extra Feature	Water resistant IP44 rating, motion & daylight sensor	Water resistant IP44 rating, motion & daylight sensor
 Price (Baht)	2,000	1,800












COMMERCIAL CODE	16245/87	16246/87
12 NC		
		
 Application	Wall light	Wall light
 Color	Gray	Gray
 Material	Metal, synthetics	Metal, synthetics
 Lamp base & wattage	Tornado E27, 12W not included	Tornado E27, 12W not included
 Dimensions (L X W X H) mm	195 X 135 X 195	195 X 135 X 195
 Extra Feature	Water resistant IP44 rating	Water resistant IP44 rating,
 Price (Baht)	1,000	1,800




myGarden

COMMERCIAL CODE	32010/93(ECB300)	32010/31(ECB300)
12 NC		
		
 Application	Ceiling/ Wall light	Ceiling/ Wall light
 Color	Anthracite	White
 Material	Metal, glass	Metal, glass
 Lamp base & wattage	Tornado E27, 20W not included	Tornado E27, 20W not included
 Dimensions (L X W X H) mm	315 X 315 X 100	315 X 315 X 100
 Extra Feature	Water resistant IP44 rating	Water resistant IP44 rating
 Price (Baht)	1,500	1,500

COMMERCIAL CODE	17273/47 String	17273/93 String
12 NC		
		
 Application	Wall light	Wall light
 Color	Inox	Anthracite
 Material	Stainless steel, synthetics	Stainless steel, synthetics
 Lamp base & wattage	LED 4W included 2700K warm white light	LED 4W included 2700K warm white light
 Dimensions (L X W X H) mm	162 X 66 X 209	162 X 66 X 209
 Extra Feature	Water resistant IP44 rating	Water resistant IP44 rating
 Price (Baht)	2,200	2,200

myGarden

COMMERCIAL CODE	17287/47 Aura	17287/30 Aura
12 NC		
		
		
	92	92
	122	122
 Application	Wall light	Wall light
 Color	Inox	Black
 Material	Stainless steel, synthetics	Stainless steel, synthetics
 Lamp base & wattage	LED 4W included 2700K warm white light	LED 4W included 2700K warm white light
 Dimensions (L X W X H) mm	92 X 103 X 122	92 X 103 X 122
 Extra Feature	Water resistant IP44 rating	Water resistant IP44 rating
 Price (Baht)	2,100	2,100

COMMERCIAL CODE	17204/87	17205/87
12 NC		
		
	185	185
	300	300
 Application	Wall / ceiling light	Wall / ceiling light
 Color	Grey	Grey
 Material	Aluminum, synthetics	Aluminum, synthetics
 Lamp base & wattage	E27, CFLi 18W x 2 not included or LED 13W x 2 not included	E27, CFLi 18W x 2 not included or LED 13W x 2 not included
 Dimensions (L X W X H) mm	185 X 90 X 300	185 X 90 X 300
 Extra Feature	Water resistant IP54 rating	Water resistant IP54 rating
 Price (Baht)	1,800	1,800



VIBRANT *Expressions*

Lighting for me shall be **eye-catching**. It should really stand out in a way that is **interesting, non-traditional, unusual** and **personalized**.



myLiving

myLiving - Kidsplace Disney

COMMERCIAL CODE

12 NC

71709/30 SoftPal Mickey

71710/30 SoftPal Minnie



Application	Table light
Color	Multi Color
Material	Synthetics
Lamp base & wattage	LED 0.18W
Dimensions (L X W X H) mm	123 X 98 X 157
Extra Feature	Tilt to on/off, induction charger
Price (Baht)	1,590

Application	Table light
Color	Multi Color
Material	Synthetics
Lamp base & wattage	LED 0.18W
Dimensions (L X W X H) mm	123 X 98 X 157
Extra Feature	Tilt to on/off, induction charger
Price (Baht)	1,590


Application	Table light
Color	Multi Color
Material	Synthetics
Lamp base & wattage	LED 0.18W
Dimensions (L X W X H) mm	123 X 98 X 166
Extra Feature	Tilt to on/off, induction charger
Price (Baht)	1,590

COMMERCIAL CODE

12 NC

71705/33 SoftPal Mike

71705/83 SoftPal Sulley





















Application	Table light
Color	Green
Material	Synthetics
Lamp base & wattage	LED 0.18W
Dimensions (L X W X H) mm	139 X 139 X 135
Extra Feature	Tilt to on/off, induction charger
Price (Baht)	1,490

Application	Table light
Color	Green
Material	Synthetics
Lamp base & wattage	LED 0.18W
Dimensions (L X W X H) mm	139 X 139 X 135
Extra Feature	Tilt to on/off, induction charger
Price (Baht)	1,490

Application	Table light
Color	Blue
Material	Synthetics
Lamp base & wattage	LED 0.18W
Dimensions (L X W X H) mm	139 X 139 X 135
Extra Feature	Tilt to on/off, induction charger
Price (Baht)	1,490

myLiving - Kidsplace Disney

COMMERCIAL CODE	71704/32 Micro Cars	71704/28 Micro Princess
12 NC		
		
 Application	Table light	Table light
 Color	Red	Pink
 Material	Synthetics	Synthetics
 Lamp base & wattage	LED 4.7W	LED 4.7W
 Dimensions (L X W X H) mm	120 X 100 X 110	120 X 100 X 110
 Extra Feature	64 colors, auto color change	64 colors, auto color change
 Price (Baht)	2,190	2,190

COMMERCIAL CODE	71767/34 Torch Winnie the Pooh	71769/32 Projector Cars
12 NC		
		
 Application	Portable light	Table light
 Color	Yellow	Red
 Material	Synthetics	Synthetics
 Lamp base & wattage	LED 0.3W	LED 0.1W
 Dimensions (L X W X H) mm	55 X 28 X 94	115 X 115 X 118
 Extra Feature	Switch on product	24 images projection light, night light
 Price (Baht)	450	900

myLiving - Kidsplace Disney

COMMERCIAL CODE

12 NC

71769/28 Projector Princess

71758/30



Table light



Suspension light

Application

Color

Material

Lamp base & wattage

Dimensions (L X W X H) mm

Extra Feature

Price (Baht)

Pink

Synthetics

LED 0.1W

115 X 115 X 118

24 images projection light, night light

900

Blue

Synthetics

E27, CFLi 15W not included

354 X 354 X 1346

Adjustable height

1,900

COMMERCIAL CODE

12 NC

71758/31



Suspension light

Application

Color

Material

Lamp base & wattage

Dimensions (L X W X H) mm

Extra Feature

Price (Baht)

Red

Synthetics

E27, CFLi 15W not included

354 X 354 X 1346

Adjustable height

1,900

myLiving

COMMERCIAL CODE

12 NC

60201/34 Silices



60201/35 Silices



Application

Suspension light

Suspension light

Color

Yellow

Blue

Material

Synthetics, metal

Synthetics, metal

Lamp base & wattage

Tornado E27, 24W X 3 not included

Tornado E27, 24W X 3 not included

Dimensions (L X W X H) mm

400 X 400 X 1700

400 X 400 X 1700

Extra Feature

Adjustable height

Adjustable height

Price (Baht)


16,900

16,900


COMMERCIAL CODE

12 NC

60202/34



60202/35



Application

Wall light

Wall light

Color

Yellow

Blue

Material

Synthetics, metal

Synthetics, metal

Lamp base & wattage

Tornado E27, 24W not included

Tornado E27, 24W not included

Dimensions (L X W X H) mm

300 X 183 X 190

300 X 183 X 190

Extra Feature

On-base switch










On-base switch










Price (Baht)

6,300










6,300










myLiving

COMMERCIAL CODE	45938/30	45938/31
12 NC		
		
 Application	Table light	Table light
 Color	Black	White
 Material	Metal, fabric, glass	Metal, fabric, glass
 Lamp base & wattage	Tornado E27, 24W not included	Tornado E27, 24W not included
 Dimensions (L X W X H) mm	300 X 300 X 522	300 X 300 X 522
 Extra Feature	On-line switch	On-line switch
 Price (Baht)	5,900	5,900










COMMERCIAL CODE	42938/30	42938/31
12 NC		
		
 Application	Floor light	Floor light
 Color	Black	White
 Material	Metal, fabric, glass	Metal, fabric, glass
 Lamp base & wattage	Tornado E27, 24W not included	Tornado E27, 24W not included
 Dimensions (L X W X H) mm	400 X 400 X 1596	400 X 400 X 1596
 Extra Feature	Foot switch	Foot switch
 Price (Baht)	10,000	10,000










myLiving

COMMERCIAL CODE	40380/30	40380/31
12 NC		
		
 Application	Suspension light	Suspension light
 Color	Black	White
 Material	Aluminium, glass	Aluminium, glass
 Lamp base & wattage	Tornado E27, 24W X 3 not included	Tornado E27, 24W X 3 not included
 Dimensions (L X W X H) mm	700 X 700 X 3000	700 X 700 X 3000
 Extra Feature	Adjustable height	Adjustable height
 Price (Baht)	28,300	28,300

COMMERCIAL CODE	41055/32	41055/35
12 NC		
		
 Application	Suspension light	Suspension light
 Color	Red	Blue
 Material	Metal	Metal
 Lamp base & wattage	Tornado E27, 24W not included	Tornado E27, 24W not included
 Dimensions (L X W X H) mm	350 X 350 X 1750	350 X 350 X 1750
 Extra Feature	Adjustable height	Adjustable height
 Price (Baht)	4,000	4,000











myLiving










COMMERCIAL CODE	41055/87	40550/01
12 NC		
		
 Application	Suspension light	Centerpiece
 Color	Gray	Brass
 Material	Metal	Metal
 Lamp base & wattage	Tornado E27, 24W not included	LED 2.5W X 24 included
 Dimensions (L X W X H) mm	350 X 350 X 1750	593 X 593 X 3210
 Extra Feature	Adjustable height	Dimmable*
 Price (Baht)	4,000	40,000

COMMERCIAL CODE	40550/30	40544/06
12 NC		
		
 Application	Centerpiece	Centerpiece
 Color	Black	Bronze
 Material	Metal	Metal
 Lamp base & wattage	LED 2.5W X 24 included	LED 2.5W X 10 included
 Dimensions (L X W X H) mm	593 X 593 X 3210	633 X 603 X 192
 Extra Feature	Dimmable*	Dimmable*
 Price (Baht)	40,000	20,000

*Dimmable / dimtone with separately available commercial trailing-edge dimmers.










myLiving









COMMERCIAL CODE	40544/12	40354/20
12 NC		
	 	
 Application	Centerpiece	Suspension light
 Color	Brass	Purple
 Material	Metal	Metal
 Lamp base & wattage	LED 2.5W X 10 included	Ambiance E27, 24W not included
 Dimensions (L X W X H) mm	633 X 603 X 192	300 X 300 X 1500
 Extra Feature	Dimmable*	Adjustable height
 Price (Baht)	20,000	4,540

COMMERCIAL CODE	40354/34	40354/35
12 NC		
		
 Application	Suspension light	Suspension light
 Color	Yellow	Blue
 Material	Metal	Metal
 Lamp base & wattage	Ambiance E27, 24W not included	Ambiance E27, 24W not included
 Dimensions (L X W X H) mm	300 X 300 X 1500	300 X 300 X 1500
 Extra Feature	Adjustable height	Adjustable height
 Price (Baht)	4,540	4,540










*Dimmable / dimtone with separately available commercial trailing-edge dimmers.










myLiving

COMMERCIAL CODE	30174/53(QCG306)	40227/53(QPG303)
12 NC		
		
 Application	Ceiling light	Suspension light
 Color	Orange	White / orange
 Material	Glass, metal	Metal
 Lamp base & wattage	Tornado E27, 24W X 2 not included	Ambiance E27, 8W not included
 Dimensions (L X W X H) mm	400 X 400 X 134.5	250 X 250 X 1300
 Extra Feature	-	Adjustable height
 Price (Baht)	2,000	2,000










COMMERCIAL CODE	40227/35(QPG303)	40227/11(QPG303)
12 NC		
		
 Application	Suspension light	Suspension light
 Color	Gray / blue	Chrome / white
 Material	Metal	Metal
 Lamp base & wattage	Ambiance E27, 8W not included	Ambiance E27, 8W not included
 Dimensions (L X W X H) mm	250 X 250 X 1300	250 X 250 X 1300
 Extra Feature	Adjustable height	Adjustable height
 Price (Baht)	2,000	2,400










myLiving

COMMERCIAL CODE	40228/53(QPG304)	40228/35(QPG304)
12 NC		
		
 Application	Suspension light	Suspension light
 Color	White / orange	Gray / blue
 Material	Metal	Metal
 Lamp base & wattage	Tornado E27, 24W not included	Tornado E27, 24W not included
 Dimensions (L X W X H) mm	400 X 400 X 1500	400 X 400 X 1500
 Extra Feature	Adjustable height	Adjustable height
 Price (Baht)	4,000	4,000










COMMERCIAL CODE	40228/11(QPG304)	33198/87(QWG303)
12 NC		
		
 Application	Suspension light	Wall light
 Color	Chrome / white	White
 Material	Metal	Glass, metal
 Lamp base & wattage	Tornado E27, 24W not included	Tornado E27, 20W not included
 Dimensions (L X W X H) mm	400 X 400 X 1500	264 X 89 X 254
 Extra Feature	Adjustable height	-
 Price (Baht)	5,000	1,600










myLiving

COMMERCIAL CODE	36880/17(QPG311)	52090/11(FWG304)
12 NC		
		
 Application	Suspension light	Ceiling / Wall light
 Color	White	Chrome
 Material	Glass, metal	Glass, metal
 Lamp base & wattage	Essential E27, 23W not included	Tornado E14, 12W not included
 Dimensions (L X W X H) mm	125 X 125 X 1500	100 X 100 X 105
 Extra Feature	Adjustable height	On-base switch
 Price (Baht)	4,000	1,400










COMMERCIAL CODE	52092/11(FCG304)	52094/11(FCG306)
12 NC		
		
 Application	Ceiling light	Ceiling light
 Color	Chrome	Chrome
 Material	Glass, metal	Glass, metal
 Lamp base & wattage	Tornado E14, 12W X 2 not included	Tornado E14, 12W X 4 not included
 Dimensions (L X W X H) mm	330 X 130 X 117	805 X 130 X 117
 Extra Feature	-	-
 Price (Baht)	2,400	4,300










myLiving

COMMERCIAL CODE	42261/30 Drin	42261/33 Drin
12 NC		
		
 Application	Floor light	Floor light
 Color	Black	Green
 Material	Metal	Metal
 Lamp base & wattage	E27, CFLi 24W not included	E27, CFLi 24W not included
 Dimensions (L X W X H) mm	250 X 360 X 1910	250 X 360 X 1910
 Extra Feature	Adjustable height, foot switch	Adjustable height, foot switch
 Price (Baht)	3,300	3,300










COMMERCIAL CODE	42261/87 Drin	43228/31 Isaca
12 NC		
		
 Application	Floor light	Table light
 Color	Grey	White
 Material	Metal, synthetics	Fabric, synthetics
 Lamp base & wattage	E27, CFLi 24W not included	E14, CFLi 12W not included
 Dimensions (L X W X H) mm	250 X 360 X 1910	140 X 140 X 275
 Extra Feature	Adjustable height, foot switch	On-line switch
 Price (Baht)	3,300	450

myLiving










COMMERCIAL CODE	43228/32 Isaca	43228/96 Isaca
12 NC		
		
 Application	Table light	Table light
 Color	Red	Purple
 Material	Fabric, synthetics	Fabric, synthetics
 Lamp base & wattage	E14, CFLi 12W not included	E14, CFLi 12W not included
 Dimensions (L X W X H) mm	140 X 140 X 275	140 X 140 X 275
 Extra Feature	On-line switch	On-line switch
 Price (Baht)	450	450

COMMERCIAL CODE	41057/32	41057/33
12 NC		
		
 Application	Suspension light	Suspension light
 Color	Red	Green
 Material	Silicone	Silicone
 Lamp base & wattage	E27, CFLi 24W not included	E27, CFLi 24W not included
 Dimensions (L X W X H) mm	280 X 280 X 1500	280 X 280 X 1500
 Extra Feature	Flexible shade, flat packaging	Flexible shade, flat packaging
 Price (Baht)	1,500	1,500

myLiving












COMMERCIAL CODE	41057/34	40755/93 Ecliptic
12 NC		
		
 Application	Suspension light	Suspension light
 Color	Yellow	Black
 Material	Silicone	Metal
 Lamp base & wattage	E27, CFLi 24W not included	LED 40W included 2700K warm white light
 Dimensions (L X W X H) mm	280 X 280 X 1500	650 X 650 X 3000
 Extra Feature	Flexible shade, flat packaging	Adjustable height, dimmable*
 Price (Baht)	1,500	32,000












myLiving - Linea

COMMERCIAL CODE	30904/31	30905/31
12 NC		
		
 Application	Cove light	Cove light
 Color	White	White
 Material	Synthetics	Synthetics
 Lamp base & wattage	LED 6.5W/meter included	LED 6.5W/meter included
 Dimensions (L X W X H) mm	5000 X 10 X 3	1000 X 10 X 3
 Extra Feature	Changeable color, remote control included	Changeable color, remote control included
 Price (Baht)	4,700	2,200










*Dimmable / dimtone with separately available commercial trailing-edge dimmers.









myLiving - Linea

COMMERCIAL CODE	30906/31	30729, 30730
12 NC		
		
		
 Application	Cove light	Cove light
 Color	White	White
 Material	Synthetics	Synthetics
 Lamp base & wattage	LED 6.5W/meter included	LED Max 30W included 3000K warm white light, 4000K cool white light
 Dimensions (L X W X H) mm	1000 X 10 X 3	5000 X 8 X 3
 Extra Feature	Changeable color	Driver included
 Price (Baht)	800	2,900










COMMERCIAL CODE	30733, 30734	30737, 30738
12 NC		
		
		
 Application	Cove light	Cove light
 Color	White	White
 Material	Synthetics	Synthetics
 Lamp base & wattage	LED Max 6W included 3000K warm white light, 4000K cool white light	LED Max 6W included 3000K warm white light, 4000K cool white light
 Dimensions (L X W X H) mm	1000 X 8 X 3	1000 X 8 X 3
 Extra Feature	Driver included	-
 Price (Baht)	1,400	600

myLiving - Linea










COMMERCIAL CODE	30731, 30732	30735, 30736
12 NC		
		
 Application	Cove light	Cove light
 Color	White	White
 Material	Synthetics	Synthetics
 Lamp base & wattage	LED Max 60W included 3000K warm white light, 4000K cool white light	LED Max 12W included 3000K warm white light, 4000K cool white light
 Dimensions (L X W X H) mm	5000 X 10 X 3	1000 X 10 X 3
 Extra Feature	Driver included	Driver included
 Price (Baht)	6,000	2,400

COMMERCIAL CODE	30739, 30740
12 NC	
	
 Application	Cove light
 Color	White
 Material	Synthetics
 Lamp base & wattage	LED Max 12W included 3000K warm white light, 4000K cool white light
 Dimensions (L X W X H) mm	1000 X 10 X 3
 Extra Feature	-
 Price (Baht)	1,200



myLiving - LivingColors



COMMERCIAL CODE	70999/60 Iris	70999/30 Iris
12 NC		
		
 Application	Table light	Table light
 Color	Clear	Black
 Material	Synthetics	Synthetics
 Lamp base & wattage	LED 11W included	LED 11W included
 Dimensions (L X W X H) mm	185 X 188 X 185	185 X 188 X 185
 Extra Feature	Remote control included	Remote control included
 Price (Baht)	9,600	9,600

myLiving - Accents

COMMERCIAL CODE	31007/31	31009/31
12 NC		
		
 Application	Candle light	Candle light
 Color	White	White
 Material	Synthetics	Synthetics
 Lamp base & wattage	LED 2 X 0.06W included	LED 0.06W X 8 included
 Dimensions (L X W X H) mm	86 X 86 X 98	76 X 76 X 153
 Extra Feature	Cool to touch, blow to on/off	Cool to touch
 Price (Baht)	500	500

myLiving - Accents

COMMERCIAL CODE	31010/31	69151/60
12 NC		
		
Application	Candle light	Wine cooler
Color	White	Clear
Material	Synthetics	Synthetics
Lamp base & wattage	RGB LED 0.18W X 1 included	RGB LED 0.18W X 8, White LED 0.09W X 6 included
Dimensions (L X W X H) mm	77 X 77 X 95	196 X 160 X 250
Extra Feature	Color changeable, tilt to on/off	Color changeable
Price (Baht)	500	7,600

COMMERCIAL CODE	69126/60	69144/31
12 NC		
		
Application	Tea lights	Candle light
Color	Clear	Clear
Material	Glass	Glass
Lamp base & wattage	LED 0.12W X 6 included	LED 0.067W X 2 included
Dimensions (L X W X H) mm	175 X 124 X 60 Cup 55 X 70	73 X 73 X 80 Cup 73 X 80
Extra Feature	Tilt to on/off, induction charger	-
Price (Baht)	4,500	250





HERITAGE *Refined*

I like my lighting to have a **warm glow** to create a sense of **belonging** and **nostalgia**.














myLiving





myGarden



myLiving

COMMERCIAL CODE	36408/43	36396/43
12 NC		
		
 Application	Centerpiece	Centerpiece
 Color	Brown brush	Brown brush
 Material	Metal, fabric	Metal, fabric
 Lamp base & wattage	Tornado E27, 24W X 12 not included	Tornado E27, 24W X 5 not included
 Dimensions (L X W X H) mm	1000 X 1000 X 2730	591 X 591 X 1774
 Extra Feature	Adjustable height, built-in VariLume technology	Adjustable height
 Price (Baht)	39,700	15,600

COMMERCIAL CODE	36378/43	36403/43
12 NC		
		
 Application	Centerpiece	Wall light
 Color	Brown brush	Brown brush
 Material	Metal, fabric	Metal, fabric
 Lamp base & wattage	Tornado E27, 24W X 6 not included	Tornado E27, 24W not included
 Dimensions (L X W X H) mm	600 X 600 X 574	184 X 264 X 311
 Extra Feature	Built-in VariLume technology	-
 Price (Baht)	12,300	2,900

myLiving

COMMERCIAL CODE	36362/43	36369/43
12 NC		
		
Application	Centerpiece	Centerpiece
Color	Brown	Brown
Material	Metal, glass	Metal, glass
Lamp base & wattage	Tornado E27, 24W X 8 not included	Tornado E27, 24W X 12 not included
Dimensions (L X W X H) mm	880 X 880 X 485	880 X 880 X 2650
Extra Feature	Built-in VariLume technology	Adjustable height, built-in VariLume technology
Price (Baht)	20,800	33,000

COMMERCIAL CODE	36366/43	60079/43(QPG326)
12 NC		
		
Application	Wall light	Centerpiece
Color	Brown	Brown brushed
Material	Metal, glass	Glass, metal
Lamp base & wattage	Tornado E27, 24W not included	Tornado E27, 24W X 8 not included
Dimensions (L X W X H) mm	200 X 208 X 230	800 X 800 X 1137
Extra Feature	-	Adjustable height
Price (Baht)	2,000	15,500

myLiving

COMMERCIAL CODE

12 NC

36491/43(QPG326)

36490/43(QPG325)



Application

Centerpiece

Suspension light

Color

Brown brushed

Brown brushed

Material

Glass, metal

Glass, metal

Lamp base & wattage

Tornado E14, 12W X 5 not included

Tornado E27, 24W not included

Dimensions (L X W X H) mm

650 X 650 X 1155

400 X 400 X 1300

Extra Feature

Adjustable height

Adjustable height

Price (Baht)

8,900

8,900

COMMERCIAL CODE

12 NC

36492/43(QWG331)

36494/43(QDG312)



Application

Wall light

Table light

Color

Brown brushed

Brown brushed

Material

Glass, metal

Glass, metal

Lamp base & wattage

Tornado E14, 12W not included

Tornado E14, 12W not included

Dimensions (L X W X H) mm

180 X 245 X 210

180 X 215 X 445

Extra Feature

-










On-line switch










Price (Baht)

1,500










2,200

myLiving










COMMERCIAL CODE	37713/06	37716/06
12 NC		
		
 Application	Centerpiece	Centerpiece
 Color	Bronze	Bronze
 Material	Alabaster glass, metal	Alabaster glass, metal
 Lamp base & wattage	Ambiance E27, 8W X 8 not included	Ambiance E27, 8W X 5 not included
 Dimensions (L X W X H) mm	815 X 815 X 350	585 X 585 X 910
 Extra Feature	-	Adjustable height
 Price (Baht)	5,100	6,300

COMMERCIAL CODE	36507/43(QWG330)	33226/30(QWG322)
12 NC		
		
 Application	Wall light	Wall light
 Color	Brown brushed	White
 Material	Fabric, metal	Sand blasted glass, metal clips
 Lamp base & wattage	Tornado E14, 12W X 2 not included	Tornado E27, 20W not included
 Dimensions (L X W X H) mm	305 X 200 X 270	254 X 89 X 264
 Extra Feature	-	-
 Price (Baht)	2,000	700



myLiving



COMMERCIAL CODE	33094/43(QWG325)	30919/43 Cluster
12 NC		
		
 Application	Wall light	Centerpiece
 Color	Brown brushed	Brown
 Material	Spray painted and sand blasted glass, synthetics	Metal, glass
 Lamp base & wattage	Tornado E27, 24W not included	E27, CFLi 15W X 8 not included
 Dimensions (L X W X H) mm	300 X 90 X 165	800 X 800 X 500
 Extra Feature		Built-in VariLume technology, adjustable light direction
 Price (Baht)	-	12,000
	900	

myGarden










COMMERCIAL CODE	15251/42	15252/42
12 NC		
		
 Application	Wall light	Post light
 Color	Black with gold brushed	Black with gold brushed
 Material	Glass, metal	Glass, metal
 Lamp base & wattage	Tornado E27, 24W not included	Tornado E27, 24W not included
 Dimensions (L X W X H) mm	170 X 204 X 286	170 X 170 X 375
 Extra Feature	Water resistant IP44 rating	Water resistant IP44 rating
 Price (Baht)	1,800	1,800










myGarden

COMMERCIAL CODE	15280/54	15282/54
12 NC		
		
Application	Wall light	Post light
Color	Black	Black
Material	Synthetics, metal	Synthetics, metal
Lamp base & wattage	Tornado E27, 24W not included	Tornado E27, 24W not included
Dimensions (L X W X H) mm	140 X 197 X 235	153 X 153 X 471
Extra Feature	Water resistant IP44 rating	Water resistant IP44 rating
Price (Baht)	3,100	3,900










COMMERCIAL CODE	15283/54	15261/42
12 NC		
		
Application	Garden light	Wall light
Color	Black	Black brushed
Material	Synthetics, metal	Synthetics, metal
Lamp base & wattage	Tornado E27, 24W not included	Essential E27, 23W not included
Dimensions (L X W X H) mm	153 X 153 X 1041	160 X 246 X 309
Extra Feature	Water resistant IP44 rating	Water resistant IP44 rating
Price (Baht)	5,600	1,600










myGarden

COMMERCIAL CODE	17157/54	01465/31
12 NC		
		
 Application	Wall light	Wall light
 Color	Black	White
 Material	Aluminum, glass	Aluminum, synthetics
 Lamp base & wattage	Genie E27, 11W not included	Essential E27, 18W not included
 Dimensions (L X W X H) mm	76 X 128 X 518	185 X 105 X 260
 Extra Feature	Water resistant IP44 rating	Water resistant IP44 rating
 Price (Baht)	2,600	600

COMMERCIAL CODE	01465/30	17131/42
12 NC		
		
 Application	Wall light	Wall light
 Color	Black	Black, gold brushing
 Material	Aluminum, synthetics	Aluminum
 Lamp base & wattage	Essential E27, 18W not included	Essential E27, 18W not included
 Dimensions (L X W X H) mm	185 X 105 X 260	230 X 92 X 260
 Extra Feature	Water resistant IP44 rating	Water resistant IP44 rating
 Price (Baht)	600	1,400

myGarden

COMMERCIAL CODE	17183/86	17118/30
12 NC		
		
 Application	Wall light	Ceiling / Wall light
 Color	Rust	Black
 Material	Synthetics, steel	Aluminum, glass
 Lamp base & wattage	Genie E27, 24W not included	Tornado E27, 12W not included
 Dimensions (L X W X H) mm	161 X 132 X 213	252 X 96 X 252
 Extra Feature	Water resistant IP44 rating	Water resistant IP44 rating
 Price (Baht)	1,500	2,000

COMMERCIAL CODE	71165/30	16026/30
12 NC		
		
 Application	Wall light	Post light
 Color	Black	Black
 Material	Glass, synthetics	Glass, synthetics
 Lamp base & wattage	Tornado E27, 12W not included	Tornado E27, 12W not included
 Dimensions (L X W X H) mm	145 X 230 X 205	135 X 135 X 940
 Extra Feature	Water resistant IP44 rating	Water resistant IP44 rating, adjustable height
 Price (Baht)	1,600	1,900





Timeless *Classics*

I want my home lighting to be **unique, exclusive** and extremely **luxurious**. I'm looking for something with a **rich** character that conveys the drama and the **sumptuousness** of modern **glamour**.



myLiving


myLiving

COMMERCIAL CODE

12 NC

30900/21

30899/21




Application	Ceiling light	Suspension light
Color	Metalic black	Metalic black
Material	Glass crystal	Glass, crystal
Lamp base & wattage	Eco Halogen E14, 42W X 6 not included	Eco Halogen E14, 42W X 4 not included
Dimensions (L X W X H) mm	500 X 500 X 220	400 X 400 X 1750
Extra Feature	-	Adjustable height
Price (Baht)	22,300	13,400

myLiving

COMMERCIAL CODE

12 NC

30690/31



Centerpiece

White

Metal, crystal

Eco Halogen E14, 42W X 3 not included

666 X 666 X 1500

Adjustable height

20,000

30699/30



Centerpiece

Black

Metal, crystal

Eco Halogen E14, 42W X 3 not included

623 X 623 X 1500

Adjustable height

20,000

Application

Color

Material

Lamp base & wattage

Dimensions (L X W X H) mm

Extra Feature

Price (Baht)

COMMERCIAL CODE

12 NC

36680/31



Centerpiece

White

Metal, fabric

Tornado E14, 12W X 5 not included

666 X 666 X 1780

Adjustable height, crystal ornamentation

13,600

36681/31



Centerpiece

White

Metal, fabric

Tornado E14, 12W X 8 not included

840 X 840 X 1780

Adjustable height, crystal ornamentation

18,500

Application

Color

Material

Lamp base & wattage

Dimensions (L X W X H) mm


Extra Feature

Price (Baht)

UTILITY COLLECTION



myBathroom





Light for your needs.

Light up your home with the Utility Collection from Philips! Designed to resist moisture and grease, our specialized lighting products will brighten up parts of your home that are most exposed to wet or oily conditions.


The my**Bathroom** range has special features to suit your needs. Some models are designed to resist moisture, while some models have a heater function for winter time.



myBathroom

I see my bathroom as a place to begin and end my day.

I like a **soft, waterproof lighting** with **premium materials** to brighten it.



The right light for the right area

At Philips, we work with a simple IP* Table to help you cross check whether the article of your choice is suitable for the area you have in mind.

Area 0 – Bathtub

Philips does not recommend any light fixtures within the bathtub.

Area 1 – General area

For the spaces immediately above the bathtub, light fixtures must be at least IP65.

Area 2 – Under the cabinet

General lighting from luminaries installed on the ceiling can provide the illumination needed here.

Safety note: This area normally stretches to 0.6m outside the bath/shower. Since there is a risk of water accidentally splashing on the fitting, an IP rating of at least IPX4 is required.

Area 3 – Inside the drawer

This area requires bright and shadow free light for task orientated activities like shaving or make-up application.



















Lights on both sides of the mirror will provide you with bright and even light.

Indirect or diffused lighting will complement the general lighting requirement in this area.

Safety note: This area stretches beyond zone 2. As long as there is no chance of the fixture being splashed with water or steam, an IPX1 rating is sufficient. A higher IP rating can always be used for added safety precaution.










* IP (Ingress Protection) – refers to the sealing effectiveness of electric equipment against the intrusion of foreign bodies and in the case of Philips AquaFit, against moisture.










myBathroom - Modern Living

COMMERCIAL CODE	34208/11	34213/11
12 NC		
	 <p>LED AREA 2 AREA 3</p> <p>Dimensions: 46 (width), 136 (height), 140 (depth)</p>	 <p>LED AREA 2 AREA 3</p> <p>Dimensions: 224 (width), 109 (height)</p>
 Application	Wall light	Wall light
 Color	Chrome	Chrome
 Material	Metal, glass	Metal
 Lamp base & wattage	Power LED 7.5W included	Power LED 7.5W X 2 included
 Dimensions (L X W X H) mm	101 X 140 X 136	224 X 114 X 109
 Extra Feature	Water resistant IP44 rating, tunable white, dimmable*	Water resistant IP44 rating, dimmable*
 Price (Baht)	7,700	10,700
COMMERCIAL CODE	34212/11	32044/11
12 NC		
	 <p>LED AREA 2 AREA 3</p> <p>Dimensions: 89 (width), 130 (height)</p>	 <p>LED AREA 3</p> <p>Dimensions: 100 (width), 167 (height), 196 (depth)</p>
 Application	Wall light	Wall light
 Color	Chrome	Chrome
 Material	Metal	Metal, glass
 Lamp base & wattage	Power LED 7.5W included	Tornado E14, 12W not included
 Dimensions (L X W X H) mm	89 X 114 X 130	196 X 100 X 167
 Extra Feature	Water resistant IP44 rating, dimmable*	Water resistant IP21 rating
 Price (Baht)	5,800	700










*Dimmable / dimtone with separately available commercial trailing-edge dimmers.










myBathroom - Contemporary Chic

COMMERCIAL CODE	32029/11	32030/11
12 NC		
		
 Application	Wall light	Wall light
 Color	Chrome	Chrome
 Material	Metal, glass	Metal, glass
 Lamp base & wattage	Tornado E14, 12W not included	Tornado E14, 12W X 2 not included
 Dimensions (L X W X H) mm	190 X 100 X 165	190 X 320 X 165
 Extra Feature	Water resistant IP21 rating	Water resistant IP21 rating
 Price (Baht)	800	1,500





COMMERCIAL CODE	32032/11	32033/11
12 NC		
		
 Application	Wall light	Wall light
 Color	Chrome	Chrome
 Material	Metal, glass	Metal, glass
 Lamp base & wattage	Tornado E14, 12W not included	Tornado E14, 12W X 2 not included
 Dimensions (L X W X H) mm	218 X 100 X 200	218 X 320 X 200
 Extra Feature	Water resistant IP21 rating	Water resistant IP21 rating
 Price (Baht)	800	1,500

myBathroom - Contemporary Chic

COMMERCIAL CODE	32035/11	30326/11
12 NC		
		
 Application	Wall light	Wall light
 Color	Chrome	Chrome
 Material	Metal, glass	Metal, glass
 Lamp base & wattage	Tornado E14, 12W not included	Tornado E14, 12W X 2 not included
 Dimensions (L X W X H) mm	241 X 100 X 247	240 X 320 X 185
 Extra Feature	Water resistant IP21 rating	Water resistant IP21 rating
 Price (Baht)	800	1,500

COMMERCIAL CODE	32068/31(QCZ808)	32064/31(QCZ805)
12 NC		
		
 Application	Ceiling light	Ceiling light
 Color	White	White
 Material	Handmade 3 layered glass	Handmade 3 layered glass
 Lamp base & wattage	Tornado E27, 24W X 2 not included	Tornado E27, 24W not included
 Dimensions (L X W X H) mm	400 X 400 X 114	260 X 260 X 110
 Extra Feature	Water resistant IP44 rating	Water resistant IP44 rating
 Price (Baht)	3,200	1,600

myBathroom - Contemporary Chic

COMMERCIAL CODE	32005/31(QCZ800)	32067/31(QCZ806)
12 NC		
		
Application	Ceiling light	Ceiling light
Color	White	White
Material	Handmade 3 layered glass	Handmade 3 layered glass
Lamp base & wattage	Tornado E27, 24W not included	Tornado E27, 24W not included
Dimensions (L X W X H) mm	260 X 260 X 120	320 X 320 X 110
Extra Feature	Water resistant IP44 rating	Water resistant IP44 rating
Price (Baht)	1,600	1,500
COMMERCIAL CODE	32010/11(QCZ802)	34006(QWZ802)
12 NC		
		
Application	Ceiling / Wall light	Wall light
Color	Chrome	Chrome
Material	Glass, steel	Handmade 3 layered glass
Lamp base & wattage	Tornado E27, 24W not included	Candle E14, 40W X 2 not included
Dimensions (L X W X H) mm	315 X 315 X 100	310 X 105 X 80
Extra Feature	Water resistant IP44 rating	Water resistant IP44 rating, double wire entry
Price (Baht)	1,200	1,200



MAINSTREAM COLLECTION



MAINSTREAM *Ceiling*



MAINSTREAM *Spot*



MAINSTREAM *Wall*



MAINSTREAM *Desk*



Light for every room.

You're proud of your home, and you want to present it in the best light possible. The Philips Mainstream Collection presents a broad range of practical lighting products that are reliable, sensible, and performance driven.

Philips delivers superior value for money by using advanced lighting technology for everyday lighting solutions. Choose from a wide range of lighting products across different applications with features to suit various needs.





MAINSTREAM Ceiling

My ceiling light should not only be **bright**, but also **warm** and **welcoming**, making each room a **comfortable** place to be in.

Different Lights, different purpose

Value

- Varilume Technology for easy light level control*
- Instant high frequency electronic operation
- Durable, yellowing & chip resistant diffuser
- Energy saving, Hybrid or LED light source
- Aesthetic designs
- Ideal for bedrooms & living rooms

Essential

- Instant, high frequency electronic operation
- Energy saving or LED light source*
- Durable, yellowing & chip resistant diffuser

*On select models










Ceiling - Value

COMMERCIAL CODE	30346/31	30347/17
12 NC		







Application	Ceiling light	Ceiling light
Color	Dark brown & light brown	Nickel
Material	Acrylic cover, metal base, wooden frame	Acrylic cover, metal base, metal frame
Lamp base & wattage	Gz10q, TL5C, 32W included 6500k cool daylight	Gz10q, TL5C, 32W included 6500k cool daylight
Dimensions (L X W X H) mm	394 X 394 X 97	394 X 394 X 97
Extra Feature	-	-
Price (Baht)	2,000	2,600

Ceiling - Value


COMMERCIAL CODE	30344/31	30345/31
12 NC		
		
	402	402
 Application	Ceiling light	Ceiling light
 Color	Dark brown & light brown	Nickel
 Material	Acrylic cover, metal base, wooden frame	Acrylic cover, metal base, metal frame
 Lamp base & wattage	Gz10q,TL5C, 32W included 6500k cool daylight	Gz10q,TL5C, 32W included 6500k cool daylight
 Dimensions (L X W X H) mm	402 X 402 X 97	402 X 402 X 97
 Extra Feature	-	-
 Price (Baht)	2,000	2,600

Ceiling - Essential

COMMERCIAL CODE	31816/61, 31816/31	33362/61, 33362/31
12 NC		
	 	 
	380	320
 Application	Ceiling light	Ceiling light
 Color	White	White
 Material	Synthetics	Synthetics, metal
 Lamp base & wattage	LED 20W 2700K/ 6500K included	LED 16W 2700K/6500K included
 Dimensions (L X W X H) mm	380 X 380 X 68	320 X 320 X 78
 Extra Feature	Wide Voltage	-
 Price (Baht)	2,900	2,000










Ceiling - *Essential*

COMMERCIAL CODE	30304/31	69624/31
12 NC		
		
	350	250
 Application	Ceiling light	Ceiling light
 Color	White	White
 Material	Synthetics, metal	Synthetics, metal
 Lamp base & wattage	Gz10q,TL5C, 32W included 6500k cool daylight	Gz10q,TL5C, 22W included 6500k cool daylight
 Dimensions (L X W X H) mm	350 X 350 X 94	250 X 250 X 82
 Extra Feature	-	-
 Price (Baht)	1,350	600

COMMERCIAL CODE	30276/31	30298/31
12 NC		
		
	350	350
 Application	Ceiling light	Ceiling light
 Color	White	White
 Material	Synthetics, metal	Synthetics, metal
 Lamp base & wattage	Gz10q,TL5C, 32W included 6500k cool daylight	Gz10q,TL5C, 32W included 6500k cool daylight
 Dimensions (L X W X H) mm	350 X 350 X 99	350 X 350 X 94
 Extra Feature	-	-
 Price (Baht)	1,350	1,350

Ceiling - *Essential*

COMMERCIAL CODE	32898/31	32899/31
12 NC		
		
 Application	Ceiling light	Ceiling light
 Color	White	White
 Material	Synthetics	Synthetics
 Lamp base & wattage	Essential E27, 15W X 4 not included	Essential E27, 15W X 3 not included
 Dimensions (L X W X H) mm	360 X 360 X 120	360 X 360 X 120
 Extra Feature	-	-
 Price (Baht)	900	900

COMMERCIAL CODE	30348/31	30352/31
12 NC		
		
 Application	Ceiling light	Ceiling light
 Color	Gold	Gold
 Material	Synthetics	Synthetics
 Lamp base & wattage	Essential E27, 15W X 3 not included	Essential E27, 15W X 3 not included
 Dimensions (L X W X H) mm	360 X 360 X 120	360 X 360 X 120
 Extra Feature	-	-
 Price (Baht)	900	900

Ceiling - *Essential*

COMMERCIAL CODE	30353/31	32896/31
12 NC		



360



360

Application	Ceiling light	Ceiling light
Color	White	Silver
Material	Synthetics	Synthetics
Lamp base & wattage	Essential E27, 15W X 3 not included	Essential E27, 15W X 3 not included
Dimensions (L X W X H) mm	360 X 360 X 120	360 X 360 X 95
Extra Feature	-	-
Price (Baht)	900	900

COMMERCIAL CODE	30358/31
12 NC	



360

Application	Ceiling light
Color	White
Material	Synthetics
Lamp base & wattage	Essential E27, 15W X 3 not included
Dimensions (L X W X H) mm	360 X 360 X 120
Extra Feature	-
Price (Baht)	900





MAINSTREAM Spot

I want an elegant and **easy-to clean** light to spark my heart with a **vibrant** environment **Energy efficiency** and **reliability** is am must.

Illuminate your favorite spot

Value






















- Toughened glass or faceted cover*
- Adjustable heads & light level*
- Average LED system lifetime 20,000 hours
- Energy Saving or LED* light source; High Lumen package
- Aesthetic designs
- Ideal for bedrooms & living rooms

Essential












- Average LED system lifetime about 15,000 hours
- Energy saving or LED light source*
- Durable, yellowing & chip resistant diffuser

*On select models

Spot - Value







COMMERCIAL CODE	45050/31, 45051/31	45060/31, 45061/31
12 NC		
		
		
 Application	Down light	Down light
 Color	White	White
 Material	Aluminium	Aluminium
 Lamp base & wattage	LED 3W included 2700K / 4000K	LED 5W included 2700K / 4000K
 Dimensions (L X W X H) mm	84 X 84 X 44	84 X 84 X 44
 Extra Feature	Adjustable head	Adjustable head
 Price (Baht)	1,000	1,200
COMMERCIAL CODE	45070/31, 45071/31	59796/48
12 NC		
		
		
 Application	Down light	Down light
 Color	White	Nickel satin
 Material	Aluminium	Glass, metal
 Lamp base & wattage	LED 7W included 2700K / 4000K	Essential E27, 14W X 2 not included
 Dimensions (L X W X H) mm	108 X 108 X 48	221 X 220 X 103
 Extra Feature	Adjustable head	With toughened glass cover
 Price (Baht)	1,500	650

Spot - Value












COMMERCIAL CODE	59793/31	59793/48
12 NC		
		
		
 Application	Down light	Down light
 Color	White	Nickel satin
 Material	Glass, metal	Glass, metal
 Lamp base & wattage	Genie E27, 14W X 2 not included	Genie E27, 14W X 2 not included
 Dimensions (L X W X H) mm	180 X 180 X 103	180 X 180 X 103
 Extra Feature	With toughened glass cover	With toughened glass cover
 Price (Baht)	600	600

COMMERCIAL CODE	59785/48	59790/48 FBG303
12 NC		
		
		
 Application	Down light	Down light
 Color	Nickel satin	Nickel satin
 Material	Glass, metal	Glass, metal
 Lamp base & wattage	Genie E27, 14W not included	Genie E27, 14W not included
 Dimensions (L X W X H) mm	145 X 145 X 130	190 X 190 X 132
 Extra Feature	With toughened glass cover	With toughened glass cover
 Price (Baht)	750	800














Spot - Value











COMMERCIAL CODE	59786/48 FBG304	59779/48
12 NC		
		
 Application	Down light	Down light
 Color	Nickel satin	Nickel satin
 Material	Glass, metal	Glass, metal
 Lamp base & wattage	Genie E27, 14W not included	Genie E27, 14W x 2 not included
 Dimensions (L X W X H) mm	120 X 120 X 82	162 X 162 X 82
 Extra Feature	With toughened glass cover	With toughened glass cover
 Price (Baht)	750	850

Spot - Essential

COMMERCIAL CODE	66065/ 66069	66053/31, 66057/31
12 NC		
	 	 
 Application	Down light	Down light
 Color	White	White
 Material	Aluminum, synthetics	Aluminum, synthetics
 Lamp base & wattage	LED 10W, 2700K, 6500K included	LED 10W, 2700K/6500K included
 Dimensions (L X W X H) mm	140 X 140 X 80	140 X 140 X 80
 Extra Feature	Integrated driver, cut out commonality	Integrated driver, cut out commonality
 Price (Baht)	2,200	2,200

Spot - *Essential*

COMMERCIAL CODE	77113/27, 77113/65	77114/27, 77114/65
12 NC		
	   <p>142</p>	   <p>192</p>
 Application	Down light	Down light
 Color	White	White
 Material	Syntheticiecs	Syntheticiecs
 Lamp base & wattage	LED 6W included 2700K/6500K	LED 7.5W included 2700K/6500K
 Dimensions (L X W X H) mm	142 X 142 X 55	192 X 192 X 72
 Extra Feature	-	-
 Price (Baht)	1,000	1,200

COMMERCIAL CODE	77071/27, 77071/65
12 NC	
	   <p>185</p>
 Application	Down light
 Color	White
 Material	Syntheticiecs
 Lamp base & wattage	LED 11W included 2700K/6500K
 Dimensions (L X W X H) mm	185 X 185 X 22
 Extra Feature	-
 Price (Baht)	2,200



MAINSTREAM Wall

I like my home to be **efficient**, I want a **versatile** yet **affordable** lighting to **brighten** my home, making it more cheerful.

Efficacy with subtlety

Essential

- Instant, high frequency electronic operation
- Energy saving light source
- Basic wall lights
- Ideal for corridors & utility areas

*On select models

Wall - Essential

COMMERCIAL CODE	45032/31	45031/31
12 NC		



Application	Wall light	Wall light
Color	White	White
Material	Synthetics	Synthetics
Lamp base & wattage	E27, 1X 23W max, not included (not suitable for use with GLS)	E27, 1X 14W max, not included (not suitable for use with GLS)
Dimensions (L X W X H) mm	91 X 212 X 172	87 X 94 X 260
Extra Feature	-	-
Price (Baht)	350	350



MAINSTREAM *Desk*

I love technology to make my life **easy**. And for me, light should be **practical** and **user-friendly**.

Superior Eyecare for a better tomorrow

Eyecare

- Limited Glare Control
- Wide choice of trendy designs

*On select models

Eyecare Plus

Eyeday

Superior Comfort for a better today

Comfort Pro










- Anti-glare
- Auto Brightness Optimization*
- Indirect/asymmetric directional beam
- Continuous Dimming control*


Comfort

- Limited Glare Control
- Wide choice of practical designs

*On select models

Desk - EyeCare



COMMERCIAL CODE	71658/38 Scope	71658/31 Scope
12 NC		
		
 Application	Desk light	Desk light
 Color	Blue	White
 Material	Metal, synthetics	Metal, synthetics
 Lamp base & wattage	3.6W LED included 6500K cool daylight	3.6W LED included 6500K cool daylight
 Dimensions (L X W X H) mm	332 X 160 X 382	332 X 160 X 382
 Extra Feature	Special honeycomb optional lens	Special honeycomb optional lens
 Price (Baht)	1,990	1,990

COMMERCIAL CODE	69202/35 (FDS201) Andrew	69202/32 (FDS201) Andrew
12 NC		
		
 Application	Desk light	Desk light
 Color	Blue	Red
 Material	Steel, synthetics	Steel, synthetics
 Lamp base & wattage	Genie E27, 11W not included	Genie E27, 11W not included
 Dimensions (L X W X H) mm	260 X 140 X 360	260 X 140 X 360
 Extra Feature	Special honeycomb optional lens	-
 Price (Baht)	570	570

Desk - EyeCare

COMMERCIAL CODE	69204/35 Billy	69204/33 Billy
12 NC		
		
Application	Desk light	Desk light
Color	Blue	Green
Material	Steel, synthetics	Steel, synthetics
Lamp base & wattage	Genie E27, 11W included 6500K cool daylight	Genie E27, 11W included 6500K cool daylight
Dimensions (L X W X H) mm	280 X 120 X 360	280 X 120 X 360
Extra Feature	-	-
Price (Baht)	490	490

Desk - EyeCare Plus

COMMERCIAL CODE	71663/35 Spade Plus	71663/96 Spade Plus
12 NC		
		
Application	Desk light	Desk light
Color	Blue	Purple
Material	Aluminum, synthetics	Aluminum, synthetics
Lamp base & wattage	LED 6W included 6500K cool daylight	LED 6W included 6500K cool daylight
Dimensions (L X W X H) mm	120 X 362 X 406	120 X 362 X 406
Extra Feature	4-steps dimming, USB charger, honeycomb lens technology	4-steps dimming, USB charger, honeycomb lens technology
Price (Baht)	2,800	2,800

Desk - **Eyeday**

COMMERCIAL CODE

12 NC

70048/32 Carl

70048/34 Carl



Application	Desk light
Color	Red
Material	Aluminium, synthetics
Lamp base & wattage	CFL-i E27, 11W included 6500K cool daylight
Dimensions (L X W X H) mm	320 X 142 X 355
Extra Feature	Flexible rubberized gooseneck
Price (Baht)	500

Application	Desk light
Color	Red
Material	Aluminium, synthetics
Lamp base & wattage	CFL-i E27, 11W included 6500K cool daylight
Dimensions (L X W X H) mm	320 X 142 X 355
Extra Feature	Flexible rubberized gooseneck
Price (Baht)	500

Application	Desk light
Color	Yellow
Material	Aluminium, synthetics
Lamp base & wattage	CFL-i E27, 11W included 6500K cool daylight
Dimensions (L X W X H) mm	320 X 142 X 355
Extra Feature	Flexible rubberized gooseneck
Price (Baht)	500

Desk - **Comfort Pro**

COMMERCIAL CODE

12 NC










69195/30 iCareV10.1












Application	Desk light
Color	Black
Material	Aluminum, synthetics
Lamp base & wattage	LED 5W included 6500K cool daylight
Dimensions (L X W X H) mm	200 X 135 X 405
Extra Feature	Slide dimmer, USB charger
Price (Baht)	5,200

Application	Desk light
Color	Black
Material	Aluminum, synthetics
Lamp base & wattage	LED 5W included 6500K cool daylight
Dimensions (L X W X H) mm	200 X 135 X 405
Extra Feature	Slide dimmer, USB charger
Price (Baht)	5,200

Desk - **Comfort**

COMMERCIAL CODE	70049/35 Bob	70049/31 Bob
12 NC		
		
 Application	Desk light	Desk light
 Color	Blue	White
 Material	Aluminium, synthetics	Aluminium, synthetics
 Lamp base & wattage	CFL-i 11W included 6500K cool daylight	CFL-i 11W included 6500K cool daylight
 Dimensions (L X W X H) mm	330 X 142 X 375	330 X 142 X 375
 Extra Feature	Flexible rubberized gooseneck	Flexible rubberized gooseneck
 Price (Baht)	550	550

COMMERCIAL CODE	70049/31 Packet	70049/93 Packet
12 NC		
		
 Application	Desk light	Desk light
 Color	White	Anthracite
 Material	Synthetics	Synthetics
 Lamp base & wattage	3W LED included 6500K cool daylight	3W LED included 6500K cool daylight
 Dimensions (L X W X H) mm	274 X 100 X 372	274 X 100 X 372
 Extra Feature	Flexible rubberized gooseneck	Flexible rubberized gooseneck
 Price (Baht)	1,390	1,390

PHILIPS



โชว์รูมโคมไฟตกแต่งฟิลิปส์ โฮม ไกลด์จิ่ง

สาขานุญถาวร รัชดา

อาคาร Boonthavorn Lighting Center ชั้น 2
243 ถ.รัชดาภิเษก แขวงดินแดง เขตดินแดง
กรุงเทพฯ 10310
โทร. 02 275 0029

สาขานุญถาวร เกษตร - นวมินทร์

อาคาร Life Style ชั้น 2
999, 999/1 ถ.ประเสริฐอนุกิจ 33
แขวงคลองกุ่ม เขตบึงกุ่ม
กรุงเทพฯ 10240
โทร. 02 791 2777

สาขานุญถาวร พระราม 2

82/4 หมู่ 1 ถ.พระรามที่ 2 ต.บางน้ำจืด
อ.เมือง จ.สมุทรสาคร 74000
โทร. 02 451 4471-2

สาขาสุภาภิบาล 3 (เทียนทอง อีลิคทริก พลัส)

980 ถ.รามคำแหง แขวงหัวหมาก
เขตบางกะปิ กรุงเทพฯ 10240
โทร. 02 370 0555
www.thianthong.com

สาขาราชพฤกษ์ (BRYANT DECOR)

292 ถ.ราชพฤกษ์ แขวงบางหว้า
เขตภาษีเจริญ กรุงเทพฯ 10160
โทร. 02 457 6906-8

สาขานุญถาวร หัวหิน

อาคาร Lighting Gallery ชั้น 2
4/48 หมู่บ้านบ่อฝ้าย ต.หัวหิน อ.หัวหิน
จ.ประจวบคีรีขันธ์ 77110
โทร. 032 522 555

สาขานุญถาวร เชียงใหม่

246 หมู่ 2 ต.หนองพึ่ง อ.สารภี
จ.เชียงใหม่ 50140
โทร. 053 105 096-99

สาขานุญถาวร พัทยา

88/8 หมู่ 9 ถ.สุขุมวิท ต.หนองปรือ
อ.บางละมุง จ.ชลบุรี 20150
โทร. 038 052 222

สาขาพัทยา (DECCO)

88/8 หมู่ 11 ถ.สุขุมวิท ต.หนองปรือ
อ.บางละมุง จ.ชลบุรี 20150
โทร. 038 231 621-2

พบกับเร็วๆ นี้ที่

Indexlivingmall



กลุ่มธุรกิจไฟฟ้าและอุปกรณ์แสงสว่าง
บริษัท ฟิลิปส์อิเล็กทรอนิกส์ (ประเทศไทย) จำกัด
1768 ชั้น 28 อาคารไทยซัมมิททาวเวอร์ ถนนเพชรบุรีตัดใหม่
แขวงบางกะปิ เขตห้วยขวาง กรุงเทพฯ 10310 โทร. 0-2614-3333
ศูนย์ข้อมูลผู้บริโภคฟิลิปส์ โทร. 0-2268-8555
www.philips.co.th | www.facebook.com/PhilipsLightingThailand.com