

**PHILIPS**

Professional lighting

Office



# Brighten your business





## A work environment **to be proud of**

A world-class workplace inspires your team to deliver an equally world-class performance. With a thoughtfully planned design, lights can make spaces more conducive for everyone to read, think and work on their laptops without easily getting tired. Good lighting can also help a person relax and energize after long meetings, so time spent in the office can be optimally productive.

With the investments you are making, your office spaces should be as attractive, responsive and human-centric as possible. Our new lighting technologies are designed to adapt to your ever-changing needs and user habits, allowing the same space to be multi-functional yet elegant at the same time. This way, you get higher value and a better return on your investment. Most important of all, improving your workplace improves the well-being of your best assets: your people.



# illuminating

your business

# Better lights, better focus



# Built to **outperform**

From the reception to the boardroom, our professional range of LED lighting solutions are perfect to impress and inspire, besides offering the best lighting that falls at all the right places.

Combine the latest portfolio from the Philips LED lighting range with our lighting controls, and you can count on the benefits that will outperform your expectations.

1. A dramatic decrease in your energy use and utility bills
2. A better work environment that enhances your team's well-being and boosts productivity
3. A decrease in your company's carbon footprint, addressing sustainability for the long run
4. Revenue boost with higher occupancy rates and rental income
5. An enhanced brand image and company reputation as a result of an effective lighting upgrade

# Making every space work



# Overview

## of office

1

Reception and indoor public area



2

Breakout area



3

Open plan office



4

Corridors and circulation areas



5

Cell office



6

Meeting room and training room



7

Stairs



8

Restrooms



9

Cafeteria and pantry



10

Façade and exterior lighting




11

Carpark



12

Loading bay





First impressions count. Because your office reception is the first place your visitors see, it should always set the right tone and atmosphere to welcome your guests.

Whether it's an elegant and warm lobby, or a dynamic and inspiring entrance, lighting is key in creating an ambience that lets you greet your visitors in flexible and attractive ways. From dramatic, vibrant schemes that reflect your company's brand identity and colors, to a soft ambience that helps soothe the senses, we have the right solutions to complement all office interior styles.



SmartBright LED Troffer G2



Coreline LED Troffer G2



BasicBright LED Spot



GreenSpace LED Downlight G4



SmartBright LED Batten G2



SmartBright Luxline LED Batten



iColorCove QLX Powercore



eW Cove QLX Powercore

# Reception and indoor public area

Make the right first impression





# Breakout area

Relax and recharge

A good office environment allows its team to freely interact for a healthy exchange of creative ideas. Informal areas such as breakout rooms or pause-and-think zones should be comfortably lit so that users can relax and enjoy some quality discussions to improve their work life and well-being.

Because lighting can affect the way people feel, good quality light that's glare-free and at the right color temperature can calm tired eyes and busy minds. Adjustable lights can come in to allow dimmability, or tunability, while cove lighting can also help create a more relaxing and casual atmosphere here to encourage teams to take a short recharge, in order to push on and deliver their best.



BasicBright LED Spot



SmartBright LED Downlight G3



SmartBright Mini LED Dimmable Downlight G2



GreenSpace LED Downlight G4



Master LEDspot MV



eW Cove QLX Powercore

# Open plan office

Open to bright ideas

Open plan offices are free-flow work areas designed with the flexibility to serve multiple needs. The lights here should be optimal to ensure work efficiency, without being too bright or too dim. Our lights are designed to help your teams see better, feel better and work better. Individual controls can be worked in to create an intelligent office where each person can adjust the lights to best suit his or her needs.

Be it a task-focused office, or a creative studio, we have the right range of office luminaires, LED tubes and lamps to create a non-disruptive, well-balanced and conducive space benefiting your teams. Apart from quality lighting, advanced sensors can also be integrated to harvest daylight and to detect occupants, giving you a smarter office with up to 75% energy savings.



SmartBright LED Troffer G2



Coreline LED Troffer G2



PowerBalance LED Troffer G2



BasicBright LED Spot



Master LEDspot MV



SmartBright LED Downlight G3



GreenSpace LED Downlight G4



SmartBright LED Batten G2



Master LEDtube

# Corridors and circulation areas

Navigate in style

Corridors and passageways are transit zones that lead you from one space to another. While your teams may not linger here for a long time, everyone appreciates bright and safely-lit corridors for functional reasons. They also serve as areas where art pieces and posters can be placed to display internal communications. To save on electricity bills, automated sensors can be worked in to turn the lights on and off intelligently. Alternating practical meeting rooms lit in cool daylight with relaxed corridors lit in warm white will also enable room users to rest their eyes and catch a breather as they prepare to leave a busy space and step into the next for a meeting.



SmartBright LED Troffer G2



BasicBright LED Spot



Master LEDspot MV



SmartBright LED Downlight G3



GreenSpace LED Downlight G4



SmartBright LED Batten G2



Master LEDtube



# Cell office

Create quiet, cozy nooks



Employees use cell offices and quiet booths when they need more privacy to conduct meetings, have a conference call or simply to focus better on their projects. Even small spaces can enjoy optimal light levels with the right products worked into the ceilings.

With no glare, and no flicker, our luminaires can deliver light that is clear and yet easy on the eyes. Built-in sensors can ensure the lights go on and off automatically to help conserve energy, while dimming functions are useful in presentation sessions when projectors are on.



SmartBright LED Troffer G2



Coreline LED Troffer G2



PowerBalance LED Troffer G2



BasicBright LED Spot



SmartBright Mini LED Dimmable Downlight G2



GreenSpace LED Downlight G4

# Meeting room and training room

In the mood for real business

When it's time to get down to business, the right lighting is crucial to ensure we have the right focus and optimal productivity in the room. Whether it's for a short and straightforward meeting or a long brainstorming workshop, flexible controls should be there to allow light levels to be adjusted - to perk the team up or dimmed down when presentations are ongoing. Cove lighting can also be integrated to create softer hues to improve the overall ambience. You can even impress your guests by switching from one pre-set scene to another with just the touch of a button.



Coreline LED Troffer G2



PowerBalance LED Troffer G2



SmartBright Mini LED Dimmable Downlight G2



GreenSpace LED Downlight G4



iColorCove QLX Powercore



eW Cove QLX Powercore



Master LEDtube

# Stairs

Make it grand

Staircases can present an opportunity for dramatic lighting. High ceilings above staircases can be stylishly lit with grids of low-maintenance LED luminaires. Above functional stairwells, Master LEDtube can be affordably worked into the designs to ensure long-lasting brightness for maximum security, while offering energy savings and lower maintenance costs.



SmartBright LED Downlight G3



SmartBright Mini LED Dimmable Downlight G2



GreenSpace LED Downlight G4



BasicBright LED Spot



SmartBright LED Batten G2



SmartBright Luxline LED Batten



Master LEDtube

# Restrooms

Awash with clean, clear light

Modern restrooms are designed not just for your employees but also for visitors and guests. Good lighting can make or break this space. When the lights are too harsh, the interiors can seem cold and unflattering. Apart from IP-rated functional lights, we can infuse elegant spots and a mix of warm white and cool daylight color temperatures to create a more pleasant, relaxed space where users can comfortably refresh and recharge.



SmartBright LED Downlight G3



SmartBright Mini LED Dimmable Downlight G2



GreenSpace LED Downlight G4



BasicBright LED Spot



Master LEDspot MV

# Cafeteria and pantry

Light that's good enough to eat

In the same way that the kitchen is the heart of a home, your cafeteria or pantry deserves the best lighting because this is where your people take their much needed coffee breaks, socialize, have a quick meal and recharge. Island counters and breakfast bars can be beautifully lit with a combination of cove and spot lighting. Colored lights can also add interest to feature walls, provide branding opportunities or simply create an inspiring perk-me-up corner.



SmartBright LED Downlight G3



SmartBright Mini LED Dimmable Downlight G2



GreenSpace LED Downlight G4



BasicBright LED Spot



GreenPerform Waterproof



GreenUp Waterproof



iColorCove MX Powercore



eW Cove MX Powercore



# Exterior façade and indoor lobbies

Make a dramatic entrance

Say hello and make a bold statement with office façade and exterior lighting that's impressive, impactful and representative of your brand. For out of reach areas or lobbies with very high ceiling, turn these characteristics into a feature wall by applying colored lighting creatively. Our wide selection of weatherproof architectural and landscape lighting can create theatrical accents for both the outdoors and connecting them indoors. Available in colored hues, warm white and cool daylight, our wall washers and façade lighting are reliable, long-lasting and energy-efficient. Timers and programmable scene settings are also designed to ensure your office is always showcased in its full brilliance, from dusk to dawn.



ColorGraz  
MX4 Powercore



ColorReach  
Powercore gen2



ColorReach  
Compact Powercore



iColor Flex  
MX gen2



ColorFuse  
Powercore



eW Fuse  
Powercore

Reception and indoor public area



Cell office



Cafeteria and pantry



Breakout area



Meeting room and training room



Exterior façade and indoor lobbies



Open plan office



Stairs



Carpark



Corridors and circulation areas



Restrooms




Loading bay



# We've got you covered

As your lighting solutions partner, we aim to give you complete one-stop solutions that can maximize your investment. We can customize our solutions and professional services to meet your specifications, standards and budgets. What's more, we stay ahead of lighting trends to make your space as multi-functional and as future-proof as possible.



# Lighting the way forward





**Alshaya Office  
Cairo, Egypt**

As one of the most dynamic and successful retail franchise operators in the Middle East and increasingly internationally, Alshaya was ready to bring in some of the best customer experiences into their offices. Philips Lighting was involved in the lighting design to recommend a modern and effective range that could impress and inspire. High end LED products were introduced along with some finest conventional range, and paired with controls and dimming systems to create an office environment that is attractive and eco-friendly. The lights also save energy, consume less heat, enjoy a longer lifetime and reduce the need for maintenance and replacements. More importantly, with dimmable downlights, the team can now freely adjust the light settings based on their preferences, enjoying more comfort while performing their best.

## UBS Singapore Singapore

The Philips Lighting Singapore team approached global financial giant UBS to propose Philips LED lighting solutions for the office. Convinced by the multitude of benefits coming from the proposal, UBS Singapore agreed to commence with a small pilot project to replace conventional lighting with LEDs in its existing office at Hansa Point in Changi Business Park, Singapore. UBS team selected products which complemented its office environment, and was pleased with the overall results. Additionally, UBS Singapore team has also recommended the same products to be designed into its office in India, thus winning another project for the Philips Lighting India team.



### Westfield Sydney HQ Sydney, Australia

For its headquarters, leading retail property group Westfield set out to minimize the use of natural resources, provide a more productive and comfortable workspace for staff, and target a five-star NABERS energy rating and a six-star Green Star rating. With Philips lighting solutions, a sophisticated and energy-efficient office lighting design was achieved, while creating a stylish and beautiful work environment. With its green office, Westfield won new fans with its design, at the same time gaining 30% energy savings and its targeted green credentials.

## Barclays Headquarters Cairo, Egypt

At Barclays Headquarters in Cairo, innovative lighting solutions from Philips were brought in to enhance the office ambience and boost the performance of the team. Light-flexible spaces were created to allow elegant but multi-functional zones. Highly efficient and sustainable solutions with consistent light output were introduced, and being fit-and-forget solutions, installation was a breeze while allowing the users to enjoy quality light of a longer lifetime. The lighting design in this office proved the point that safe and reliable lighting can also be stylish and relatively affordable. Giving the company energy savings and cost savings for the long run.



**Westraven**  
Utrecht, The Netherlands

For the upgrade of Westraven Tower – the office block housing the Rijkswaterstaat of the Dutch Ministry of Transport, Public Works and Water Management – Philips was commissioned to bring in lighting solutions to improve the well-being of employees and boost their productivity. Philips Dynamic Lighting simulated daylight indoors, creating a stimulating ambience that matched the rhythm of the staff's daily activities. It also gave each employee a chance to control individual lighting according to his or her own preferences and usage habits. As a result, employees felt more energized and inspired to do their best.



**Tower 42**  
London, United Kingdom

Tower 42, the tallest building in the City of London, called upon Philips expertise for the highest quality, sustainable lighting solution for its 9,000 sq ft office space on Level 12. Philips customized Savio remote-phosphor LED luminaires and Philips Light Master Modular lighting controls to create an edge-to-edge lighting appearance with a uniform and comfortable 'surface of light.' As a result, Level 12 on Tower 42 earned the distinction of being the UK's first office space to be entirely lit by LEDs, while achieving 40% energy savings compared to conventional technologies.




**Dubai Municipality**  
Dubai, United Arab Emirates

Philips and Dubai Municipality, one of the largest government institutions in Dubai, made a pact to transform Dubai into one of the world's most sustainable cities. After conducting an energy audit in 15 of Dubai's buildings, Philips replaced the old lighting fixtures with the most innovative LED lighting technology: CoreLine and GreenSpace luminaires that produced crisp and brighter lighting with better color rendering. This allowed Dubai Municipality to save over 50% on energy and 6,200 tons of CO2 emissions per year. The improved light levels and better quality of light helped to inspire and motivate Dubai Municipality's team, while making the environment more pleasant for its visitors.



# Beyond illumination





# Support from **start to finish**

With offices around the world, we have extensive experience handling lighting challenges on behalf of our customers. We aim to be your best business partner, offering the right expertise and solutions. Allow us to help you with planning, implementing and maintaining your project every step of the way.



## **Advisory Services**

Can a lighting upgrade help your business grow? Get an expert light audit from Philips Advisory Services

- Auditing your energy consumption
- Bringing creative ideas to life
- Helping you plan, making it happen
- Helping you convince the team



## **Project Services**

Get your lighting installation completed quickly and efficiently, with Philips Lighting Project Services

- Project management
- Installing your system
- Integrating and programming
- Lighting performance contracts
- Energy savings projects



## **Lifecycle Services**

Let Philips handle your installation with service agreements that can be tailored to your needs. These could include:

- Helpdesk, remote diagnostics and fault investigation, system health checks and spare parts replacement
- Qualified service engineers for preventive and corrective maintenance of your installation
- Asset management, data analytics and consultancy, system optimization and more



## **Philips Lighting Capital**

Finance your new lighting system with little to no upfront investment

- Protecting your cash flow
- Saving you time and money

**Note:** Certain services may not be available in all countries. Kindly check with your local Philips representative for details.

# Spotlight on our products

A quick overview of Philips lighting solutions - features and benefits.

For more information, visit [www.philips.com](http://www.philips.com) or contact our sales team.



### Coreline LED Troffer G2

Cost-effective troffer with different mounting options: surface-mounted, recessed or suspended

- 60% more energy efficient vs conventional TL solution
- Up to 50% more energy savings when used with controls
- Recessed and suspended types bear the same design as the last generation of Coreline luminaires



### PowerBalance LED Troffer G2

Highly efficient LED luminaire specially developed to meet all office needs. Longer lifetime, lower energy consumption

- Operational cost savings
- Office norm-compliant
- Advanced LED technology
- Smart Pyramid Optics (SPO)
- Dedicated lumen package for office applications



### GreenSpace LED Downlight G4

Elegant design, with a great look and feel for both WH reflector and AL reflector types

- Diversity of choices: 4 lumen packages; 3 CCT; 3 Cut-out size; UGR22/25; Fixed/DALI;
- Lifetime up to 50,000 hours
- High efficacy



### GreenUp Waterproof

With professional optic design and Philips LED module, gives the most comfortable light experience of CRI 85

- Up to 62% energy savings
- Reliable, with humidity and dust protection
- Extra-long life of 40,000 hours
- Flexible installations



### iColor Cove QLX Powercore

Delivers saturated color and dynamic effects in an economical, energy-efficient package

- Wide and medium beam angles
- Integrated 180° rotating mount for precise positioning, with flexible mounting options
- Professional-grade illuminance
- Delivers uniformity and consistency of hues, millions of colors and full-color, dynamic effect



### SmartBright LED Troffer G2

Ideal replacement for conventional fluorescent lights, delivers comfortable light with good color rendering and color consistency

- Up to 58% energy savings vs existing T8 general lighting
- Multiple mounting options for various applications: recessed and plaster ceiling



### SmartBright LED Downlight G3

LED downlights bearing the same cut-out as CFLi/CFLni downlights, making an easy retrofit switch possible

- Up to 55% more savings vs CFLi Downlight
- Very reliable integrated advanced cooling solution
- Lasts up to 7 years, based on 10 hours' daily use
- Various sizes, brightness and color temperatures available



### SmartBright LED Batten G2

Timeless, elegant design. Offers perfect, continuous light effect with its slim end cap

- Easy to install; can be mixed and matched with various batten lengths
- Up to 50% more energy savings vs T5 Essential Batten
- Comes in 3 or 4 color temperatures



### Master LEDtube

Mercury-free LED light source in traditional fluorescent form

- Up to 55% energy savings vs fluorescent tubes
- Extra-long life of 40,000 hours
- Retrofit to existing T8 lamps on EM ballast installations
- Full safety features and EM Protector safety device



### ColorGraze MX4 Powercore

Intelligent fixtures with an expanded range of intensely saturated full-colour light output in a variety of beam angles

- Comes in 4 standard lengths and 5 beam angles
- Significantly expanded palette of saturated colors
- New standard of color consistency and uniformity
- Customizable configurations for special applications

	Reception and indoor public area	Breakout area	Open plan office	Corridors and circulation areas	Cell office	Meeting room and training room	Stairs	Restrooms	Cafeteria and pantry	Exterior façade	Indoor lobbies	Carpark	Loading bay
Coreline LED Troffer G2	•		•		•	•							
PowerBalance LED Troffer 2.0			•	•	•	•							
SmartBright LED Troffer 2.0	•		•		•								
SmartBright LED Downlight G3		•	•	•			•	•	•				
SmartBright Mini LED Dimmable Downlight G2		•			•	•	•	•	•				
SmartBright LED Batten G2	•		•	•			•						
SmartBright Luxline LED Batten	•						•						
SmartBright LED Waterproof												•	
BasicBright LED Spot	•	•	•	•	•		•	•	•				
Master LEDspot MV		•	•	•				•					
Master LEDtube			•	•		•	•					•	•
GreenSpace LED Downlight G4	•	•	•	•	•	•	•	•	•				
GreenPerform Waterproof									•			•	•
GreenUp Waterproof									•			•	
ColorGraze MX4 Powercore										•			
ColorReach Compact Powercore										•			
ColorReach Powercore gen2										•			
iColor Flex MX gen2										•			
iColorCove MX Powercore									•				
iColorCove QLX Powercore	•					•							
ColorFuse Powercore												•	
eW Fuse Powercore												•	
eW Cove QLX Powercore	•	•				•							
eW Cove MX Powercore									•				

Notes





©2015 Koninklijke Philips N.V.

All rights reserved. Reproduction in whole or in part is prohibited without prior written consent of the copyright owner. The information presented in this document does not form part of any quotation or contract, is believed to be accurate and reliable and may be changed without notice. No liability will be accepted by the publisher for any consequence of its use. Publication thereof does not convey nor imply any license under patent – or other industrial or intellectual property rights.