



All about Philips LED

Fill your home with quality light and create countless memories with Philips LED. Our LED has a lifespan of up to 20,000 hours†, and it provides greater energy efficiency when compared to similar LED lights with the same wattage and color temperature, ensuring you brighter illumination with the same consumption.

- 

1
Even and comfortable light
- 

2
Up to 20,000 hours long life
- 

3
Quality light for natural colors
- 

4
Safety & quality certification
- 

5
Up to 80% energy savings*
- 

6
Premium materials
- 

7
Light turns on in an instant
- 

8
Adjustable light intensity
- 

9
Adjustable color temperature

Light for every style.

You've built a home, and lovingly furnished it to make it your own. A lush sofa set to lounge in comfort, an elegant dining table for family meals and sleek cupboards to hold your possessions. However, no home is complete until the lights are turned on to bathe everything in a welcoming glow.

For the proud homeowner, Philips offers the home lighting decorative collection consisting of Modern living, Contemporary chic, Vibrant expressions, Heritage refined and Timeless classics stylistic genres that span the home décor spectrum to help light up your lifestyle, the right light is everything.

Philips LED luminaires may be equipped with other functions to add value to your daily experience, providing functions such as adjustable light intensity or color temperature to allow for greater customization.

†Based on 6 hours use per day


*Efficient LED light source saves up to 80% energy vs. Philips incandescent bulbs with similar output.

Good CRI

Color Rendering Index (CRI)

The CRI is an indication of light quality and its ability to reproduce colors naturally. Natural vibrant colors are represented by a higher value.

Philips LED light has a CRI above 80 and is amongst the best in class.



CRI range from 80 – 90

CRI range from 70 – 80

Concept **benefits**

- High quality LED for clean bright light
- Adjustable head
- Remote control
- Adjustable height
- Independent slide modules
- Cut to size
- Dimmable
- Touch switch easy light control
- Adjustable light intensity
- Tunable
- Weather proof - IP44
- Ultra slim design



58088/48 Orbit

- Ceiling light
- Aluminum
- Aluminum
- LED integrated 105W, 4000K cool white light
- 4800lm
- 100 - 240V
- 750 X 750 X 75mm
- 3-step dimming, adjustable height




58089/48 Orbit

- Ceiling light
- Aluminum
- Aluminum
- LED integrated 36W, 4000K cool white light
- 1600lm
- 100 - 240V
- 420 X 420 X 156mm
- 3-step dimming, adjustable height



My Living



58080/30 Piano

- Ceiling light
- Black, white
- Aluminum
- LED integrated 76W, 4000K cool white light
- 4200lm
- 110 - 240V
- 700(max.900) X 560 X 80mm
- Independent slide modules, dimmable with remote control included



จังหวะและมนต์เสน่ห์ของสีขาว-ดำ

ด้วยชุดโคมไฟ Philips myLiving LED Piano Collection ที่จะมอบอิสระในการปรับแต่งโคมไฟของคุณให้เข้ากับการตกแต่งห้องของคุณ ออกแบบโดยใช้โครงสร้างจากอลูมิเนียมให้อารมณ์เหมือนเครื่องดนตรีวงออร์เคสตรา



58086/48 Orbit

- Suspension light
- Aluminum
- Aluminum
- LED integrated 46W, 4000K cool white light
- 1500lm
- 100 - 240V
- 1282 X 403 X 1500mm
- 3-step dimming, adjustable height



58087/48 Orbit

- Suspension light
- Aluminum
- Aluminum
- LED integrated 107W, 4000K cool white light
- 4500lm
- 110 - 240V
- 760 X 760 X 1500mm
- Adjustable height, adjustable light intensity: 100% - 50% - 20% with wall switch



58090/48 Orbit

- Suspension light
- Aluminum
- Aluminum
- LED integrated 71W, 4000K cool white light
- 2000lm
- 220 - 240V
- 750 X 750 X 1500mm
- 3-step dimming



58081/30 Piano

- Ceiling light
- Black, white
- Aluminum
- LED integrated 32W, 4000K cool white light
- 2000lm
- 110 - 240V
- 420(max.570) X 375 X 80mm
- Independent slide modules



58082/30 Piano

- Suspension light
- Black, white
- Aluminum
- LED integrated 32W, 4000K cool white light
- 1200lm
- 100 - 240V
- 435 X 70 X 1500mm
- Independent slide modules, adjustable height



58083/30 Piano

- Table light
- Black, white
- Aluminum
- LED integrated 12W, 4000K cool white light
- 600lm (light source)
- 110 - 240V
- 365 X 170 X 440mm
- Adjustable light intensity: 100%-70%-40%-5%



*Dimmable with separately available commercial trailing-edge dimmers.



My Garden



16343/47 Wish

- Wall light
- Aluminum
- Stainless steel, synthetic
- E27, CFLi 14W not included
- 220 - 240V
- 100 X 100 X 350mm
- Weather proof - IP44



สวยงามและดูดีได้ทุกสภาพอากาศ

ด้วยชุดโคมไฟ Philips myGarden Wish Collection คุณจะได้รับโคมไฟสมัยใหม่ที่สวยงามและดูดีได้ทุกสภาพอากาศ ไม่ว่าจะฝนตกหรือแดดออก ตัวโคมทำจากสแตนเลสสตีลที่ทนทานต่อทุกสภาพอากาศ และดูสะอาดตลอดเวลา ให้ส่วนหรือระเบียบของคุณดูสวยงามสะอาดตาอยู่เสมอ



49021/31 Embrace

- Suspension light
- White
- Ash wood
- LED integrated 24W, 2700K warm white light
- 1000lm
- 100 - 240V
- 505 X 505 X 1500mm
- Adjustable height, 3-step dimming



49022/31 Embrace

- Wall light
- White
- Ash wood
- LED integrated 8.5W, 2700K warm white light
- 280lm
- 100 - 240V
- 163 X 214 X 124mm
- Adjustable head



16344/47 Wish

- Pedestal light
- Aluminum
- Stainless steel, synthetic
- E27, CFLi 14W not included
- 220 - 240V
- 100 X 100 X 393mm
- Weather proof - IP44



16345/47 Wish

- Post light
- Aluminum
- Stainless steel, synthetic
- E27, CFLi 14W not included
- 220 - 240V
- 100 X 100 X 790mm
- Weather proof - IP44



17515/87 Botanic

- Wall light
- Gray
- Aluminum, glass
- E27, CFLi 23W X 2 not included
- 220 - 240V
- 166 X 98 X 402mm
- Weather proof - IP44, adjustable head



49019/31 Embrace

- Ceiling light
- White
- Ash wood
- LED integrated 70W, 2700K - 6500K warm white light to cool daylight
- 3800lm
- 100 - 240V
- 864 X 864 X 137mm
- Dimmable, tunable (remote control included)



49020/31 Embrace

- Ceiling light
- White
- Ash wood
- LED integrated 24W, 2700K warm white light
- 1000lm
- 100 - 240V
- 505 X 505 X 128mm
- 3-step dimming



49023/31 Embrace

- Table light
- White
- Ash wood
- LED integrated 10W, 2700K warm white light
- 320lm
- 100 - 240V
- 283 X 283 X 385mm
- 3-step touch dimming



My Living

เพื่อการใช้งานที่ยาวนานกว่า

ทางเลือกในการเปลี่ยนทดแทนโคมไฟหลอดฟลูออเรสเซนต์ T5 และยังมีอายุการใช้งานที่ยาวนานขึ้นถึง 20,000 ชั่วโมง คือการเปลี่ยนมาใช้โคมไฟ Philips myLiving Linea LED trunk batten ที่ติดตั้งง่ายและเปลี่ยนทดแทนได้ทันที สะดวก รวดเร็ว



31091/31094/31097/31 Trunk

- Cove light
- White
- Synthetic
- LED integrated 13W, 3000K warm white light, 4000K cool white light, 6500K cool daylight
- 1000lm
- 220 - 240V
- 1182 X 22 X 36mm
-



31085/31 Trunk

- Cove light
- White
- Synthetic
- LED integrated 9W, 3000K warm white light, 4000K cool white light, 6500K cool daylight
- 750lm
- 220 - 240V
- 882 X 22 X 36mm
-



31089/31

- Connection wire
- White
- Synthetic
-
-
- 220 - 240V
- 200mm (Length only)
-



31092/31095/31098/31 Trunk

- Cove light
- White
- Synthetic
- LED integrated 7W, 3000K warm white light, 4000K cool white light, 6500K cool daylight
- 500lm
- 220 - 240V
- 548 X 22 X 36mm
-



31093/31096/31099/31 Trunk

- Cove light
- White
- Synthetic
- LED integrated 4W, 3000K warm white light, 4000K cool white light, 6500K cool daylight
- 250lm
- 220 - 240V
- 322 X 22 X 36mm
-



31090/31

- Connector
- White
- Synthetic
-
-
- 220 - 240V
- 300mm (Length only)
-



30913/87

- Strip light
- Gray
- Metal
- LED integrated 2.7W, 4000K cool white light
- 220lm
- 220 - 240V
- 300 X 25 X 8.4mm
- Touch on/off, extendable



30914/87

- Strip light
- Gray
- Metal
- LED integrated 3W, 4000K cool white light
- 240lm
- 220 - 240V
- 300 X 25 X 8.4mm
- Extension of 30913



My Garden



11211/30 Teralis

- 🏠 Wall light
- 🖨 Black
- 🏠 Aluminum, synthetic
- 💡 LED integrated 4W, 4000K cool white light
- 📏 130lm
- 🔌 100 - 240V
- 📏 140 X 54 X 140mm
- 🛡 Weather proof - IP44



แสงสว่างที่กลมกลืน ไปกับความมืดมิด

ให้แสงสว่างกับพื้นที่นอกบ้านของคุณด้วยโคมไฟ Philips myGarden LED Wall Light คุณจะได้ชุดโคมไฟประดับและกลมกลืนไปกับผนังนอกบ้าน เเดลิยง บริเวณประตูบ้านหรือกำแพงบ้านของคุณ ทนทานต่อทุกสภาพอากาศ ด้วยการรับรองการป้องกันน้ำและฝุ่น IP44



11212/30 Teralis

- 🏠 Wall light
- 🖨 Black
- 🏠 Aluminum, synthetic
- 💡 LED integrated 4W, 4000K cool white light
- 📏 130lm
- 🔌 100 - 240V
- 📏 140 X 57 X 140mm
- 🛡 Weather proof - IP44



17287/47 Aura

- 🏠 Wall light
- 🏠 Inox
- 🏠 Stainless steel, synthetic
- 💡 LED integrated 4W, 2700K warm white light
- 📏 270lm
- 🔌 220 - 240V
- 📏 92 X 103 X 122mm
- 🛡 Weather proof - IP44



17287/30 Aura

- 🏠 Wall light
- 🖨 Black
- 🏠 Stainless steel, synthetic
- 💡 LED integrated 4W, 2700K warm white light
- 📏 270lm
- 🔌 220 - 240V
- 📏 92 X 103 X 122mm
- 🛡 Weather proof - IP44



My Garden



- 17300/47 Parrot**
- ☑ Wall light
 - ☑ Inox
 - ☑ Synthetic, stainless steel
 - ☑ LED integrated 3.5W, 2700K warm white light
 - ☑ 150lm
 - ☑ 220 - 240V
 - ☑ 122 X 88 X 130mm
 - ☑ Weather proof - IP44



บุรุษเหล็กผู้พิทักษ์

ด้วยชุดโคมไฟทรงระบอก Philips myGarden Parrotlet LED wall Light ตัวโคมทำจากสแตนเลสตีลเคลือบด้วยสี ให้ความงามและแสงสว่างที่สมบูรณ์แบบแก่ผนังนอกบ้านของคุณ



- 17301/47 Parrotlet**
- ☑ Wall light
 - ☑ Inox
 - ☑ Synthetic, stainless steel
 - ☑ LED integrated 3.5W, 2700K warm white light
 - ☑ 90lm
 - ☑ 220 - 240V
 - ☑ 122 X 88 X 130mm
 - ☑ Weather proof - IP44



- 17302/30 Caiques**
- ☑ Wall light
 - ☑ Black
 - ☑ Synthetic
 - ☑ LED integrated 3.5W, 2700K warm white light
 - ☑ 120lm
 - ☑ 110V, 220-240V
 - ☑ 122 X 85 X 130mm
 - ☑ Weather proof - IP44



- 17304/30 Eagle**
- ☑ Wall light
 - ☑ Black
 - ☑ Synthetic, aluminum
 - ☑ LED integrated 3.5W, 2700K warm white light
 - ☑ 170lm
 - ☑ 220 - 240V
 - ☑ 170 X 74 X 170mm
 - ☑ Weather proof - IP44



Ceiling light



- 45116/01 Mimosa**
- ☑ Suspension light
 - ☑ Brass
 - ☑ Metal
 - ☑ LED integrated 80W, 2700K warm white light
 - ☑ 3200lm
 - ☑ 100 - 240V
 - ☑ 812 X 812 X 1500mm
 - ☑ Dimmable (remote control included), adjustable head



- 45116/48 Mimosa**
- ☑ Suspension light
 - ☑ Aluminum
 - ☑ Metal
 - ☑ LED integrated 80W, 2700K warm white light
 - ☑ 3200lm
 - ☑ 100 - 240V
 - ☑ 812 X 812 X 1500mm
 - ☑ Dimmable (remote control included), adjustable head



My Living



40227/53 (QPG303)

- Suspension light
- Orange
- Metal
- E27, CFLi 8W not included
-
- 220 - 240V
- 250 X 250 X 1300mm
- Adjustable height



40227/35 (QPG303)

- Suspension light
- Blue
- Metal
- E27, CFLi 8W not included
-
- 220 - 240V
- 250 X 250 X 1300mm
- Adjustable height



แสงสว่างใต้โดมที่งดงาม

ด้วยโคมไฟแขวนทรงโดมครึ่งทรงกลม Philips myLiving Suspension Light สวยงามด้วยโคมสีเหล็กหรือสีสนิมสดใสที่หลากหลาย ให้ภายในบ้านของคุณดูทันสมัยได้อย่างลงตัว



40227/11 (QPG303)

- Suspension light
- Chrome
- Metal
- E27, CFLi 8W not included
-
- 220 - 240V
- 250 X 250 X 1300mm
- Adjustable height



40228/53 (QPG304)

- Suspension light
- Orange
- Metal
- E27, CFLi 24W not included
-
- 220 - 240V
- 400 X 400 X 1500mm
- Adjustable height



Linea light



30731, 30732

- Cove light
- White
- Synthetic
- LED integrated 60W, 3000K warm white light, 4500K cool white light
- 900lm/m
- 220 - 240V
- 5000 X 10 X 3mm
- Driver included



30729, 30730

- Cove light
- White
- Synthetic
- LED integrated 30W, 3000K warm white light, 4500K cool white light
- 360lm/m
- 220 - 240V
- 5000 X 8 X 3mm
- Driver included



31058/31

- Cove light
- White
- Synthetic
- LED integrated 18W, 3000K warm white light
- 380lm/m
- 220 - 240V
- 5000 X 8 X 2mm
- Driver not included



31059/31

- Cove light
- White
- Synthetic
- LED integrated 18W, 3000K warm white light
- 380lm/m
- 220 - 240V
- 5000 X 8 X 2mm
- Driver included



30924/31

- Connection wire
- White
- Synthetic
-
-
-
- Wire length 200mm



30925/31

- Connector
- White
- Synthetic
-
-
-
-



30904/31

- Cove light
- White
- Synthetic
- LED integrated 6.5W/m
- 150lm/m
- 220 - 240V
- 5000 X 10 X 3mm
- Changeable color, driver and remote control included



30905/31

- Cove light
- White
- Synthetic
- LED integrated 6.5W/m
- 150lm/m
- 220 - 240V
- 1000 X 10 X 3mm
- Changeable color, driver and remote control included



30906/31

- Cove light
- White
- Synthetic
- LED integrated 6.5W/m
- 150lm/m
- 220 - 240V
- 1000 X 10 X 3mm
- Changeable color





Functional collection

Home lighting collection 2016



My Living



31826/31

- 🏠 Ceiling light
- 👉 White
- 🏠 Synthetic
- 💡 LED integrated 20W, 2700K warm white light, 6500K cool daylight
- 💡 1400lm
- 🔌 220 - 240V
- 📏 380 X 380 X 68
- 📏 -



ทางเลือกที่ลงตัว

ด้วยชุดโคมไฟ Philips Essential Ceiling Light ที่ผลิตจากวัสดุที่ทนทาน ทำความสะอาดง่าย ใช้งานได้อย่างไร้กังวล มีรุ่นที่มาพร้อมชุดหลอดไฟ LED ให้เลือก สามารถเปลี่ยนทดแทนโคมไฟเดิมได้ทันที ให้การกระจายแสงที่สม่ำเสมอและทั่วถึง เหมาะกับระเบียงบ้าน พื้นที่ซักล้างหรือห้องนอนที่ไม่ใหญ่มากนัก

My Living



31825/31

- 🏠 Ceiling light
- 👉 White
- 🏠 Synthetic
- 💡 LED integrated 17W, 2700K warm white light, 6500K cool daylight
- 💡 1100lm
- 🔌 220 - 240V
- 📏 350 X 350 X 66
- 📏 -



31825/87

- 🏠 Ceiling light
- 👉 Gray
- 🏠 Synthetic
- 💡 LED integrated 17W, 2700K warm white light, 6500K cool daylight
- 💡 1100lm
- 🔌 220 - 240V
- 📏 350 X 350 X 66
- 📏 -



31826/87

- 🏠 Ceiling light
- 👉 Gray
- 🏠 Synthetic
- 💡 LED integrated 20W, 2700K warm white light, 6500K cool daylight
- 💡 1400lm
- 🔌 220 - 240V
- 📏 380 X 380 X 68
- 📏 -



33361/61, 33361/31

- 🏠 Ceiling light
- 👉 White
- 🏠 Synthetic
- 💡 LED integrated 6W, 2700K warm white light, 4000K cool white light, 6500K cool daylight
- 💡 480lm
- 🔌 220 - 240V
- 📏 225 X 225 X 72
- 📏 -



33369/61, 33369/31

- 🏠 Ceiling light
- 👉 White
- 🏠 Synthetic
- 💡 LED integrated 10W, 2700K warm white light, 6500K cool daylight
- 💡 650lm
- 🔌 220 - 240V/ 100 - 240V
- 📏 265 X 265 X 70
- 📏 -



แสงสว่างที่ปรับได้ ตามอารมณ์ของคุณ

ด้วยชุดโคมไฟ Philips Smart LED Downlight Collection ที่มีความสามารถเสริมให้คุณสามารถปรับเปลี่ยนอารมณ์แสงในห้องของคุณตามกิจกรรมของคุณ เพียงแค่หมุนปรับหรือกดปุ่ม Wall Dimmer ทุกสิ่งก็จะอยู่ใต้การควบคุมของคุณ

Down light

ความสามารถ :

สวิตช์ควบคุม Wall Dimmer จะให้คุณสามารถปรับแต่งความสว่างและอุณหภูมิสีของแสงได้อย่างอิสระ เพียงแค่กดและหมุนปรับเท่านั้น

Tunable

6500K cool daylight

2700K warm white light

2700K cool white light

Press to ON

OFF-ON

OFF-ON

Adjustable light intensity

Turn to 100% brightness

Turn to 50% brightness

Turn to 25% brightness



59061/31 Smalu

- ☑ Down light
- ☑ White
- ☑ Die-cast aluminum
- ☑ LED integrated 9W, step tune: 2700K – 4000K– 6500K
- ☑ 540lm
- ☑ 100 - 240V
- ☑ 139 X 139 X 77
- ☑ Tunable, link up to 50 units with one remote control (remote control not included)



59062/31 Smalu

- ☑ Down light
- ☑ White
- ☑ Die-cast aluminum
- ☑ LED integrated 9W, step tune: 2700K – 4000K– 6500K
- ☑ 540lm
- ☑ 100 - 240V
- ☑ 139 X 139 X 77
- ☑ Tunable, link up to 50 units with one remote control (remote control included)



แสงเรืองอ่อนที่อบอุ่น

ยกระดับคุณภาพของแสงสว่างในบ้านของคุณด้วยชุดโคมไฟ Philips Essential LED Recessed Down Light สามารถติดตั้งและทดแทนโคมไฟเดิมได้ทันที สะดวกและง่ายตาย มาพร้อมกระจกครอบลดแสง แยกตา ให้แสงที่อ่อนโยนและอบอุ่นแก่บ้านคุณ

Down light



59511/31 Slimlit

- ☑ Down light
- ☑ White
- ☑ Synthetic
- ☑ LED integrated 12W, 2700K warm white light, 4000K cool white light, 6500K cool daylight
- ☑ 550lm, 600lm, 600lm
- ☑ 100 - 240V
- ☑ 140 X 140 X 26
- ☑ Ultra slim design



59512/31 Slimlit

- ☑ Down light
- ☑ White
- ☑ Synthetic
- ☑ LED integrated 13W, 2700K warm white light, 4000K cool white light, 6500K cool daylight
- ☑ 600lm, 650lm, 650lm
- ☑ 100 - 240V
- ☑ 170 X 170 X 26
- ☑ Ultra slim design



59513/31 Slimlit

- ☑ Down light
- ☑ White
- ☑ Synthetic
- ☑ LED integrated 23W, 2700K warm white light, 4000K cool white light, 6500K cool daylight
- ☑ 1200lm, 1300lm, 1300lm
- ☑ 100 - 240V
- ☑ 200 X 200 X 26
- ☑ Ultra slim design



59514/31 Slimlit

- ☑ Down light
- ☑ White
- ☑ Synthetic
- ☑ LED integrated 12W, 2700K warm white light, 4000K cool white light, 6500K cool daylight
- ☑ 550lm, 600lm, 600lm
- ☑ 100 - 240V
- ☑ 140 X 140 X 26
- ☑ Ultra slim design



59515/31 Slimlit

- ☑ Down light
- ☑ White
- ☑ Synthetic
- ☑ LED integrated 13W, 2700K warm white light, 4000K cool white light, 6500K cool daylight
- ☑ 600lm, 650lm, 650lm
- ☑ 100 - 240V
- ☑ 170 X 170 X 26
- ☑ Ultra slim design



59721/31 Esscus


- ☑ Spot light
- ☑ White
- ☑ Metal
- ☑ LED integrated 3W, 2700K warm white light, 6500K cool daylight
- ☑ 210lm, 250lm
- ☑ 100 - 240V
- ☑ 84 X 84 X 30
- ☑ Adjustable head



59721/48 Esscus

- ☑ Spot light
- ☑ Silver
- ☑ Metal
- ☑ LED integrated 3W, 2700K warm white light, 6500K cool daylight
- ☑ 210lm, 250lm
- ☑ 100 - 240V
- ☑ 84 X 84 X 30
- ☑ Adjustable head





โคมไฟพื้นฐาน ที่คุณขาดไม่ได้

ด้วยชุดโคมไฟ Philips Essential Range ที่จะช่วย
เพิ่มความสว่างเฉพาะจุดที่คุณต้องการได้อย่างลงตัว
ตัวโคมไฟมีหลากหลายรูปแบบหลากสี สัน ให้คุณได้เลือก
ตามสไตล์ที่เป็นคุณ



71571/31 Dino

- Desk light
- White
- Aluminum, synthetic
- LED integrated 4.8W
- 350lm
- 100 - 240V
- 186 X 135 X 435
- 4-level step dimming



Desk light



71571/93 Dino

- Desk light
- Anthracite
- Aluminum, synthetic
- LED integrated 4.8W
- 350lm
- 100 - 240V
- 186 X 135 X 435
- 4-level step dimming



72008/32 Jelly

- Desk light
- Red
- Aluminum, synthetic
- LED integrated 3.6W
- 230lm
- 100 - 240V
- 344 X 150 X 382
-



72008/34 Jelly

- Desk light
- Yellow
- Aluminum, synthetic
- LED integrated 3.6W
- 230lm
- 100 - 240V
- 344 X 150 X 382
-



72008/35 Jelly

- Desk light
- Blue
- Aluminum, synthetic
- LED integrated 3.6W
- 230lm
- 100 - 240V
- 344 X 150 X 382
-



71566/31 Packet

- Desk light
- White
- Synthetic
- LED integrated 2.5W, 6500K cool daylight
-
- 100 - 240V
- 274 X 100 X 372
-



71566/93 Packet

- Desk light
- Anthracite
- Synthetic
- LED integrated 2.5W, 6500K cool daylight
-
- 100 - 240V
- 274 X 100 X 372
-



72007/92 Lever

- Desk light
- Gold
- Aluminum, synthetic
- LED integrated 5W, 4000K cool white light
-
- 100 - 240V
- 156 X 290 X 435
- 4-step dimming



72007/14 Lever

- Desk light
- Silver
- Aluminum, synthetic
- LED integrated 5W, 4000K cool white light
-
- 100 - 240V
- 156 X 290 X 435
- 4-step dimming



71661/31 Taffy

- Desk light
- White
- Aluminum, synthetic
- LED integrated 3.6W, 4000K cool white light
- 170lm
- 100 - 240V
- 150 X 295 X 385
-



71661/93 Taffy

- Desk light
- Anthracite
- Aluminum, synthetic
- LED integrated 3.6W, 4000K cool white light
- 170lm
- 100 - 240V
- 150 X 295 X 385
-



70023/30 Cap

- Desk light
- Dark gray
- Aluminum, synthetic
- LED integrated 4.5W, 6500K cool daylight (RoA)
-
- 100 - 240V
- 260 X 155 X 370
- Easily adjustable head



70023/31 Cap

- Desk light
- White
- Aluminum, synthetic
- LED integrated 4.5W, 6500K cool daylight (RoA)
-
- 100 - 240V
- 260 X 155 X 370
- Easily adjustable head

