



EU Declaration of Conformity

We, Philips Lighting

I.B.R.S./C.C.R.I. /Numéro 10461

5600 VB Eindhoven, The Netherlands

Internal Ref. Nr.: BMS-BLHI-QUA-814-OT-0

Year in which CE Mark was first affixed: 2006

Declare under our responsibility for the product(s):

Product Range:	Medium Source lamps
Product Code:	Please refer to appendix

The designated product(s) is (are) in conformity with the essential requirements of the following European Directives and harmonized standards:

Low Voltage Directive (LVD), 2014/35/EU

List of applicable Standards:

- EN 62035:2014
- EN 61549:2003 + A1:2005, A2:2010, A3:2012

Restriction of the use of certain Hazardous Substances in electrical and electronic equipment Directive (RoHS), 2011/65/EU

- EN 50581:2012

and is/are produced under a quality scheme at least in conformity with ISO 9001, ISO 14001 and OHSAS 18001.

Signature:**Name:**

Hans Bruneel

Function:

Head of Product Quality, Business Professional Lamps

Date:

15-09-2017



EU Declaration of Conformity

Appendix: Specification of the products:

10NC	12NC	Material Description	EAN/UPC	EAN3
924840600000	924840600040	MSI 1200HR.1CT/10	8711500212450	8711500212467
924841000000	924841000040	MSI 575HR.1CT/10	8711500212474	8711500212481
928050205100	928050205115	MSR 400 HR 1CT/4	8718291227960	8718291227977
928050405100	928050405114	MSR 4000 HR 1CT/1	8727900926767	8727900926774
928060205100	928060205114	MSR 125 HR 1CT/40	8727900922486	8727900922493
928060205100	928060205115	MSR 125 HR 1CT/4	8718696414927	8718696414934
928077905100	928077905108	MSR 400 1CT/4	8711500190277	8711500190284
928077905100	928077905114	MSR 400 1CT/40	8727900914689	8727900914696
928077905100	928077905115	MSR 400 1CT/4	8718696416006	8718696416013
928078005100	928078005114	MSR 700 1CT/8	8727900915754	8727900915761
928078105100	928078105114	MSR 1200 1CT/3	8727900911213	8727900911220
928097205100	928097205114	MSD 200 1CT/40	8727900914702	8727900914719
928097605100	928097605115	MSD 200/2 1CT/4	8718696415900	8718696415917
928097705100	928097705115	MSR 575 HR 1CT/4	8718291221050	8718291221067
928097905100	928097905114	MSR 200 HR 1CT/40	8727900924169	8727900924176
928097905100	928097905115	MSR 200 HR 1CT/4	8718696416044	8718696416051
928098705100	928098705114	MSD 250.1CT/40	8727900915679	8727900915686
928098705100	928098705115	MSD 250 1CT/4	8718696415887	8718696415894
928098805100	928098805114	MSD 575 1CT/16	8727900917550	8727900917567
928098905100	928098905114	MSD 575 HR 1CT/8	8727900916485	8727900916492
928099005100	928099005115	MSD 250/2 30H 1CT/4	8718291228066	8718291228073
928099405100	928099405103	MSA 2500 DE UNP/1	8718291548300	8711500202086
928099605100	928099605112	MSR Gold 1200 SA/DE UNP/108	8711500207111	8711500206909
928099605100	928099605115	MSR Gold 1200 SA/DE 1CT/4	8718291221210	8718291221227
928104905100	928104905114	MSR 2500 HR 1CT/2	8727900926040	8727900926057
928105005100	928105005114	MSR 1200 HR 1CT/2	8727900926064	8727900926071
928106005100	928106005115	MSR Gold 700 FastFit 1CT/4	8718291221197	8718291221203
928106105100	928106105114	MSR Gold 2000/2 FastFit 1CT/8	8727900908305	8727900908312
928106205100	928106205114	MSR Gold 700/2 FastFit 1CT/8	8727900908503	8727900908510
928106305100	928106305109	MSD 250/2 20H 1CT/12	8727900861655	8727900861662
928106405100	928106405115	MSR Gold 2500/2 FastFit 1CT/4	8718291221319	8718291221326
928106705100	928106705120	MSR 1800 DE 1CT	8727900800944	8727900800951
928107305100	928107305115	MSR Gold 1500 FastFit 1CT/4	8718291221340	8718291221357
928107705100	928107705109	MSR 575/2 7H 1CT/12	8727900864649	8727900864656
928108905100	928108905115	MSR Gold 1500/1 FastFit 1CT/4	8718696402757	8718696402764
928170205100	928170205114	MSR 400 SA 1CT/40	8727900924213	8727900924220
928170305100	928170305115	MSR 700 SA 1CT/4	8718291228028	8718291228035
928170405100	928170405114	MSD 700.1CT/3	8727900911299	8727900911305
928170905100	928170905115	MSR 1200 SA 1CT/4	8718291221258	8718291221265
928171405100	928171405115	MSR Gold 1000 MiniFastFit 1CT/4	8718291785088	8718291785095
928171505100	928171505114	MSR 700/2 1CT/8	8727900916386	8727900916393
928171605100	928171605115	MSR 575/2 10H 1CT/4	8718291221272	8718291221289
928171805100	928171805114	MSR 1200/2.1CT/3	8727900911336	8727900911343
928172005100	928172005114	MSD 1200.1CT/3	8727900911350	8727900911367
928172705100	928172705120	MSR 6000 HR UNP/1	8718291548393	8711500200938
928172805100	928172805115	MSD 150/2. 1CT/4	8718696415986	8718696415993
928173205100	928173205114	MSR 2000 SA 1CT/8	8727900915730	8727900915747
928173305100	928173305120	MSR 12000 HR	8718291548409	8711500202574
928173805100	928173805114	MSR 4000 HR/J 1CT/1	8727900926743	8727900926750
928174205100	928174205114	MSR 2500 HR/J 1CT/2	8727900926088	8727900926095
928174605100	928174605114	MSR Gold 1200 SA/SE 1CT/3	8727900926026	8727900926033

928174705100	928174705115	MSR Gold 700 SA/2 DE 1CT/4	8718291221234	8718291221241
928175005100	928175005115	MSR Gold 1200 FastFit 1CT/4	8718291221296	8718291221302
928175105100	928175105114	MSR Gold 575 SA/2 DE 1CT/40	8727900914641	8727900914658
928175305100	928175305112	MSR Gold 1200 SA/2 DE UNP/108	8711500208996	8711500209009
928175305100	928175305115	MSR Gold 1200 SA/2 DE 1CT/4	8718291221074	8718291221081
928175605100	928175605114	MSR 250 HR 1CT/40	8727900917499	8727900917505
928175605100	928175605115	MSR 250 HR 1CT/4	8718696416020	8718696416037
928176605100	928176605112	MSR Gold 1510 SA/DE UNP/108	8711500213426	8711500213433
928176605100	928176605115	MSR Gold 1510 SA/DE 1CT/4	8718291221135	8718291221142
928176905100	928176905114	MSR Gold 2000 FastFit 1CT/8	8727900919493	8727900919509
928177105100	928177105115	MSR Gold 300/2 MiniFastFit 1CT/4	8718291221111	8718291221128
928184005100	928184005115	MSR Gold 575/2 MiniFastFit 1CT/4	8718291221098	8718291221104
928190805300	928190805308	MSD Platinum 5 R UNP/24	8727900783506	8727900887334
928190805300	928190805314	MSD Platinum 5 R 1CT/8	8727900930702	8727900930719
928190905100	928190905114	MSR Platinum 35 1CT	8718291120063	8718291120070
928191605300	928191605308	MSD Platinum 15 R UNP/24		8727900943771
928191605300	928191605314	MSD Platinum 15 R 1CT/8	8718291135357	8718291135364
928191705300	928191705308	MSD Platinum 11 R UNP/24	8718696538821	8718696538838
928191705300	928191705314	MSD Platinum 11 R 1CT/8	8718696539767	8718696539774
928194005100	928194005114	MSR Gold 400 MiniFastFit 1CT/16	8718291158288	8718291158295
928194105100	928194105114	MSR Gold 700 MiniFastFit 1CT/16	8718291141037	8718291141044
928194505100	928194505114	MSR Platinum 35 ST	8718291704065	8718291704072
928195205300	928195205308	MSD Platinum 16 R UNP/24		8718291703778
928195205300	928195205314	MSD Platinum 16 R 1CT/8	8718291704386	8718291704393
928196105300	928196105308	MSD Platinum 14 R UNP/24	8718696440681	8718696440698
928196105300	928196105314	MSD Platinum 14 R 1CT/8	8718696440612	8718696440629
928197205300	928197205308	MSD Platinum 20 R UNP/24	8718291768883	8718291768890
928197205300	928197205314	MSD Platinum 20 R 1CT/8	8718696478127	8718696478134
928197305300	928197305308	MSD Platinum 17 RA UNP/24	8718291767718	8718291767725
928197305300	928197305314	MSD Platinum 17 RA 1CT/8	8718291767794	8718291767800
928197405100	928197405115	MSR Gold 700/1 MiniFastFit 1CT/4	8718291696636	8718291696643
928197605300	928197605308	MSD Platinum 2 R UNP/24		8718291678977
928197605300	928197605314	MSD Platinum 2 R 1CT/8	8718291735540	8718291735557
928197805300	928197805308	MSD Platinum 21 R UNP/24	8718696678329	8718696678336
928197805300	928197805314	MSD Platinum 21 R 1CT/8	8718696678268	8718696678275
928199805100	928199805114	MSD Gold 300/2 MiniFastFit 1CT/16	8727900912579	8727900912586
928199905100	928199905115	MSR Gold 700/2 MiniFastFit 1CT/4	8718291221173	8718291221180
928410005100	928410005112	MSR Gold 1510 SA/1 DE UNP/108	8718696536117	8718696536124
928410005100	928410005115	MSR Gold 1510 SA/1 DE 1CT/4	8718696536131	8718696536148
928410105100	928410105114	MSR Gold 2000/1 FastFit 1CT/8	8718696679449	8718696679456
928495205300	928495205308	MSD Platinum 20 RB UNP/24	8718696684221	8718696684238
928495205300	928495205314	MSD Platinum 20 RB 1CT/8	8718696684207	8718696684214