

# Cross Reference Guide: Ace to Philips Advance

Competitor Name	Competitor Part Number	Philips Advance	Notes	Ballast Type	Ballast Family
Ace	AC-2/39MHUVXS	IMH-239-A-LF		Electronic HID	e-Vision
Ace	AC-2/39MHUVXS-BM	IMH-239-A-BLS		Electronic HID	e-Vision
Ace	AC-MH100UVS	IMH-100-D-LF		Electronic HID	e-Vision
Ace	AC-MH100UVS-BM	IMH-100-D-BLS		Electronic HID	e-Vision
Ace	AC-MH20UVS	None		Electronic HID	None
Ace	AC-MH20UVS-BM	None		Electronic HID	None
Ace	AC-MH35UVS	IMH-39-G-LF		Electronic HID	e-Vision
Ace	AC-MH35UVS-BM	IMH-39-G-BLS		Electronic HID	e-Vision
Ace	AC-MH50UVS	IMH-50-G-LF		Electronic HID	e-Vision
Ace	AC-MH50UVS-BM	IMH-50-G-LF		Electronic HID	e-Vision
Ace	AC-MH70EPL	IMH-70-E-LF		Electronic HID	e-Vision
Ace	AC-MH70EPL-BM	None		Electronic HID	None
Ace	AC-MH70UVS	IMH-70-D-LF		Electronic HID	e-Vision
Ace	AC-MH70UVS-BM	IMH-70-D-BLS		Electronic HID	e-Vision
Ace	AC-MHB150SDT	None		Electronic HID	None
Ace	AC-T150MHUVS	IMH-150-H-LF		Electronic HID	e-Vision
Ace	CSSUV42PS	ICF-2S26-H1-LD-K		Electronic Fluorescent	SmartMate

NOTE: Philips Lighting Company does not warrant or guarantee the correctness or accuracy of this cross-reference guide. It is provided for the information and convenience of the user. The user is advised to consult the current Philips Advance Atlas or Online Catalog to ascertain and verify that the ballast selected is the appropriate and correct choice for the user's requirements.  
PAAd-1419CR