

# Cross Reference Guide: Hatch to Philips Advance

Competitor Name	Competitor Part Number	Philips Advance	Notes	Ballast Type	Ballast Family
Hatch	MC100-1-F-120U	IMH-100-D-LF	Advance unit is IntelliVolt. Hatch unit is DedicatedVoltage.	Electronic HID	e-Vision
Hatch	MC100-1-F-240U	IMH-100-D-LF	Advance unit is IntelliVolt. Hatch unit is DedicatedVoltage.	Electronic HID	e-Vision
Hatch	MC100-1-F-277U	IMH-100-D-LF	Advance unit is IntelliVolt. Hatch unit is DedicatedVoltage.	Electronic HID	e-Vision
Hatch	MC100-1F-UNNS	None		Electronic HID	None
Hatch	MC100-1F-UNNS-HB	None		Electronic HID	None
Hatch	MC100-1F-UNNSL-HB	None		Electronic HID	None
Hatch	MC100-1-F-UNNU	IMH-100-D-LF		Electronic HID	e-Vision
Hatch	MC100-1F-UNNU-HB	IMH-100-D-LF		Electronic HID	e-Vision
Hatch	MC100-1-J-120U	IMH-100-D-BLS	Advance unit is IntelliVolt. Hatch unit is Dedicated Voltage.	Electronic HID	e-Vision
Hatch	MC100-1-J-240U	IMH-100-D-BLS	Advance unit is IntelliVolt. Hatch unit is Dedicated Voltage.	Electronic HID	e-Vision
Hatch	MC100-1-J-277U	IMH-100-D-BLS	Advance unit is IntelliVolt. Hatch unit is Dedicated Voltage.	Electronic HID	e-Vision
Hatch	MC100-1J-UNNS-HB	None		Electronic HID	None
Hatch	MC100-1-J-UNNU	IMH-100-D-BLS		Electronic HID	e-Vision
Hatch	MC100-1J-UNNU-HB	IMH-100-D-BLS		Electronic HID	e-Vision
Hatch	MC100-1T-UNNS-HB	None		Electronic HID	None
Hatch	MC100-1T-UNNSL-HB	None		Electronic HID	None
Hatch	MC150-1-F-120U	IMH-150-H-LF		Electronic HID	e-Vision
Hatch	MC150-1-F-240U	IMH-150-H-LF		Electronic HID	e-Vision
Hatch	MC150-1-F-277U	IMH-150-H-LF		Electronic HID	e-Vision
Hatch	MC150-1-J-120U	IMH-150-H-BLS	Check size	Electronic HID	e-Vision
Hatch	MC150-1-J-240U	IMH-150-H-BLS	Check size	Electronic HID	e-Vision
Hatch	MC150-1-J-277U	IMH-150-H-BLS	Check size	Electronic HID	e-Vision
Hatch	MC20-1-F-120X	IMH-G20-K-LFS		Electronic HID	e-Vision
Hatch	MC20-1F-120Z	IMH-G20-K-LF	CHECK FOR FIT! Philips is 0.65" longer overall.	Electronic HID	e-Vision
Hatch	MC20-1-F-240U	IMH-G20-G-LF		Electronic HID	e-Vision
Hatch	MC20-1F-277X	None		Electronic HID	None
Hatch	MC20-1-F-UNNS	IMH-G20-E-LF		Electronic HID	e-Vision
Hatch	MC20-1F-UNNSL	IMH-G20-E-LF	Leads out one end on Hatch, both ends on Philips	Electronic HID	e-Vision
Hatch	MC20-1-F-UNNU	IMH-G20-G-LF		Electronic HID	e-Vision
Hatch	MC20-1-J-120U	IMH-G20-G-BLS		Electronic HID	e-Vision
Hatch	MC20-1J-120X	None		Electronic HID	None
Hatch	MC20-1-J-240U	None		Electronic HID	None
Hatch	MC20-1-J-277VN	None		Electronic HID	None
Hatch	MC20-1J-277X	None		Electronic HID	None
Hatch	MC20-1-J-UNNU	IMH-G20-G-BLS		Electronic HID	e-Vision
Hatch	MC20-1T-120Z	None		Electronic HID	None

NOTE: Philips Lighting Company does not warrant or guarantee the correctness or accuracy of this cross-reference guide. It is provided for the information and convenience of the user. The user is advised to consult the current Philips Advance Atlas or Online Catalog to ascertain and verify that the ballast selected is the appropriate and correct choice for the user's requirements.  
PA4-1424CR

# Cross Reference Guide: Hatch to Philips Advance

Competitor Name	Competitor Part Number	Philips Advance	Notes	Ballast Type	Ballast Family
Hatch	MC20-1T-UNNS	IMH-G20-E-LF	No mounting feet on Universal. Philips has mounting feet.	Electronic HID	e-Vision
Hatch	MC20-1T-UNNSL	IMH-G20-E-LF	Leads out one end on Hatch, both ends on Philips	Electronic HID	e-Vision
Hatch	MC20-2-J-UNNU	None		Electronic HID	None
Hatch	MC22-1F-12LX	RMH-20-K-LF		Electronic HID	e-Vision
Hatch	MC22-1F-27LX	None		Electronic HID	None
Hatch	MC22-1F-UNLU	None		Electronic HID	None
Hatch	MC22-1-F-UNNU	RMH-20-K-LF	Philips has not approved Hatch ballast for Mini MasterColor® Lamp	Electronic HID	e-Vision
Hatch	MC22-1J-12LX	RMH-20-K-BLS		Electronic HID	e-Vision
Hatch	MC22-1J-27LX	None		Electronic HID	None
Hatch	MC22-1J-UNLU	None		Electronic HID	None
Hatch	MC22-1-J-UNNU	None		Electronic HID	None
Hatch	MC22-2-F-UNNU	None		Electronic HID	None
Hatch	MC22-2-F-UNNV	None		Electronic HID	None
Hatch	MC22-2-J-UNNU	None		Electronic HID	None
Hatch	MC22-2-J-UNNVN	None		Electronic HID	None
Hatch	MC39-1-F-120U	IMH-39-K-LF		Electronic HID	e-Vision
Hatch	MC39-1F-120X	RMH-39-K-LFS		Electronic HID	e-Vision
Hatch	MC39-1F-12LX	RMH-39-K-LFS		Electronic HID	e-Vision
Hatch	MC39-1-F-240U	IMH-39-G-LF		Electronic HID	e-Vision
Hatch	MC39-1F-277X	None		Electronic HID	None
Hatch	MC39-1F-27LX	None		Electronic HID	None
Hatch	MC39-1F-UNLU	IMH-P39-G-LF		Electronic HID	e-Vision
Hatch	MC39-1F-UNNS	IMH-39-E-LF		Electronic HID	e-Vision
Hatch	MC39-1F-UNNSL	IMH-39-E-LF	Leads out one end on Hatch, both ends on Philips	Electronic HID	e-Vision
Hatch	MC39-1-F-UNNU	IMH-39-G-LF		Electronic HID	e-Vision
Hatch	MC39-1F-UNNUG3	IMH-39-G-LF		Electronic HID	e-Vision
Hatch	MC39-1-J-120U	IMH-39-G-BLS		Electronic HID	e-Vision
Hatch	MC39-1J-120X	RMH-39-K-BLS		Electronic HID	e-Vision
Hatch	MC39-1J-12LX	RMH-39-K-BLS		Electronic HID	e-Vision
Hatch	MC39-1-J-240U	IMH-39-G-BLS		Electronic HID	e-Vision
Hatch	MC39-1J-277X	None		Electronic HID	None
Hatch	MC39-1J-27LX	None		Electronic HID	None
Hatch	MC39-1J-UNLU	IMH-P39-G-BLS		Electronic HID	e-Vision
Hatch	MC39-1-J-UNNU	IMH-39-G-BLS		Electronic HID	e-Vision
Hatch	MC39-1J-UNNUG3	IMH-39-G-BLS		Electronic HID	e-Vision
Hatch	MC39-1T-UNNSL	IMH-39-E-LF	Leads out one end on Hatch, both ends on Philips	Electronic HID	e-Vision

NOTE: Philips Lighting Company does not warrant or guarantee the correctness or accuracy of this cross-reference guide. It is provided for the information and convenience of the user. The user is advised to consult the current Philips Advance Atlas or Online Catalog to ascertain and verify that the ballast selected is the appropriate and correct choice for the user's requirements.  
PA4-1424CR

## Cross Reference Guide: Hatch to Philips Advance

Competitor Name	Competitor Part Number	Philips Advance	Notes	Ballast Type	Ballast Family
Hatch	MC39-2-F-UNNU	IMH-239-A-LF		Electronic HID	e-Vision
Hatch	MC39-2-J-UNNU	IMH-239-A-BLS		Electronic HID	e-Vision
Hatch	MC50-1-F-120U	IMH-50-G-LF		Electronic HID	e-Vision
Hatch	MC50-1-F-120V	IMH-50-G-LF		Electronic HID	e-Vision
Hatch	MC50-1-F-120VN	IMH-50-E-LF		Electronic HID	e-Vision
Hatch	MC50-1-F-277V	IMH-50-G-LF		Electronic HID	e-Vision
Hatch	MC50-1-F-277VN	IMH-50-E-LF		Electronic HID	e-Vision
Hatch	MC50-1F-UNNU	IMH-50-G-LF	Leads out one end on Hatch, both ends on Philips	Electronic HID	e-Vision
Hatch	MC50-1-J-120U	IMH-50-G-BLS		Electronic HID	e-Vision
Hatch	MC50-1J-UNNU	IMH-50-G-BLS		Electronic HID	e-Vision
Hatch	MC70-1-F-120V	IMH-70-G-LF		Electronic HID	e-Vision
Hatch	MC70-1-F-120VN	IMH-70-E-LF		Electronic HID	e-Vision
Hatch	MC70-1-F-277V	IMH-70-E-LF		Electronic HID	e-Vision
Hatch	MC70-1F-UNNS	IMH-70-E-LF		Electronic HID	e-Vision
Hatch	MC70-1F-UNNS-HB	IMH-70-E-LF	Hatch case is larger	Electronic HID	e-Vision
Hatch	MC70-1F-UNNSL	IMH-70-E-LF	Leads out one end on Hatch, both ends on Philips	Electronic HID	e-Vision
Hatch	MC70-1F-UNNSL-HB	IMH-70-E-LF	Leads out one end on Hatch, both ends on Philips. Hatch case larger.	Electronic HID	e-Vision
Hatch	MC70-1F-UNNU	IMH-70-G-LF		Electronic HID	e-Vision
Hatch	MC70-1F-UNNU-HB	IMH-70-D-LF		Electronic HID	e-Vision
Hatch	MC70-1J-UNNU	IMH-70-G-BLS		Electronic HID	e-Vision
Hatch	MC70-1T-UNNS	IMH-70-E-LF	Hatch has no mounting feet.	Electronic HID	e-Vision
Hatch	MC70-1T-UNNS-HB	IMH-70-E-LF	Hatch has no mounting feet. Hatch case is larger.	Electronic HID	e-Vision
Hatch	MC70-1T-UNNSL	IMH-70-E-LF	Leads out one end on Hatch, both ends Philips. Hatch no mounting feet.	Electronic HID	e-Vision
Hatch	MC70-1T-UNNSL-HB	IMH-70-E-LF	Hatch leads out one end both ends Philips. Hatch no mounting feet. Hatch case is larger.	Electronic HID	e-Vision

NOTE: Philips Lighting Company does not warrant or guarantee the correctness or accuracy of this cross-reference guide. It is provided for the information and convenience of the user. The user is advised to consult the current Philips Advance Atlas or Online Catalog to ascertain and verify that the ballast selected is the appropriate and correct choice for the user's requirements.  
PAAd-1424CR