

Cross Reference Guide: Metrolight to Philips Advance

Competitor Name	Competitor Part Number	Philips Advance	Notes	Ballast Type	Ballast Family
Metrolight	M100MHS-UX-US-C-AD-NC	None		Electronic HID	None
Metrolight	M100MHS-UX-US-C-ND-NC	IMH-100-D-LF	IMH100-D is smaller than the Metrolight unit	Electronic HID	e-Vision
Metrolight	M100MHS-UX-US-S-AD-NC	None		Electronic HID	None
Metrolight	M100MHS-UX-US-S-ND-NC	IMH-100-D-BLS		Electronic HID	e-Vision
Metrolight	M100WS-UX-US-C-AD-NC	None		Electronic HID	None
Metrolight	M100WS-UX-US-C-ND-NC	None		Electronic HID	None
Metrolight	M100WS-UX-US-S-AD-NC	None		Electronic HID	None
Metrolight	M100WS-UX-US-S-ND-NC	None		Electronic HID	None
Metrolight	M150MHS-UX-US-C-AD-NC	None		Electronic HID	None
Metrolight	M150MHS-UX-US-C-ND-NC	IMH-150-H-LF		Electronic HID	e-Vision
Metrolight	M150MHS-UX-US-R-AD-NC	None		Electronic HID	None
Metrolight	M150MHS-UX-US-R-ND-NC	None		Electronic HID	None
Metrolight	M150MHS-UX-US-S-AD-NC	None		Electronic HID	None
Metrolight	M150MHS-UX-US-S-ND-NC	IMH-150-H-BL:S		Electronic HID	e-Vision
Metrolight	M20MH-1-US-C-AD-NC	None		Electronic HID	None
Metrolight	M20MH-1-US-C-ND-NC	None		Electronic HID	None
Metrolight	M20MH-1-US-S-AD-NC	None		Electronic HID	None
Metrolight	M20MH-1-US-S-ND-NC	None		Electronic HID	None
Metrolight	M20MH-2-US-C-AD-NC	None		Electronic HID	None
Metrolight	M20MH-2-US-C-ND-NC	None		Electronic HID	None
Metrolight	M20MH-2-US-S-AD-NC	None		Electronic HID	None
Metrolight	M20MH-2-US-S-ND-NC	None		Electronic HID	None
Metrolight	M20MH-3-US-C-AD-NC	None		Electronic HID	None
Metrolight	M20MH-3-US-C-ND-NC	None		Electronic HID	None
Metrolight	M20MH-3-US-S-AD-NC	None		Electronic HID	None
Metrolight	M20MH-3-US-S-ND-NC	None		Electronic HID	None
Metrolight	M20MH-UX-US-C-AD-NC	None		Electronic HID	None
Metrolight	M20MH-UX-US-C-ND-NC	None		Electronic HID	None
Metrolight	M20MH-UX-US-S-AD-NC	None		Electronic HID	None
Metrolight	M20MH-UX-US-S-ND-NC	None		Electronic HID	None
Metrolight	M250HPS-3-US-C-AD-COM	None		Electronic HID	None
Metrolight	M250HPS-3-US-C-AD-NC	None		Electronic HID	None
Metrolight	M250HPS-3-US-C-ND-COM	None		Electronic HID	None
Metrolight	M250HPS-3-US-C-ND-NC	None		Electronic HID	None
Metrolight	M250MH-3-US-C-AD-COM	None		Electronic HID	None
Metrolight	M250MH-3-US-C-AD-NC	None		Electronic HID	None

NOTE: Philips Lighting Company does not warrant or guarantee the correctness or accuracy of this cross-reference guide. It is provided for the information and convenience of the user. The user is advised to consult the current Philips Advance Atlas or Online Catalog to ascertain and verify that the ballast selected is the appropriate and correct choice for the user's requirements.
PA-d-1429CR

Cross Reference Guide: Metrolight to Philips Advance

Competitor Name	Competitor Part Number	Philips Advance	Notes	Ballast Type	Ballast Family
Metrolight	M250MH-3-US-C-ND-COM	None		Electronic HID	None
Metrolight	M250MH-3-US-C-ND-NC	None		Electronic HID	None
Metrolight	M2x39MH-1-US-C-AD-NC	None		Electronic HID	None
Metrolight	M2X39MH-1-US-C-ND-NC	IMH-239-A-LF	unit is IntelliVolt. Metrolight unit is Dedicated Voltage.	Electronic HID	e-Vision
Metrolight	M2x39MH-1-US-S-AD-NC	None		Electronic HID	None
Metrolight	M2X39MH-1-US-S-ND-NC	IMH-239-A-BLS	Advance unit is IntelliVolt. Metrolight unit is Dedicated Voltage.	Electronic HID	e-Vision
Metrolight	M2x39MH-2-US-C-AD-NC	None		Electronic HID	None
Metrolight	M2X39MH-2-US-C-ND-NC	IMH-239-A-LF	Advance unit is IntelliVolt. Metrolight unit is Dedicated Voltage.	Electronic HID	e-Vision
Metrolight	M2x39MH-2-US-S-AD-NC	None		Electronic HID	None
Metrolight	M2X39MH-2-US-S-ND-NC	IMH-239-A-BLS	Advance unit is IntelliVolt. Metrolight unit is Dedicated Voltage.	Electronic HID	e-Vision
Metrolight	M2x39MH-3-US-C-AD-NC	None		Electronic HID	None
Metrolight	M2X39MH-3-US-C-ND-NC	IMH-239-A-LF	Advance unit is IntelliVolt. Metrolight unit is Dedicated Voltage.	Electronic HID	e-Vision
Metrolight	M2x39MH-3-US-S-AD-NC	None		Electronic HID	None
Metrolight	M2X39MH-3-US-S-ND-NC	IMH-239-A-BLS	Advance unit is IntelliVolt. Metrolight unit is Dedicated Voltage.	Electronic HID	e-Vision
Metrolight	M2x39MH-UX-US-C-AD-NC	None		Electronic HID	None
Metrolight	M2X39MH-UX-US-C-ND-NC	IMH-239-A-LF		Electronic HID	e-Vision
Metrolight	M2x39MH-UX-US-S-AD-NC	None		Electronic HID	None
Metrolight	M2X39MH-UX-US-S-ND-NC	IMH-239-A-BLS		Electronic HID	e-Vision
Metrolight	M320HPS-3-US-C-AD-COM	None		Electronic HID	None
Metrolight	M320HPS-3-US-C-AD-NC	None		Electronic HID	None
Metrolight	M320HPS-3-US-C-ND-COM	None		Electronic HID	None
Metrolight	M320HPS-3-US-C-ND-NC	None		Electronic HID	None
Metrolight	M320MH-3-US-C-AD-COM	None		Electronic HID	None
Metrolight	M320MH-3-US-C-AD-NC	None		Electronic HID	None
Metrolight	M320MH-3-US-C-ND-COM	None		Electronic HID	None
Metrolight	M320MH-3-US-C-ND-NC	None		Electronic HID	None
Metrolight	M350HPS-3-US-C-AD-COM	None		Electronic HID	None
Metrolight	M350HPS-3-US-C-AD-NC	None		Electronic HID	None
Metrolight	M350HPS-3-US-C-ND-COM	None		Electronic HID	None
Metrolight	M350HPS-3-US-C-ND-NC	None		Electronic HID	None
Metrolight	M350MH-3-US-C-AD-COM	None		Electronic HID	None
Metrolight	M350MH-3-US-C-AD-NC	None		Electronic HID	None
Metrolight	M350MH-3-US-C-ND-COM	None		Electronic HID	None
Metrolight	M350MH-3-US-C-ND-NC	None		Electronic HID	None
Metrolight	M39MH-1-US-C-AD-NC	None		Electronic HID	None
Metrolight	M39MH-1-US-C-ND-NC	RMH-39-K-LF		Electronic HID	e-Vision

NOTE: Philips Lighting Company does not warrant or guarantee the correctness or accuracy of this cross-reference guide. It is provided for the information and convenience of the user. The user is advised to consult the current Philips Advance Atlas or Online Catalog to ascertain and verify that the ballast selected is the appropriate and correct choice for the user's requirements.
PA-d-1429CR

Cross Reference Guide: Metrolight to Philips Advance

Competitor Name	Competitor Part Number	Philips Advance	Notes	Ballast Type	Ballast Family
Metrolight	M39MH-1-US-S-AD-NC	None		Electronic HID	None
Metrolight	M39MH-1-US-S-ND-NC	RMH-39-K-LFS		Electronic HID	e-Vision
Metrolight	M39MH-2-US-C-AD-NC	None		Electronic HID	None
Metrolight	M39MH-2-US-C-ND-NC	IMH-39-G-LF	Advance unit is IntelliVolt. Metrolight unit is Dedicated Voltage.	Electronic HID	e-Vision
Metrolight	M39MH-2-US-S-AD-NC	None		Electronic HID	None
Metrolight	M39MH-2-US-S-ND-NC	IMH-39-G-BLS	Advance unit is IntelliVolt. Metrolight unit is Dedicated Voltage.	Electronic HID	e-Vision
Metrolight	M39MH-3-US-C-AD-NC	None		Electronic HID	None
Metrolight	M39MH-3-US-C-ND-NC	IMH-39-G-LF	Advance unit is IntelliVolt. Metrolight unit is Dedicated Voltage.	Electronic HID	e-Vision
Metrolight	M39MH-3-US-S-AD-NC	None		Electronic HID	None
Metrolight	M39MH-3-US-S-ND-NC	IMH-39-A-BLS	Advance unit is IntelliVolt. Metrolight unit is Dedicated Voltage.	Electronic HID	e-Vision
Metrolight	M39MH-UX-US-C-AD-NC	None		Electronic HID	None
Metrolight	M39MH-UX-US-C-ND-NC	IMH-39-G-LF		Electronic HID	e-Vision
Metrolight	M39MH-UX-US-S-AD-NC	None		Electronic HID	None
Metrolight	M39MH-UX-US-S-ND-NC	IMH-39-G-BLS		Electronic HID	e-Vision
Metrolight	M400HPS-3-US-C-AD-COM	None		Electronic HID	None
Metrolight	M400HPS-3-US-C-AD-NC	None		Electronic HID	None
Metrolight	M400HPS-3-US-C-ND-COM	None		Electronic HID	None
Metrolight	M400HPS-3-US-C-ND-NC	None		Electronic HID	None
Metrolight	M400MH-3-US-C-AD-COM	None		Electronic HID	None
Metrolight	M400MH-3-US-C-AD-NC	None		Electronic HID	None
Metrolight	M400MH-3-US-C-ND-COM	None		Electronic HID	None
Metrolight	M400MH-3-US-C-ND-NC	None		Electronic HID	None
Metrolight	M450HPS-3-US-C-AD-COM	None		Electronic HID	None
Metrolight	M450HPS-3-US-C-AD-NC	None		Electronic HID	None
Metrolight	M450HPS-3-US-C-ND-COM	None		Electronic HID	None
Metrolight	M450HPS-3-US-C-ND-NC	None		Electronic HID	None
Metrolight	M450MH-3-US-C-AD-COM	None		Electronic HID	None
Metrolight	M450MH-3-US-C-AD-NC	None		Electronic HID	None
Metrolight	M450MH-3-US-C-ND-COM	None		Electronic HID	None
Metrolight	M450MH-3-US-C-ND-NC	None		Electronic HID	None
Metrolight	M50MHS-UX-US-C-AD-NC	None		Electronic HID	None
Metrolight	M50MHS-UX-US-C-ND-NC	IMH-50-G-LF		Electronic HID	e-Vision
Metrolight	M50MHS-UX-US-S-AD-NC	None		Electronic HID	None
Metrolight	M50MHS-UX-US-S-ND-NC	IMH-50-G-BLS		Electronic HID	e-Vision
Metrolight	M50VVS-UX-US-C-AD-NC	None		Electronic HID	None
Metrolight	M50VVS-UX-US-C-ND-NC	None		Electronic HID	None

NOTE: Philips Lighting Company does not warrant or guarantee the correctness or accuracy of this cross-reference guide. It is provided for the information and convenience of the user. The user is advised to consult the current Philips Advance Atlas or Online Catalog to ascertain and verify that the ballast selected is the appropriate and correct choice for the user's requirements.
PA-d-1429CR

Cross Reference Guide: Metrolight to Philips Advance

Competitor Name	Competitor Part Number	Philips Advance	Notes	Ballast Type	Ballast Family
Metrolight	M50WS-UX-US-S-AD-NC	None		Electronic HID	None
Metrolight	M50WS-UX-US-S-ND-NC	None		Electronic HID	None
Metrolight	M70MHS-UX-US-C-ND-NC	IMH-70-D-LF	IMH70-D is smaller than the Metrolight unit	Electronic HID	e-Vision
Metrolight	M70MHS-UX-US-S-AD-NC	None		Electronic HID	None
Metrolight	M70MHS-UX-US-S-ND-NC	IMH-70-D-BLS		Electronic HID	e-Vision

NOTE: Philips Lighting Company does not warrant or guarantee the correctness or accuracy of this cross-reference guide. It is provided for the information and convenience of the user. The user is advised to consult the current Philips Advance Atlas or Online Catalog to ascertain and verify that the ballast selected is the appropriate and correct choice for the user's requirements.
PA-1429CR