

Cross Reference Guide: Reliable to Philips Advance

Competitor Name	Competitor Part Number	Philips Advance	Notes	Ballast Type	Ballast Family
Reliable	PS13B90S	IMH-50-G-BLS		Electronic HID	e-Vision
Reliable	PS13B90T	IMH-50-G-LF		Electronic HID	e-Vision
Reliable	PS13D90S	IMH-50-G-BLS		Electronic HID	e-Vision
Reliable	PS13D90T	IMH-50-G-LF		Electronic HID	e-Vision
Reliable	PS13E90S	None		Electronic HID	None
Reliable	PS13E90T	None		Electronic HID	None
Reliable	PS13U90S	IMH-50-G-BLS		Electronic HID	e-Vision
Reliable	PS13U90T	IMH-50-G-LF		Electronic HID	e-Vision
Reliable	PS15B90L	IMH-150-H-LF		Electronic HID	e-Vision
Reliable	PS15B90S	IMH-150-H-BLS		Electronic HID	e-Vision
Reliable	PS15B90T	IMH-150-H-LF		Electronic HID	e-Vision
Reliable	PS15D90L	IMH-150-H-LF		Electronic HID	e-Vision

NOTE: Philips Lighting Company does not warrant or guarantee the correctness or accuracy of this cross-reference guide. It is provided for the information and convenience of the user. The user is advised to consult the current Philips Advance Atlas or Online Catalog to ascertain and verify that the ballast selected is the appropriate and correct choice for the user's requirements.
PAAd-1435CR