

# Cross Reference Guide: Venture to Philips Advance

Competitor Name	Competitor Part Number	Philips Advance	Notes	Ballast Type	Ballast Family
Venture	V905AE7520	None		Magnetic HID	None
Venture	V905AJ7120	71A54N2-500D	Advance is 120/220/240V HX-HPF; Venture is 220/230/240V Reactor	Magnetic HID	Core and Coil
Venture	V905AL6111	71A55N0-500		Magnetic HID	Core and Coil
Venture	V905AL6210	71A57N0-500D		Magnetic HID	Core and Coil
Venture	V905AL6411	71A60N1-500		Magnetic HID	Core and Coil
Venture	V90AA2050	None		Magnetic HID	None
Venture	V90AA2150	71A85F5-500D	Advance is CWA; Venture is CWI. No cross available with isolated secondary	Magnetic HID	Core and Coil
Venture	V90AA6910	None		Magnetic HID	None
Venture	V90AD7411	71A58A2-500DA	Advance is 127/220V; Venture is 220V	Magnetic HID	Core and Coil
Venture	V90AM6410	71A6051-001D		Magnetic HID	Core and Coil
Venture	V90AM6514	71A6552-001CU		Magnetic HID	Core and Coil
Venture	V90AM7230	71A5593-001D	Venture includes 480V; for 480V use 71A5543-500DT (480V/120T)	Magnetic HID	Core and Coil
Venture	V90AM7330	71A5692-001D	Venture includes 480V; for 480V use 71A5642-500DT (480V/120T)	Magnetic HID	Core and Coil
Venture	V90AM7430	71A5892-001D	Venture includes 480V; for 480V use 71A5842-500DT (480V/120T)	Magnetic HID	Core and Coil
Venture	V90AM7530	71A5993-001D	Venture includes 480V; for 480V use 71A5943-500DT (480V/120T)	Magnetic HID	Core and Coil
Venture	V90AM7630	71A6092-001D	Venture includes 480V; for 480V use 71A6042-500DT (480V/120T)	Magnetic HID	Core and Coil
Venture	V90AM8430	71A5792-001D	Venture includes 480V; for 480V use 71A5742-500DT (480V/120T)	Magnetic HID	Core and Coil
Venture	V90AM8530	71A6393-500DEE	Venture includes 480V; for 480V use 71A6343-500DT (480V/120T)	Magnetic HID	Core and Coil
Venture	V90B1020	71A7707-001DB	Advance kit includes integral ignitor	Magnetic HID	Core and Coil
Venture	V90B1020C	71A7707-001DB	Advance kit includes integral ignitor	Magnetic HID	Core and Coil
Venture	V90B1120	71A7807-001DB	Advance kit includes integral ignitor	Magnetic HID	Core and Coil
Venture	V90B1120C	71A7807-001DB	Advance kit includes integral ignitor	Magnetic HID	Core and Coil
Venture	V90B1222	71A7907-001DB	Advance kit includes integral ignitor	Magnetic HID	Core and Coil
Venture	V90B1222C	71A7907-001DB	Advance kit includes integral ignitor	Magnetic HID	Core and Coil
Venture	V90B1322	71A8007-001DB	Advance kit includes integral ignitor	Magnetic HID	Core and Coil
Venture	V90B1322C	71A8007-001DB	Advance kit includes integral ignitor	Magnetic HID	Core and Coil
Venture	V90B1422	71A8107-001DB	Advance kit includes integral ignitor	Magnetic HID	Core and Coil
Venture	V90B1422C	71A8107-001DB	Advance kit includes integral ignitor	Magnetic HID	Core and Coil
Venture	V90B6112	71A5570-001D		Magnetic HID	Core and Coil
Venture	V90B6514	71A6572-001		Magnetic HID	Core and Coil
Venture	V90C2050	None		Magnetic HID	None
Venture	V90C2150	71A85E5-500D	Advance is CWA; Venture is CWI. No cross available with isolated secondary	Magnetic HID	Core and Coil
Venture	V90C6910	None		Magnetic HID	None
Venture	V90D1232	71A7971-001D		Magnetic HID	Core and Coil
Venture	V90D1233	71A7971-001D		Magnetic HID	Core and Coil
Venture	V90D1332	71A8071-001D		Magnetic HID	Core and Coil

NOTE: Philips Lighting Company does not warrant or guarantee the correctness or accuracy of this cross-reference guide. It is provided for the information and convenience of the user. The user is advised to consult the current Philips Advance Atlas or Online Catalog to ascertain and verify that the ballast selected is the appropriate and correct choice for the user's requirements.  
PA-d-1441CR

# Cross Reference Guide: Venture to Philips Advance

Competitor Name	Competitor Part Number	Philips Advance	Notes	Ballast Type	Ballast Family
Venture	V90D1333	71A8071-001D		Magnetic HID	Core and Coil
Venture	V90D1430	71A8172-001D		Magnetic HID	Core and Coil
Venture	V90D1434	71A8172-001D		Magnetic HID	Core and Coil
Venture	V90D1435	71A8172-001D		Magnetic HID	Core and Coil
Venture	V90D1436	71A8172-001D		Magnetic HID	Core and Coil
Venture	V90D1610	71A8970-001D		Magnetic HID	Core and Coil
Venture	V90D1711	71A8271-001D		Magnetic HID	Core and Coil
Venture	V90D1810	71A8371-001D		Magnetic HID	Core and Coil
Venture	V90D1911	71A8473-001D		Magnetic HID	Core and Coil
Venture	V90D1912	71A8473-001D		Magnetic HID	Core and Coil
Venture	V90D2110	71A85E5-500D	Advance is 120/208/240V; Venture is 120/208/240/277V; for 277V CWA use Advance 71A85F5	Magnetic HID	Core and Coil
Venture	V90D2311	71A8773-001		Magnetic HID	Core and Coil
Venture	V90D2312	71A8773-001	Venture = 4X5 core	Magnetic HID	Core and Coil
Venture	V90D5710	71A5191-001D		Magnetic HID	Core and Coil
Venture	V90D5731	71A5191-001D		Magnetic HID	Core and Coil
Venture	V90D5810	71A5292-001D	Advance is 120/277V; Venture is 120/208/240/277V	Magnetic HID	Core and Coil
Venture	V90D5832	71A5292-001D		Magnetic HID	Core and Coil
Venture	V90D5910	71A5383-500D	Advance is 120/277V; Venture is 120/208/240/277V	Magnetic HID	Core and Coil
Venture	V90D5931	71A5390-001D		Magnetic HID	Core and Coil
Venture	V90D5932	71A5390-001D		Magnetic HID	Core and Coil
Venture	V90D6111	71A5570-001D		Magnetic HID	Core and Coil
Venture	V90D6211	71A5771-001D		Magnetic HID	Core and Coil
Venture	V90D6212	71A5770-001D		Magnetic HID	Core and Coil
Venture	V90D6413	71A6071-001D		Magnetic HID	Core and Coil
Venture	V90D6514	71A6572-001		Magnetic HID	Core and Coil
Venture	V90D6611	71A6772-001		Magnetic HID	Core and Coil
Venture	V90D6612	71A6772-001		Magnetic HID	Core and Coil
Venture	V90D7110	71A5492-500D	Advance is HX-HPF; Venture is CWA	Magnetic HID	Core and Coil
Venture	V90D7130	71A5492-500D		Magnetic HID	Core and Coil
Venture	V90D7210	71A5593-001D		Magnetic HID	Core and Coil
Venture	V90D7310	71A5692-001D		Magnetic HID	Core and Coil
Venture	V90D7410	71A5892-001D		Magnetic HID	Core and Coil
Venture	V90D7411	71A5892-001D		Magnetic HID	Core and Coil
Venture	V90D7512	71A5993-001D		Magnetic HID	Core and Coil
Venture	V90D7612	71A6092-001D		Magnetic HID	Core and Coil

NOTE: Philips Lighting Company does not warrant or guarantee the correctness or accuracy of this cross-reference guide. It is provided for the information and convenience of the user. The user is advised to consult the current Philips Advance Atlas or Online Catalog to ascertain and verify that the ballast selected is the appropriate and correct choice for the user's requirements.  
PA-1441CR

# Cross Reference Guide: Venture to Philips Advance

Competitor Name	Competitor Part Number	Philips Advance	Notes	Ballast Type	Ballast Family
Venture	V90D7810	71A6593-500		Magnetic HID	Core and Coil
Venture	V90D7910	None		Magnetic HID	None
Venture	V90D8410	71A5792-001D		Magnetic HID	Core and Coil
Venture	V90D8511	71A6393-500DEE		Magnetic HID	Core and Coil
Venture	V90D8512	71A6393-500DEE		Magnetic HID	Core and Coil
Venture	V90D8611	71A6498-500		Magnetic HID	Core and Coil
Venture	V90E1131	71A7801-001D	Advance is 120/277V; Venture is 120/240V	Magnetic HID	Core and Coil
Venture	V90E1250	71A79E6-500D	Advance is 120/208/240V; Venture is 120/240V	Magnetic HID	Core and Coil
Venture	V90E1252	71A79E6-500D	Advance is 120/208/240V; Venture is 120/240V	Magnetic HID	Core and Coil
Venture	V90E1350	71A80E6-500D	Advance is 120/208/240V; Venture is 120/240V	Magnetic HID	Core and Coil
Venture	V90E1352	71A80E6-500D	Advance is 120/208/240V; Venture is 120/240V	Magnetic HID	Core and Coil
Venture	V90E1454	71A81E6-500D	Advance is 120/208/240V; Venture is 120/240V	Magnetic HID	Core and Coil
Venture	V90E1650	None		Magnetic HID	None
Venture	V90E1750	71A82E6-500D	Advance is 120/208/240V; Venture is 120/240V	Magnetic HID	Core and Coil
Venture	V90E1950	71A84E6-500D	Advance is 120/208/240V; Venture is 120/240V	Magnetic HID	Core and Coil
Venture	V90E2353	71A8773-001	Advance is 120/208/240/277V CWA; Venture is 120/240V CWI. No cross available with isolated secondary	Magnetic HID	Core and Coil
Venture	V90E6150	71A5570-001D	Advance is 120/208/240/277V CWA; Venture is 120/240V CWI. No cross available with isolated secondary	Magnetic HID	Core and Coil
Venture	V90E6250	None		Magnetic HID	None
Venture	V90E6350	None		Magnetic HID	None
Venture	V90E6450	71A60E6-500	Advance is 120/208/240V; Venture is 120/240V	Magnetic HID	Core and Coil
Venture	V90E6550	71A65E6-500DT	Advance is 208/240/120T; Venture is 120/240V	Magnetic HID	Core and Coil
Venture	V90F7512	71A5993-001D		Magnetic HID	Core and Coil
Venture	V90H1132	71A7801-001D		Magnetic HID	Core and Coil
Venture	V90H5731	71A5181-001D	For 120/277V or 71A5191-001D for 120/208/240/277V	Magnetic HID	Core and Coil
Venture	V90H5832	71A5292-001D	Advance is 120/208/240/277V; Venture is 120/277V	Magnetic HID	Core and Coil
Venture	V90H5931	71A5390-001D		Magnetic HID	Core and Coil
Venture	V90H5932	71A5390-001D		Magnetic HID	Core and Coil
Venture	V90H7130	71A5492-500D		Magnetic HID	Core and Coil
Venture	V90J1232	71A79A1-001D		Magnetic HID	Core and Coil
Venture	V90J1332	71A80A1-001D		Magnetic HID	Core and Coil
Venture	V90J1434	71A81A2-001D		Magnetic HID	Core and Coil
Venture	V90J1711	71A82A1-001D		Magnetic HID	Core and Coil
Venture	V90J1911	71A84A3-001D		Magnetic HID	Core and Coil
Venture	V90J1912	71A84A3-001D		Magnetic HID	Core and Coil
Venture	V90J2310	71A87A3-001		Magnetic HID	Core and Coil

NOTE: Philips Lighting Company does not warrant or guarantee the correctness or accuracy of this cross-reference guide. It is provided for the information and convenience of the user. The user is advised to consult the current Philips Advance Atlas or Online Catalog to ascertain and verify that the ballast selected is the appropriate and correct choice for the user's requirements.  
PA4-1441CR

# Cross Reference Guide: Venture to Philips Advance

Competitor Name	Competitor Part Number	Philips Advance	Notes	Ballast Type	Ballast Family
Venture	V90J2311	71A87A3-001		Magnetic HID	Core and Coil
Venture	V90J5832	71A52A2-500D		Magnetic HID	Core and Coil
Venture	V90J5932	71A53A0-001D		Magnetic HID	Core and Coil
Venture	V90J6111	71A55A0-001D		Magnetic HID	Core and Coil
Venture	V90J6211	71A57A0-001D	Dimensions differ significantly	Magnetic HID	Core and Coil
Venture	V90J6212	71A57A0-001D		Magnetic HID	Core and Coil
Venture	V90J6411	71A60A1-001D		Magnetic HID	Core and Coil
Venture	V90J6413	71A60A1-001D		Magnetic HID	Core and Coil
Venture	V90J6514	71A65A2-001		Magnetic HID	Core and Coil
Venture	V90J6612	71A67A2-600		Magnetic HID	Core and Coil
Venture	V90J7110	71A54A3-500D		Magnetic HID	Core and Coil
Venture	V90J7130	71A54A2-500D		Magnetic HID	Core and Coil
Venture	V90J7210	71A55A3-500D		Magnetic HID	Core and Coil
Venture	V90J7310	71A56A2-500D		Magnetic HID	Core and Coil
Venture	V90J7410	71A58A2-500DA		Magnetic HID	Core and Coil
Venture	V90J7411	71A58A2-500DA		Magnetic HID	Core and Coil
Venture	V90J7512	71A59A3-500DA		Magnetic HID	Core and Coil
Venture	V90J7612	71A60A2-500DA		Magnetic HID	Core and Coil
Venture	V90J7810	71A65F3-500T	Advance is 347/480V/120T; Venture is 120/277/347V	Magnetic HID	Core and Coil
Venture	V90J7910	71A64F2-500DT	Advance is 277/347/480V; Venture is 120/277/347V	Magnetic HID	Core and Coil
Venture	V90J8410	71A57A2-500D		Magnetic HID	Core and Coil
Venture	V90J8510	71A6593 (or 71A65F3T)	(71A6593 for 120/208/240/277 or 71A65F3T for 347/480/120T))	Magnetic HID	Core and Coil
Venture	V90J8511	71A6593 (or 71A65F3T)	(71A6593 for 120/208/240/277 or 71A65F3T for 347/480/120T))	Magnetic HID	Core and Coil
Venture	V90J8611	71A64F8-500T	Advance is 347/480V/120T; Venture is 120/277/347V	Magnetic HID	Core and Coil
Venture	V90P1252	71A79E6-500D	Advance is 120/208/240V; Venture is 208V	Magnetic HID	Core and Coil
Venture	V90P1352	71A80E6-500D	Advance is 120/208/240V; Venture is 208V	Magnetic HID	Core and Coil
Venture	V90P1454	71A81E6-500D	Advance is 120/208/240V; Venture is 208V	Magnetic HID	Core and Coil
Venture	V90P1750	71A82E6-500D	Advance is 120/208/240V; Venture is 208V	Magnetic HID	Core and Coil
Venture	V90P1950	71A84E6-500D	Advance is 120/208/240V; Venture is 208V	Magnetic HID	Core and Coil
Venture	V90P2353	71A8773-001	Advance is 120/208/240/277V CWA; Venture is 208V CWI. No cross available with isolated secondary	Magnetic HID	Core and Coil
Venture	V90P6150	71A5570-001D	Advance is 120/208/240/277V CWA; Venture is 208V CWI. No cross available with isolated secondary	Magnetic HID	Core and Coil
Venture	V90P6250	None		Magnetic HID	None
Venture	V90P6450	71A60E6-500	Advance is 120/208/240V; Venture is 208V	Magnetic HID	Core and Coil
Venture	V90P6550	71A6572-001	Advance is 120/208/240/277V CWA; Venture is 277V CWI. No cross available with isolated secondary	Magnetic HID	Core and Coil

NOTE: Philips Lighting Company does not warrant or guarantee the correctness or accuracy of this cross-reference guide. It is provided for the information and convenience of the user. The user is advised to consult the current Philips Advance Atlas or Online Catalog to ascertain and verify that the ballast selected is the appropriate and correct choice for the user's requirements.  
PA4-1441CR

# Cross Reference Guide: Venture to Philips Advance

Competitor Name	Competitor Part Number	Philips Advance	Notes	Ballast Type	Ballast Family
Venture	V90U1131	71A7801-001D	Advance is 120/277V;Venture is 120/240V	Magnetic HID	Core and Coil
Venture	V90U1950	None		Magnetic HID	None
Venture	V90U5720	71A5137-500DBP		Magnetic HID	Core and Coil
Venture	V90U5820	71A5237-500DP	71A5237-500DB and 71A5237-500DJ also available	Magnetic HID	Core and Coil
Venture	V90U5920	71A5337-500DP	71A5337-500DB also available	Magnetic HID	Core and Coil
Venture	V90U5932	71A53A0-001D		Magnetic HID	Core and Coil
Venture	V90U6311	None		Magnetic HID	None
Venture	V90U6450T	None		Magnetic HID	None
Venture	V90U6550	71A65E6-500DT	Advance is 208/240/120T;Venture is 208V only	Magnetic HID	Core and Coil
Venture	V90U6810	None		Magnetic HID	None
Venture	V90U7120	71A5437-500DBP		Magnetic HID	Core and Coil
Venture	V90U7321	71A5692-001D	Advance is Quad CWA,Venture is 277V reactor	Magnetic HID	Core and Coil
Venture	V90U7322	71A5692-001D	Advance is Quad CWA,Venture is 277V reactor	Magnetic HID	Core and Coil
Venture	V90U7421	None		Magnetic HID	None
Venture	V90U7521	None		Magnetic HID	None
Venture	V90U7621	None		Magnetic HID	None
Venture	V90U8421	None		Magnetic HID	None
Venture	V90U8521	None		Magnetic HID	None
Venture	V90V1252	71A79A1-001D	Advance is 120/277/347V HX-HPF;Venture is 347V CWI. No cross available with isolated secondary	Magnetic HID	Core and Coil
Venture	V90V1352	71A80A1-001D	Advance is 120/277/347V HX-HPF;Venture is 347V CWI. No cross available with isolated secondary	Magnetic HID	Core and Coil
Venture	V90V1454	71A81A2-001D	Advance is 120/277/347V HX-HPF;Venture is 347V CWI. No cross available with isolated secondary	Magnetic HID	Core and Coil
Venture	V90V1750	71A82A1-001D		Magnetic HID	Core and Coil
Venture	V90V1950	None		Magnetic HID	None
Venture	V90V2353	71A87A3-001	Advance is 120/277/347V CWA;Venture is 347V CWI. No cross available with isolated secondary	Magnetic HID	Core and Coil
Venture	V90V6150	71A55A0-001D	Advance is 120/277/347V CWA;Venture is 347V CWI. No cross available with isolated secondary	Magnetic HID	Core and Coil
Venture	V90V6250	71A57A0-001D	Advance is 120/277/347V CWA;Venture is 347V CWI. No cross available with isolated secondary	Magnetic HID	Core and Coil
Venture	V90V6450	None		Magnetic HID	None
Venture	V90V6550	71A65A2-001	Advance is 120/277/347V CWA;Venture is 347V CWI. No cross available with isolated secondary	Magnetic HID	Core and Coil
Venture	V90V6610	71A67A2-600	Advance is 120/277/347V;Venture is 347V only	Magnetic HID	Core and Coil
Venture	V90Y1252	71A7941-500D	Advance is HX-HPF;Venture is CWI. No cross available with isolated secondary	Magnetic HID	Core and Coil
Venture	V90Y1352	71A8041-001D	Advance is HX-HPF;Venture is CWI. No cross available with isolated secondary	Magnetic HID	Core and Coil

NOTE: Philips Lighting Company does not warrant or guarantee the correctness or accuracy of this cross-reference guide. It is provided for the information and convenience of the user. The user is advised to consult the current Philips Advance Atlas or Online Catalog to ascertain and verify that the ballast selected is the appropriate and correct choice for the user's requirements.  
PA4-1441CR



# Cross Reference Guide: Venture to Philips Advance

Competitor Name	Competitor Part Number	Philips Advance	Notes	Ballast Type	Ballast Family
Venture	V90Y1454	71A8142-001D	Advance is HX-HPF; Venture is CWI. No cross available with isolated secondary	Magnetic HID	Core and Coil
Venture	V90Y1610T	71A8940-001D	Venture ballast has a 120V tap	Magnetic HID	Core and Coil
Venture	V90Y1711T	71A8241-001D	Venture has a 120V tap	Magnetic HID	Core and Coil
Venture	V90Y1750	None		Magnetic HID	None
Venture	V90Y1911T	71A8443-001D	Venture has a 120V tap	Magnetic HID	Core and Coil
Venture	V90Y1912T	71A8443-001D	Venture has a 120V tap	Magnetic HID	Core and Coil
Venture	V90Y1950	None		Magnetic HID	None
Venture	V90Y2310	71A8743-001		Magnetic HID	Core and Coil
Venture	V90Y2311T	71A8743-001	Venture ballast has a 120V tap	Magnetic HID	Core and Coil
Venture	V90Y2353	71A8743-001	Advance is CWA; Venture is CWI. No cross available with isolated secondary	Magnetic HID	Core and Coil
Venture	V90Y6111	71A5540-001D		Magnetic HID	Core and Coil
Venture	V90Y6111T	71A5540-001D		Magnetic HID	Core and Coil
Venture	V90Y6150	71A5540-001D	Advance is CWA; Venture is CWI. No cross available with isolated secondary	Magnetic HID	Core and Coil
Venture	V90Y6211	71A5741-001D		Magnetic HID	Core and Coil
Venture	V90Y6211T	71A5741-001D	Venture ballast has a 120V tap	Magnetic HID	Core and Coil
Venture	V90Y6212T	None		Magnetic HID	None
Venture	V90Y6250	None		Magnetic HID	None
Venture	V90Y6350	None		Magnetic HID	None
Venture	V90Y6413T	71A6041-001D		Magnetic HID	Core and Coil
Venture	V90Y6450	71A6041-001D	Advance is CWA; Venture is CWI. No cross available with isolated secondary	Magnetic HID	Core and Coil
Venture	V90Y6514T	71A6542-001	Venture has a 120V tap	Magnetic HID	Core and Coil
Venture	V90Y6550	71A6542-001	Advance is CWA; Venture is CWI. No cross available with isolated secondary	Magnetic HID	Core and Coil
Venture	V90Y6611	71A6742-001		Magnetic HID	Core and Coil
Venture	V90Y6612T	71A6742-001	Venture has a 120V tap	Magnetic HID	Core and Coil
Venture	V90Y7110T	71A5442-500DT	Advance is HX-HPF; Venture is CWA	Magnetic HID	Core and Coil
Venture	V90Y7210T	71A5543-500DTEE		Magnetic HID	Core and Coil
Venture	V90Y7310T	71A5642-500DTEE		Magnetic HID	Core and Coil
Venture	V90Y7410T	71A5842-001DT		Magnetic HID	Core and Coil
Venture	V90Y7411T	71A5842-001DT		Magnetic HID	Core and Coil
Venture	V90Y7512T	71A5943-500DTAEE		Magnetic HID	Core and Coil
Venture	V90Y7612T	71A6042-001D		Magnetic HID	Core and Coil
Venture	V90Y7810T	71A65F3-500T	Advance is 347/480V/120T; Venture is 480V	Magnetic HID	Core and Coil
Venture	V90Y7910T	71A64F2-500DT	Advance is 277/347/480V; Venture is 480V/120T	Magnetic HID	Core and Coil
Venture	V90Y8410T	None		Magnetic HID	None
Venture	V90Y8510T	71A6343-500DTEE		Magnetic HID	Core and Coil
Venture	V90Y8511T	71A6343-500DTEE		Magnetic HID	Core and Coil

NOTE: Philips Lighting Company does not warrant or guarantee the correctness or accuracy of this cross-reference guide. It is provided for the information and convenience of the user. The user is advised to consult the current Philips Advance Atlas or Online Catalog to ascertain and verify that the ballast selected is the appropriate and correct choice for the user's requirements.  
PA4-1441CR

# Cross Reference Guide: Venture to Philips Advance

Competitor Name	Competitor Part Number	Philips Advance	Notes	Ballast Type	Ballast Family
Venture	V90Y861IT	71A64F8-500T	Advance is 347/480V/120T; Venture is 480V/120T	Magnetic HID	Core and Coil
Venture	V93D1710	None		Magnetic HID	None
Venture	V93D1910	78E8493-001		Magnetic HID	Indoor Enclosed
Venture	V93D2310	None		Magnetic HID	None
Venture	V93D6110	None		Magnetic HID	None
Venture	V93D6210	None		Magnetic HID	None
Venture	V93D6411	78E6091-001		Magnetic HID	Indoor Enclosed
Venture	V93D6511	78E6592-001		Magnetic HID	Indoor Enclosed
Venture	V93E1950	78E8493-001	Advance is CWA; Venture is CWI. No cross available with isolated secondary	Magnetic HID	Indoor Enclosed
Venture	V93E2353	None		Magnetic HID	None
Venture	V93E6350	None		Magnetic HID	None
Venture	V93E6351	None		Magnetic HID	None
Venture	V93E6550	78E6592-001	Advance is CWA; Venture is CWI. No cross available with isolated secondary	Magnetic HID	Indoor Enclosed
Venture	V93J1910	None		Magnetic HID	None
Venture	V93J2310	None		Magnetic HID	None
Venture	V93J6411	None		Magnetic HID	None
Venture	V93J6511	None		Magnetic HID	None
Venture	V93P6550	78E6592-001	Advance is CWA; Venture is CWI. No cross available with isolated secondary	Magnetic HID	Indoor Enclosed
Venture	V93U1950	78E8493-001	Advance is CWA; Venture is CWI. No cross available with isolated secondary	Magnetic HID	Indoor Enclosed
Venture	V93U6351	None		Magnetic HID	None
Venture	V93V1950	None		Magnetic HID	None
Venture	V93V2353	None		Magnetic HID	None
Venture	V93V6510	None		Magnetic HID	None
Venture	V93Y1910	78E8443-001	Advance is CWA; Venture is CWI. No cross available with isolated secondary	Magnetic HID	Indoor Enclosed
Venture	V93Y1950	78E8443-001	Advance is CWA; Venture is CWI. No cross available with isolated secondary	Magnetic HID	Indoor Enclosed
Venture	V93Y2310	None		Magnetic HID	None
Venture	V93Y2353	None		Magnetic HID	None
Venture	V93Y6210	None		Magnetic HID	None
Venture	V93Y6350	None		Magnetic HID	None
Venture	V93Y6351	None		Magnetic HID	None
Venture	V93Y6411	78E6041-001	Advance is CWA; Venture is CWI. No cross available with isolated secondary	Magnetic HID	Indoor Enclosed
Venture	V93Y6511	78E6542-001	Advance is CWA; Venture is CWI. No cross available with isolated secondary	Magnetic HID	Indoor Enclosed
Venture	V93Y6550	78E6542-001	Advance is CWA; Venture is CWI. No cross available with isolated secondary	Magnetic HID	Indoor Enclosed
Venture	V93Y9150	78E9379-001	Advance is CWA; Venture is CWI. No cross available with isolated secondary	Magnetic HID	Indoor Enclosed
Venture	V94E1750	None		Magnetic HID	None
Venture	V94E1950	79W8493-001	Advance is CWA; Venture is CWI. No cross available with isolated secondary	Magnetic HID	Outdoor Weatherproof

NOTE: Philips Lighting Company does not warrant or guarantee the correctness or accuracy of this cross-reference guide. It is provided for the information and convenience of the user. The user is advised to consult the current Philips Advance Atlas or Online Catalog to ascertain and verify that the ballast selected is the appropriate and correct choice for the user's requirements.  
PA-1441CR

## Cross Reference Guide: Venture to Philips Advance

Competitor Name	Competitor Part Number	Philips Advance	Notes	Ballast Type	Ballast Family
Venture	V94E2353	79W8793-001	Advance is CWA;Venture is CWI. No cross available with isolated secondary	Magnetic HID	Outdoor Weatherproof
Venture	V94E6150	79W5590-001	Advance is CWA;Venture is CWI. No cross available with isolated secondary	Magnetic HID	Outdoor Weatherproof
Venture	V94E6250	79W5790-001	Advance is CWA;Venture is CWI. No cross available with isolated secondary	Magnetic HID	Outdoor Weatherproof
Venture	V94E6350	79W6351-001	Advance is CWA;Venture is CWI. No cross available with isolated secondary	Magnetic HID	Outdoor Weatherproof
Venture	V94E6351	79W6351-001	Advance is CWA;Venture is CWI. No cross available with isolated secondary	Magnetic HID	Outdoor Weatherproof
Venture	V94E6450	79W6091-001	Advance is CWA;Venture is CWI. No cross available with isolated secondary	Magnetic HID	Outdoor Weatherproof
Venture	V94E6550	79W6592-001	Advance is CWA;Venture is CWI. No cross available with isolated secondary	Magnetic HID	Outdoor Weatherproof
Venture	V94E6610	None		Magnetic HID	None
Venture	V94P2353	79W8793-001	Advance is CWA;Venture is CWI. No cross available with isolated secondary	Magnetic HID	Outdoor Weatherproof
Venture	V94P6450	79W6091-001	Advance is CWA;Venture is CWI. No cross available with isolated secondary	Magnetic HID	Outdoor Weatherproof
Venture	V94P6550	79W6592-001	Advance is CWA;Venture is CWI. No cross available with isolated secondary	Magnetic HID	Outdoor Weatherproof
Venture	V94U6450	79W6091-001	Advance is CWA;Venture is CWI. No cross available with isolated secondary	Magnetic HID	Outdoor Weatherproof
Venture	V94U6550	79W6592-001	Advance is CWA;Venture is CWI. No cross available with isolated secondary	Magnetic HID	Outdoor Weatherproof
Venture	V94Y2353	79W8743-001	Advance is CWA;Venture is CWI. No cross available with isolated secondary	Magnetic HID	Outdoor Weatherproof
Venture	V94Y6350	79W6341-001	Advance is CWA;Venture is CWI. No cross available with isolated secondary	Magnetic HID	Outdoor Weatherproof
Venture	V94Y6351	79W6341-001	Advance is CWA;Venture is CWI. No cross available with isolated secondary	Magnetic HID	Outdoor Weatherproof
Venture	V94Y6450	79W6041-001	Advance is CWA;Venture is CWI. No cross available with isolated secondary	Magnetic HID	Outdoor Weatherproof
Venture	V94Y6550	79W6542-001	Advance is CWA;Venture is CWI. No cross available with isolated secondary	Magnetic HID	Outdoor Weatherproof

NOTE: Philips Lighting Company does not warrant or guarantee the correctness or accuracy of this cross-reference guide. It is provided for the information and convenience of the user. The user is advised to consult the current Philips Advance Atlas or Online Catalog to ascertain and verify that the ballast selected is the appropriate and correct choice for the user's requirements.  
PA-d-1441CR