



Distributor Luminaire Stocking Guide

Philips Chloride, Philips Controls,
Philips Day-Brite, Philips Lightolier,
and Philips Stonco October 2013

PHILIPS



Human life revolves around light. Light affects our mood, improves our well-being, and enables us to experience and achieve more. It is a vital part of making our lives fuller, more productive and safer.

At Philips Lighting, we focus on innovative ways of using light to simply enhance people's lives where they live and work—in the home, at school, at work, in shops and public places, as well as on the road. Recognizing how resource conservation and climate protection will play an increasingly significant part in human health and well-being, we pay special attention to maximizing the effects of lighting while minimizing the energy required to produce it.

Philips Lighting provides your business with the broadest portfolio of innovative, energy-efficient products your customers need to light their world, reduce their energy costs, and reduce their carbon footprint. We also offer a broad range of market development tools, promotional services, and educational resources to help you engage your customers more effectively.

PHILIPS

**PHILIPS
CHLORIDE**

**PHILIPS
Day-Brite**

**PHILIPS
LIGHTOLIER**

**PHILIPS
Stonco**

DISTRIBUTOR STOCK GUIDE

Philips is committed to providing our customers with the products they need when they need them. This stock guide contains hundreds of our best selling Philips luminaires and controls. **Our commitment is to ship these items within 48 hours from the time the order is entered and received by our Philips warehouses.**

Customer Service

In order to enhance our customer experience, we have embraced the concept of providing seamless support in the areas of customer fulfillment and sales support. We have established a customer contact center that provides a single point of contact across all brands and products, with first line technical support capability and three supporting hubs. This hub model will improve our efficiency and increase response time to our customers for quotations, order processing management, technical support, warranties and returns. Customers will also see improved fill rates and lead times to ensure on-time order delivery. Our goal is to be the industry leader in providing seamless support to our customer.

Philips Contact Center: 1-855-486-2216

Warehouse Legend and Stock Availability

Philips Lighting maintains stock levels of our lighting products at multiple warehouses. Our warehouses are located in multiple regions across the US in order to provide our customers with quick access to the inventory they require.

Look for the code in the "Warehouse Location" column of this stock guide.

Warehouse legend:

- C** = Carrollton, Texas
- F** = Fontana, California
- N** = Norwich, Connecticut

Stock orders for large quantities should be confirmed by customer service prior to order placement.

In order to avoid delays, it is recommended that stock orders be "stand alone" so that they may be shipped within the promised time-frame.

Terms and Conditions

Freight Terms: Individual order minimum of \$1,000;
\$100 shipping and handling fee for orders less than \$1,000.

1% 10th Prox 2nd, Net 25th Prox 2nd for Stock Orders

1% 10th Prox, Net 25th Prox for Drop Ship/Project Business

Our delivery promise is backed by a significant investment in finished goods and component inventory. If any unforeseen issues arise or if order volume exceeds maximum order quantity, we will do our best to meet your needs.

COMMERCIAL 4

- Troffers
- Direct/Indirect
- Strips
- Wraps

DOWNLIGHTS 7

- Commercial
- Residential

EMERGENCY 15

- Exits
- Combos
- Battery Packs

INDUSTRIAL 20

- High Bays
- Low Bays
- Wet Location

OUTDOOR 22

- Canopy Lighting
- Floods
- Wall Packs
- Wall Sconces
- Area/Site
- Landscape

TRACK 30

- Basic
- Advent
- Lytespan
- Radius
- Track Heads

CONTROLS 35

- OccuSwitch
- Relay Panel
- Sunrise
- MultiSet Pro



Cover photo features Philips Day-Brite recessed LED fixtures installed in an office application.

COMMERCIAL




PHILIPS DAY-BRITE FLUORESCENT Lens Troffers

UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
734340976526	2TG8332-01-UNV-1/21-EB	2' x 4', Grid, 3 Lamp, 32T8, Universal Voltage 120/277V, (2) Electronic Ballast	1	C, N, F	
734340976533	2TG8332-01-UNV-1/3-EB	2' x 4', Grid, 3 Lamp, 32T8, Universal Voltage 120/277V, (1) Electronic Ballast	1	C, N, F	
734340976595	2TG8432-01-UNV-1/4-EB	2' x 4', Grid, 4 Lamp, 32T8, Universal Voltage 120/277V, (1) Electronic Ballast	1	C, N, F	
734340981889	2TG8232-01-UNV-1/2-EB	2' x 4', Grid, 2 Lamp, 32T8, Universal Voltage 120/277V, Electronic Ballast	1	C, N, F	
734340996845	2TG8432-01-UNV-2/2-EB	2' x 4', Grid, 4 Lamp, 32T8, Universal Voltage 120/277V, (2) Electronic Ballast	1	C, N, F	
781370943776	2TG8231U6R-01-UNV-1/2-EB	2' x 2', Grid, 2 Lamp, 31U6T8, Universal Voltage 120/277V, (1) Electronic Ballast	1	C, N, F	
734340007206	2STG217-D-UNV-1/2-EB-LPT735	2' x 2', SofTrace, 2 Lamp, 17WT8, 120/277V, (1) 2 Lamp Electronic Ballast, 35K Lamps Included	1	C	
734340072617	2STG228-D-UNV-1/2-EB95-LPT835	2' x 4', SofTrace, 2 Lamp, 28WT8, 120/277V, (1) 2 Lamp Electronic Ballast, 35K Lamps Included	1	C	
781370017293	2TG8332-01-UNV-1/3-EB101-LPT741	2' x 4', Troffer; 3 Lamp, 32W T8, 120/277V, (1) 3 Lamp Electronic Ballast, 41K Lamps Included	1	C	
734340981896	2TG8332-01-UNV-1/3-EB-LPT735	2' x 4', Troffer; 3 Lamp, 32W T8, 120/277V, (1) 3 Lamp Electronic Ballast, 35K Lamps Included	1	C	
734340981902	2TG8432-01-UNV-1/4-EB-LPT735	2' x 4', Troffer; 4 Lamp, 32W T8, 120/277V, (1) 4 Lamp Electronic Ballast, 35K Lamps Included	1	C, N, F	
734340981919	2TG8432-01-UNV-1/4-EB-LPT741	2' x 4', Troffer; 4 Lamp, 32W T8, 120/277V, (1) 4 Lamp Electronic Ballast, 41K Lamps Included	1	C, N, F	
734340976540	2TG8332-01-UNV-1/3-EB-FI-LPT735	2' x 4', Troffer; 3 Lamp, 32W T8, 120/277V, (1) 3 Lamp Electronic Ballast, 35K Lamps and Flex Included	1	C, F	
782343338797	2TG8332-01-UNV-1/3-EB-FI-LPT741	2' x 4', Troffer; 3 Lamp, 32W T8, 120/277V, (1) 3 Lamp Electronic Ballast, 41K Lamps and Flex Included	1	C	
734340976601	2TG8432-01-UNV-1/4-EB-FI-LPT735	2' x 4', Troffer; 4 Lamp, 32W T8, 120/277V, (1) 4 Lamp Electronic Ballast, 35K Lamps and Flex Included	1	C, F	
734340976618	2TG8432-01-UNV-1/4-EB-FI-LPT741	2' x 4', Troffer; 4 Lamp, 32W T8, 120/277V, (1) 4 Lamp Electronic Ballast, 41K Lamps and Flex Included	1	C	

C = Carrollton, Texas F = Fontana, California N = Norwich, Connecticut

PHILIPS DAY-BRITE FLUORESCENT Option/Accessory/Replacement

UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
782343608647	DSP-IR	Distributor Spare Parts Kit, Fluorescent (Socket Plates, Lampholders, ¼ Turn Fasteners) for T8	1	C, N, F	



PHILIPS DAY-BRITE FLUORESCENT Parabolic Troffers

UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
781370134808	2LP3GS332-36AL-UNV-1/3-EB-LPT735	2' x 4', Grid, 3 Lamp, 32T8, 18 Cells, Universal Voltage 120/277V, (1) Electronic Ballast, Static, 3500K Lamps Inst.	1	C, N, F	
734340079876	2LP3GS231U6R-33AL-UNV-1/2-EB	2' x 2', Grid, 2 Lamp, 31U6T8, 9 Cells, Universal Voltage 120/277V, Electronic Ballast, Static	1	C, N, F	
734340608151	2LP3GC332-36AL-UNV-1/3-EB-ASC	2' x 4', Grid, 3 Lamp, 32T8, 18 Cells, Universal Voltage 120/277V, (1) Electronic Ballast, Combo Air Supply/Return/Heat Removal w/Air Slot Covers	1	C, N, F	
734340728095	2LP3GS332-36AL-UNV-1/3-EB	2' x 4', Grid, 3 Lamp, 32T8, 18 Cells, Universal Voltage 120/277V, (1) Electronic Ballast, Static	1	C, N, F	
734340941807	2LP3GC231U6R-33AL-UNV-1/2-EB-ASC	2' x 2', Grid, 2 Lamp, 31U6T8, 9 Cells, Universal Voltage 120/277V, Electronic Ballast, Combo Air Supply/Return/Heat Removal w/Air Slot Covers	1	C, N, F	
734340971729	2LP3GS332-36AL-UNV-1/21-EB	2' x 4', Grid, 3 Lamp, 32T8, 18 Cells, Universal Voltage 120/277V, (2) Electronic Ballasts, Static	1	C, N, F	
781370200565	2LP3GS332-36AL-UNV-1/3-EB10I-LPT741	2' x 4', Grid, 3 Lamp, 32WT8, 18 Cells, Universal Voltage 120/277V, (1) Electronic Ballast, 41K Lamps Included	1	C,	
781370134808	2LP3GS332-36AL-UNV-1/3-EB-LPT735	2' x 4', Grid, 3 Lamp, 32WT8, 18 Cells, Universal Voltage 120/277V, (1) Electronic Ballast, 35K Lamps Included	1	C, N, F	
734340985634	2LP3GS332-36AL-UNV-1/3-EB-F1-LPT735	2' x 4', Grid, 3 Lamp, 32WT8, 18 Cells, Universal Voltage 120/277V, (1) Electronic Ballast, 35K Lamps and Flex Included	1	C, F	



PHILIPS DAY-BRITE FLUORESCENT Recessed Direct/Indirect

UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
662057204246	CFS2GPF232UNVHI	Coffaire, 2' x 4', Grid, 2 Lamp, 32T8, Universal Voltage 120/277V, Electronic Ballast, Center Basket	1	C, N, F	
782343969861	CFS2GPF332UNVH3	Coffaire, 2' x 4', Grid, 3 Lamp, 32T8, Universal Voltage 120/277V, (1) Electronic Ballast, Center Basket	1	C, N, F	
782343969847	CFS2GPF2FTUNVPR	Coffaire, 2' x 2', Grid, 2 Lamp, Compact Fluorescent, 40WTT5, Universal Voltage 120/277V, Electronic Ballast, Center Basket	1	C, N, F	

C = Carrollton, Texas F = Fontana, California N = Norwich, Connecticut

Pictures are representative of product categories and may not illustrate the exact products listed on the pages of this stock guide. Product information may change without notice. Contact your local Philips sales representative for additional product information.

COMMERCIAL



PHILIPS DAY-BRITE FLUORESCENT Architectural

UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
782343332184	2HVAG217-D-UNV-1/2-EB-LPT735	2' HVA Recessed Grid, 2 Lamp, 17W T8, 120/277V, (1) 2 Lamp Electronic Ballast, 35K Lamps Included	1	C, N, F	
782343517345	2HVAG228-D-UNV-1/2-EB-LPT835	2' HVA Recessed Grid, 2 Lamp, 28W T8, 120/277V, (1) 2 Lamp Electronic Ballast, 35K Lamps Included	1	C, N, F	
782343332160	2HVAG232-D-UNV-1/2-EB-LPT735	2' HVA Recessed Grid, 2 Lamp, 32W T8, 120/277V, (1) 2 Lamp Electronic Ballast, 35K Lamps Included	1	C, N, F	



PHILIPS DAY-BRITE FLUORESCENT Strips

UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
734340776195	NI32-UNV-1/1-EB	4' Length, 1 Lamp, 32T8, Universal Voltage 120/277V, Electronic Ballast	1	C, N, F	
734340608328	T232-UNV-1/2-EB	4' Length, 2 Lamp, 32T8, Universal Voltage 120/277V, Electronic Ballast	1	C, N, F	
734340608342	TT232-UNV-1/4-EB	8' Length, 2 Lamp Tandem (4 lamps), 32T8, Universal Voltage 120/277V, (1) Electronic Ballast	1	C, N, F	
734340698688	T259-UNV-1/2-EB	8' Length, 2 Lamp, 59T8, Universal Voltage 120/277V, Electronic Ballast	1	C, N, F	
781370064440	TH296HO-120-1/2-EB	8' Length, Heavy Duty Channel, 2 Lamp, 110T12HO 800mA, 120V, Electronic Ballast	1	C, N, F	

PHILIPS DAY-BRITE FLUORESCENT Wraps

UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
734340608281	OWN232-UNV-1/2-EB	8 $\frac{5}{8}$ " Width, 4' Length, Narrow, 2 Lamp, 32T8, Universal Voltage 120/277V, Electronic Ballast	1	C, N, F	
734340608298	OWWW432-UNV-1/4-EB	13 $\frac{7}{8}$ " Width, 4' Length, Wide, 4 Lamp, 32T8, Universal Voltage 120/277V, (1) Electronic Ballast	1	C, N, F	

C = Carrollton, Texas F = Fontana, California N = Norwich, Connecticut

DOWNLIGHTS



PHILIPS LIGHTOLIER DOWNLIGHTING 3 3/4" Recessed Frame

UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
784197200022	2000AIC	3 3/4" Recessed Aperture Incandescent Insulated Ceiling AirSeal® Frame-In Kit	2	N	
784197200015	2000IC	3 3/4" Recessed Aperture Incandescent Insulated Ceiling Frame-In Kit	2	N	
784197146672	2000LV	3 3/4" Recessed Aperture Low Voltage MR16 Standard Frame-In Kit	1	N	
784197200053	2000LVR	3 3/4" Recessed Aperture Standard Low Voltage MR16 Remodeler Frame-In Kit	1	N	
784197146658	2002PI	3 3/4" Recessed Aperture Incandescent Standard Non-IC Frame-In Kit	6	N	
784197174590	2003R	3 3/4" Recessed Aperture Lytening Incandescent Non-IC Remodeler Frame-In Kit	6	N	
784197239541	2004ICV	3 3/4" Recessed Aperture Lytening Low Voltage AirSeal® Insulated Frame-In Kit, 50W MR16	1	N	



PHILIPS LIGHTOLIER DOWNLIGHTING 3 3/4" Recessed Trim

UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
784197146627	2013	3 3/4" Recessed Clear Specular Cone Reflector	6	N	
784197200107	2005WH	3 3/4" Recessed Aperture Step Baffle Reflector Trim, Matte White	6	F	
784197201302	2013WH	3 3/4" Recessed Aperture Cone Reflector Trim, Matte White	1	C	
784197386962	2025WH	3 3/4" Recessed MR16 Mini Swivel Round Reflector Trim, Matte White	1	F	
662057206080	2076WH	3 3/4" Recessed Aperture Step Baffle Reflector Trim, Gloss White	6	N	

C = Carrollton, Texas F = Fontana, California N = Norwich, Connecticut

Pictures are representative of product categories and may not illustrate the exact products listed on the pages of this stock guide. Product information may change without notice. Contact your local Philips sales representative for additional product information.

DOWNLIGHTS



PHILIPS LIGHTOLIER DOWNLIGHTING 5" Recessed Frame

UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
784197119959	I000IC	5" Recessed Aperture Incandescent Insulated Ceiling, AirSeal® Frame-In Kit	4	N	
784197120078	I002PI	5" Recessed Aperture Incandescent Non-IC Standard Frame-In Kit	6	N	
784197174576	I003R	5" Recessed Aperture Lytening Incandescent Non-IC Remodeler Frame-In Kit	6	N	
784197523985	I004F26ESN	5" Recessed Aperture Lytening 1 Lt 26W Quad/Triple Tube Compact Fluorescent IC Frame-In Kit	1	N	
784197159290	I004IC	5" Recessed Aperture Lytening AirSeal® Incandescent Convertible IC/Non-IC Frame-In Kit	8	N	
784197198596	I004ICN	5" Recessed Aperture Lytening AirSeal® Incandescent Convertible IC/Non-IC Frame-In Kit Pre-installed Nailer Bars	8	N	
784197291839	I004ICNQ	5" Recessed Aperture Lytening AirSeal® Incandescent Convertible IC/Non-IC Frame-In Kit Pre-installed Nailer Bars Quick Connectors	8	N	
784197159320	I004ICR	5" Recessed Aperture Lytening Incandescent Convertible IC/Non-IC Remodeler Frame-In Kit	1	N	
784197219826	I004ICX	5" Recessed Aperture Lytening High Wattage Incandescent AirSeal® Insulated Ceiling Frame-In Kit	4	N	
784197198503	I004SIC	5" Recessed Aperture Lytening Shallow Incandescent Convertible IC/Non-IC Frame-In Kit for 2 x 6 Constar	8	N	



PHILIPS LIGHTOLIER DOWNLIGHTING 5" Recessed Trim

UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
784197120450	I013	5" Recessed Aperture Cone Reflector Trim, Specular Clear	6	N	
784197120696	I071	5" Recessed Aperture Basic White Open Reflector Trim	6	N	
784197120702	I076	5" Recessed Aperture, Basic Black Baffle Reflector Trim	6	N	
784197107604	I076WH	5" Recessed Aperture, Basic White Baffle Reflector Trim	6	N	
784197359706	I013CD	5" Recessed Aperture Cone Reflector Trim, Clear Diffuse	6	N	
784197101305	I013WH	5" Recessed Aperture Cone Reflector Trim, Matte White	1	N	
784197100506	I005WH	5" Recessed Aperture Step Baffle Reflector Trim, Matte White	6	N	
784197205874	C76WH	5" Recessed Spun White Baffle Reflector Trim	12	F	

C = Carrollton, Texas F = Fontana, California N = Norwich, Connecticut

DOWNLIGHTS



PHILIPS LIGHTOLIER DOWNLIGHTING 6¾" Recessed Frame

UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
784197110239	I100IC	6¾" Recessed Aperture Incandescent Insulated Ceiling Non-IC Frame-In Kit	4	N	
784197110222	I102PI	6¾" Recessed Aperture Incandescent Standard Non-IC Frame-In Kit	6	N	
784197174583	I103R	6¾" Recessed Aperture Lytening Incandescent Non-IC Remodeler Frame-In Kit	6	N	
662057517995	I104IC	6¾" Recessed Apertures Lytening Incandescent Convertible IC/Non-IC Frame-In Kit	8	N	
784197198589	I104ICN	6¾" Recessed Apertures Lytening Incandescent Convertible IC/Non-IC Frame-In Kit Pre-Installed Nailers	8	N	
784197291815	I104ICNQ	6¾" Recessed Apertures Lytening Incandescent Convertible IC/Non-IC Frame-In Kit Pre-Installed Nailers Quick Connector	8	N	
784197159337	I104ICR	6¾" Recessed Lytening AirSeal® IC/Non-IC Remodeler Frame-In Kit	1	N	
784197219819	I104ICX	6¾" Recessed Aperture Lytening High Wattage Incandescent AirSeal® Insulated Ceiling Frame-In Kit	4	N	
784197239015	I104ICXN	6¾" Recessed Aperture Lytening High Wattage Incandescent AirSeal® Insulated Ceiling Frame-In Kit Pre-Installed Nailers	4	N	



PHILIPS LIGHTOLIER DOWNLIGHTING 6¾" Recessed Trim

UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
784197546069	I101CD	6¾" Recessed Aperture Vertical Open Downlight, Clear Diffuse	1	N	
784197546052	I101CL	6¾" Recessed Aperture Vertical Open Downlight, Specular Clear	1	N	
784197973094	I101HCD	6¾" Recessed Horizontal Open Downlight, Clear Diffuse	1	N	
784197546144	I101HCL	6¾" Recessed Horizontal Open Downlight, Specular Clear	1	N	
784197123352	I113	6¾" Recessed Aperture Cone Reflector Trim, Specular Clear	6	F	
784197117108	I171	6¾" Recessed Aperture Basic White Reflector Trim	6	N	
784197003500	I176	6¾" Recessed Aperture Basic Baffle Reflector Trim, Black	6	N	
784197110703	I105WH	6¾" Recessed Aperture Step Baffle Reflector Trim, Matte White	6	N	
784197243609	I117WH	6¾" Recessed White Baffle Reflector Trim	12	F	

C = Carrollton, Texas F = Fontana, California N = Norwich, Connecticut


Pictures are representative of product categories and may not illustrate the exact products listed on the pages of this stock guide. Product information may change without notice. Contact your local Philips sales representative for additional product information.

DOWNLIGHTS



PHILIPS LIGHTOLIER DOWNLIGHTING 6 3/4" Recessed Trim

UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
784197113520	I131WH	6 3/4" Recessed Aperture Shallow Slope Ceiling Reflector Trim 14°-30° Angle, 3/2"-7/2" Pitch, White Step Baffle	1	F	
784197003517	I176WH	6 3/4" Recessed Aperture Basic White Baffle Reflector Trim	6	N	
784197194758	I177LX	6 3/4" Recessed Aperture Flush Glass Shower Trim Reflector	1	N	
784197290580	B17WH	6 3/4" Recessed Aperture Lytensing B-Series Incandescent Reflector Trim, Gloss White	12	F	



PHILIPS LIGHTOLIER DOWNLIGHTING 5" XCEED LED



UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
662057482880	I050LRN0927	Xceed Lytecaster LED 5", Round Lensed Downlight, Light Engine, 900 Lumens, 2700K	1	N	
662057483139	I050LRN0935	Xceed Lytecaster LED 5", Round Lensed Downlight, Light Engine, 900 Lumens, 3500K	1	N	
662057482613	I050LRN09DI	Xceed Lytecaster LED 5", Round Lensed Downlight, 900 Lumen, 120V Dimming	1	N	
662057482804	I050LRN09DIN	Xceed Lytecaster LED 5", Round Lensed Downlight, 900 Lumens, 120V Dimming, with Nailers Bars	1	N	
662057483504	I050LRNDLCDW	Xceed Lytecaster LED 5", Round Lensed Downlight, Trim, Clear Diffuse, White Flange	1	N	
662057483511	I050LRNDLWB	Xceed Lytecaster LED 5", Round Lensed Downlight, Trim, White Baffle, White Flange	1	N	



PHILIPS LIGHTOLIER DOWNLIGHTING 5" Lytensing LED Frame



UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
662057784625	I004ICNLED	5" Lytensing LED, IC Frame-In Kit, with Nails	8	N	
662057784618	I004ICLED	5" Lytensing LED, IC Frame-In Kit, with Screws	8	N	

C = Carrollton, Texas F = Fontana, California N = Norwich, Connecticut

DOWNLIGHTS



PHILIPS LIGHTOLIER DOWNLIGHTING 5" Lytening LED Trim



UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
662057788517	I076WHL27K	Lytening LED, White Baffle Trim, 650 Lumen, 2700K, 120V, Dimming	1	N	
662057788524	I076WHL30K	Lytening LED, White Baffle Trim, 650 Lumen, 3000K, 120V, Dimming	1	N	



PHILIPS LIGHTOLIER DOWNLIGHTING 4" and 6" LED Retrofit




UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
662057878928	CP630K6	6" CorePro LED Downlight, 600 Lumens, 30K, 120V	1	N	
662057878942	CP630K10	6" CorePro LED Downlight, 1000 Lumens, 30K, 120V	1	N	
662057878959	CP430K6	4" CorePro LED Downlight, 600 Lumens, 30K, 120V	1	N	



PHILIPS LIGHTOLIER DOWNLIGHTING 6 3/4" CFL Non IC Uniframe

UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
784197545499	I101F2642U	6 3/4" Aperture, 1 Light, Compact Fluorescent, Non-IC, Frame-In Kit, 120/277V, 26W Quad/Triple, 32W Triple, 42W Triple	6	N	



PHILIPS LIGHTOLIER DOWNLIGHTING 5" LED Non IC Uniframe



UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
662057383668	I001LED09N271	Lytecaster LED 5", Non-IC, 120V, 900 Lumens, 2700K, Frame-In Kit	1	N	
662057383750	I001LED09N352	Lytecaster LED 5", Non-IC, 277V, 900 Lumens, 3500K, Frame-In Kit	1	N	

C = Carrollton, Texas F = Fontana, California N = Norwich, Connecticut

Pictures are representative of product categories and may not illustrate the exact products listed on the pages of this stock guide. Product information may change without notice. Contact your local Philips sales representative for additional product information.

DOWNLIGHTS



PHILIPS LIGHTOLIER DOWNLIGHTING 6¾" LED Non IC Uniframe



UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
662057441108	1101LED09N351	Lytecaster LED 6¾", 900 Lumen, Non-IC, 120V, 3500K	1	N	
662057383538	1101LED09N352	Lytecaster LED 6¾", 900 Lumen, Non-IC 277V, 3500K	1	N	



PHILIPS LIGHTOLIER DOWNLIGHTING Accessories

UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
784197367237	LAS56	Lytecaster AirSeal® Gasket for Use with 1004 & 1104 Lytening Frame-In Kits	12	N	
784197145132	1956	T-Bar Ceiling Clips for Use with Series 2000, 1000 and 1102HF	12	N	
662057794396	LARFA	Lytening Incandescent-to-LED Retrofit Adapter	1	N	



PHILIPS LIGHTOLIER DOWNLIGHTING Lytepoints

UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
662057037233	302MRIC7SPX	Lytepoints, MR16 Mag. 7" IC Frame-In-Kit Silent Pack, Accepts All 3¾" (95mm) 300X Series Trims, 50W	1	N	
662057037226	302MRIC9SPX	Lytepoints, MR16 Mag. 9" IC Frame-In-Kit Silent Pack, Accepts All 3¾" (95mm) 300X Series Trims, 50W	1	N	
662057037196	300MRSPX	Lytepoints, MR16 Magnetic, Remodeler, Silent Pack, Accepts All 3¾" (95mm) 300X Series Trims, 50W	1	N	
662057037141	302MRSPX	Lytepoints, MR16 Magnetic, Non-IC Frame-In-Kit, Silent Pack, Accepts All 3¾" (95mm) 300X Series Trims, 50W	1	N	
784197316341	303MRE	3¾" Aperture Lytepoints Low Voltage MR16 12V Ultra Shallow Electronic Remodeler (Non-IC)	1	N	
624563100962	304CCDX	Lytepoints, 3¾" (95mm) Aperture Adjustable Specular Cone MR16 & ES/ESD16, Clear Diffuse/White Flange, 50W	1	N	
624563083418	304CLX	Lytepoints, 3¾" (95mm) Aperture Adjustable Specular Cone MR16 & ES/ESD16, Clear Specular/White Flange	1	N	
624563083319	305WHWX	Lytepoints, 3¾" (95mm) Aperture Adjustable Premium Die-Cast Step Baffle MR16 & ES/ESD16, Matte White	1	N	

C = Carrollton, Texas F = Fontana, California N = Norwich, Connecticut

DOWNLIGHTS



PHILIPS LIGHTOLIER DOWNLIGHTING Lytepoints

UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
784197435714	313WHX	Lytepoints, 3¾" (95mm) Aperture Deep Residence MRI 6, White	I	N	
784197436018	340IMREX	Lytepoints, 3¾" (95mm) Aperture, Low Voltage MRI 6 12V, Low-Profile Electronic Remodeler	I	N	
784197436070	374CHX	Lytepoints, 3¾" (95mm) Aperture Basic Adjustable Cone MRI 6 & ES/ESD 16, Chrome/White Flange	I	F	
784197436094	375WHX	Lytepoints, 3¾" (95mm) Aperture Basic Baffle MRI 6 & ES/ESD 16, White Baffle/Flange	I	N	
784197436339	378WHX	Lytepoints, 3¾" (95mm) Aperture Adjustable Elbow MRI 6, White	I	N	



PHILIPS LIGHTOLIER DOWNLIGHTING 6" C Plus Incandescent Frames

UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
783238169021	PR75ASICNB	6" AirSeal®/IC New Construction Recessed Housing, No Bracket	6	C, N, F	
783238131233	CRR1NBQP	6" IC/Non-IC Remodeler Recessed Housing, No Bracket, Quick Plugs	8	C, N, F	
783238188886	QL6NBQP	6" IC/Non-IC, AirSeal® Quicklights Recessed Housing, No Bracket, Quick Plugs	8	C, N, F	
783238154447	P4	4" Non-IC Recessed Housing	6	C, N, F	
783238154454	P4ASIC	4" IC Recessed Housing	6	C, N, F	
783238154461	P4R	4" Non-IC Remodeler Recessed Housing	6	C, N, F	

C = Carrollton, Texas F = Fontana, California N = Norwich, Connecticut

Pictures are representative of product categories and may not illustrate the exact products listed on the pages of this stock guide. Product information may change without notice. Contact your local Philips sales representative for additional product information.

DOWNLIGHTS



PHILIPS LIGHTOLIER DOWNLIGHTING 6" C Plus Incandescent Trim

UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
783238137020	RBC30WM	6" PAR38, PAR30, BR30 Cone Grooved Baffle, White	8	C, N, F	
783238137013	RBC30M-CS	6" PAR38, PAR30, BR30 Cone Grooved Baffle, Black	8	C, N, F	
783238121388	RB30W	6" PAR38, PAR30, BR30 Grooved Baffle, White	8	C, N, F	
783238121395	RB40W	6" PAR38, BR40 Grooved Baffle, White	8	C, N, F	
783238039850	RB30	6" PAR38, PAR30, BR30 Grooved Baffle, Black	8	C, N, F	
783238039966	RS30W	6" PAR30 White Spay Trim	8	C, N, F	
783238154386	RF30W	6" PAR30 White Large Flange Trim	8	C, N, F	
783238121166	R18P	6" Eyeball BR30, White	6	C, N, F	
783238015267	SHR16IC	6" A19 Drop Opal Shower Trim, White Plastic Flange	6	C, N, F	
783238017551	SHR12IC	6" A19 Albalite Regressed Lens Shower Trim, White Plastic Flange	6	C, N, F	
783238039928	RC30W	6" A19 White Cone, White Flange	8	C, N, F	



PHILIPS LIGHTOLIER DOWNLIGHTING 6" C Plus CFL Frame

UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
783238182891	PR26ASICNBNE1	6" AirSeal®/IC 26W CFL Vertical New Construction Recessed Housings	1	C, N, F	



PHILIPS LIGHTOLIER DOWNLIGHTING 6" C Plus CFL Trim

UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
783238161476	SHR6ICW	6" Regressed Shower Trim, Wet Location, CFL Vertical White	6	C, N, F	
783238039904	RC30C	6" Clear Cone for INC or CFL White Flange	8	C, N, F	

C = Carrollton, Texas F = Fontana, California N = Norwich, Connecticut



PHILIPS CHLORIDE 44R Line Universal Edge-Lit LED Exit

UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
734340234497	44RLUIR	44R LINE-LED Edge-Lit (AC Only) Exit Sign, Universal Mounting; Surface (Ceiling, Wall, & End) and Recessed (Ceiling & Wall), Red, Single Face, Clear Background, Satin Aluminum Housing, 120/277V Selectable Input	3	C, N, F	
734340234503	44RLU2R	44R LINE-LED Edge-Lit (AC Only) Exit Sign, Universal Mounting; Surface (Ceiling, Wall, & End) and Recessed (Ceiling & Wall), Red, Double Face, Mirror Background, Satin Aluminum Housing, 120/277V Selectable Input	3	C, N, F	
734340234510	44RLUIG	44R LINE-LED Edge-Lit (AC Only) Exit Sign, Universal Mounting; Surface (Ceiling, Wall, & End) and Recessed (Ceiling & Wall), Green, Single Face, Clear Background, Satin Aluminum Housing, 120/277V Selectable Input	3	C, F	
734340234527	44RLU2G	44R LINE-LED Edge-Lit (AC Only) Exit Sign, Universal Mounting; Surface (Ceiling, Wall, & End) and Recessed (Ceiling & Wall), Green, Double Face, Mirror Background, Satin Aluminum Housing, 120/277V Selectable Input	3	C, F	
734340234367	ER44RLDU1R	44R LINE-LED Edge-Lit (Self-powered) Exit Sign, Universal Mounting; Surface (Ceiling, Wall, & End) and Recessed (Ceiling & Wall), Red, Single Face, Clear Background, Satin Aluminum Housing, 120/277V Selectable Input	3	C, N, F	
734340234374	ER44RLDU2R	44R LINE-LED Edge-Lit (Self-powered) Exit Sign, Universal Mounting; Surface (Ceiling, Wall, & End) and Recessed (Ceiling & Wall), Red, Double Face, Mirror Background, Satin Aluminum Housing, 120/277V Selectable Input	3	C, N, F	
734340234404	ER44RLDU1G	44R LINE-LED Edge-Lit (Self-powered) Exit Sign, Universal Mounting; Surface (Ceiling, Wall, & End) and Recessed (Ceiling & Wall), Green, Single Face, Clear Background, Satin Aluminum Housing, 120/277V Selectable Input	3	C, N, F	
734340234411	ER44RLDU2G	44R LINE-LED Edge-Lit (Self-powered) Exit Sign, Universal Mounting; Surface (Ceiling, Wall, & End) and Recessed (Ceiling & Wall), Green, Double Face, Mirror Background, Satin Aluminum Housing, 120/277V Selectable Input	3	C, N, F	



PHILIPS CHLORIDE 55 Line Die Cast Aluminum LED Exit



UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
781370104085	55L3R	55 LINE-Die Cast Aluminum (AC Only) Exit Sign, Black Housing with Brushed Aluminum Face Plate, Red Letters, Universal Mount, Single or Double Face, 120/277V Selectable Input, Concealed Chevrons	6	C, N, F	
781370104047	ER55L3R	55 LINE-Die Cast Aluminum (Self-powered) Exit Sign, Black Housing with Brushed Aluminum Face Plate, Red Letters, Universal Mount, Single or Double Face, 120/277V Selectable Input, Concealed Chevrons	6	C, N, F	
782343390580	55L3WR	55 LINE-Die Cast Aluminum (AC Only) Exit Sign, White Housing with White Face Plate, Red Letters, Universal Mount, Single or Double Face, 120/277V Selectable Input, Concealed Chevrons	6	C, N, F	
781370621698	ER55L3WR	55 LINE-Die Cast Aluminum (Self-powered) Exit Sign, White Housing with White Face Plate, Red Letters, Universal Mount, Single or Double Face, 120/277V Selectable Input, Concealed Chevrons	6	C, F	
781370104054	ER55L3G	55 LINE-Die Cast Aluminum (Self-powered) Exit Sign, Black Housing with Brushed Aluminum Face, Green Letters, Universal Mount, Single or Double Face, 120/277V Selectable Input, Concealed Chevrons	6	C, F	

C = Carrollton, Texas F = Fontana, California N = Norwich, Connecticut

EMERGENCY



PHILIPS CHLORIDE Architectural Patron Series Die Cast Emergency Unit

UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
781370379858	PDNBZ	Patron Series—Die Cast Aluminum Emergency Unit, Nickel Cadmium Battery, Two 6V—6W Bi-pin Halogen Lamps, Wet Location, Operating Temperature Range 0°F—122°F, Dark Bronze Finish	2	C, N, F	
781370379889	PDNW	Patron Series—Die Cast Aluminum Emergency Unit, Nickel Cadmium Battery, Two 6V—6W Bi-pin Halogen Lamps, Wet Location, Operating Temperature Range 0°F—122°F, White Finish	2	C, N, F	



PHILIPS CHLORIDE Emergency Battery Packs

UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
734340643596	DEB-1W	Fluorescent Emergency Ballast, Damp Listed, 350—400 Lumens, 1 or 2 Lamp Operation—FIELD INSTALLED	20	C, N, F	
782343823422	DEB-7W	Fluorescent Emergency Ballast, Damp Listed, 600—700 Lumens, 1 or 2 Lamp Operation—FIELD INSTALLED	20	C, N, F	
734340624021	DEB-5W	Fluorescent Emergency Ballast, Damp Listed, 1100—1400 Lumens, 1 or 2 Lamp Operation, End of Lamp Life Compatible—FIELD INSTALLED	10	C, N, F	



PHILIPS CHLORIDE VALUE+ VE Series Thermoplastic LED Exit

UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
782343263006	VERW	Value+ VE Series (Contractor Grade) Thermoplastic Exit Sign, AC Only, White Housing, Red Letters, 120/277V Selectable Input, Removable Chevrons	12	C, N, F	
782343263020	VEGW	Value+ VE Series (Contractor Grade) Thermoplastic Exit Sign, AC Only, White Housing, Green Letters, 120/277V Selectable Input, Removable Chevrons	12	C, N, F	
782343263037	VERWEM	Value+ VE Series (Contractor Grade) Thermoplastic Exit Sign, Self-powered, White Housing, Red Letters, 120/277V Selectable Input, Removable Chevrons	12	C, N, F	
781370213190	VRERWEM	Value+ VE Series (Contractor Grade) Thermoplastic Exit Sign, Self-powered, White Housing, Red Letters, 120/277V Selectable Input, 22W Remote Capability	6	C, N, F	
782343263044	VEGWEM	Value+ VE Series (Contractor Grade) Thermoplastic Exit Sign, Self-powered, White Housing, Green Letters, 120/277V Selectable Input, Removable Chevrons	12	C, N, F	

C = Carrollton, Texas F = Fontana, California N = Norwich, Connecticut



PHILIPS CHLORIDE VALUE+ VC Series Thermoplastic Combo

UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
782343262986	VCRW	Value+ VC Series (Contractor Grade) White Thermoplastic Combo, 6V-5.4W Tungsten Lamps, Sealed Lead Calcium Battery, 120/277V Selectable Input, Red Letters, 12W Remote Capability	2	C, N, F	
781370908478	VCRWLRC	Value+ VC Series (Contractor Grade) White Thermoplastic Combo, 6V-5.4W Tungsten Lamps, Sealed Lead Calcium Battery, 120/277V Selectable Input, Red Letters	2	C, N, F	
782343262993	VCGW	Value+ VC Series (Contractor Grade) White Thermoplastic Combo, 6V-5.4W Tungsten Lamps, Sealed Lead Calcium Battery, 120/277V Selectable Input, Green Letters, 12W Remote Capability	2	C, F	



PHILIPS CHLORIDE VALUE+ VU6F Series Thermoplastic Unit

UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
782343579749	VU6F	Value+ VU6F Series (Contractor Grade) Fixed Lens Thermoplastic Unit, Sealed Lead Calcium Battery, 6V-5.4W Tungsten Lamps, White Housing, 120/277V Selectable Input	6	C, F	



PHILIPS CHLORIDE VALUE+ VU6 Series Thermoplastic Unit

UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
782343558386	VU6-CS	Value+ VU6 Series (Contractor Grade) Thermoplastic Unit, Sealed Lead Calcium Battery, 6V-5.4W Tungsten Lamps, White Housing, 120/277V Selectable Input	6	C, N, F	



PHILIPS CHLORIDE VALUE+ II VX Series Thermoplastic LED Exit

UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
782343753545	VXL3RW	Value+ II VX Series (Spec Grade) Thermoplastic Exit Sign, AC Only, White Housing, Red Letters, 120/277V Selectable Input, Removable Chevrons	12	C, N, F	
782343753552	VXL3GW	Value+ II VX Series (Spec Grade) Thermoplastic Exit Sign, AC Only, White Housing, Green Letters, 120/277V Selectable Input, Removable Chevrons	12	C, N, F	
782343753569	VXL3RWEM	Value+ II VX Series (Spec Grade) Thermoplastic Exit Sign, Self-powered, White Housing, Red Letters, 120/277V Selectable Input Removable Chevrons	12	C, N, F	
782343753576	VXL3GWEM	Value+ II VX Series (Spec Grade) Thermoplastic Exit Sign, Self-powered, White Housing, Green Letters, 120/277V Selectable Input, Removable Chevrons	12	C, N, F	

C = Carrollton, Texas F = Fontana, California N = Norwich, Connecticut

EMERGENCY



PHILIPS CHLORIDE VALUE+ II VCA Series Thermoplastic Combo

UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
782343753583	VCAL3RW	Value+ II VCA Series (Spec Grade) Semi-Recessed Lamp Heads Thermoplastic Combo, Sealed Lead Calcium Battery, White Housing, Red Letters, 6V-6W MR16 Lamps, 120/277V Selectable Input, Removable Chevrons	4	C, N, F	
782343753590	VCAL3GW	Value+ II VCA Series (Spec Grade) Semi-Recessed Lamp Heads Thermoplastic Combo, Sealed Lead Calcium Battery, White Housing, Green Letters, 6V-6W MR16 Lamps, 120/277V Selectable Input, Removable Chevrons	4	C, N, F	



PHILIPS CHLORIDE VALUE+ II VCT Series Thermoplastic Combo

UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
782343753606	VCTL3RW	Value+ II VCT Series (Spec Grade) Thermoplastic Combo, Sealed Lead Calcium Battery, White Housing, Red Letters, 6V-5.4W Tungsten Lamps, 120/277V Selectable Input, Removable Chevrons	4	C, N, F	
782343753613	VCTL3GW	Value+ II VCT Series (Spec Grade) Thermoplastic Combo, Sealed Lead Calcium Battery, White Housing, Green Letters, 6V-5.4W Tungsten Lamps, 120/277V Selectable Input, Removable Chevrons	4	C, N, F	



PHILIPS CHLORIDE VALUE+ II VF6 Series Thermoplastic Unit

UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
782343753644	VF6	Value+ II VF6 Series (Spec Grade) Fixed Lens Thermoplastic Unit, Sealed Lead Calcium Battery, White Housing, 6V-5W MR11 Lamp, 120/277V Selectable Input	6	C, N, F	



PHILIPS CHLORIDE VALUE+ II VA6 Series Thermoplastic Unit

UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
782343753651	VA6	Value+ II VA6 Series (Spec Grade) Semi-Recessed Lamp Head Thermoplastic Unit, Sealed Lead Calcium Battery, White Housing, 6V-6W MR16 Lamps, 120/277V Selectable Input	6	C, N, F	

C = Carrollton, Texas F = Fontana, California N = Norwich, Connecticut



PHILIPS CHLORIDE VALUE+ II VT6 Series Thermoplastic Unit

UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
782343753668	VT6	Value+ II VT6 Series (Spec Grade) Thermoplastic Unit, Sealed Lead Calcium Battery, White Housing, 6V-5.4W Tungsten Lamps, 120/277V Selectable Input	6	C, N, F	
782343753675	VT618	Value+ II VT6 Series (Spec Grade) Thermoplastic Unit, Sealed Lead Calcium Battery, White Housing, 6V-9W Tungsten Lamps, 120/277V Selectable Input	6	C, N, F	



PHILIPS CHLORIDE VALUE+ II VT Series Thermoplastic Unit

UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
782343753682	VT6L24WCSWF	Value+ II VT Series (Spec Grade) Thermoplastic Unit, Sealed Lead Calcium Battery, White Housing, 6V-12W Halogen Lamps, 120/277V Selectable Input	6	C, N, F	




PHILIPS CHLORIDE CCRHP Series Outdoor Single Remote Metal Chrome Lamp Head

UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
734340592573	CCRHP	Weatherproof Remote Metal Chrome Lamp Head (Includes Mounting Plate), 6V-6W Sealed Beam Halogen Lamps	1	C, N, F	

C = Carrollton, Texas F = Fontana, California N = Norwich, Connecticut

Pictures are representative of product categories and may not illustrate the exact products listed on the pages of this stock guide. Product information may change without notice. Contact your local Philips sales representative for additional product information.

INDUSTRIAL



PHILIPS DAY-BRITE FLUORESCENT High Bay

UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
782343264003	FBD654HO-UNV-1/42-EB	T5 Fluorescent High Bay, Steel Housing w/Miro 4 Reflectors, 6 Lamp, 54WT5HO, (1) 4 Lamp and (1) 2 Lamp Universal Voltage Electronic Ballasts	1	C, N, F	
782343199558	FBD454HO-UNV-1/4-EB-2LS	Fluorescent High Bay, 4 Lamp, 54W T5HO, One Step Level Universal Voltage Electronic Ballast	1	C, N, F	
782343393406	FBD632-UNV-1/42-EB	T8 Fluorescent High Bay, Steel Housing w/Miro 4 Reflectors, 6 Lamp, 32WT8, (1) 4 & (1) 2 Lamp. Electronic Ballasts. 120/277V	1	C, N, F	
781370531225	FBF/FBE CHAIN KIT	2 Heavy Duty Mounting Chains & V Hooks , for FBF and FBE Fluorescent High Bays	1	C, N, F	



PHILIPS DAY-BRITE FLUORESCENT Industrial Solid Top Reflector

UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
734340608250	TIS232-UNV-1/4-EB	8' Length, 2 Lamp Tandem (4 lamps), Solid Top, 32T8, Universal Voltage 120/277V, (1) Electronic Ballast	1	C, N, F	
734340608243	IS232-UNV-1/2-EB	4' Length, 2 Lamp, Solid Top, 32T8, Universal Voltage 120/277V, Electronic Ballast	1	C, N, F	



PHILIPS DAY-BRITE HID High Bay and Low Bay

UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
734340703603	HBO400PMT-PSC-OR	400W, Pulse Start MH, Open Rated Socket, Multi-Tap, Die Cast Aluminum Housing	1	C,	

PHILIPS DAY-BRITE HID High Bay and Low Bay Accessories

UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
734340157468	HMR-CS	Male Suspension Hook	1	C, N, F	

C = Carrollton, Texas F = Fontana, California N = Norwich, Connecticut

PHILIPS DAY-BRITE HID Reflectors and Optical Assembly

UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
734340014884	LR23-CS	23" Low Bay Optical Assembly	I	C, N, F	
734340402087	AL15	15" Aluminum Reflector	I	C, N, F	




PHILIPS DAY-BRITE Special Purpose Industrial Wet Location

UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
734340608267	DWAE232-UNV-1/2-EB	4' Length, 2 Lamp, 32T8, Universal Voltage 120/277V, Electronic Ballast	I	C, N, F	

C = Carrollton, Texas F = Fontana, California N = Norwich, Connecticut

Pictures are representative of product categories and may not illustrate the exact products listed on the pages of this stock guide. Product information may change without notice. Contact your local Philips sales representative for additional product information.

OUTDOOR



PHILIPS STONCO Lyte Cube Canopy

UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
786034380096	LCQ105MAL-6	Lyte Cube 100W MH Dual Voltage, w/Lamp, Bronze	1	C	
786034893299	LCQ155PMAL-8	Lyte Cube 150W PMA Multi-Tap, w/Lamp, Bronze	1	C	



PHILIPS STONCO Lyte Prism Series

UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
786034037761	LPQ155PMAL-8	Lyte Prism 150W PMA Multi-Tap, w/Lamp, Bronze	1	C	
786034801560	LPQ85840IND-4	Lyte Prism Induction, 85W, 4000K Color Temp, 200/277V, w/Lamp, Bronze	1	C	



PHILIPS STONCO Twilighter Series Canopy Light

UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
786034945851	TLC51NLXL-1	Twilighter Series 50W HPS 120V, w/Lamp, Bronze	6	C	
786034945868	TLC51NMAL-1	Twilighter Series 50W MH 120V, w/Lamp, Bronze	6	C	
786034945875	TLC71NLXL-1	Twilighter Series 70W HPS 120V, w/Lamp, Bronze	6	C	




PHILIPS STONCO Designer Canopy LED Luminaire



UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
786034956437	DCL20LED4K-8	LED Canopy 20 Hi-Lumen LEDs, 4700K Color Temp, Multi-Tap, Bronze	6	C	

C = Carrollton, Texas F = Fontana, California N = Norwich, Connecticut



PHILIPS GARDCO G3 LED Parking Garage and Canopy Series



UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
N/A	STK-G3-5-2-73VAR-NW-UNIV-NP	G3 Garage, Type-5, 2-Board, 73W Neutral White, 6341 Lumens, 120/277V, Natural Paint	1	C	
N/A	STK-G3-5-2-73VAR-CW-UNIV-NP	G3 Garage, Type-5, 2-Board, 73W, Cool White, 6341 Lumens, 120/277V, Natural Paint	1	C	
N/A	STK-G3-MR-5-2-73VAR-NW-120/277-NP	G3 Garage, Motion Response, Type-5, 2-Board, 73W, Neutral White, 6341 Lumens, 120/277V, Natural Paint	1	C	
N/A	STK-G3-MR-5-2-73VAR-CW-120/277-NP	G3 Garage, Motion Response, Type-5, 2-Board, 73W, Cool White, 6341 Lumens, 120/277V, Natural Paint	1	C	
N/A	STK-G3-5-1-55LA-161A-NW-UNIV-NP	G3 Garage, Type-5, 1-Board, 55W, Neutral White, 4423 Lumens, 120/277V, Natural Paint	1	C	
N/A	STK-G3-5-1-55LA-161A-CW-UNIV-NP	G3 Garage, Type-5, 1-Board, 55W, Cool White, 4423 Lumens, 120/277V, Natural Paint	1	C	
N/A	STK-G3-MR-5-1-55LA-161A-NW-120/277-NP	G3 Garage, Motion Response, Type-5, 1-Board, 55W, Neutral White, 4423 Lumens, 120/277V, Natural Paint	1	C	
N/A	STK-G3-MR-5-1-55LA-161A-CW-120/277-NP	G3 Garage, Motion Response, Type-5, 1-Board, 55W, Cool White, 4423 Lumens, 120/277V, Natural Paint	1	C	
N/A	STK-PB-NP	Balanced J-Box for Pendant Mount, Natural Paint, 12" Minimum Pendant Required by Others	1	C	



PHILIPS STONCO SLA Mini-Flood

UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
786034839792	SLA101MAL-6	Mini-Flood Dual Voltage 100W MH, w/Lamp, Bronze	4	C	
786034839808	SLA101NLXL-1	Mini-Flood 120V 100W HPS, w/Lamp, Bronze	4	C	
786034893466	SLA150PMAL-6	Mini-Flood Dual Voltage 150W PMA, w/Lamp, Bronze	4	C	
786034839815	SLA151NLXL-1	Mini-Flood 120V 150W HPS, w/Lamp, Bronze	6	C	
786034839846	SLA71MAL-6	Mini-Flood Dual Voltage 70W MH, w/Lamp, Bronze	4	C	
786034839853	SLA71NLXL-1	Mini-Flood 120V 70W HPS, w/Lamp, Bronze	6	C	

C = Carrollton, Texas F = Fontana, California N = Norwich, Connecticut

OUTDOOR



PHILIPS STONCO SLM Maxi Flood Family

UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
786034768146	SLM250PMAL-8	Maxi-Flood, Multi-Tap, 250W PS, w/Lamp, Bronze	1	C	
786034895934	SLM400PMAL-8	Maxi-Flood, Multi-Tap, 400W PS, w/Lamp, Bronze	1	C	



PHILIPS STONCO GP Flood

UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
786034853569	GP2A100PMAL-6	Small Floodlight 100W PMA Dual Voltage, w/Lamp, Bronze	2	C	
786034853613	GP2A150PMAL-6	Small Floodlight 150W PMA Dual Voltage, w/Lamp, Bronze	2	C	
786034884709	GP3S250PMAL-8	Medium Floodlight 250W PMA Multi-Tap, w/Lamp and Tenon Slip Fitter; Bronze	1	C	
786034859158	GP3S400PMAL-8	Medium Floodlight 400W PMA Multi-Tap, w/Lamp and Tenon Slip Fitter; Bronze	1	C	
786034878906	GP3T250PMAL-8	Medium Floodlight 250W PMA Multi-Tap, w/Lamp and Trunnion Mount, Bronze	1	C	
786034874953	GP3T400PMAL-8	Medium Floodlight 400W PMA Multi-Tap, w/Lamp and Trunnion Mount, Bronze	1	C	
786034843850	GP5S1000MAL-8	X-Large Floodlight 1000W MH Multi-Tap, w/Lamp and Tenon Slip Fitter; Bronze	1	C	
786034844017	GP5T1000MAL-8	X-Large Floodlight 1000W MH Multi-Tap, w/Lamp and Trunnion Mount, Bronze	1	C	



PHILIPS STONCO EQX Series Quartz Flood

UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
786034484268	EQX1500	EQ Quartz Flood w/Lens Frame, 1500W, Bronze *1500W Lamp Ordered Separately (Available in 208, 240 and 277V Only)	4	C	
786034484466	EQX150LBRZ	EQ Quartz Flood w/Lens Frame, 150W, w/Lamp, Bronze	24	C	
786034484459	EQX150LWHT	EQ Quartz Flood w/Lens Frame, 150W, w/Lamp, White	24	C	
786034484282	EQX500L	EQ Quartz Flood w/Lens Frame, 500W, w/Lamp, Bronze	12	C	
786034484305	EQX500LWHT	EQ Quartz Flood w/Lens Frame, 500W, w/Lamp, White	24	C	

C = Carrollton, Texas F = Fontana, California N = Norwich, Connecticut



PHILIPS STONCO EQ Series Quartz Flood

UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
786034484244	EQ500L	EQ Quartz Flood, No Lens Frame, 500W, w/Lamp, Bronze	12	C	



PHILIPS STONCO FloodPak Small

UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
786034765732	FPS100NLXL-I	FloodPak Size 1 100W HPS 120V, w/Lamp, Bronze	1	C	
786034765749	FPS150NLXL-I	FloodPak Size 1 150W HPS 120V, w/Lamp, Bronze	1	C	
786034772976	FPS42HFL-8	FloodPak Size 1 42W CF 120V, w/Lamp, Bronze	1	C	
786034765756	FPS70NLXL-I	FloodPak Size 1 70W HPS 120V, w/Lamp, Bronze	1	C	



PHILIPS STONCO FloodPak Medium

UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
786034765701	FPM100PMAL-8	FloodPak Size 2 100W PSMH Multi-Tap, w/Lamp, Bronze	1	C	
786034773720	FPM150LXL-8	FloodPak Size 2 150W HPS Multi-Tap, w/Lamp, Bronze	1	C	
786034765718	FPM150PMAL-8	FloodPak Size 2 150W PSMH Multi-Tap, w/Lamp, Bronze	1	C	
786034771320	FPM70PMAL-8	FloodPak Size 2 70W PSMH Multi-Tap, w/Lamp, Bronze	1	C	



PHILIPS STONCO FloodPak Large

UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
786034765664	FPL250LXL-8	FloodPak Size 3 250W HPS Multi-Tap, w/Lamp, Bronze	1	C	
786034787574	FPL250PMAL-8	FloodPak Size 3 250W PSMH Multi-Tap, w/Lamp, Bronze	1	C	
786034828864	FPL400PMAL-8	FloodPak Size 3 400W PSMH Multi-Tap, w/Lamp, Bronze	1	C	

C = Carrollton, Texas F = Fontana, California N = Norwich, Connecticut

OUTDOOR



PHILIPS STONCO Twilighter LED Wall Pak

UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
786034956444	TLW10LED4KPCB-I	Twilighter LED Wall Pak 10 Hi-Lumen LEDs, 4K Color Temp, Built in Photocontrol, 120V, Bronze	6	C	



PHILIPS STONCO Twilighter Series Wall Pack

UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
786034338776	TLW50NLXL-I	Twilighter Series Wall Pack 50W HPS 120V, w/Lamp, Bronze	6	C	
786034338783	TLW50NLXLPC-I	Twilighter Series Wall Pack 50W HPS 120V, Photo Control w/Lamp, Bronze	6	C	
786034746809	TLW42HFL-8	Twilighter Series Wall Pack 42W CF Multi-Tap, w/Lamp, Bronze	6	C	
786034953818	TLW70NLXL-I	Twilighter Series Wall Pack 70W HPS 120V, w/Lamp, Bronze	6	C	
786034338653	TLW70NLXLPC-I	Twilighter Series Wall Pack 70W HPS 120V Photo Control, w/Lamp, Bronze	6	C	



PHILIPS STONCO WNPS Series Mini Wall Pack

UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
786034266888	WNPS101NLXL-I	Mini Wall Pack 120V 100W HPS, w/Lamp, Bronze	6	C	



PHILIPS STONCO NPM Series Wall Pack

UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
786034947381	NPM101PMAL-8	NytPro Architectural Full Cutoff Wall Prism, 100W PSMH, 120/277V, w/Lamp, Bronze	1	C	
786034950138	NPM151PMAL-8	NytPro Architectural Full Cutoff Wall Prism, 150W PSMH, 120/277V, w/Lamp, Bronze	1	C	

C = Carrollton, Texas F = Fontana, California N = Norwich, Connecticut



PHILIPS STONCO WPM Series Wall Pack

UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
786034743426	WNPM1101MAL-6	WPM Wall Pack, 100W PSMH, 120/277V, w/Lamp, Bronze	1	C	
786034890984	WNPM150PMAL-8	WPM Wall Pack, 150W PSMH, Multi-Tap, w/Lamp, Bronze	1	C	
786034743433	WNPM151NLXL-1	WPM Wall Pack, 150W HPS, 120V, w/Lamp, Bronze	1	C	
786034699839	WPM71MAL-6	WPM Wall Pack, 70W PSMH, 120/277V, w/Lamp, Bronze	1	C	
786034739184	WPM71MAL-8	WPM Wall Pack, 70W PSMH, Multi-Tap, w/Lamp, Bronze	1	C	



PHILIPS STONCO WPM Medium Series LED Wall Pack



UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
786034953993	WPM30LED4K-8	WPM Wall Pack, 30 LEDs, 65W, 120/277V, Titanium	1	C	



PHILIPS STONCO WP Large Series Wall Pack

UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
786034728997	WP251LX-8	WP Wall Pack, 250W HPS, Multi-Tap, Bronze	1	C	
786034892766	WP251PMA-8	WP Wall Pack, 250W PSMH, Multi-Tap, Bronze	1	C	
786034920735	WP251PMAL-8	WP Wall Pack, 250W PSMH, Multi-Tap, w/Lamp, Bronze	1	C	
786034729000	WP401LX-8	WP Wall Pack, 400W HPS, Multi-Tap, Bronze	1	C	
786034892773	WP401PMA-8	WP Wall Pack, 400W PSMH, Multi-Tap, Bronze	1	C	
786034920742	WP401PMAL-8	WP Wall Pack, 400W PSMH, Multi-Tap, w/Lamp, Bronze	1	C	

C = Carrollton, Texas F = Fontana, California N = Norwich, Connecticut

OUTDOOR



PHILIPS STONCO WP Large Series LED Wall Pack

UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
786034938099	WP49LED4K-8	WPM Wall Pack, 49 LEDs, 92W, 120/277V, Titanium	1	C	



PHILIPS STONCO LytePro Architectural LED Wall Sconce

UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
786034928625	LP7T	LytePro7 Wall Sconce, Type 3, 7 LEDs, 13W, Neutral White, 613 Lumens, 120/220V, Titanium Finish	6	C	
786034928632	LP7W	LytePro7 Wall Sconce, Type 3, 7 LEDs, 13W, Neutral White, 613 Lumens, 120/220V, White Finish	6	C	
786034954174	LPI6T	LytePro16 Wall Sconce, Type 3, 16 LEDs, 40W, Neutral White, 2500 Lumens, 120/277V, Titanium Finish	6	C	
786034954181	LPI6W	LytePro16 Wall Sconce, Type 3, 16 LEDs, 40W, Neutral White, 2500 Lumens, 120/277V, White Finish	6	C	
786034956796	LP32T	LytePro32 Wall Sconce, Type 3, 32 LEDs, 71W, Neutral White, 5680 Lumens, 120/277V, Titanium Finish	3	C	
786034956819	LP32W	LytePro32 Wall Sconce, Type 3, 32 LEDs, 71W, Neutral White, 5680 Lumens, 120/277V, White Finish	3	C	
786034956802	LP32P	LytePro32 Wall Sconce, Type 3, 32 LEDs, 71W, Neutral White, 5680 Lumens, 120/277V, Bronze Finish	3	C	



PHILIPS STONCO Dusk to Dawn LED

UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
786034956420	DTD12LED4KPCB-I	LED Dusk to Dawn Luminaire 12 Hi-Lumen LEDs, 4K Color-Temp, Built in Photocontrol, 120V, Gray	4	C	



PHILIPS STONCO Dusk to Dawn HID

UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
786034266246	DTDA70NLXL-I	Dusk To Dawn, 70W HPS, 120V, Twist Lock Photocontrol, Gray	1	C	
786034266253	DTDA100NLXL-I	Dusk To Dawn, 100W HPS, 120V, Twist Lock Photocontrol, Gray	1	C	
786034266239	DTDA150NLXL-I	Dusk To Dawn, 150W HPS, 120V, Twist Lock Photocontrol, Gray	1	C	

C = Carrollton, Texas F = Fontana, California N = Norwich, Connecticut



PHILIPS STONCO MCL Area Luminaire

UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
786034237086	MCL3250LX-8	MCL Area Full Cutoff, Type 3, 250W HPS, Multi-Tap, Bronze	1	C	
786034781640	MCL3250PMA-8	MCL Area Full Cutoff, Type 3, 250W PSMH, Multi-Tap, Bronze	1	C	
786034039376	MCL3400PMA-8	MCL Area Full Cutoff, Type 3, 400W PSMH, Multi-Tap, Bronze	1	C	



PHILIPS STONCO Roughlyte Series

UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
786034871426	VCXLI1GCN	Roughlyte Ceiling Mount 100W Glass Globe Cast Guard	12	C	
786034871433	VWXLI1GCN	Roughlyte Wall Mount 100W Glass Globe Cast Guard	12	C	



PHILIPS STONCO Medium Base Lampholder

UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
786034100113	I50L	250W Max, Die Cast Aluminum Medium Base Lampholder	12	C	



PHILIPS STONCO Architectural Bullet Series

UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
NA	920GRY	Gray Open Bullet, 75W Max	12	C	

C = Carrollton, Texas F = Fontana, California N = Norwich, Connecticut

Pictures are representative of product categories and may not illustrate the exact products listed on the pages of this stock guide. Product information may change without notice. Contact your local Philips sales representative for additional product information.

TRACK

PHILIPS LIGHTOLIER BASIC Lytespan Track

UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
784197594183	6000NBK	Basic Lytespan Track, 2' Ind Basic Track, Black	I	N	
784197594190	6000NWH	Basic Lytespan Track, 2' Ind Basic Track, White	I	N	
784197594206	6001NBK	Basic Lytespan Track, 4' Ind Basic Track, Black	I	N	
784197594213	6001NWH	Basic Lytespan Track, 8' Ind Basic Track, White	I	N	
784197594220	6002NBK	Basic Lytespan Track, 8' Ind Basic Track, Black	I	N	
784197594237	6002NWH	Basic Lytespan Track, 8' Ind Basic Track, White	I	N	
784197594251	6003NWH	Basic Lytespan Track, 8' Join Basic Track, White	I	N	
784197594268	6004NBK	Basic Lytespan Track, 4' Ind Basic Track W/O Live End, Black	I	N	
784197594275	6004NWH	Basic Lytespan Track, 4' Ind Basic Track W/O Live End, White	I	N	
662057572185	6006NBK	Basic Lytespan Track, 6' Basic Plain Track W/O Live End, Black	I	N	
784197594282	6008NBK	Basic Lytespan Track, 8' Basic Plain Track W/O Live End, Black	I	N	
784197594299	6008NWH	Basic Lytespan Track, 8' Basic Plain Track W/O Live End, White	I	N	



PHILIPS LIGHTOLIER BASIC Track Accessories

UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
784197594541	6046NBK	Basic Power Extension Connector, Black	I	N	
784197594589	6048NBK	Basic Lytespan Track, Live End, Black	I	N	
784197594596	6048NWH	Basic Lytespan Track, Live End, White	I	N	
784197594565	6049NBK	Basic Lytespan Track, Basic Mini Coupler, Black	I	N	

C = Carrollton, Texas F = Fontana, California N = Norwich, Connecticut


PHILIPS LIGHTOLIER BASIC Track Accessories

UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
784197274320	7586	Basic Lytespan Track, 48" Stem Mounting Kit, Matte White	I	N	
784197594572	6049NWH	Basic Lytespan Track, Basic Mini Coupler, White	I	N	
784197594473	6050NWH	Basic Lytespan Track, Basic "L" Connector, White	I	N	
784197594480	6051NBK	Basic Lytespan Track, Basic "T" Connector, Black	I	N	
784197594497	6051NWH	Basic Lytespan Track, Basic "T" Connector, White	I	N	
784197594503	6052NBK	Basic Lytespan Track, Basic "X" Connector, Black	I	N	
784197594350	6054NWH	Basic Lytespan Track, Basic In-Line Connector, White	I	N	
784197606015	6060BK	Track, Basic End Feed Canopy, Matte Black	I	N	
784197606008	6060WH	Track, Basic End Feed Canopy, Matte White	I	N	
784197606114	6061BK	Track, Floating Canopy Kit, Black	I	N	


PHILIPS LIGHTOLIER ADVENT Lytespan Two-Circuit Track

UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
784197572907	6102NWH	Advent Lytespan Two-Circuit Track, 8' Ind Advent Track, White	I	N	
784197572938	6103NWH	Advent Lytespan Two-Circuit Track, 8' Join Advent Track, White	I	N	
784197572952	6104NBK	Advent Lytespan Two-Circuit Track, 4' Track W/O Live End, Black	I	N	
784197572990	6108NWH	Advent Lytespan Two-Circuit Track, 8' Track W/O Live End, White	I	N	

C = Carrollton, Texas F = Fontana, California N = Norwich, Connecticut

TRACK



PHILIPS LIGHTOLIER ADVENT Lytespan Two-Circuit Track Accessories

UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
784197573195	6146NBK	Advent Lytespan Two-Circuit Track, Power Extension Connector, Black	1	N	
784197573201	6146NWH	Advent Lytespan Two-Circuit Track, Power Extension Connector, White	1	N	
784197573256	6148NWH	Advent Lytespan Two-Circuit Track, Advent Live End, White	1	N	
784197573089	6150NBK	Advent Lytespan Two-Circuit Track, Advent "L" Connector, Black	1	N	
784197573119	6151NBK	Advent Lytespan Two-Circuit Track, Advent "T" Connector, Black	1	N	
784197573126	6151NWH	Advent Lytespan Two-Circuit Track, Advent "T" Connector, White	1	N	
784197573638	6152NBK	Advent Lytespan Two-Circuit Track, Advent "X" Connector, Black	1	N	
784197573140	6152NWH	Advent Lytespan Two-Circuit Track, Advent "X" Connector, White	1	N	
784197573065	6154NWH	Advent Lytespan Two-Circuit Track, Advent In-Line Connector, White	1	N	



PHILIPS LIGHTOLIER LYTESPAN Monopoint Track

UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
784197619015	6190BK	Lytespan Monopoint, Matte Black	1	N	
784197619022	6190WH	Lytespan Monopoint, Matte White	1	N	

C = Carrollton, Texas F = Fontana, California N = Norwich, Connecticut



PHILIPS LIGHTOLIER RADIUS Track

UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
784197910228	9106BK	Radius Track, 6' Plain Track, Matte Black	1	N	
784197910242	9108WH	Radius Track, 8' Plain Track, Matte White	1	N	



PHILIPS LIGHTOLIER RADIUS Track Accessories

UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
784197000523	9147BK	Radius Track, Surface Feed Connector, Matte Black	1	N	
784197910280	9148WH	Radius Track, Radius Live End Feed, Matte White	1	N	
784197910327	9149WH	Radius Track, Mini Coupler, Matte White	1	N	
784197910389	9150BK	Radius Track, Flush Non-Feed Conn Comb L or In-Line	1	N	
784197910365	9150WH	Radius Track, Flush Non-Feed Conn Comb L or In-Line	1	N	
784197170400	9151BK	Radius Track, Feed "T" Connector, Matte Black	1	N	
784197136864	9155BK	Radius Track, Feed Conn Comb L or In-Line, Matte Black	1	N	
784197608507	6085	Convenience Outlet, Lytespan Track, White	1	N	



PHILIPS LIGHTOLIER Track Heads

UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
784197526306	6276BWH	Sof-Tech Low Voltage Enclosed Spot MR16, Matte White	1	N	
784197820114	8201BK	PAR-Tech Low Profile Adapter, Black	1	N	
784197820107	8201WH	PAR-Tech Low Profile Adapter, White	1	N	
784197842024	8420BK	Sof-Tech Spots 50W, PAR20, Black	1	N	
784197902117	9021BK	Mini-Universal 250W Max, Matte Black	1	N	

C = Carrollton, Texas F = Fontana, California N = Norwich, Connecticut

TRACK



PHILIPS LIGHTOLIER Track Heads

UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
784197902100	9021WH	Mini-Universal 250W Max, Matte White	I	N	
784197902230	9022BK	Budget PAR 38 Ring, Matte Black	I	N	
784197902209	9022WH	Budget PAR 38 Ring, Matte White	I	N	
784197140410	9023BK	Budget PAR30 Ring, Matte Black	I	N	
784197140496	9023WH	Budget PAR30 Ring, Matte White	I	N	
784197483661	22MC6WH	Alcyon MR16 Mini Cylinder, White	I	N	
784197483722	22OR6WH	Alcyon MR16 Open Ring, White	I	N	
784197483630	22SS6WH	Alcyon MR16 Enclosed Step Spot, White	I	N	
662057577555	LLAB030RNF BK	Lytespan Spot LED Narrow Flood 15W, 3000K, Black	I	N	
662057577548	LLAB030RNF WH	Lytespan Spot LED Narrow Flood 15W, 3000K, White	I	N	
662057610702	LLAB130RNF WH	Lytespan Spot LED Large Flood 34W, 3000K, White	I	N	
662057609645	LLAB130RNF BK	Lytespan Spot LED Large Narrow Flood, 34W, 3000K, Black	I	N	
662057609638	LLAB130RNF WH	Lytespan Spot LED Large Narrow Flood, 34W, 3000K, White	I	N	



PHILIPS LIGHTOLIER TRACK ACCESSORY

UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
784197282424	AF2SF	2" Solite Diffusion Lens	I	N	

C = Carrollton, Texas F = Fontana, California N = Norwich, Connecticut



PHILIPS CONTROLS OccuSwitch Classic

UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
662057646084	LRS2210/00	Occupancy Sensor;Wall Mount, PIR, 120/277V,White	10	C	
734340079920	LRS2220/00	Occupancy Sensor;Wall Mount, Dual Technology, 120/277V,White	10	C	
662057646183	LRM2250/00	Occupancy Sensor; Ceiling Mount, PIR, 24VDC, 1500 Sq. Ft.	10	C	
662057646190	LRM2255/00	Occupancy Sensor; Ceiling Mount, Dual Technology, 24VDC, 2000 Sq. Ft.	10	C	
662057646251	LCA2285/00	Power Pack, 20A, 120/277V	10	C	
662057646022	LRA1721/00	Wireless Occupancy Sensor Switch, 120/277V,White	10	C	
662057646060	LRM1743/00	Wireless Occupancy Sensor; Ceiling Mount, PIR	10	C	
662057646077	LRM1760/00	Wireless Occupancy Sensor; Ceiling Mount, PIR, Photocell	10	C	



PHILIPS CONTROLS Relay Panel

UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
662057634579	LRC2410/00	Relay Panel, 8 Circuit,Timeclock, BACnet	1	C	



PHILIPS CONTROLS Sunrise

UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
NA	ZP600W	Preset Slide Dimmer; Incandescent, 600W, 120V,White	12	C	
NA	ZP600VAW	Preset Slide Dimmer; Inductive, 600VA, 120V,White	12	C	
NA	ZP600FAM120W	Preset Slide Dimmer; 0-10V, 600W, 120V,White	12	C	
NA	ZP600EBW	Preset Slide Dimmer; Mark 10, 600VA, 120V,White	12	C	

C = Carrollton, Texas F = Fontana, California N = Norwich, Connecticut

CONTROLS



PHILIPS CONTROLS MultiSet Pro

UPC NUMBER	CATALOG NUMBER	DESCRIPTION	CASE QTY.	STOCKED IN	PRICE
NA	MSP600VAW	Digital Preset Dimmer, Inductive, 600VA, 120V, White	12	C	
NA	MSP600EBW	Digital Preset Dimmer, Mark 10, 600VA, 120V, White	12	C	
NA	MSP300QEW	Digital Preset Dimmer, Trailing Edge, 300W, 120V, White	12	C	
NA	MSP5ESW	5-Scene, Plus Off Scene, Control Keypad	12	C	

C = Carrollton, Texas F = Fontana, California N = Norwich, Connecticut



Philips Lighting Company
200 Franklin Square Drive
Somerset, NJ 08873
1-855-486-2216
A Division of Philips North America
www.philips.com



© 2013 Koninklijke Philips Electronics N.V. All rights reserved.
Specifications are subject to change without notice. 10/13