

PHILIPS

LED

Single Optic PAR38



Accent without distraction

Philips LED Single Optic PAR38 Lamps with AirFlux Technology improves visual experience with superior lighting aesthetics and optimal thermal efficiency in a sleek, lightweight design.

High efficacy dimmable LED reflector lamp

- Single Optic reduces glare to improve shopper experience
- 25,000-hour rated average life for Energy Star® Qualified lamps*
- 50,000-hour design life**
- 17W PAR38 saves 103 watts when compared to a 120W halogen PAR38†
- 83 CRI for excellent color rendering
- Virtually UV/IR free in the beam
- Contains no mercury
- Select lamps available in black finish
- Available color temperatures include 2700K, 3000K and 4000K

Easy to experience

- Will not fade colors, avoids inventory spoilage
- Lowers maintenance costs by reducing re-lamp frequency
- 5-year limited warranty†

(See back page for footnotes)

Ordering, Electrical and Technical Data (Subject to change without notice)

Product Number	Model Number	Ordering Code	Nom. Watts	Energy Star® Rated Avg Life (Hrs) ¹	Rated Avg Life (yrs) ²	Approx. Lumens	Beam Angle	MBCP ³	CRI	Est Energy Cost ^{2,4}	Color Temp (K)
45472-8	9290011319	13PAR38/F25/827 DIM AF SO	13	25000	22.7	900	25	5300	80	\$1.57	2700
45473-6	9290011320	13PAR38/F25/830 DIM AF SO	13	25000	22.7	950	25	5500	80	\$1.57	3000
45474-4	9290011321	13PAR38/F35/827 DIM AF SO	13	25000	22.7	900	35	2600	80	\$1.57	2700
45475-1	9290011322	13PAR38/F35/830 DIM AF SO	13	25000	22.7	950	35	2750	80	\$1.57	3000
43535-4	9290011131	17PAR38/S15/827 DIM AF SO	17	25000	22.7	1200	15	10000	80	\$2.05	2700
43536-2	9290011132	17PAR38/S15/830 DIM AF SO	17	25000	22.7	1250	15	10500	80	\$2.05	3000
43537-0	9290011133	17PAR38/S15/840 DIM AF SO	17	25000	22.7	1300	15	11000	80	\$2.05	4000
43538-8	9290011134	17PAR38/F25/827 DIM AF SO	17	25000	22.7	1200	25	6800	80	\$2.05	2700
43539-6	9290011135	17PAR38/F25/830 DIM AF SO	17	25000	22.7	1250	25	7100	80	\$2.05	3000
43540-4	9290011136	17PAR38/F25/840 DIM AF SO	17	25000	22.7	1300	25	7500	80	\$2.05	4000
43541-2	9290011137	17PAR38/F35/827 DIM AF SO	17	25000	22.7	1200	35	3200	80	\$2.05	2700
43542-0	9290011138	17PAR38/F35/830 DIM AF SO	17	25000	22.7	1250	35	3400	80	\$2.05	3000
43543-8	9290011139	17PAR38/F35/840 DIM AF SO	17	25000	22.7	1300	35	3600	80	\$2.05	4000

1. Early initial qualification for Energy Star allows for directional lamp life claims of 25,000 hours (L70) with 3,000 hour actual test data, LM80 data and in-situ temperature measurements. As the lamps pass Energy Star requirements, manufacturers may increase the lifetime of a product as dictated by Energy Star guidelines. See http://www.energystar.gov/index.cfm?fuseaction=products_for_partners.showLightbulbs for further details.

2. Based on average usage of 3 hrs/day, 7 days/week.

3. Based on photometric testing consistent with IES LM-79. Maximum Beam Candlepower.

4. Based on 3 hrs/day, 11¢/kWh. Cost depends on rates and use.

■ This lamp is ENERGY STAR® Certified.

Footnotes from font:

* Early initial qualification for Energy Star allows for directional lamp life claims of 25,000 hours (L70) with 3,000 hour actual test data, LM80 data and in-situ temperature measurements. As the lamps pass Energy Star requirements, manufacturers may increase the lifetime of a product as dictated by Energy Star guidelines. See http://www.energystar.gov/index.cfm?fuseaction=products_for_partners.showLightbulbs for further details.

** Design life is based on engineering testing and probability analysis

‡ For details, please visit http://www.usa.lighting.philips.com/connect/tools_literature/warranties.wpd

† Light output comparison based upon the ENERGY STAR® Integral LED Lamp Center Beam Intensity Benchmark tool which can be found at EnergyStar.gov/LEDbulbs_LED.



Shipping Data (Subject to change without notice)

Product Number	SKU UPC (0-46677)	Outer Bar Code (5-00-46677)	Case Qty.	Case Weight (lbs.)	Case Cube (cu. Ft.)	Pallet Qty	SKUs per Layer	Layers High	SKU Dimensions (W x D x H) (In.)	Case Dimensions (W x D x H) (In.)	Pallet Dimensions (W x D x H) (In.)
45472-8	45472-2	45472-7	6	6.11	0.549	504	72	7	4.8 x 4.8 x 5.4	15.1 x 10.3 x 6.1	48 x 40 x 43.7
45473-6	45473-9	45473-4	6	6.11	0.549	504	72	7	4.8 x 4.8 x 5.4	15.1 x 10.3 x 6.1	48 x 40 x 43.7
45474-4	45474-6	45474-1	6	6.11	0.549	504	72	7	4.8 x 4.8 x 5.4	15.1 x 10.3 x 6.1	48 x 40 x 43.7
45475-1	45475-3	45475-8	6	6.11	0.549	504	72	7	4.8 x 4.8 x 5.4	15.1 x 10.3 x 6.1	48 x 40 x 43.7
43535-4	43535-6	43535-1	6	6.11	0.549	504	72	7	4.8 x 4.8 x 5.4	15.1 x 10.3 x 6.1	48 x 40 x 43.7
43536-2	43536-3	43536-8	6	6.11	0.549	504	72	7	4.8 x 4.8 x 5.4	15.1 x 10.3 x 6.1	48 x 40 x 43.7
43537-0	43537-0	43537-5	6	6.11	0.549	504	72	7	4.8 x 4.8 x 5.4	15.1 x 10.3 x 6.1	48 x 40 x 43.7
43538-8	43538-7	43538-2	6	6.11	0.549	504	72	7	4.8 x 4.8 x 5.4	15.1 x 10.3 x 6.1	48 x 40 x 43.7
43539-6	43539-4	43539-9	6	6.11	0.549	504	72	7	4.8 x 4.8 x 5.4	15.1 x 10.3 x 6.1	48 x 40 x 43.7
43540-4	43540-0	43540-5	6	6.11	0.549	504	72	7	4.8 x 4.8 x 5.4	15.1 x 10.3 x 6.1	48 x 40 x 43.7
43541-2	43541-7	43541-2	6	6.11	0.549	504	72	7	4.8 x 4.8 x 5.4	15.1 x 10.3 x 6.1	48 x 40 x 43.7
43542-0	43542-4	43542-9	6	6.11	0.549	504	72	7	4.8 x 4.8 x 5.4	15.1 x 10.3 x 6.1	48 x 40 x 43.7
43543-8	43543-1	43543-6	6	6.11	0.549	504	72	7	4.8 x 4.8 x 5.4	15.1 x 10.3 x 6.1	48 x 40 x 43.7



WARNINGS AND CAUTIONS

- Suitable for use in damp locations.
- Not for use in totally enclosed luminaires.
- Before replacing, turn off power and let lamp cool to avoid electrical shock or burn.

CAUTION: Risk of electric shock— do not use where directly exposed to water

NOTES: This device complies with Part 15 of the FCC rule.

Operation is subject to the following two conditions: (1) this device may not cause harmful interference, and (2) this device must accept any interference received, including interference that may cause undesired operation. This Class B digital apparatus complies with Canadian ICES-003.



© 2014 Koninklijke Philips N.V. All rights reserved.
Philips reserves the right to make changes in specifications and/or to discontinue any product at any time without notice or obligation and will not be liable for any consequences resulting from the use of this publication.



Philips Lighting, North America Corporation
200 Franklin Square Drive, Somerset, NJ 08873
Tel. 855-486-2216

Imported by: Philips Lighting,
A division of Philips Electronics Ltd.
281 Hillmount Rd, Markham, ON, Canada L6C 2S3
Tel. 800-668-9008