

The Philips logo is displayed in a white rounded rectangle on a blue background. The background of the entire advertisement is a blurred photograph of a construction site with a worker on a ladder and a Philips LED spot lamp in the foreground.

MASTER LEDspot

Value



Quality, **value** and lifetime

You've got it in one with the new range of MASTER LEDspot Value lamps. They offer high quality at an affordable price with a 24, 36 and 40 degree beam angle for general lighting applications. As a 20 W, 35 W or 50 W equivalent, with a choice of three colour temperatures, dimmable options and a 25,000 and 35,000 hour lifetime, these lamps are everything you value in LED.



MASTER LEDspot MV Value



Product type	LED	Traditional	Lumen output	Efficacy	Beam intensity	Beam angle	CRI	Colour temperature	EOC
MASTER LEDspot MV 3.5-35W	W	W	lm	lm/W	cd	°		K	8718696
VLE D 3.5-35W GU10 827 40D	3.5	35	260	74	600	40	80	2700	45703000
VLE D 3.5-35W GU10 830 40D	3.5	35	270	77	600	40	80	3000	45705400
VLE D 3.5-35W GU10 840 40D	3.5	35	290	83	600	40	80	4000	45707800
MASTER LEDspot MV 4.3-50W	W	W	lm	lm/W	cd	°		K	8718696
VLE D 4.3-50W GU10 827 40D	4.3	50	355	83	800	40	80	2700	45709200
VLE D 4.3-50W GU10 830 40D	4.3	50	365	85	800	40	80	3000	45711500
VLE D 4.3-50W GU10 840 40D	4.3	50	390	91	800	40	80	4000	45713900



MASTER LEDspot LV Value



Product type	LED	Traditional	Lumen output	Efficacy	Beam intensity	Beam angle	CRI	Colour temperature	EOC
MASTER LEDspot LV 3.4-20W	W	W	lm	lm/W	cd	°		K	8718696
VLE 3.4-20W 827 MR16 24D	3.4	20	220	65	1000	24	80	2700	47570600
VLE 3.4-20W 830 MR16 24D	3.4	20	225	66	1000	24	80	3000	47576800
VLE 3.4-20W 827 MR16 36D	3.4	20	220	65	550	36	80	2700	47572000
VLE 3.4-20W 830 MR16 36D	3.4	20	225	66	600	36	80	3000	47574400
Product type	LED	Traditional	Lumen output	Efficacy	Beam intensity	Beam angle	CRI	Colour temperature	EOC
MASTER LEDspot LV-6.5-35W	W	W	lm	lm/W	cd	°		K	
D 6.5-35W 2700K MR16 36D	6.5	35	390	60	900	36	80	2700	77533100
D 6.5-35W 3000K MR16 36D	6.5	35	420	65	960	36	80	3000	78543900
D 6.5-35W 4000K MR16 36D	6.5	35	460	71	990	36	80	4000	78545300

