

PHILIPS


Application bundles



Office

Combine an LED luminaire with an intelligent control for maximum performance and savings

Up to
65%
energy savings



Your Office application bundle:
CoreLine Recessed LED34S & Presence detector LRM1011

Office lighting insights

When you arrive at the office, you know what you'll be working on and who you'll be working with. And you want to be at your best.

In an office workspace, lighting can help people to concentrate, communicate and cooperate. The right light will create a healthy, comfortable and inspiring environment. Philips office lighting solutions meet all European norms for this application, and can reduce energy costs by up to 65% when combined with smart controls.



More info:
www.philips.co.uk/coreline

Traditional

Conventional 4x18 W TLD (18x)

Savings over life*

£4656-

£6793-

£2137-

Application bundle

CoreLine Recessed LED34S VAR-PC (18x) incl. detector

*Based on the UK average of 10p/kWh (including maintenance and lamp replacement cost) and the lighting design for this application bundle.

Bundle benefits

CoreLine Recessed LED34S VAR-PC




- Replacing conventional TL-D & TL-5
- Energy saving
- UGR < 19
- 3-year warranty

Presence detector LRM1011



- Automatically switches off light when not required
- Small, unobtrusive sensor

Detection coverage diagram



Bundle specifications

CoreLine Recessed LED34S VAR-PC

Type	RC120B LED34S/830 PSD W60L60 VAR-PC
	RC120B LED34S/840 PSD W60L60 VAR-PC
Power	35.5 W
Luminous Flux	3400 lm
Colour temperature	3000 K, 4000 K
Colour Render Index	≥ 80
Lifetime	50,000 hours (L70B50)
Number of luminaires on MCB 16A type B	≤ 24
Ordering (EOC) code	26656300 3000 K
	26648800 4000 K
	Also available in emergency

Presence detector LRM1011

Detecting range at 2 - 5 m height	Ø 6 - 11 m
Recommended mounting height	2 m - 5 m
Switch off delay	10 sec. - 30 min. in 6 steps
Number of luminaires on one control	≤ 15
Ordering (EOC) code	44209800

Lighting design insights

Display reflections

Minimise reflected glare on displays by using luminaires with proper office light distribution and a low glare ratio (UGR ≤ 19).

Illuminance requirements



EN12464-1 requirement at desk ≥ 500 lux. Higher levels increase visibility.

Controls


Controls are located above desks to create optimum effect for presence detection.

Brightness

Create bright walls and ceilings by using wide light beams. This will make the entire space look more spacious and pleasant.



Lighting design office



Luminaire types	# Lum.	Em [lux]	Sys. Power	Installed Power	W/m2	W/m2/100lux
Conventional 4xTLD 18 W	18	539	69.5 W	1251 W	13.2	2.4
CoreLine Recessed LED34S VAR-PC	18	515	35.5 W	639 W	6.7	1.2