


LED driver





# Datasheet

# LED drivers – mini Xitanium 36W/m 0.3-1.05A 54V 230V

#### Enabling future-proof LED technology

Xitanium LED drivers are designed to operate LED solutions for general lighting applications. Reliability is enhanced by features that protect the connected LED module, e.g. hot wiring, reduced ripple current and thermal derating. Most drivers feature central DC operation. In the coming years LEDs will continue to increase in efficiency, creating challenges for OEMs. With Xitanium LED drivers, flexibility in luminaire design is assured thanks to an adjustable output current. Application-oriented operating windows offer stable lumen output and light quality levels that specifiers and architects demand. The adjustable output current also enables operation of various LED PCB solutions from different manufacturers.

#### **Benefits**

- High reliability underpinned by 5 year warranty
- Future-proof flexibility application-oriented operating windows enable LED generation and complexity management
- Compatibility can also be used for other manufacturers' modules or OEMs' own PCB designs

#### Features

- Operating windows output current can be adjusted via the Philips MultiOne configurator ('TD' drivers) or with a resistor outside the driver
- Multiple versions DALI dimmable & programmable, trailing-edge dimmable, fixed-current/fixed-output trailing-edge dimmable, fixed-output, and fixed-current/fixed-output
- Power ratings: 10-110 W
- Choice of housing designs linear housing for tracks in '3 in 1' in design, conventional HID housings for downand spotlighting, and SH housing for independent use with strain relief and loop through

#### Application

# • Retail

# Electrical input data

Specification item	Value	Unit	Condition
Nominal input voltage	220240	V <sub>ac</sub>	performance range
Nominal input frequency	5060	Hz	
Nominal input current	0.2	A	@230V @ full load
Input voltage	230	V <sub>ac</sub>	
Nominal input power	42	W	@230V @ full load
Power factor	≥ 0.9		@ full load. See graph.
Total harmonic distortion	≤ 20	%	@ full load. See graph.
Efficiency	88	%	@230V @ full load
Input voltage AC	202254	V <sub>ac</sub>	Operational range
Input frequency AC	47.563	Hz	Maximum permissible range
Isolation Input to Output	SELV		

# Electrical output data

Specification item	Value	Unit	Condition
Regulation method	Constant Current		
Output voltage	2454	V <sub>dc</sub>	
Output voltage max.	60	V	Peak voltage at open load
Output current	0.31.05	A	Full output current setting
Output current tolerance	± 5	%	
Output current ripple LF	≤ 4	%	Ripple = peak / average
Output current ripple HF	≤ 30	%	
Output power	7.236	W	Full output

## Electrical data controls input


Specification item	Value	Unit	Condition
Control method	Fixed		

# Logistical data

Specification item	Value
Product name	Xitanium 36W/m 0.3-1.05A 54V 230V
Order code	
Logistic code 12NC	9290 014 15106
EAN3	
Pieces per box	20


# Wiring & Connections

Specification item	Value	Unit	Condition
Input wire cross-section	0.21.5	mm <sup>2</sup>	WAGO250 (3.5 mm), solid / stranded wire
	1624	AWG	WAGO250 (3.5 mm), solid / stranded wire
Input wire strip length	8.59.5	mm	
Output wire cross-section	0.21.5	mm <sup>2</sup>	WAGO250 (3.5 mm), solid / stranded wire
	1624	AWG	WAGO250 (3.5 mm), solid / stranded wire
Output wire strip length	8.59.5	mm	
Maximum cable length	600	mm	Total length of wiring including LED module, one way



# Dimensions and weight

Specification item	Value	Unit	Condition
Length (A1)	97.2	mm	
Width (B1)	43	mm	
Height (C1)	30	mm	
Fixing hole diameter (D1)	4.2	mm	
Fixing hole distance (A2)	88.5	mm	
Weight	88	gram	



## Operational temperatures and humidity

Specification item	Value	Unit	Condition
Ambient temperature	-20+50	°C	Higher ambient temperature allowed as long as Tcase-max is not
			exceeded.
Tcase-max	80	°C	Maximum temperature measured at T <sub>case</sub> -point
Tcase-life	80	°C	Measured at T <sub>case</sub> -point
Maximum housing temperature	110	°C	In case of a failure
Relative humidity	1090	%	Non-condensing

## Storage temperature and humidity

Specification item	Value	Unit	Condition
Ambient temperature	-25+85	°C	
Relative humidity	595	%	Non-condensing

#### Lifetime

Specification item	Value	Unit	Condition
Driver lifetime	50,000	hours	Measured temperature at $T_{case}$ -point is $T_{case}$ -life.
			Maximum failures = 10%

## Programmable features

Specification item	Value	Remark	Condition
Set output current (AOC)	SimpleSet	See Design-in guide.	Default output current: ≤ 1050 mA
LED module temperature derating (MTP)	No		
Constant Lumen Over Lifetime (CLO)	No		
DC emergency dimming (DCemDIM)	No		
Corridor mode	No		
Energy metering	No		
Diagnostics	No		
Adjustable Light Output ALO	No		

#### Features

Specification item	Value	Remark	Condition
Open load protection	Yes		Automatic recovering
Short circuit protection	Yes		Automatic recovering
Over power protection	Yes		Automatic recovering
Hot wiring	No		
Suitable for fixtures with protection class	I and II		per IEC60598

# **Certificates and standards**

Specification item	Value
Approval marks	CCC / CE / ENEC / F-mark
Ingress Protection classification	20

#### Inrush current

Specification item	Value	Unit			Condition
Inrush current I <sub>peak</sub>	18	A	A		Input voltage 230V
Inrush current T <sub>width</sub>	250	μs	μs		Input voltage 230V, measured at 50% I <sub>peak</sub>
Drivers / MCB 16A type B	≤ 34	pcs			
			МСВ	Rating	Relative number of LED drivers
	-	В	10A	63%	
		-	В	13A	81%
Ipeak	$\backslash$	_	В	16A	100% (stated in datasheet)
Twidth	*	_	В	20A	125%
		_	В	25A	156%
		_	с	10A	104%
<b>↓</b>			с	13A	135%

С

С

С

С

Unit

mA peak

16A

20A

25A

170%

208%

260%

Condition

Acc. IEC61347-1. LED module contribution not included

# Surge immunity

Specification item

Typical touch current

Driver touch current


Specification item	Value	Unit	Condition
Mains surge immunity (diff. mode)	1	kV	Acc. IEC61000-4-5. 2 Ohm, 1.2/50us, 8/20us
Mains surge immunity (comm. mode)	2	kV	Acc. IEC61000-4-5. 12 Ohm, 1.2/50us, 8/20us

Value


0.7


#### Graphs

# Operating window




## Power factor versus output power





#### THD versus output power





©2016 Philips Lighting B.V.

All rights reserved. Reproduction in whole or in part is prohibited without the prior written consent of the copyright owner. The information presented in this document does not form part of any quotation or contract, is believed to be accurate and reliable and may be changed without notice. No liability will be accepted by the publisher for any consequence of its use. Publication thereof does not convey nor imply any license under patent- or other industrial or intellectual property rights. Data subject to change.

Date of release: August 8, 2016

www.philips.com/technology