



**PHILIPS**

MultiOne

Software

Engineering

Supported Devices list – MultiOne Engineering 2.7 and MultiOne Workflow 2.0

Device Type	Device Name	Version
<b>CONTROL</b>	LLC1663/00 ActiLume DALI gen2	1
<b>CONTROL</b>	LLC1663/01 ActiLume DALI gen2	2
<b>CONTROL</b>	LLC1681/10 ActiLume	4.1.10.30011
<b>CONTROL</b>	LLC1682/11 ActiLume	4.1.10.30011
<b>CONTROL</b>	LLC1682/13 ActiLume	4.1.13.30377
<b>CONTROL</b>	LLC1685/11 ActiLume	4.1.10.30011
<b>CONTROL</b>	LLC1685/12 ActiLume	4.1.13.30377
<b>CONTROL</b>	LLC1686/11 ActiLume	4.1.10.30011
<b>CONTROL</b>	LLC1686/12 ActiLume	4.1.13.30377
<b>CONTROL</b>	LLC1687/12 ActiLume	4.1.13.30377
<b>FLUO</b>	HF-Ri TD 1 14/21/24/39 TL5 E+	1
<b>FLUO</b>	HF-Ri TD 1 14/21/24/39 TL5 E+	1.1
<b>FLUO</b>	HF-Ri TD 1 14/21/24/39 TL5 E+	1.11
<b>FLUO</b>	HF-Ri TD 1 14/21/24/39 TL5 E+	1.2
<b>FLUO</b>	HF-Ri TD 1 14/21/24/39 TL5 E+	2.41
<b>FLUO</b>	HF-Ri TD 1 14/21/24/39 TL5 E+	2.61
<b>FLUO</b>	HF-Ri TD 1 28/35/49/54 TL5 E+	1

FLUO	HF-Ri TD 1 28/35/49/54 TL5 E+	1.1
FLUO	HF-Ri TD 1 28/35/49/54 TL5 E+	1.11
FLUO	HF-Ri TD 1 28/35/49/54 TL5 E+	1.2
FLUO	HF-Ri TD 1 28/35/49/54 TL5 E+	2.4
FLUO	HF-Ri TD 1 28/35/49/54 TL5 E+	2.6
FLUO	HF-Ri TD 1 35/49/80 TL5 E+	1
FLUO	HF-Ri TD 1 35/49/80 TL5 E+	1.1
FLUO	HF-Ri TD 1 35/49/80 TL5 E+	1.11
FLUO	HF-Ri TD 1 35/49/80 TL5 E+	1.2
FLUO	HF-Ri TD 1 35/49/80 TL5 E+	2.4
FLUO	HF-Ri TD 1 35/49/80 TL5 E+	2.6
FLUO	HF-Ri TD 1/2 26-42 PL-T/C E+	1
FLUO	HF-Ri TD 1/2 26-42 PL-T/C E+	1.1
FLUO	HF-Ri TD 2 14/21/24/39 TL5 E+	1
FLUO	HF-Ri TD 2 14/21/24/39 TL5 E+	1.1
FLUO	HF-Ri TD 2 14/21/24/39 TL5 E+	1.11
FLUO	HF-Ri TD 2 14/21/24/39 TL5 E+	1.2
FLUO	HF-Ri TD 2 14/21/24/39 TL5 E+	2.41
FLUO	HF-Ri TD 2 14/21/24/39 TL5 E+	2.61
FLUO	HF-Ri TD 2 28/35/49/54 TL5 E+	1
FLUO	HF-Ri TD 2 28/35/49/54 TL5 E+	1.1
FLUO	HF-Ri TD 2 28/35/49/54 TL5 E+	1.11
FLUO	HF-Ri TD 2 28/35/49/54 TL5 E+	1.2
FLUO	HF-Ri TD 2 28/35/49/54 TL5 E+	2.4
FLUO	HF-Ri TD 2 28/35/49/54 TL5 E+	2.6
FLUO	HF-Ri TD 280 TL5/PL-L E+	1
FLUO	HF-Ri TD 280 TL5/PL-L E+	1.2
FLUO	HF-Ri TD 3 14/24 TL5 E+	1.4
FLUO	HF-Ri TD 3 14/24 TL5 E+	1.7
FLUO	HF-Ri TD 3 14/24 TL5 E+	2.7
FLUO	HF-Ri TD 4 14/24 TL5 E+	1.4
FLUO	HF-Ri TD 4 14/24 TL5 E+	1.7
FLUO	HF-Ri TD 4 14/24 TL5 E+	2.7
HID	Dynavision DALI	R1.5
HID	Dynavision DALI	R1.6
HID	Dynavision DALI	R1.7
HID	Dynavision DALI	R1.8
HID	Dynavision DALI	R2.0
HID	Dynavision Prog	R2.1
HID	Dynavision Prog	R2.2
LED	LED 929000712603	1.1
LED	LED 929000712803	1.1
LED	LED HP 350W 1.10	1.16
LED	LED HP 350W 1.20	1.32
LED	LHP 350W 110-277V	2

<b>LED</b>	LHP 350W 347-480V	2
LED	X*050C100V054XPM1M	1.12
LED	X*050C100V054XPM1M	1.18
LED	X*060C100V080XPM1M	1.12
LED	X*060C100V080XPM1M	1.18
LED	XH075C120V075KPF1M	3.2
LED	XH075C120V075KPF1M	4.2
LED	XH150C120V150KPF1M	3.2
LED	XH150C120V150KPF1M	4.2
LED	XI050C100V054XPL1M	1.1
LED	XI050C100V054XPL1M	1.18
LED	XI075C200V054XPT1	1.1
LED	XI075C200V054XPT1	1.2
LED	XI075C200V054XPT1	1.4
LED	XI075C200V054XPT1	1.5
LED	XI075C200V054XPT1	1.6
LED	XI075C200V054XPT1	1.7
LED	XI075C200V054XPT1	2
LED	XI075C200V054XPT1	2.1
LED	XI075C200V054XPT1	2.3
LED	XI075C200V054YPT1	1.1
LED	XI075C200V054YPT1	1.2
LED	XI075C200V054YPT1	1.4
LED	XI075C200V054YPT1	1.5
LED	XI075C200V054YPT1	1.6
LED	XI075C200V054YPT1	2.2
LED	XI075C200V054YPT1	2.4
LED	XR025C100V036YPM1M	1.1
LED	XR025C100V036YPM1M	1.4
<b>LED</b>	Xi LP 110W 0.2-0.7A S1 230V C150 sXt	1
<b>LED</b>	Xi LP 110W 0.2-0.7A SL 230V C150 sXt	1
<b>LED</b>	Xi LP 110W 0.3-1.0A S1 230V C150 sXt	1
<b>LED</b>	Xi LP 110W 0.3-1.0A SL 230V C150 sXt	1
<b>LED</b>	Xi LP 40W 0.2-0.7A S1 230V S175 sXt	1
<b>LED</b>	Xi LP 40W 0.2-0.7A SL 230V S175 sXt	1
<b>LED</b>	Xi LP 40W 0.3-1.0A S1 230V S175 sXt	1
<b>LED</b>	Xi LP 40W 0.3-1.0A SL 230V S175 sXt	1
<b>LED</b>	Xi LP 70W 0.2-0.7A S1 230V C150 sXt	1
<b>LED</b>	Xi LP 70W 0.2-0.7A SL 230V C150 sXt	1
<b>LED</b>	Xi LP 70W 0.3-1.0A S1 230V C150 sXt	1
<b>LED</b>	Xi LP 70W 0.3-1.0A SL 230V C150 sXt	1
LED	Xitanium 110W 0.2-0.6A 215V TD 230V iXt	1
LED	Xitanium 110W 0.2-0.6A 215V TD 230V iXt	1.1
LED	Xitanium 110W 0.2-0.6A 215V TD 230V iXt	1.2
<b>LED</b>	Xitanium 110W 0.2-0.6A 215V TD 230V iXt	1.3

LED	Xitanium 150W 0.2-0.7A 300V TD 230V iXt	1.1
LED	Xitanium 150W 0.2-0.7A 300V TD 230V iXt	1.2
LED	Xitanium 150W 0.7A sProg 230V-6 I66	2.3
LED	Xitanium 150W 0.7A sProg 230V-6 I66	3.3
LED	Xitanium 150W 0.7A sProg 230V-6C I66	2.3
LED	Xitanium 150W 0.7A sProg 230V-6C I66	3.3
LED	Xitanium 150W 1.1A Prog+ GL-F sXt	1.1
LED	Xitanium 150W 1.2A sProg 230V-F sXt	1.2
LED	Xitanium 150W 1.2A sProg GL-F sXt	1.2
LED	Xitanium 17W 0.12-0.4A 54V 1-10V 230V	1.7
LED	Xitanium 17W 0.12-0.4A 54V TD 230V	1.13
LED	Xitanium 17W 0.12-0.4A 54V TD 230V	1.14
LED	Xitanium 17W 0.12-0.4A 54V TD 230V	1.7
LED	Xitanium 17W 0.3-1A 24V TD/Is 230V	1
LED	Xitanium 17W 0.3-1A 24V TD/Is 230V	1.1
LED	Xitanium 17W 0.3-1A 24V TD/Is 230V	1.2
LED	Xitanium 17W 0.3-1A 24V TD/Is 230V	1.3
LED	Xitanium 20W 0.1-0.56A 54V 0-10V 120-277	1
LED	Xitanium 20W LH 0.15-0.5A 48V 230V	1
LED	Xitanium 20W LH 0.15-0.5A 48V TD/Is 230V	1.2
LED	Xitanium 25W 0-10V 120V/277V	1.1
LED	Xitanium 25W 0-10V 120V/277V	1.18
LED	Xitanium 25W 0-10V 120V/277V	1.4
LED	Xitanium 25W 0-10V 120V/277V	1.5
LED	Xitanium 25W 0-10V 120V/277V	1.6
LED	Xitanium 25W 0-10V 120V/277V	1.7
LED	Xitanium 25W 0-10V 120V/277V	1.9
LED	Xitanium 25W 0.3-1A 36V TD/Is 230V	1.2
LED	Xitanium 25W 0.3-1A 36V TD/Is 230V	1.3
LED	Xitanium 25W 0.3-1A 36V TD/Is 230V	1.4
LED OUTDOOR	Xitanium 300W 1.5A Prog+ GL-F2 sXt	1.1
LED	Xitanium 36W 0.12-0.4A 100V 1-10V 230V	1.7
LED	Xitanium 36W 0.12-0.4A 100V TD 230V	1.13
LED	Xitanium 36W 0.12-0.4A 100V TD 230V	1.14
LED	Xitanium 36W 0.12-0.4A 100V TD 230V	1.16
LED	Xitanium 36W 0.12-0.4A 100V TD 230V	1.17
LED	Xitanium 36W 0.12-0.4A 100V TD 230V	1.7
LED	Xitanium 36W 0.12-0.4A 110V TD 230V	1.3
LED	Xitanium 36W 0.12-0.4A 110V TD 230V	1.4
LED	Xitanium 36W 0.12-0.4A 110V TD 230V	1.5
LED	Xitanium 36W 0.3-1A 54V TD 230V	1.1
LED	Xitanium 36W 0.3-1A 54V TD 230V	1.2
LED	Xitanium 36W 0.3-1A 54V TD 230V	1.3
LED	Xitanium 36W 0.3-1A 54V TD 230V	1.5
LED	Xitanium 36W 0.3-1A 54V TD 230V	1.6

LED	Xitanium 36W 0.3-1A 54V TD 230V	1.7
LED	Xitanium 36W 0.3-1A 54V TD 230V	1.8
LED	Xitanium 36W 0.3-1A 54V TD 230V	1.9
LED	Xitanium 36W LH 0.3-1A 48V TD/I 230V	1.1
LED	Xitanium 36W LH 0.3-1A 48V TD/I 230V	1.2
LED	Xitanium 36W LH 0.3-1A 48V TD/I 230V	1.3
LED	Xitanium 36W LH 0.3-1A 48V TD/I 230V	1.4
LED	Xitanium 36W/S 0.3-1A 48V TD 230V	1
LED	Xitanium 36W/S 0.3-1A 48V TD 230V	1.1
LED	Xitanium 40W 0.1-1.1A 54V 0-10V 120-277V	1
LED	Xitanium 40W 0.1-1.1A 54V 0-10V 120-277V	1.1
LED	Xitanium 40W 0.1-1.1A 54V 0-10V 120-277V	1.2
LED	Xitanium 50W LH 0.7-1.5A 48V 230V	1
LED	Xitanium 50/75W 0.3-1A 62V TD/TE 230V	1
LED	Xitanium 50W 0.3-1A 62V TD/Is 230V	1.1
LED	Xitanium 50W 0.3-1A 62V TD/Is 230V	1.2
LED	Xitanium 50W 0.3-1A 62V TD/Is 230V	1.3
LED	Xitanium 50W 0.3-1A 62V TD/TE 230V	1.1
LED	Xitanium 50W 0.3-1A 62V TD/TE 230V	1.11
LED	Xitanium 50W 0.3-1A 62V TD/TE 230V	1.16
LED	Xitanium 50W 0.3-1A 62V TD/TE 230V	1.18
LED	Xitanium 50W 0.3-1A 62V TD/TE 230V	1.8
LED	Xitanium 50W LH 0.7-1.5A 48V TD/I 230V	1.1
LED	Xitanium 75W 0.1-2.0A 54V 0-10V 120-277V	1
LED	Xitanium 75W 0.1-2.0A 54V 0-10V 120-277V	1.1
LED	Xitanium 75W 0.12-0.4A 215V TD 230V	1.3
LED	Xitanium 75W 0.12-0.4A 215V TD 230V	1.4
LED	Xitanium 75W 0.12-0.4A 215V TD 230V	1.5
LED	Xitanium 75W 0.12-0.4A 215V TD 230V	1.6
LED	Xitanium 75W 0.7-2A 54V 0-10V 230V	1.3
LED	Xitanium 75W 0.7-2A 54V 0-10V 230V	1.4
LED	Xitanium 75W 0.7-2A 54V 0-10V 230V	1.5
LED	Xitanium 75W 0.7-2A 54V 0-10V 230V	1.6
LED	Xitanium 75W 0.7-2A 54V 0-10V 230V	1.7
LED	Xitanium 75W 0.7-2A 54V 0-10V 230V	2
LED	Xitanium 75W 0.7-2A 54V 0-10V 230V	2.1
LED	Xitanium 75W 0.7-2A 54V TD 230V	1.3
LED	Xitanium 75W 0.7-2A 54V TD 230V	1.4
LED	Xitanium 75W 0.7-2A 54V TD 230V	1.5
LED	Xitanium 75W 0.7-2A 54V TD 230V	1.6
LED	Xitanium 75W 0.7-2A 54V TD 230V	2.2
LED	Xitanium 75W 0.7-2A 54V TD 230V	2.4
LED	Xitanium 75W 0.7-2A 54V TD 230V	3
LED	Xitanium 75W 0.7-2A 54V TD 230V	3.1
LED	Xitanium 75W 0.7-2A 54V TD 230V	3.2

<b>LED</b>	Xitanium 75W 1.1A Prog+ GL-F sXt	1.1
<b>LED</b>	Xitanium 75W 1.2A sProg 230V-F sXt	1.2
<b>LED</b>	Xitanium 75W 1.2A sProg GL-F sXt	1.2
<b>LED</b>	Xitanium 75W SH 0.3-1A 110V TD/I 230V	1.1
<b>LED</b>	Xitanium 75W SH 0.3-1A 110V TD/I 230V	1.2
<b>LED</b>	Xitanium 75W SH 0.3-1A 110V TD/I 230V	1.3
<b>LED</b>	Xitanium 75W SH 0.3-1A 110V TD/I 230V	1.4
<b>LED</b>	Xitanium 75W SH 0.3-1A 110V TD/I 230V	1.5
<b>LED</b>	Xitanium 75W/0.15-0.4A 200V TD 230V	1.14
<b>LED</b>	Xitanium 75W/0.15-0.4A 200V TD 230V	1.15
<b>LED</b>	Xitanium 75W/0.15-0.4A 200V TD 230V	1.16
<b>LED</b>	Xitanium 75W/0.15-0.4A 200V TD 230V	1.3
<b>LED</b>	Xitanium 75W/0.2-0.4A 200V 1-10V 230V	1.3
<b>LED OUTDOOR</b>	Xitanium FULL PROG 110W1000 NL1 C150 Xt	1.3
<b>LED OUTDOOR</b>	Xitanium FULL PROG 110W1000 NLD C150 Xt	1.3
<b>LED OUTDOOR</b>	Xitanium FULL PROG 35W1000 NL1 C150 Xt	1.3
<b>LED OUTDOOR</b>	Xitanium FULL PROG 35W1000 NLD C150 Xt	1.3
<b>LED OUTDOOR</b>	Xitanium FULL PROG 70W1000 NL1 C150 Xt	1.3
<b>LED OUTDOOR</b>	Xitanium FULL PROG 70W1000 NLD C150 Xt	1.3
<b>LED OUTDOOR</b>	Xitanium LITE PROG 110W1000 NL C150 OD	1.3
<b>LED OUTDOOR</b>	Xitanium LITE PROG 70W1000 NL C150 OD	1.3
<b>LED OUTDOOR</b>	Xitanium Outdoor 100W .53 Prog+	V02E01
<b>LED OUTDOOR</b>	Xitanium Outdoor 100W .53 Prog+	V03E01
<b>LED OUTDOOR</b>	Xitanium Outdoor 100W 0.7 Prog+	V02E01
<b>LED OUTDOOR</b>	Xitanium Outdoor 100W 0.7 Prog+	V03E01
<b>LED OUTDOOR</b>	Xitanium Outdoor 125W JP Prog+	V01E01
<b>LED OUTDOOR</b>	Xitanium Outdoor 125W JP Prog+	V02E01
<b>LED OUTDOOR</b>	Xitanium Outdoor 125W JP Prog+	V03E02
<b>LED OUTDOOR</b>	Xitanium Outdoor 125W JP Prog+	V04E03
<b>LED OUTDOOR</b>	Xitanium Outdoor 125W JP Prog+	V05E03
<b>LED OUTDOOR</b>	Xitanium Outdoor 125W JP Prog+	V06E03
<b>LED OUTDOOR</b>	Xitanium Outdoor 150W .35 Prog+ H	V01E01
<b>LED OUTDOOR</b>	Xitanium Outdoor 150W .35 Prog+ H	V02E01
<b>LED OUTDOOR</b>	Xitanium Outdoor 150W .35 Prog+ H	V03E02
<b>LED OUTDOOR</b>	Xitanium Outdoor 150W .35 Prog+ H	V04E03
<b>LED OUTDOOR</b>	Xitanium Outdoor 150W .35 Prog+ H	V05E03
<b>LED OUTDOOR</b>	Xitanium Outdoor 150W .35 Prog+ H	V06E03
<b>LED OUTDOOR</b>	Xitanium Outdoor 150W 0.7 Prog+ 230V	V01E01
<b>LED OUTDOOR</b>	Xitanium Outdoor 150W 0.7 Prog+ 230V	V02E01
<b>LED OUTDOOR</b>	Xitanium Outdoor 150W 0.7 Prog+ 230V	V03E01
<b>LED OUTDOOR</b>	Xitanium Outdoor 150W 0.7 Prog+ H	V02E01
<b>LED OUTDOOR</b>	Xitanium Outdoor 150W 0.7 Prog+ H	V03E02
<b>LED OUTDOOR</b>	Xitanium Outdoor 150W 0.7 Prog+ H	V04E02
<b>LED OUTDOOR</b>	Xitanium Outdoor 150W 0.7 Prog+ H	V05E02
<b>LED OUTDOOR</b>	Xitanium Outdoor 150W 1.0 Prog+	V01E01

LED OUTDOOR	Xitanium Outdoor 150W 1.0 Prog+	V02E02
LED OUTDOOR	Xitanium Outdoor 150W 1.0 Prog+	V03E03
LED OUTDOOR	Xitanium Outdoor 150W 1.0 Prog+	V04E03
LED OUTDOOR	Xitanium Outdoor 150W 1.0 Prog+	V05E03
LED OUTDOOR	Xitanium Outdoor 150W Prog	V03E02
LED OUTDOOR	Xitanium Outdoor 150W Prog	V04E03
LED OUTDOOR	Xitanium Outdoor 150W Prog	V05E03
LED OUTDOOR	Xitanium Outdoor 150W Prog	V06E03
LED OUTDOOR	Xitanium Outdoor 150W Prog	V07E04
LED OUTDOOR	Xitanium Outdoor 150W Prog	V08E05
LED OUTDOOR	Xitanium Outdoor 150W Prog	V09E05
LED OUTDOOR	Xitanium Outdoor 150W Prog	V10E05
LED OUTDOOR	Xitanium Outdoor 150W Prog+	V01E01
LED OUTDOOR	Xitanium Outdoor 150W Prog+	V02E01
LED OUTDOOR	Xitanium Outdoor 150W Prog+	V03E01
LED OUTDOOR	Xitanium Outdoor 150W Prog+	V04E02
LED OUTDOOR	Xitanium Outdoor 150W Prog+	V05E03
LED OUTDOOR	Xitanium Outdoor 150W Prog+	V06E03
LED OUTDOOR	Xitanium Outdoor 150W Prog+	V07E03
LED OUTDOOR	Xitanium Outdoor 27W 1.0 Prog	V01E01
LED OUTDOOR	Xitanium Outdoor 27W 1.0 Prog	V02E01
LED OUTDOOR	Xitanium Outdoor 40W .53 Prog+	V01E01
LED OUTDOOR	Xitanium Outdoor 40W .53 Prog+	V02E01
LED OUTDOOR	Xitanium Outdoor 40W 0.7 Prog 230V	V01E01
LED OUTDOOR	Xitanium Outdoor 40W 0.7 Prog 230V	V02E01
LED OUTDOOR	Xitanium Outdoor 40W 0.7 Prog+	V01E01
LED OUTDOOR	Xitanium Outdoor 40W 0.7 Prog+	V02E01
LED OUTDOOR	Xitanium Outdoor 40W 0.7 Prog+	V03E01
LED OUTDOOR	Xitanium Outdoor 75W 0.7 Prog+	V02E01
LED OUTDOOR	Xitanium Outdoor 75W 0.7 Prog+	V03E01
LED OUTDOOR	Xitanium Outdoor 75W 0.7 Prog+ 230V	V01E01
LED OUTDOOR	Xitanium Outdoor 75W 0.7 Prog+ 230V	V02E01
LED OUTDOOR	Xitanium Outdoor 75W 0.7 Prog+ 230V	V03E01
LED OUTDOOR	Xitanium Outdoor 75W 1.0 Prog+	V01E01
LED OUTDOOR	Xitanium Outdoor 75W 1.0 Prog+	V02E02
LED OUTDOOR	Xitanium Outdoor 75W 1.0 Prog+	V03E03
LED OUTDOOR	Xitanium Outdoor 75W 1.0 Prog+	V04E03
LED OUTDOOR	Xitanium Outdoor 75W 1.0 Prog+	V05E03
LED OUTDOOR	Xitanium Outdoor 75W JP Prog+	V01E01
LED OUTDOOR	Xitanium Outdoor 75W JP Prog+	V02E01
LED OUTDOOR	Xitanium Outdoor 75W JP Prog+	V03E02
LED OUTDOOR	Xitanium Outdoor 75W JP Prog+	V04E03
LED OUTDOOR	Xitanium Outdoor 75W JP Prog+	V05E03
LED OUTDOOR	Xitanium Outdoor 75W JP Prog+	V06E03
LED OUTDOOR	Xitanium Outdoor 75W Prog	V02E02



<b>LED OUTDOOR</b>	Xitanium Outdoor 75W Prog	V03E03
<b>LED OUTDOOR</b>	Xitanium Outdoor 75W Prog	V04E03
<b>LED OUTDOOR</b>	Xitanium Outdoor 75W Prog	V05E03
<b>LED OUTDOOR</b>	Xitanium Outdoor 75W Prog	V06E04
<b>LED OUTDOOR</b>	Xitanium Outdoor 75W Prog	V07E05
<b>LED OUTDOOR</b>	Xitanium Outdoor 75W Prog	V08E05
<b>LED OUTDOOR</b>	Xitanium Outdoor 75W Prog	V09E05
<b>LED OUTDOOR</b>	Xitanium Outdoor 75W Prog+	V01E01
<b>LED OUTDOOR</b>	Xitanium Outdoor 75W Prog+	V02E01
<b>LED OUTDOOR</b>	Xitanium Outdoor 75W Prog+	V03E01
<b>LED OUTDOOR</b>	Xitanium Outdoor 75W Prog+	V04E02
<b>LED OUTDOOR</b>	Xitanium Outdoor 75W Prog+	V05E03
<b>LED OUTDOOR</b>	Xitanium Outdoor 75W Prog+	V06E03
<b>LED OUTDOOR</b>	Xitanium Outdoor 75W Prog+	V07E03



© 2013 Koninklijke Philips Electronics N.V.

All rights reserved. Reproduction in whole or in part is prohibited without the prior written consent of the copyright owner.

The information presented in this document does not form part of any quotation or contract, is believed to be accurate and reliable and may be changed without notice. No liability will be accepted by the publisher for any consequence of its use. Publication thereof does not convey nor imply any license under patent or other industrial or intellectual property rights.

Data subject to change.

Document: 20-01-2015