



PHILIPS

MultiOne

Software

Engineering

Supported Devices list – MultiOne Engineering 2.10 and MultiOne Workflow 2.3

Device Type	Device Name	Version
CONTROL	CT_OLC CB	0
CONTROL	CT_OLC PB	0
CONTROL	LLC1663/00 ActiLume DALI gen2	1
CONTROL	LLC1663/01 ActiLume DALI gen2	2
CONTROL	LLC1663/01 ActiLume DALI gen2	2.1
CONTROL	LLC1663/01 ActiLume DALI gen2	2.2
CONTROL	LLC1681/10 ActiLume	4.1.10.30011
CONTROL	LLC1682/11 ActiLume	4.1.10.30011
CONTROL	LLC1682/13 ActiLume	4.1.13.30377
CONTROL	LLC1682/13 ActiLume	4.1.15.30594
CONTROL	LLC1685/11 ActiLume	4.1.10.30011
CONTROL	LLC1685/12 ActiLume	4.1.13.30377
CONTROL	LLC1685/13 ActiLume	4.1.15.30594
CONTROL	LLC1686/11 ActiLume	4.1.10.30011
CONTROL	LLC1686/12 ActiLume	4.1.13.30377
CONTROL	LLC1686/13 ActiLume	4.1.15.30594
CONTROL	LLC1687/12 ActiLume	4.1.13.30377
CONTROL	LLC1687/13 ActiLume	4.1.15.30594
FLUO	HF-Ri TD 1 14/21/24/39 TL5 E+	1
FLUO	HF-Ri TD 1 14/21/24/39 TL5 E+	1.1
FLUO	HF-Ri TD 1 14/21/24/39 TL5 E+	1.11
FLUO	HF-Ri TD 1 14/21/24/39 TL5 E+	1.2
FLUO	HF-Ri TD 1 14/21/24/39 TL5 E+	2.41

FLUO	HF-Ri TD 1 14/21/24/39 TL5 E+	2.61
FLUO	HF-Ri TD 1 28/35/49/54 TL5 E+	1
FLUO	HF-Ri TD 1 28/35/49/54 TL5 E+	1.1
FLUO	HF-Ri TD 1 28/35/49/54 TL5 E+	1.11
FLUO	HF-Ri TD 1 28/35/49/54 TL5 E+	1.2
FLUO	HF-Ri TD 1 28/35/49/54 TL5 E+	2.4
FLUO	HF-Ri TD 1 28/35/49/54 TL5 E+	2.6
FLUO	HF-Ri TD 1 35/49/80 TL5 E+	1
FLUO	HF-Ri TD 1 35/49/80 TL5 E+	1.1
FLUO	HF-Ri TD 1 35/49/80 TL5 E+	1.11
FLUO	HF-Ri TD 1 35/49/80 TL5 E+	1.2
FLUO	HF-Ri TD 1 35/49/80 TL5 E+	2.4
FLUO	HF-Ri TD 1 35/49/80 TL5 E+	2.6
FLUO	HF-Ri TD 1/2 26-42 PL-T/C E+	1
FLUO	HF-Ri TD 1/2 26-42 PL-T/C E+	1.1
FLUO	HF-Ri TD 2 14/21/24/39 TL5 E+	1
FLUO	HF-Ri TD 2 14/21/24/39 TL5 E+	1.1
FLUO	HF-Ri TD 2 14/21/24/39 TL5 E+	1.11
FLUO	HF-Ri TD 2 14/21/24/39 TL5 E+	1.2
FLUO	HF-Ri TD 2 14/21/24/39 TL5 E+	2.41
FLUO	HF-Ri TD 2 14/21/24/39 TL5 E+	2.61
FLUO	HF-Ri TD 2 28/35/49/54 TL5 E+	1
FLUO	HF-Ri TD 2 28/35/49/54 TL5 E+	1.1
FLUO	HF-Ri TD 2 28/35/49/54 TL5 E+	1.11
FLUO	HF-Ri TD 2 28/35/49/54 TL5 E+	1.2
FLUO	HF-Ri TD 2 28/35/49/54 TL5 E+	2.4
FLUO	HF-Ri TD 2 28/35/49/54 TL5 E+	2.6
FLUO	HF-Ri TD 280 TL5/PL-L E+	1
FLUO	HF-Ri TD 280 TL5/PL-L E+	1.2
FLUO	HF-Ri TD 3 14/24 TL5 E+	1.4
FLUO	HF-Ri TD 3 14/24 TL5 E+	1.7
FLUO	HF-Ri TD 3 14/24 TL5 E+	2.7
FLUO	HF-Ri TD 4 14/24 TL5 E+	1.4
FLUO	HF-Ri TD 4 14/24 TL5 E+	1.7
FLUO	HF-Ri TD 4 14/24 TL5 E+	2.7
HID	Dynavision DALI	R1.5
HID	Dynavision DALI	R1.6
HID	Dynavision DALI	R1.7
HID	Dynavision DALI	R1.8
HID	Dynavision DALI	R2.0
HID	Dynavision Prog	R2.1
HID	Dynavision Prog	R2.2
LED	LED 929000712603	1.1
LED	LED 929000712803	1.1
LED	LED HP 350W 1.10	1.16
LED	LED HP 350W 1.20	1.32
LED	LHP 1710W 230-400V	1
LED	LHP 350W 347-480V	2

LED	LHP 350W 110-277V	2
LED	LHP 350W 110-277V E2	2.1
LED	TrustSight DALI L 20-95V 3W 1hr kit	1
LED	TrustSight DALI L 20-95V 3W 3hrs kit	1
LED	TrustSight DALI L 20-95V 3W xxhrs kit	1
LED	TrustSight DALI L 20-95V 6W 1hr kit	1
LED	TrustSight DALI P 15-55V 3W 1hr kit	1
LED	TrustSight DALI P 15-55V 3W 3hrs kit	1
LED	TrustSight DALI P 15-55V 3W xxhrs kit	1
LED	X*050C100V054XPM1M	1.12
LED	X*050C100V054XPM1M	1.18
LED	X*060C100V080XPM1M	1.12
LED	X*060C100V080XPM1M	1.18
LED	X*060C100V080XPM1M	1.2
LED	XH075C120V075KPF1M	3.2
LED	XH075C120V075KPF1M	4.2
LED	XH150C120V150KPF1M	3.2
LED	XH150C120V150KPF1M	4.2
LED	XI050C100V054XPL1M	1.1
LED	XI050C100V054XPL1M	1.18
LED	XI025C070V054DSM1	1
LED	XI025C070V054DSM5	1
LED	XI036C100V054DSM1	1
LED	XI036C100V054DSM5	1
LED	XI050C140V054DSM1	1
LED	XI050C140V054DSM5	1
LED	XI075C200V054XPT1	1.1
LED	XI075C200V054XPT1	1.2
LED	XI075C200V054XPT1	1.4
LED	XI075C200V054XPT1	1.5
LED	XI075C200V054XPT1	1.6
LED	XI075C200V054XPT1	1.7
LED	XI075C200V054XPT1	2
LED	XI075C200V054XPT1	2.1
LED	XI075C200V054XPT1	2.3
LED	XI075C200V054YPT1	1.1
LED	XI075C200V054YPT1	1.2
LED	XI075C200V054YPT1	1.4
LED	XI075C200V054YPT1	1.5
LED	XI075C200V054YPT1	1.6
LED	XI075C200V054YPT1	2.2
LED	XI075C200V054YPT1	2.4
LED	XI095C275V054BSS1M	1
LED	XI100C110V143BSY1	1
LED	XR025C100V036YPM1M	1.1
LED	XI100C110V143DSY1	1
LED	XI100C110V143DSY1	1.1
LED	XI180C090V285BSF1M	1

LED	XI180C125V200BSF1M	1
LED	XI180C180V144BSF1M	1
LED	XR025C100V036YPM1M	1.1
LED	XR025C100V036YPM1M	1.4
LEDOUTDOOR	Xi FP 110W 0.3-1.0A NLD 230V C150 sXt	1.4
LEDOUTDOOR	Xi FP 150W 0.2-0.7A SNLDAE 230V S240 sXt	1
LEDOUTDOOR	Xi FP 150W 0.3-1.0A SNLDAE 230V S240 sXt	1
LEDOUTDOOR	Xi FP 22W 0.3-1.0A SNLDAE 230V S175 sXt	1
LEDOUTDOOR	Xi FP 35W 0.3-1.0A NLD 230V C150 sXt	1.4
LEDOUTDOOR	Xi FP 40W 0.2-0.7A SNLDAE 230V S175 sXt	1
LEDOUTDOOR	Xi FP 40W 0.3-1.0A SNLDAE 230V S175 sXt	1
LEDOUTDOOR	Xi FP 70W 0.3-1.0A NLD 230V C150 sXt	1.4
LEDOUTDOOR	Xi FP 75W 0.2-0.7A SNLDAE 230V S240 sXt	1
LEDOUTDOOR	Xi FP 75W 0.3-1.0A SNLDAE 230V S240 sXt	1
LEDOUTDOOR	Xi LP 110W 0.2-0.7A SL 230V C150 sXt	1.1
LEDOUTDOOR	Xi LP 110W 0.2-0.7A SL 230V C150 sXt	1.2
LEDOUTDOOR	Xi LP 110W 0.3-1.0A S1 230V C150 sXt	1.1
LEDOUTDOOR	Xi LP 110W 0.2-0.7A S1 230V C150 sXt	1.2
LEDOUTDOOR	Xi LP 110W 0.3-1.0A SL 230V C150 sXt	1.1
LEDOUTDOOR	Xi LP 110W 0.3-1.0A SL 230V C150 sXt	1.2
LEDOUTDOOR	Xi LP 110W 0.3-1.0A S1 230V C150 sXt	1.1
LEDOUTDOOR	Xi LP 110W 0.3-1.0A S1 230V C150 sXt	1.2
LEDOUTDOOR	Xi LP 150W 0.2-0.7A S1 230V S240 sXt	1
LEDOUTDOOR	Xi LP 150W 0.2-0.7A SL 230V S240 sXt	1
LEDOUTDOOR	Xi LP 150W 0.2-0.7A SN 230V S240 sXt	1
LEDOUTDOOR	Xi LP 150W 0.3-1.0A S1 230V S240 sXt	1
LEDOUTDOOR	Xi LP 150W 0.3-1.0A SL 230V S240 sXt	1
LEDOUTDOOR	Xi LP 75W 0.2-0.7A S1 230V S240 sXt	1
LEDOUTDOOR	Xi LP 75W 0.2-0.7A SL 230V S240 sXt	1
LEDOUTDOOR	Xi LP 75W 0.2-0.7A SN 230V S240 sXt	1
LEDOUTDOOR	Xi LP 75W 0.3-1.0A S1 230V S240 sXt	1
LEDOUTDOOR	Xi LP 75W 0.3-1.0A SL 230V S240 sXt	1
LEDOUTDOOR	Xi LP 70W 0.2-0.7A S1 230V C150 sXt	1.1
LEDOUTDOOR	Xi LP 70W 0.2-0.7A S1 230V C150 sXt	1.2
LEDOUTDOOR	Xi LP 70W 0.2-0.7A SL 230V C150 sXt	1.1
LEDOUTDOOR	Xi LP 70W 0.2-0.7A SL 230V C150 sXt	1.2
LEDOUTDOOR	Xi LP 70W 0.3-1.0A S1 230V C150 sXt	1.1
LEDOUTDOOR	Xi LP 70W 0.3-1.0A S1 230V C150 sXt	1.2
LEDOUTDOOR	Xi LP 70W 0.3-1.0A SL 230V C150 sXt	1.1
LEDOUTDOOR	Xi LP 70W 0.3-1.0A SL 230V C150 sXt	1.2
LEDOUTDOOR	Xi LP 40W 0.2-0.7A S1 230V S175 sXt	1.1
LEDOUTDOOR	Xi LP 40W 0.2-0.7A S1 230V S175 sXt	1.2
LEDOUTDOOR	Xi LP 40W 0.2-0.7A SL 230V S175 sXt	1.1
LEDOUTDOOR	Xi LP 40W 0.2-0.7A SL 230V S175 sXt	1.2
LEDOUTDOOR	Xi LP 40W 0.3-1.0A S1 230V S175 sXt	1.1
LEDOUTDOOR	Xi LP 40W 0.3-1.0A S1 230V S175 sXt	1.2
LEDOUTDOOR	Xi LP 40W 0.3-1.0A SL 230V S175 sXt	1.1
LEDOUTDOOR	Xi LP 40W 0.3-1.0A SL 230V S175 sXt	1.2

LEDOUTDOOR	Xi LP 35W 0.3-1.0A S1 230V C150 sXt	1.2
LED	Xitanium 100W 0.15-0.5A 300V iXt 230V	1
LED	Xitanium 110W 0.2-0.6A 215V TD 230V iXt	1
LED	Xitanium 110W 0.2-0.6A 215V TD 230V iXt	1.1
LED	Xitanium 110W 0.2-0.6A 215V TD 230V iXt	1.2
LED	Xitanium 110W 0.2-0.6A 215V TD 230V iXt	1.3
LED	Xitanium 150W 0.2-0.7A 300V TD 230V iXt	1.1
LED	Xitanium 150W 0.2-0.7A 300V TD 230V iXt	1.2
LED	Xitanium 150W 0.2-0.7A 300V iXt 230V	1
LED	Xitanium 150W 0.7A sProg 230V-6 I66	2.3
LED	Xitanium 150W 0.7A sProg 230V-6 I66	3.3
LED	Xitanium 150W 0.7A sProg 230V-6C I66	2.3
LED	Xitanium 150W 0.7A sProg 230V-6C I66	3.3
LED	Xitanium 150W 1.1A Prog+ GL-F sXt	1.1
LED	Xitanium 150W 1.2A sProg 230V-F sXt	1.2
LED	Xitanium 150W 1.2A sProg GL-F sXt	1.2
LED	Xitanium 17W 0.12-0.4A 54V 1-10V 230V	1.7
LED	Xitanium 17W 0.12-0.4A 54V TD 230V	1.13
LED	Xitanium 17W 0.12-0.4A 54V TD 230V	1.14
LED	Xitanium 17W 0.12-0.4A 54V TD 230V	1.7
LED	Xitanium 17W 0.3-1A 24V TD/Is 230V	1
LED	Xitanium 17W 0.3-1A 24V TD/Is 230V	1.1
LED	Xitanium 17W 0.3-1A 24V TD/Is 230V	1.2
LED	Xitanium 17W 0.3-1A 24V TD/Is 230V	1.3
LED	Xitanium 20W 0.1-0.56A 54V 0-10V 120-277	1
LED	Xitanium 20W LH 0.15-0.5A 48V 230V	1
LED	Xitanium 20W LH 0.15-0.5A 48V TD/Is 230V	1.2
LED	Xitanium 25W 0-10V 120V/277V	1.1
LED	Xitanium 25W 0-10V 120V/277V	1.18
LED	Xitanium 25W 0-10V 120V/277V	1.4
LED	Xitanium 25W 0-10V 120V/277V	1.5
LED	Xitanium 25W 0-10V 120V/277V	1.6
LED	Xitanium 25W 0-10V 120V/277V	1.7
LED	Xitanium 25W 0-10V 120V/277V	1.9
LED	Xitanium 25W 0.3-1A 36V TD/Is 230V	1.2
LED	Xitanium 25W 0.3-1A 36V TD/Is 230V	1.3
LED	Xitanium 25W 0.3-1A 36V TD/Is 230V	1.4
LED OUTDOOR	Xitanium 300W 0.1-1.5A 0-10V 120-277V	1
LED OUTDOOR	Xitanium 300W 0.1-1.5A 0-10V 120-277V	1.1
LED OUTDOOR	Xitanium 300W 1.5A Prog+ GL-F2 sXt	1.1
LED	Xitanium 35W 0.08-0.35A 150V S 230V	1
LED	Xitanium 36W 0.12-0.4A 100V 1-10V 230V	1.7
LED	Xitanium 36W 0.12-0.4A 100V TD 230V	1.13
LED	Xitanium 36W 0.12-0.4A 100V TD 230V	1.14
LED	Xitanium 36W 0.12-0.4A 100V TD 230V	1.16
LED	Xitanium 36W 0.12-0.4A 100V TD 230V	1.17
LED	Xitanium 36W 0.12-0.4A 100V TD 230V	1.7
LED	Xitanium 36W 0.12-0.4A 110V TD 230V	1.3

LED	Xitanium 36W 0.12-0.4A 110V TD 230V	1.4
LED	Xitanium 36W 0.12-0.4A 110V TD 230V	1.5
LED	Xitanium 36W 0.12-0.4A 110V TD 230V	2
LED	Xitanium 36W 0.12-0.4A 110V TD 230V	2.1
LED	Xitanium 36W 0.3-1A 54V TD 230V	1.1
LED	Xitanium 36W 0.3-1A 54V TD 230V	1.2
LED	Xitanium 36W 0.3-1A 54V TD 230V	1.3
LED	Xitanium 36W 0.3-1A 54V TD 230V	1.5
LED	Xitanium 36W 0.3-1A 54V TD 230V	1.6
LED	Xitanium 36W 0.3-1A 54V TD 230V	1.7
LED	Xitanium 36W 0.3-1A 54V TD 230V	1.8
LED	Xitanium 36W 0.3-1A 54V TD 230V	1.9
LED	Xitanium 36W LH 0.3-1A 48V I 230V	1
LED	Xitanium 36W LH 0.3-1A 48V TD/I 230V	1.1
LED	Xitanium 36W LH 0.3-1A 48V TD/I 230V	1.2
LED	Xitanium 36W LH 0.3-1A 48V TD/I 230V	1.3
LED	Xitanium 36W LH 0.3-1A 48V TD/I 230V	1.4
LED	Xitanium 36W WH 0.3-1A 54V TD/Is 230V	1
LED	Xitanium 36W WH 0.3-1A 54V TD/Is 230V	1.1
LED	Xitanium 36W WH 0.3-1A 54V TD/Is 230V	1.3
LED	Xitanium 36W/S 0.3-1A 48V TD 230V	1
LED	Xitanium 36W/S 0.3-1A 48V TD 230V	1.1
LED	Xitanium 40W 0.1-1.1A 54V 0-10V 120-277V	1
LED	Xitanium 40W 0.1-1.1A 54V 0-10V 120-277V	1.1
LED	Xitanium 40W 0.1-1.1A 54V 0-10V 120-277V	1.2
LED	Xitanium 40W 0.1-1.1A 54V 0-10V 120-277V	1.3
LED	Xitanium 40W 1.1A 54V DALI SR INT	1
LED	Xitanium 40W 1.1A 54V DALI SR INT	1.2
LED	Xitanium 40W 1.1A 54V DALI SR INT	1.3
LED	Xitanium 40W 1.1A 54V DALI SR INT	1.4
LED	Xitanium 40W 1.1A 54V DALI SR INT	1.5
LED	Xitanium 50/75W 0.3-1A 62V TD/TE 230V	1
LED	Xitanium 50W 0.3-1A 62V TD/Is 230V	1.1
LED	Xitanium 50W 0.3-1A 62V TD/Is 230V	1.2
LED	Xitanium 50W 0.3-1A 62V TD/Is 230V	1.3
LED	Xitanium 50W 0.3-1A 62V TD/TE 230V	1.1
LED	Xitanium 50W 0.3-1A 62V TD/TE 230V	1.11
LED	Xitanium 50W 0.3-1A 62V TD/TE 230V	1.16
LED	Xitanium 50W 0.3-1A 62V TD/TE 230V	1.18
LED	Xitanium 50W 0.3-1A 62V TD/TE 230V	1.8
LED	Xitanium 50W LH 0.7-1.5A 48V 230V	1
LED	Xitanium 50W LH 0.7-1.5A 48V 230V	1.1
LED	Xitanium 50W LH 0.7-1.5A 48V TD/I 230V	1.1
LED	Xitanium 54W 0.1-1.5A 54V 0-10V 347V	1
LED	Xitanium 60W 0.08-0.35A 220V S 230V	1
LED	Xitanium 60W 0.08-0.35A 300V S 230V	1
LED	Xitanium 75W 0.1-2.0A 54V 0-10V 120-277V	1
LED	Xitanium 75W 0.1-2.0A 54V 0-10V 120-277V	1.1

LED	Xitanium 75W 0.12-0.4A 215V TD 230V	1.3
LED	Xitanium 75W 0.12-0.4A 215V TD 230V	1.4
LED	Xitanium 75W 0.12-0.4A 215V TD 230V	1.5
LED	Xitanium 75W 0.12-0.4A 215V TD 230V	1.6
LED	Xitanium 75W 0.12-0.4A 215V TD 230V	2
LED	Xitanium 75W 0.12-0.4A 215V TD CL 230V	1.3
LED	Xitanium 75W 0.7-2A 54V 0-10V 230V	1.3
LED	Xitanium 75W 0.7-2A 54V 0-10V 230V	1.4
LED	Xitanium 75W 0.7-2A 54V 0-10V 230V	1.5
LED	Xitanium 75W 0.7-2A 54V 0-10V 230V	1.6
LED	Xitanium 75W 0.7-2A 54V 0-10V 230V	1.7
LED	Xitanium 75W 0.7-2A 54V 0-10V 230V	2
LED	Xitanium 75W 0.7-2A 54V 0-10V 230V	2.1
LED	Xitanium 75W 0.7-2A 54V TD 230V	1.3
LED	Xitanium 75W 0.7-2A 54V TD 230V	1.4
LED	Xitanium 75W 0.7-2A 54V TD 230V	1.5
LED	Xitanium 75W 0.7-2A 54V TD 230V	1.6
LED	Xitanium 75W 0.7-2A 54V TD 230V	2.2
LED	Xitanium 75W 0.7-2A 54V TD 230V	2.4
LED	Xitanium 75W 0.7-2A 54V TD 230V	3
LED	Xitanium 75W 0.7-2A 54V TD 230V	3.1
LED	Xitanium 75W 0.7-2A 54V TD 230V	3.2
LED	Xitanium 75W 1.1A Prog+ GL-F sXt	1.1
LED	Xitanium 75W 1.2A sProg 230V-F sXt	1.2
LED	Xitanium 75W 1.2A sProg GL-F sXt	1.2
LED	Xitanium 75W 2A 54V DALI SR INT	1
LED	Xitanium 75W 2A 54V DALI SR INT	1.1
LED	Xitanium 75W 2A 54V DALI SR INT	1.2
LED	Xitanium 75W 2A 54V DALI SR INT	1.4
LED	Xitanium 75W 2A 54V DALI SR INT	1.5
LED	Xitanium 75W SH 0.3-1A 110V TD/I 230V	1.1
LED	Xitanium 75W SH 0.3-1A 110V TD/I 230V	1.2
LED	Xitanium 75W SH 0.3-1A 110V TD/I 230V	1.3
LED	Xitanium 75W SH 0.3-1A 110V TD/I 230V	1.4
LED	Xitanium 75W SH 0.3-1A 110V TD/I 230V	1.5
LED	Xitanium 75W/0.15-0.4A 200V TD 230V	1.14
LED	Xitanium 75W/0.15-0.4A 200V TD 230V	1.15
LED	Xitanium 75W/0.15-0.4A 200V TD 230V	1.16
LED	Xitanium 75W/0.15-0.4A 200V TD 230V	1.3
LED	Xitanium 75W/0.2-0.4A 200V 1-10V 230V	1.3
LED OUTDOOR	Xitanium FULL PROG 110W1000 NL1 C150 Xt	1.3
LED OUTDOOR	Xitanium FULL PROG 110W1000 NLD C150 Xt	1.3
LED OUTDOOR	Xitanium FULL PROG 35W1000 NL1 C150 Xt	1.3
LED OUTDOOR	Xitanium FULL PROG 35W1000 NLD C150 Xt	1.3
LED OUTDOOR	Xitanium FULL PROG 70W1000 NL1 C150 Xt	1.3
LED OUTDOOR	Xitanium FULL PROG 70W1000 NLD C150 Xt	1.3
LED OUTDOOR	Xitanium LITE PROG 110W1000 NL C150 OD	1.3
LED OUTDOOR	Xitanium LITE PROG 70W1000 NL C150 OD	1.3

LED OUTDOOR	Xitanium Outdoor 100W .53 Prog+	V02E01
LED OUTDOOR	Xitanium Outdoor 100W .53 Prog+	V03E01
LED OUTDOOR	Xitanium Outdoor 100W 0.7 Prog+	V02E01
LED OUTDOOR	Xitanium Outdoor 100W 0.7 Prog+	V03E01
LED OUTDOOR	Xitanium Outdoor 125W JP Prog+	V01E01
LED OUTDOOR	Xitanium Outdoor 125W JP Prog+	V02E01
LED OUTDOOR	Xitanium Outdoor 125W JP Prog+	V03E02
LED OUTDOOR	Xitanium Outdoor 125W JP Prog+	V04E03
LED OUTDOOR	Xitanium Outdoor 125W JP Prog+	V05E03
LED OUTDOOR	Xitanium Outdoor 125W JP Prog+	V06E03
LED OUTDOOR	Xitanium Outdoor 150W .35 Prog+ H	V01E01
LED OUTDOOR	Xitanium Outdoor 150W .35 Prog+ H	V02E01
LED OUTDOOR	Xitanium Outdoor 150W .35 Prog+ H	V03E02
LED OUTDOOR	Xitanium Outdoor 150W .35 Prog+ H	V04E03
LED OUTDOOR	Xitanium Outdoor 150W .35 Prog+ H	V05E03
LED OUTDOOR	Xitanium Outdoor 150W .35 Prog+ H	V06E03
LED OUTDOOR	Xitanium Outdoor 150W 0.7 Prog+ 230V	V01E01
LED OUTDOOR	Xitanium Outdoor 150W 0.7 Prog+ 230V	V02E01
LED OUTDOOR	Xitanium Outdoor 150W 0.7 Prog+ 230V	V03E01
LED OUTDOOR	Xitanium Outdoor 150W 0.7 Prog+ H	V02E01
LED OUTDOOR	Xitanium Outdoor 150W 0.7 Prog+ H	V03E02
LED OUTDOOR	Xitanium Outdoor 150W 0.7 Prog+ H	V04E02
LED OUTDOOR	Xitanium Outdoor 150W 0.7 Prog+ H	V05E02
LED OUTDOOR	Xitanium Outdoor 150W 1.0 Prog+	V01E01
LED OUTDOOR	Xitanium Outdoor 150W 1.0 Prog+	V02E02
LED OUTDOOR	Xitanium Outdoor 150W 1.0 Prog+	V03E03
LED OUTDOOR	Xitanium Outdoor 150W 1.0 Prog+	V04E03
LED OUTDOOR	Xitanium Outdoor 150W 1.0 Prog+	V05E03
LED OUTDOOR	Xitanium Outdoor 150W Prog	V03E02
LED OUTDOOR	Xitanium Outdoor 150W Prog	V04E03
LED OUTDOOR	Xitanium Outdoor 150W Prog	V05E03
LED OUTDOOR	Xitanium Outdoor 150W Prog	V06E03
LED OUTDOOR	Xitanium Outdoor 150W Prog	V07E04
LED OUTDOOR	Xitanium Outdoor 150W Prog	V08E05
LED OUTDOOR	Xitanium Outdoor 150W Prog	V09E05
LED OUTDOOR	Xitanium Outdoor 150W Prog	V10E05
LED OUTDOOR	Xitanium Outdoor 150W Prog+	V01E01
LED OUTDOOR	Xitanium Outdoor 150W Prog+	V02E01
LED OUTDOOR	Xitanium Outdoor 150W Prog+	V03E01
LED OUTDOOR	Xitanium Outdoor 150W Prog+	V04E02
LED OUTDOOR	Xitanium Outdoor 150W Prog+	V05E03
LED OUTDOOR	Xitanium Outdoor 150W Prog+	V06E03
LED OUTDOOR	Xitanium Outdoor 150W Prog+	V07E03
LED OUTDOOR	Xitanium Outdoor 27W 1.0 Prog	V01E01
LED OUTDOOR	Xitanium Outdoor 27W 1.0 Prog	V02E01
LED OUTDOOR	Xitanium Outdoor 40W .53 Prog+	V01E01
LED OUTDOOR	Xitanium Outdoor 40W .53 Prog+	V02E01
LED OUTDOOR	Xitanium Outdoor 40W 0.7 Prog 230V	V01E01

LED OUTDOOR	Xitanium Outdoor 40W 0.7 Prog 230V	V02E01
LED OUTDOOR	Xitanium Outdoor 40W 0.7 Prog+	V01E01
LED OUTDOOR	Xitanium Outdoor 40W 0.7 Prog+	V02E01
LED OUTDOOR	Xitanium Outdoor 40W 0.7 Prog+	V03E01
LED OUTDOOR	Xitanium Outdoor 75W 0.7 Prog+	V02E01
LED OUTDOOR	Xitanium Outdoor 75W 0.7 Prog+	V03E01
LED OUTDOOR	Xitanium Outdoor 75W 0.7 Prog+ 230V	V01E01
LED OUTDOOR	Xitanium Outdoor 75W 0.7 Prog+ 230V	V02E01
LED OUTDOOR	Xitanium Outdoor 75W 0.7 Prog+ 230V	V03E01
LED OUTDOOR	Xitanium Outdoor 75W 1.0 Prog+	V01E01
LED OUTDOOR	Xitanium Outdoor 75W 1.0 Prog+	V02E02
LED OUTDOOR	Xitanium Outdoor 75W 1.0 Prog+	V03E03
LED OUTDOOR	Xitanium Outdoor 75W 1.0 Prog+	V04E03
LED OUTDOOR	Xitanium Outdoor 75W 1.0 Prog+	V05E03
LED OUTDOOR	Xitanium Outdoor 75W JP Prog+	V01E01
LED OUTDOOR	Xitanium Outdoor 75W JP Prog+	V02E01
LED OUTDOOR	Xitanium Outdoor 75W JP Prog+	V03E02
LED OUTDOOR	Xitanium Outdoor 75W JP Prog+	V04E03
LED OUTDOOR	Xitanium Outdoor 75W JP Prog+	V05E03
LED OUTDOOR	Xitanium Outdoor 75W JP Prog+	V06E03
LED OUTDOOR	Xitanium Outdoor 75W Prog	V02E02
LED OUTDOOR	Xitanium Outdoor 75W Prog	V03E03
LED OUTDOOR	Xitanium Outdoor 75W Prog	V04E03
LED OUTDOOR	Xitanium Outdoor 75W Prog	V05E03
LED OUTDOOR	Xitanium Outdoor 75W Prog	V06E04
LED OUTDOOR	Xitanium Outdoor 75W Prog	V07E05
LED OUTDOOR	Xitanium Outdoor 75W Prog	V08E05
LED OUTDOOR	Xitanium Outdoor 75W Prog	V09E05
LED OUTDOOR	Xitanium Outdoor 75W Prog+	V01E01
LED OUTDOOR	Xitanium Outdoor 75W Prog+	V02E01
LED OUTDOOR	Xitanium Outdoor 75W Prog+	V03E01
LED OUTDOOR	Xitanium Outdoor 75W Prog+	V04E02
LED OUTDOOR	Xitanium Outdoor 75W Prog+	V05E03
LED OUTDOOR	Xitanium Outdoor 75W Prog+	V06E03
LED OUTDOOR	Xitanium Outdoor 75W Prog+	V07E03



© 2013 Koninklijke Philips Electronics N.V.
All rights reserved. Reproduction in whole or in part is prohibited without the prior written consent of the copyright owner.
The information presented in this document does not form part of any quotation or contract, is believed to be accurate and reliable and may be changed without notice. No liability will be accepted by the publisher for any consequence of its use. Publication thereof does not convey nor imply any license under patent or other industrial or intellectual property rights.
Data subject to change.