



MultiOne
configuration software



Use our
MultiOne software
to configure the devices
to your customers needs.
Free download via
philips.com/multione

Customize your devices, simple and fast.

With MultiOne configuration software, our intuitive tool, you can meet specific requirements of your customers with a limited portfolio of programmable devices. Depending on the type of device, driver or sensor, a combination of features can be configured to create diversity, extra security and costdown improvements.

Main benefits

✓ **One multi-functional tool**

You can program a luminaire, test it, configure it automatically in production, read out its status and do a complete quality analysis if there are returns from the field. All with one intuitive tool compatible with all Philips configurable drivers.

✓ **Ultimate flexibility**

Access to the features built into the device (driver or sensor) offers you the flexibility to configure your devices to match specific requirements. It enables optimization of installation, last minute changes, easy diagnostics and maintenance.

✓ **Innovative**

We bring innovation to your business by allowing you to wirelessly program all Xitanium LED drivers using our MultiOne SimpleSet technology.

Specific features

✓ **Functionality**

- Adjustable output current
- Adjustable light output
- Adjustable startup time
- End of life indication

✓ **Security**

- Module temperature protection
- Active cooling
- DC emergency
- OEM write protection
- OEM traceability

✓ **Cost Down**

- Constant light output
- Energy meter
- Dimming interface
 - * 1-10 V dim level
 - * AmpDim
 - * LumiStep
 - * DynaDimmer
 - * Corridor mode
 - * Touch and dim

Just choose the right interface to get started



We made it very easy to get started. The MultiOne software is free to download from our website. You only need a windows operating pc or laptop with USB connections and choose the MultiOne interface that fits best into your process.




Jan Fitters
Product manager



Configuration set-up

For (re)configuration after installation you can use Philips Field App



Philips MultiOne interface	
Product name	12 NC
LCN8600/00 MultiOne interface USB2DALI	9137 003 46703
LCN9610 MultiOne SimpleSet interface	9290 009 99406
LCN9620 MultiOne SimpleSet interface	9290 009 99506

LCN8600/00 MultiOne interface USB2DALI
The interface that can be used with the MultiOne PC software to commission, configure, diagnose devices via the DALI interface.

LCN9610 and LCN9620 MultiOne SimpleSet interface
The interface that can be used with the MultiOne PC software to powerless configure, diagnose devices via the wireless SimpleSet interface.

SimpleSet, for wireless configuration



We immediately recognized the benefits of SimpleSet in our organisation to be flexible in our product-offering for spot- and downlight.

Wim Gielen
R&D Manager, Orbit




Suitable for:


Office


Retail


Industry


Outdoor