



Release note – MultiOne Workflow 3.12

In this release the following items were changed (compared to the previous version):

CHANGES

1. Added:

- Support for new (versions of) LED devices

| name | 12nc |
|--|--------------|
| LDP 100W 1.05A IP67 | 929002129004 |
| LDP 150W 1.05A IP67 | 929002129104 |
| LDP 220W 1.05A IP67 | 929002129204 |
| LDP 65W 1.05A IP67 | 929002128904 |
| SR Bridge SRB-BS2 | 929001780413 |
| SR Bridge SRB-LD2 | 929001780513 |
| Xi BP 22W 0.2-0.7A S 230V C123 sXt | 929001499306 |
| Xi BP 40W 0.2-0.7A S 230V C123 sXt | 929001499406 |
| Xi BP 40W 0.3-1.0A S 230V C123 sXt | 929001499506 |
| Xi FP 150W 0.2-0.7A SNLDAE 230V S240 sXt | 929002128606 |
| Xi FP 150W 0.3-1.0A SNLDAE 230V S240 sXt | 929002128706 |
| Xi FP 40W 0.2-0.7A SNLDAE 230V S175 sXt | 929002128306 |
| Xi FP 75W 0.2-0.7A SNLDAE 230V S240 sXt | 929002128406 |

| | |
|---|--------------|
| Xi FP 75W 0.3-1.0A SNLDAE 230V S240 sXt | 929002128506 |
| Xi LP 100W 0.3-1.05A S1 230V I175 | 929002115680 |
| Xi LP 100W 0.3-1.05A S1 230V I175CF | 929002115780 |
| Xi LP 100W 0.5-1.5A S1 230V I175 | 929002115080 |
| Xi LP 100W 0.5-1.5A S1 230V I175CF | 929002115280 |
| Xi LP 150W 0.3-1.05A S1 230V I175 | 929002115480 |
| Xi LP 150W 0.3-1.05A S1 230V I175CF | 929002115580 |
| Xi LP 150W 0.5-1.5A S1 230V I175 | 929002114980 |
| Xi LP 150W 0.5-1.5A S1 230V I175CF | 929002115180 |
| Xi LP 22W 0.2-0.7A S1 230V C123 sXt | 929002102906 |
| Xi LP 22W 0.3-1.0A S1 230V C123 sXt | 929002103006 |
| Xi LP 40W 0.2-0.7A S1 230V C123 sXt | 929002103106 |
| Xi LP 40W 0.3-1.0A S1 230V C123 sXt | 929002103206 |
| XI030C090V054PST1 | 929001759113 |
| XI040C110V050VWT1 | 929001758313 |
| XI075C200V054PST1 | 929001758413 |
| Xitanium 20W/m 0.15-0.5A 54V TD 230V | 929001419006 |
| XJ180C090V285BSF2 | 929001782113 |
| XJ180C125V200BSF2 | 929001782213 |
| XJ180C180V144BSF2 | 929001782313 |

- New Features:

- Auxiliary Power Supply
- Tunable White

- Updated features

- DTL (Device Temperature Limit): new version is introduced for new drivers:

| | |
|-------------------|--------------|
| XJ180C090V285BSF2 | 929001782113 |
| XJ180C125V200BSF2 | 929001782213 |
| XJ180C180V144BSF2 | 929001782313 |

- Improved functionality:

- Silent install of Workflow will deinstall previous version of Workflow if it was already installed.

IMPORTANT NOTICE

Make sure that also the extra conditions are fulfilled:

- Put the *Power mode* of your PC settings in *best performance*
- The correct Microsoft Windows version,
 - No Windows XP support

The MultiOne software is tested on a wide variety of virus scanners (latest versions), no issues detected.



Document: 19-06-2019
No: RNW2 2019v2
Author: E.Bos

© Signify NV, 2019. All rights reserved. Signify reserves the right to make changes in specifications and/or to discontinue any product at any time without notice or obligation and will not be liable for any consequences resulting from the use of this publication