

PHILIPS

MultiOne

Supported Device

Philips MultiOne 3.0 application mode selector

MultiOne

Application mode

- ▢ All
- ▢ Commands
- ▢ Features
- ▢ Query
- ▢ Diagnostics
- ▢ Scheduler

▢ Single device programming

- ▢ Getting started...
- ▢ User manual...

Recent documents

Supported Device list – MultiOne Engineering/Workflow 3.6

Device Type	Device Name	Version	Interface		
CTL	CT_OLC CB	0	DALI		
CTL	CT_OLC PB	0	DALI		
CTL	EasySense	1.13		SimpleSet	
CTL	EasySense	1.14		SimpleSet	
CTL	EasySense	2.1		SimpleSet	
CTL	EasySense	2.39		SimpleSet	
CTL	LLC1663/00 ActiLume DALI gen2	1	DALI		
CTL	LLC1663/01 ActiLume DALI gen2	2	DALI		
CTL	LLC1663/01 ActiLume DALI gen2	2.1	DALI		
CTL	LLC1663/01 ActiLume DALI gen2	2.2	DALI		
CTL	LLC1663/01 ActiLume DALI gen2	2.3	DALI		
CTL	LLC1663/01 ActiLume DALI gen2	2.4	DALI		
CTL	LLC1681/10 ActiLume	4.1.10.30011			ZigBee
CTL	LLC1682/11 ActiLume	4.1.10.30011			ZigBee
CTL	LLC1682/13 ActiLume	4.1.13.30377			ZigBee
CTL	LLC1682/13 ActiLume	4.1.15.30594			ZigBee
CTL	LLC1682/13 ActiLume	4.1.16.30731			ZigBee
CTL	LLC1682/13 ActiLume	4.1.18.31450			ZigBee

CTL	LLC1685/11 ActiLume	4.1.10.30011			ZigBee
CTL	LLC1685/12 ActiLume	4.1.13.30377			ZigBee
CTL	LLC1685/13 ActiLume	4.1.15.30594			ZigBee
CTL	LLC1685/13 ActiLume	4.1.16.30731			ZigBee
CTL	LLC1685/13 ActiLume	4.1.18.31394			ZigBee
CTL	LLC1685/13 ActiLume	4.1.18.31450			ZigBee
CTL	LLC1685/14 ActiLume	4.1.19.31531			ZigBee
CTL	LLC1685/15 ActiLume	4.1.20.31800			ZigBee
CTL	LLC1686/11 ActiLume	4.1.10.30011			ZigBee
CTL	LLC1686/12 ActiLume	4.1.13.30377			ZigBee
CTL	LLC1686/13 ActiLume	4.1.15.30594			ZigBee
CTL	LLC1686/13 ActiLume	4.1.16.30731			ZigBee
CTL	LLC1686/13 ActiLume	4.1.18.31450			ZigBee
CTL	LLC1686/14 ActiLume	4.1.19.31531		SimpleSet	
CTL	LLC1686/15 ActiLume	4.1.20.31800		SimpleSet	
CTL	LLC1687/12 ActiLume	4.1.13.30377			ZigBee
CTL	LLC1687/13 ActiLume	4.1.15.30594			ZigBee
CTL	LLC1687/13 ActiLume	4.1.16.30731			ZigBee
CTL	LLC1687/13 ActiLume	4.1.18.31450			ZigBee
CTL	PoELC Gen2 25W	2		SimpleSet	
CTL	PoELC Gen2 45W	2		SimpleSet	
CTL	SNS200	2.51		SimpleSet	
CTL	SNS200	2.57		SimpleSet	
CTL	SNS200	2.58		SimpleSet	
FLUO	HF-Ri TD 1 14/21/24/39 TL5 E+	1	DALI		
FLUO	HF-Ri TD 1 14/21/24/39 TL5 E+	1.1	DALI		
FLUO	HF-Ri TD 1 14/21/24/39 TL5 E+	1.11	DALI		
FLUO	HF-Ri TD 1 14/21/24/39 TL5 E+	1.2	DALI		
FLUO	HF-Ri TD 1 14/21/24/39 TL5 E+	2.41	DALI		
FLUO	HF-Ri TD 1 14/21/24/39 TL5 E+	2.61	DALI		
FLUO	HF-Ri TD 1 28/35/49/54 TL5 E+	1	DALI		
FLUO	HF-Ri TD 1 28/35/49/54 TL5 E+	1.1	DALI		
FLUO	HF-Ri TD 1 28/35/49/54 TL5 E+	1.11	DALI		
FLUO	HF-Ri TD 1 28/35/49/54 TL5 E+	1.2	DALI		
FLUO	HF-Ri TD 1 28/35/49/54 TL5 E+	2.4	DALI		
FLUO	HF-Ri TD 1 28/35/49/54 TL5 E+	2.6	DALI		
FLUO	HF-Ri TD 1 35/49/80 TL5 E+	1	DALI		
FLUO	HF-Ri TD 1 35/49/80 TL5 E+	1.1	DALI		
FLUO	HF-Ri TD 1 35/49/80 TL5 E+	1.11	DALI		
FLUO	HF-Ri TD 1 35/49/80 TL5 E+	1.2	DALI		
FLUO	HF-Ri TD 1 35/49/80 TL5 E+	2.4	DALI		
FLUO	HF-Ri TD 1 35/49/80 TL5 E+	2.6	DALI		
FLUO	HF-Ri TD 1/2 26-42 PL-T/C E+	1	DALI		
FLUO	HF-Ri TD 1/2 26-42 PL-T/C E+	1.1	DALI		
FLUO	HF-Ri TD 2 14/21/24/39 TL5 E+	1	DALI		
FLUO	HF-Ri TD 2 14/21/24/39 TL5 E+	1.1	DALI		
FLUO	HF-Ri TD 2 14/21/24/39 TL5 E+	1.11	DALI		
FLUO	HF-Ri TD 2 14/21/24/39 TL5 E+	1.2	DALI		
FLUO	HF-Ri TD 2 14/21/24/39 TL5 E+	2.41	DALI		

FLUO	HF-Ri TD 2 14/21/24/39 TL5 E+	2.61	DALI		
FLUO	HF-Ri TD 2 28/35/49/54 TL5 E+	1	DALI		
FLUO	HF-Ri TD 2 28/35/49/54 TL5 E+	1.1	DALI		
FLUO	HF-Ri TD 2 28/35/49/54 TL5 E+	1.11	DALI		
FLUO	HF-Ri TD 2 28/35/49/54 TL5 E+	1.2	DALI		
FLUO	HF-Ri TD 2 28/35/49/54 TL5 E+	2.4	DALI		
FLUO	HF-Ri TD 2 28/35/49/54 TL5 E+	2.6	DALI		
FLUO	HF-Ri TD 280 TL5/PL-L E+	1	DALI		
FLUO	HF-Ri TD 280 TL5/PL-L E+	1.2	DALI		
FLUO	HF-Ri TD 3 14/24 TL5 E+	1.4	DALI		
FLUO	HF-Ri TD 3 14/24 TL5 E+	1.7	DALI		
FLUO	HF-Ri TD 3 14/24 TL5 E+	2.7	DALI		
FLUO	HF-Ri TD 4 14/24 TL5 E+	1.4	DALI		
FLUO	HF-Ri TD 4 14/24 TL5 E+	1.7	DALI		
FLUO	HF-Ri TD 4 14/24 TL5 E+	2.7	DALI		
HID	Dynavision DALI	R1.5	DALI		
HID	Dynavision DALI	R1.6	DALI		
HID	Dynavision DALI	R1.7	DALI		
HID	Dynavision DALI	R1.8	DALI		
HID	Dynavision DALI	R2.0	DALI		
HID	Dynavision Prog	R2.1	DALI		
HID	Dynavision Prog	R2.2	DALI		
LED	BAC40EM10	1		SimpleSet	
LED	BAC40EM6	1		SimpleSet	
LED	LED 929000712603	1.1	DALI		
LED	LED 929000712803	1.1	DALI		
LED	LED HP 350W 1.10	1.16	DALI		
LED	LED HP 350W 1.20	1.32	DALI		
LED	LHP 1710W 220-400V E2 DALI	2.1	DALI		
LED	LHP 1710W 220-400V E2 RDM	2.1	DALI		
LED	LHP 1710W 230-400V	1	DALI		
LED	LHP 1710W 230-400V E2 DALI	2	DALI		
LED	LHP 1710W 230-400V E2 RDM	2	DALI		
LED	LHP 350W 110-277V	2	DALI		
LED	LHP 350W 110-277V E2	2.1	DALI		
LED	LHP 350W 347-480V	2	DALI		
LED	TrustSight DALI L 20-95V 3W 1hr kit	1	DALI		
LED	TrustSight DALI L 20-95V 3W 3hrs kit	1	DALI		
LED	TrustSight DALI L 20-95V 3W xxhrs kit	1	DALI		
LED	TrustSight DALI L 20-95V 6W 1hr kit	1	DALI		
LED	TrustSight DALI P 15-55V 3W 1hr kit	1	DALI		
LED	TrustSight DALI P 15-55V 3W 3hrs kit	1	DALI		
LED	TrustSight DALI P 15-55V 3W xxhrs kit	1	DALI		
LED	X*050C100V054XPM1M	1.12	DALI		
LED	X*050C100V054XPM1M	1.18	DALI		
LED	X*060C100V080XPM1M	1.12	DALI		
LED	X*060C100V080XPM1M	1.18	DALI		
LED	X*060C100V080XPM1M	1.2	DALI		
LED	XG020C056V054BST1	1		SimpleSet	

LED	XG040C110V054BST1	1		SimpleSet	
LED	XG054C150V054BST1	1		SimpleSet	
LED	XG075C200V054BST1	1		SimpleSet	
LED	XH055C180V054BSY1	1		SimpleSet	
LED	XH075C120V075KPF1M	3.2	DALI		
LED	XH075C120V075KPF1M	4.2	DALI		
LED	XH095C275V054BSF1	1.1		SimpleSet	
LED	XH100C110V143BSY1	1		SimpleSet	
LED	XH100C150V091BSY1	1		SimpleSet	
LED	XH150C120V150KPF1M	3.2	DALI		
LED	XH150C120V150KPF1M	4.2	DALI		
LED	XH180C090V285BSF1	1.1		SimpleSet	
LED	XH180C125V200BSF1	1.1		SimpleSet	
LED	XH180C125V200PSF1	1		SimpleSet	
LED	XH180C180V144BSF1	1.1		SimpleSet	
LED	XH300C150V300BSR1	1		SimpleSet	
LED	XH300C150V300BSR1M	1		SimpleSet	
LED	XI 100W 0.15-0.5A 300V iXt TDCL 230V	2.1	DALI	SimpleSet	
LED	XI 150W 0.2-0.7A 300V iXt TDCL 230V	2.1	DALI	SimpleSet	
LED	XI 60W 0.08-0.35A 300V TD16CL 230V	2.1	DALI	SimpleSet	
LED	XI020C056V054BST2	2		SimpleSet	
LED	XI025C070V054DSM1	1		SimpleSet	
LED	XI025C070V054DSM1	2		SimpleSet	
LED	XI025C070V054DSM5	1		SimpleSet	
LED	XI025C070V054DSM5	2		SimpleSet	
LED	XI025C100V036DSM1	1		SimpleSet	
LED	XI025C100V036DSM5	1		SimpleSet	
LED	XI036C100V054DSM1	1		SimpleSet	
LED	XI036C100V054DSM1	2		SimpleSet	
LED	XI036C100V054DSM5	1		SimpleSet	
LED	XI036C100V054DSM5	2		SimpleSet	
LED	XI040C110V054BST1	2		SimpleSet	
LED	XI040C110V054BST1	3		SimpleSet	
LED	XI040C110V054SST1	1		SimpleSet	
LED	XI050C100V054XPL1M	1.1	DALI		
LED	XI050C100V054XPL1M	1.18	DALI		
LED	XI050C140V054DSM1	1		SimpleSet	
LED	XI050C140V054DSM1	2		SimpleSet	
LED	XI050C140V054DSM5	1		SimpleSet	
LED	XI050C140V054DSM5	2		SimpleSet	
LED	XI054C150V054BST1	2		SimpleSet	
LED	XI054C150V054BST1	3		SimpleSet	
LED	XI054C150V054SST1	1		SimpleSet	
LED	XI055C180V054BSJ1	1		SimpleSet	
LED	XI055C180V054BSJ1	1.1		SimpleSet	
LED	XI075C070V118VSY1M	1	DALI	SimpleSet	
LED	XI075C105V079VSY1M	1	DALI	SimpleSet	
LED	XI075C200V054BST1	2		SimpleSet	
LED	XI075C200V054DSM1	1		SimpleSet	

LED	XI075C200V054DSM5	1		SimpleSet	
LED	XI075C200V054SST1	1		SimpleSet	
LED	XI075C200V054XPT1	1.1	DALI		
LED	XI075C200V054XPT1	1.2	DALI		
LED	XI075C200V054XPT1	1.4	DALI		
LED	XI075C200V054XPT1	1.5	DALI		
LED	XI075C200V054XPT1	1.6	DALI		
LED	XI075C200V054XPT1	1.7	DALI		
LED	XI075C200V054XPT1	2	DALI		
LED	XI075C200V054XPT1	2.1	DALI		
LED	XI075C200V054XPT1	2.3	DALI		
LED	XI075C200V054YPT1	1.1	DALI		
LED	XI075C200V054YPT1	1.2	DALI		
LED	XI075C200V054YPT1	1.4	DALI		
LED	XI075C200V054YPT1	1.5	DALI		
LED	XI075C200V054YPT1	1.6	DALI		
LED	XI075C200V054YPT1	2.2	DALI		
LED	XI075C200V054YPT1	2.4	DALI		
LED	XI095C275V054BSF1	1		SimpleSet	
LED	XI095C275V054BSS1	1.1		SimpleSet	
LED	XI095C275V054VPPF1M	1	DALI	SimpleSet	
LED	XI095C275V054VSF1M	1	DALI	SimpleSet	
LED	XI100C110V143BSY1	1		SimpleSet	
LED	XI100C110V143DSY1	1		SimpleSet	
LED	XI100C110V143DSY1	1.1		SimpleSet	
LED	XI100C150V091BSY1	1		SimpleSet	
LED	XI150C070V235VSF1M	1	DALI	SimpleSet	
LED	XI150C070V235VSF1M	1.1	DALI	SimpleSet	
LED	XI150C105V157VSF1M	1	DALI	SimpleSet	
LED	XI150C105V157VSF1M	1.1	DALI	SimpleSet	
LED	XI180C090V285BSF1	1.1		SimpleSet	
LED	XI180C125V200BSF1	1.1		SimpleSet	
LED	XI180C125V200PSF1	1		SimpleSet	
LED	XI180C180V144BSF1	1.1		SimpleSet	
LED	XI190C275V054BSG1	1		SimpleSet	
LED	XI190C275V054BSG1	1.1		SimpleSet	
LED	XR025C100V036YPM1M	1.1	DALI		
LED	XR025C100V036YPM1M	1.4	DALI		
LED	Xi FP 100W 0.2-0.7A SNLDAE 230V C165 sXt	1	DALI	SimpleSet	
LED	Xi FP 100W 0.2-0.7A SNLDAE 230V C165 sXt	1.1	DALI	SimpleSet	
LED	Xi FP 110W 0.3-1.0A NLD 230V C150 sXt	1.4	DALI		
LED	Xi FP 150W 0.2-0.7A SNLCDAE 230V S240 sX	1	DALI	SimpleSet	
LED	Xi FP 150W 0.2-0.7A SNLDAE 230V S240 sXt	1	DALI	SimpleSet	
LED	Xi FP 150W 0.2-0.7A SNLDAE 230V S240 sXt	1.1	DALI	SimpleSet	
LED	Xi FP 150W 0.3-1.0A SNLDAE 230V S240 sXt	1	DALI	SimpleSet	
LED	Xi FP 150W 0.3-1.0A SNLDAE 230V S240 sXt	1.1	DALI	SimpleSet	
LED	Xi FP 165W 0.2-0.7A SNLDAE 230V C170 sXt	1	DALI	SimpleSet	
LED	Xi FP 165W 0.2-0.7A SNLDAE 230V C170 sXt	1.1	DALI	SimpleSet	
LED	Xi FP 165W 0.2-0.7A SNLDAE 230V C170 sXt	1.2	DALI	SimpleSet	

LED	Xi FP 165W 0.2-0.7A SNLDAE 230V C170 sXt	1.3	DALI	SimpleSet	
LED	Xi FP 165W 0.3-1.0A SNLDAE 230V C170 sXt	1	DALI	SimpleSet	
LED	Xi FP 165W 0.3-1.0A SNLDAE 230V C170 sXt	1.1	DALI	SimpleSet	
LED	Xi FP 165W 0.3-1.0A SNLDAE 230V C170 sXt	1.2	DALI	SimpleSet	
LED	Xi FP 165W 0.3-1.0A SNLDAE 230V C170 sXt	1.3	DALI	SimpleSet	
LED	Xi FP 22W 0.2-0.7A SNLDAE 230V C123 sXt	2	DALI	SimpleSet	
LED	Xi FP 22W 0.2-0.7A SNLDAE 230V S175 sXt	2	DALI	SimpleSet	
LED	Xi FP 22W 0.3-1.0A SNLDAE 230V C123 sXt	1	DALI	SimpleSet	
LED	Xi FP 22W 0.3-1.0A SNLDAE 230V C123 sXt	2	DALI	SimpleSet	
LED	Xi FP 22W 0.3-1.0A SNLDAE 230V S175 sXt	1	DALI	SimpleSet	
LED	Xi FP 22W 0.3-1.0A SNLDAE 230V S175 sXt	1.1	DALI	SimpleSet	
LED	Xi FP 22W 0.3-1.0A SNLDAE 230V S175 sXt	2	DALI	SimpleSet	
LED	Xi FP 330W 2:0.2-0.75A SNDAE C240 sXt	1	DALI	SimpleSet	
LED	Xi FP 35W 0.3-1.0A NLD 230V C150 sXt	1.4	DALI		
LED	Xi FP 40W 0.2-0.7A SNLDAE 230V C123 sXt	1	DALI	SimpleSet	
LED	Xi FP 40W 0.2-0.7A SNLDAE 230V C123 sXt	2	DALI	SimpleSet	
LED	Xi FP 40W 0.2-0.7A SNLDAE 230V S175 sXt	1	DALI	SimpleSet	
LED	Xi FP 40W 0.2-0.7A SNLDAE 230V S175 sXt	1.1	DALI	SimpleSet	
LED	Xi FP 40W 0.2-0.7A SNLDAE 230V S175 sXt	2	DALI	SimpleSet	
LED	Xi FP 40W 0.3-1.0A SNLDAE 230V C123 sXt	1	DALI	SimpleSet	
LED	Xi FP 40W 0.3-1.0A SNLDAE 230V C123 sXt	2	DALI	SimpleSet	
LED	Xi FP 40W 0.3-1.0A SNLDAE 230V S175 sXt	1	DALI	SimpleSet	
LED	Xi FP 40W 0.3-1.0A SNLDAE 230V S175 sXt	1.1	DALI	SimpleSet	
LED	Xi FP 40W 0.3-1.0A SNLDAE 230V S175 sXt	2	DALI	SimpleSet	
LED	Xi FP 70W 0.3-1.0A NLD 230V C150 sXt	1.4	DALI		
LED	Xi FP 75W 0.2-0.7A SNLCDAE 230V S240 sX	1	DALI	SimpleSet	
LED	Xi FP 75W 0.2-0.7A SNLDAE 230V C133 sXt	1	DALI	SimpleSet	
LED	Xi FP 75W 0.2-0.7A SNLDAE 230V S240 sXt	1	DALI	SimpleSet	
LED	Xi FP 75W 0.2-0.7A SNLDAE 230V S240 sXt	1.1	DALI	SimpleSet	
LED	Xi FP 75W 0.3-1.0A SNLDAE 230V C133 sXt	1	DALI	SimpleSet	
LED	Xi FP 75W 0.3-1.0A SNLDAE 230V S240 sXt	1	DALI	SimpleSet	
LED	Xi FP 75W 0.3-1.0A SNLDAE 230V S240 sXt	1.1	DALI	SimpleSet	
LED	Xi FP 75W 0.5-1.5A SNLDAE 230V C133 sXt	1	DALI	SimpleSet	
LED	Xi LP 100W 0.3-1.05A S1 230V I175	1		SimpleSet	
LED	Xi LP 100W 0.3-1.05A S1 230V I175C	1		SimpleSet	
LED	Xi LP 110W 0.2-0.7A S1 230V C150 sXt	1.1		SimpleSet	
LED	Xi LP 110W 0.2-0.7A S1 230V C150 sXt	1.2		SimpleSet	
LED	Xi LP 110W 0.2-0.7A SL 230V C150 sXt	1.1		SimpleSet	
LED	Xi LP 110W 0.2-0.7A SL 230V C150 sXt	1.2		SimpleSet	
LED	Xi LP 110W 0.3-1.0A S1 230V C150 sXt	1.1		SimpleSet	
LED	Xi LP 110W 0.3-1.0A S1 230V C150 sXt	1.2		SimpleSet	
LED	Xi LP 110W 0.3-1.0A SL 230V C150 sXt	1.1		SimpleSet	
LED	Xi LP 110W 0.3-1.0A SL 230V C150 sXt	1.2		SimpleSet	
LED	Xi LP 150W 0.2-0.7A S1 230V S240 sXt	1		SimpleSet	
LED	Xi LP 150W 0.2-0.7A S1 230V S240 sXt	2		SimpleSet	
LED	Xi LP 150W 0.2-0.7A SL 230V S240 sXt	1		SimpleSet	
LED	Xi LP 150W 0.2-0.7A SN 230V S240 sXt	1		SimpleSet	
LED	Xi LP 150W 0.3-1.05A S1 230V I175	1		SimpleSet	
LED	Xi LP 150W 0.3-1.05A S1 230V I175C	1		SimpleSet	

LED	Xi LP 150W 0.3-1.0A S1 230V S240 sXt	1		SimpleSet	
LED	Xi LP 150W 0.3-1.0A S1 230V S240 sXt	2		SimpleSet	
LED	Xi LP 150W 0.3-1.0A SL 230V S240 sXt	1		SimpleSet	
LED	Xi LP 150W 0.5-1.5A S1 230V S240 sXt	1		SimpleSet	
LED	Xi LP 150W 0.5-1.5A S1 230V S240 sXt	2		SimpleSet	
LED	Xi LP 165W 0.2-0.7A S1 230V C170 sXt	1		SimpleSet	
LED	Xi LP 165W 0.3-1.0A S1 230V C170 sXt	1		SimpleSet	
LED	Xi LP 165W 0.5-1.5A S1 230V C170 sXt	1		SimpleSet	
LED	Xi LP 22W 0.2-0.7A S1 230V S175 sXt	2		SimpleSet	
LED	Xi LP 22W 0.3-1.0A S1 230V C123 sXt	1		SimpleSet	
LED	Xi LP 22W 0.3-1.0A S1 230V S175 sXt	2		SimpleSet	
LED	Xi LP 35W 0.3-1.0A S1 230V C150 sXt	1.2		SimpleSet	
LED	Xi LP 40W 0.2-0.7A S1 230V C123 sXt	1		SimpleSet	
LED	Xi LP 40W 0.2-0.7A S1 230V S175 sXt	1.1		SimpleSet	
LED	Xi LP 40W 0.2-0.7A S1 230V S175 sXt	1.2		SimpleSet	
LED	Xi LP 40W 0.2-0.7A S1 230V S175 sXt	2		SimpleSet	
LED	Xi LP 40W 0.2-0.7A SL 230V S175 sXt	1.1		SimpleSet	
LED	Xi LP 40W 0.2-0.7A SL 230V S175 sXt	1.2		SimpleSet	
LED	Xi LP 40W 0.2-0.7A SN 230V S175 sXt	1.2		SimpleSet	
LED	Xi LP 40W 0.3-1.0A S1 230V C123 sXt	1		SimpleSet	
LED	Xi LP 40W 0.3-1.0A S1 230V S175 sXt	1.1		SimpleSet	
LED	Xi LP 40W 0.3-1.0A S1 230V S175 sXt	1.2		SimpleSet	
LED	Xi LP 40W 0.3-1.0A S1 230V S175 sXt	2		SimpleSet	
LED	Xi LP 40W 0.3-1.0A SL 230V S175 sXt	1.1		SimpleSet	
LED	Xi LP 40W 0.3-1.0A SL 230V S175 sXt	1.2		SimpleSet	
LED	Xi LP 70W 0.2-0.7A S1 230V C150 sXt	1.1		SimpleSet	
LED	Xi LP 70W 0.2-0.7A S1 230V C150 sXt	1.2		SimpleSet	
LED	Xi LP 70W 0.2-0.7A SL 230V C150 sXt	1.1		SimpleSet	
LED	Xi LP 70W 0.2-0.7A SL 230V C150 sXt	1.2		SimpleSet	
LED	Xi LP 70W 0.3-1.0A S1 230V C150 sXt	1.1		SimpleSet	
LED	Xi LP 70W 0.3-1.0A S1 230V C150 sXt	1.2		SimpleSet	
LED	Xi LP 70W 0.3-1.0A SL 230V C150 sXt	1.1		SimpleSet	
LED	Xi LP 70W 0.3-1.0A SL 230V C150 sXt	1.2		SimpleSet	
LED	Xi LP 75W 0.2-0.7A S1 230V S240 sXt	1		SimpleSet	
LED	Xi LP 75W 0.2-0.7A S1 230V S240 sXt	2		SimpleSet	
LED	Xi LP 75W 0.2-0.7A SL 230V S240 sXt	1		SimpleSet	
LED	Xi LP 75W 0.2-0.7A SN 230V S240 sXt	1		SimpleSet	
LED	Xi LP 75W 0.3-1.0A S1 230V S240 sXt	1		SimpleSet	
LED	Xi LP 75W 0.3-1.0A S1 230V S240 sXt	2		SimpleSet	
LED	Xi LP 75W 0.3-1.0A SL 230V S240 sXt	1		SimpleSet	
LED	Xi LP 75W 0.5-1.5A S1 230V S240 sXt	2		SimpleSet	
LED	Xi SR 12W 0.2-0.7A SNEMP 230V C133 sXt	1	DALI	SimpleSet	
LED	Xi SR 150W 0.2-0.7A SNDAEMP 230V S240 sXt	1	DALI	SimpleSet	
LED	Xi SR 150W 0.2-0.7A SNEMP 230V S240 sXt	1	DALI	SimpleSet	
LED	Xi SR 150W 0.2-0.7A SNEMP 230V S240 sXt	1.1	DALI	SimpleSet	
LED	Xi SR 150W 0.2-0.7A SNEMP 230V S240 sXt	1.2	DALI	SimpleSet	
LED	Xi SR 150W 0.2-0.7A SNEMP 230V S240 sXt	1.3	DALI	SimpleSet	
LED	Xi SR 150W 0.2-0.7A SNEMP 230V S240 sXt	1.4	DALI	SimpleSet	
LED	Xi SR 150W 0.3-1.0A SNEMP 230V S240 sXt	1	DALI	SimpleSet	

LED	Xi SR 150W 0.3-1.0A SNEMP 230V S240 sXt	1.1	DALI	SimpleSet	
LED	Xi SR 150W 0.3-1.0A SNEMP 230V S240 sXt	1.2	DALI	SimpleSet	
LED	Xi SR 150W 0.3-1.0A SNEMP 230V S240 sXt	1.3	DALI	SimpleSet	
LED	Xi SR 150W 0.3-1.0A SNEMP 230V S240 sXt	1.4	DALI	SimpleSet	
LED	Xi SR 22W 0.2-0.7A SNEMP 230V C133 sXt	1	DALI	SimpleSet	
LED	Xi SR 22W 0.3-1.0A SNEMP 230V C133 sXt	1	DALI	SimpleSet	
LED	Xi SR 40W 0.2-0.7A SNEMP 230V C133 sXt	1	DALI	SimpleSet	
LED	Xi SR 40W 0.2-0.7A SNEMP 230V C133 sXt	1.1	DALI	SimpleSet	
LED	Xi SR 40W 0.3-1.0A SNEMP 230V C133 sXt	1	DALI	SimpleSet	
LED	Xi SR 75W 0.2-0.7A SNDAEMP 230V S240 sXt	1	DALI	SimpleSet	
LED	Xi SR 75W 0.2-0.7A SNEMP 230V S240 sXt	1	DALI	SimpleSet	
LED	Xi SR 75W 0.2-0.7A SNEMP 230V S240 sXt	1.1	DALI	SimpleSet	
LED	Xi SR 75W 0.2-0.7A SNEMP 230V S240 sXt	1.2	DALI	SimpleSet	
LED	Xi SR 75W 0.2-0.7A SNEMP 230V S240 sXt	1.3	DALI	SimpleSet	
LED	Xi SR 75W 0.2-0.7A SNEMP 230V S240 sXt	1.4	DALI	SimpleSet	
LED	Xi SR 75W 0.3-1.0A SNEMP 230V S240 sXt	1	DALI	SimpleSet	
LED	Xi SR 75W 0.3-1.0A SNEMP 230V S240 sXt	1.1	DALI	SimpleSet	
LED	Xi SR 75W 0.3-1.0A SNEMP 230V S240 sXt	1.2	DALI	SimpleSet	
LED	Xi SR 75W 0.3-1.0A SNEMP 230V S240 sXt	1.3	DALI	SimpleSet	
LED	Xi SR 75W 0.3-1.0A SNEMP 230V S240 sXt	1.4	DALI	SimpleSet	
LED	Xitanium 100W 0.15-0.5A 300V CL 230V iXt	2	DALI	SimpleSet	
LED	Xitanium 100W 0.15-0.5A 300V SR 230V iXt	2	DALI	SimpleSet	
LED	Xitanium 100W 0.15-0.5A 300V SR 230V iXt	2.1	DALI	SimpleSet	
LED	Xitanium 100W 0.15-0.5A 300V TD 230V iXt	2	DALI	SimpleSet	
LED	Xitanium 100W 0.15-0.5A 300V iXt 230V	1		SimpleSet	
LED	Xitanium 100W 0.15-0.5A 300V iXt TD 230V	2.1	DALI	SimpleSet	
LED	Xitanium 100W 0.25-0.7A 220V S 230V	1		SimpleSet	
LED	Xitanium 100W 0.25-0.7A 220V SR 230V	2	DALI	SimpleSet	
LED	Xitanium 100W 0.25-0.7A 220V TD16 230V	2	DALI	SimpleSet	
LED	Xitanium 100W 0.25-0.7A 220V TD16 230V	2.1	DALI	SimpleSet	
LED	Xitanium 110W 0.2-0.6A 215V TD 230V iXt	1	DALI		
LED	Xitanium 110W 0.2-0.6A 215V TD 230V iXt	1.1	DALI		
LED	Xitanium 110W 0.2-0.6A 215V TD 230V iXt	1.2	DALI		
LED	Xitanium 110W 0.2-0.6A 215V TD 230V iXt	1.3	DALI		
LED	Xitanium 150W 0.2-0.7A 300V CL 230V iXt	2	DALI	SimpleSet	
LED	Xitanium 150W 0.2-0.7A 300V SR 230V iXt	2	DALI	SimpleSet	
LED	Xitanium 150W 0.2-0.7A 300V SR 230V iXt	2.1	DALI	SimpleSet	
LED	Xitanium 150W 0.2-0.7A 300V TD 230V iXt	1.1	DALI		
LED	Xitanium 150W 0.2-0.7A 300V TD 230V iXt	1.2	DALI		
LED	Xitanium 150W 0.2-0.7A 300V TD 230V iXt	2	DALI	SimpleSet	
LED	Xitanium 150W 0.2-0.7A 300V iXt 230V	1		SimpleSet	
LED	Xitanium 150W 0.2-0.7A 300V iXt TD 230V	2.1	DALI	SimpleSet	
LED	Xitanium 150W 0.7A sProg 230V-6 I66	2.3	DALI		
LED	Xitanium 150W 0.7A sProg 230V-6 I66	3.3	DALI		
LED	Xitanium 150W 0.7A sProg 230V-6C I66	2.3	DALI		
LED	Xitanium 150W 0.7A sProg 230V-6C I66	3.3	DALI		
LED	Xitanium 150W 1.1A Prog+ GL-F sXt	1.1	DALI		
LED	Xitanium 150W 1.2A sProg 230V-F sXt	1.2	DALI		
LED	Xitanium 150W 1.2A sProg GL-F sXt	1.2	DALI		

LED	Xitanium 17W 0.12-0.4A 54V 1-10V 230V	1.7	DALI		
LED	Xitanium 17W 0.12-0.4A 54V TD 230V	1.13	DALI		
LED	Xitanium 17W 0.12-0.4A 54V TD 230V	1.14	DALI		
LED	Xitanium 17W 0.12-0.4A 54V TD 230V	1.7	DALI		
LED	Xitanium 17W 0.3-1A 24V TD/Is 230V	1	DALI		
LED	Xitanium 17W 0.3-1A 24V TD/Is 230V	1.1	DALI		
LED	Xitanium 17W 0.3-1A 24V TD/Is 230V	1.2	DALI		
LED	Xitanium 17W 0.3-1A 24V TD/Is 230V	1.3	DALI		
LED	Xitanium 20W 0.1-0.56A 54V 0-10V 120-277	1		SimpleSet	
LED	Xitanium 20W LH 0.15-0.5A 48V 230V	1		SimpleSet	
LED	Xitanium 20W LH 0.15-0.5A 48V TD/Is 230V	1.2	DALI		
LED	Xitanium 20W WH 0.15-0.5A 54V Is	1		SimpleSet	
LED	Xitanium 20W WH 0.15-0.5A 54V S	1		SimpleSet	
LED	Xitanium 20W WH 0.15-0.5A 54V TD/Is 230V	1	DALI	SimpleSet	
LED	Xitanium 20W WH 0.15-0.5A 54V TD/Is 230V	1.1	DALI	SimpleSet	
LED	Xitanium 20W WH 0.15-0.5A 54V TD/Is CL	1	DALI	SimpleSet	
LED	Xitanium 20W/m 0.15-0.5A 54V 230V	1		SimpleSet	
LED	Xitanium 20W/m 0.15-0.5A 54V TD 230V	1.8	DALI		
LED	Xitanium 25W 0-10V 120V/277V	1.1	DALI		
LED	Xitanium 25W 0-10V 120V/277V	1.18	DALI		
LED	Xitanium 25W 0-10V 120V/277V	1.4	DALI		
LED	Xitanium 25W 0-10V 120V/277V	1.5	DALI		
LED	Xitanium 25W 0-10V 120V/277V	1.6	DALI		
LED	Xitanium 25W 0-10V 120V/277V	1.7	DALI		
LED	Xitanium 25W 0-10V 120V/277V	1.9	DALI		
LED	Xitanium 25W 0.3-1A 36V TD/Is 230V	1.2	DALI		
LED	Xitanium 25W 0.3-1A 36V TD/Is 230V	1.3	DALI		
LED	Xitanium 25W 0.3-1A 36V TD/Is 230V	1.4	DALI		
LED	Xitanium 300W 0.1-1.5A 0-10V 120-277V	1		SimpleSet	
LED	Xitanium 300W 0.1-1.5A 0-10V 120-277V	1.1		SimpleSet	
LED	Xitanium 300W 1.5A Prog+ GL-F2 sXt	1.1	DALI		
LED	Xitanium 35W 0.08-0.35A 150V S 230V	1		SimpleSet	
LED	Xitanium 35W 0.08-0.35A 150V S/16 230V	1		SimpleSet	
LED	Xitanium 35W 0.08-0.35A 150V SR 230V	2	DALI	SimpleSet	
LED	Xitanium 35W 0.08-0.35A 150V SR 230V	2.1	DALI	SimpleSet	
LED	Xitanium 35W 0.08-0.35A 150V TD 230V	2	DALI	SimpleSet	
LED	Xitanium 35W 0.08-0.35A 150V TD16 230V	2	DALI	SimpleSet	
LED	Xitanium 35W 0.08-0.35A 150V TD16 230V	2.1	DALI	SimpleSet	
LED	Xitanium 36W 0.12-0.4A 100V 1-10V 230V	1.7	DALI		
LED	Xitanium 36W 0.12-0.4A 100V TD 230V	1.13	DALI		
LED	Xitanium 36W 0.12-0.4A 100V TD 230V	1.14	DALI		
LED	Xitanium 36W 0.12-0.4A 100V TD 230V	1.16	DALI		
LED	Xitanium 36W 0.12-0.4A 100V TD 230V	1.17	DALI		
LED	Xitanium 36W 0.12-0.4A 100V TD 230V	1.7	DALI		
LED	Xitanium 36W 0.12-0.4A 110V TD 230V	1.3	DALI		
LED	Xitanium 36W 0.12-0.4A 110V TD 230V	1.4	DALI		
LED	Xitanium 36W 0.12-0.4A 110V TD 230V	1.5	DALI		
LED	Xitanium 36W 0.12-0.4A 110V TD 230V	2	DALI		
LED	Xitanium 36W 0.12-0.4A 110V TD 230V	2.1	DALI		

LED	Xitanium 36W 0.3-1.05A 54V S 230V	1		SimpleSet	
LED	Xitanium 36W 0.3-1A 54V SR 230V	4	DALI	SimpleSet	
LED	Xitanium 36W 0.3-1A 54V SR 230V	4.1	DALI	SimpleSet	
LED	Xitanium 36W 0.3-1A 54V SR 230V	4.2	DALI	SimpleSet	
LED	Xitanium 36W 0.3-1A 54V TD 230V	1.1	DALI		
LED	Xitanium 36W 0.3-1A 54V TD 230V	1.2	DALI		
LED	Xitanium 36W 0.3-1A 54V TD 230V	1.3	DALI		
LED	Xitanium 36W 0.3-1A 54V TD 230V	1.5	DALI		
LED	Xitanium 36W 0.3-1A 54V TD 230V	1.6	DALI		
LED	Xitanium 36W 0.3-1A 54V TD 230V	1.7	DALI		
LED	Xitanium 36W 0.3-1A 54V TD 230V	1.8	DALI		
LED	Xitanium 36W 0.3-1A 54V TD 230V	1.9	DALI		
LED	Xitanium 36W 0.3-1A 54V TD 230V	4	DALI	SimpleSet	
LED	Xitanium 36W 0.3-1A 54V TD 230V	4.1	DALI	SimpleSet	
LED	Xitanium 36W LH 0.3-1A 48V I 230V	1		SimpleSet	
LED	Xitanium 36W LH 0.3-1A 48V TD/I 230V	1.1	DALI		
LED	Xitanium 36W LH 0.3-1A 48V TD/I 230V	1.2	DALI		
LED	Xitanium 36W LH 0.3-1A 48V TD/I 230V	1.3	DALI		
LED	Xitanium 36W LH 0.3-1A 48V TD/I 230V	1.4	DALI		
LED	Xitanium 36W WH 0.3-1.05A 54V Is	1		SimpleSet	
LED	Xitanium 36W WH 0.3-1.05A 54V S	1		SimpleSet	
LED	Xitanium 36W WH 0.3-1A 54V TD/Is 230V	1	DALI	SimpleSet	
LED	Xitanium 36W WH 0.3-1A 54V TD/Is 230V	1.1	DALI	SimpleSet	
LED	Xitanium 36W WH 0.3-1A 54V TD/Is 230V	1.3	DALI	SimpleSet	
LED	Xitanium 36W WH 0.3-1A 54V TD/Is 230V	1.4	DALI	SimpleSet	
LED	Xitanium 36W WH 0.3-1A 54V TD/Is 230V	1.5	DALI	SimpleSet	
LED	Xitanium 36W WH 0.3-1A 54V TD/Is CL	1	DALI	SimpleSet	
LED	Xitanium 36W/S 0.3-1A 48V TD 230V	1	DALI		
LED	Xitanium 36W/S 0.3-1A 48V TD 230V	1.1	DALI		
LED	Xitanium 36W/m 0.3-1.05A 54V 230V	1		SimpleSet	
LED	Xitanium 36W/m 0.3-1.05A 54V OffDiag	1		SimpleSet	
LED	Xitanium 36W/m 0.3-1.05A 54V TD 230V	1.5	DALI		
LED	Xitanium 40W 0.1-1.1A 54V 0-10V 120-277V	1		SimpleSet	
LED	Xitanium 40W 0.1-1.1A 54V 0-10V 120-277V	1.1		SimpleSet	
LED	Xitanium 40W 0.1-1.1A 54V 0-10V 120-277V	1.2		SimpleSet	
LED	Xitanium 40W 0.1-1.1A 54V 0-10V 120-277V	1.3		SimpleSet	
LED	Xitanium 40W 1.1A 54V DALI INT	2	DALI	SimpleSet	
LED	Xitanium 40W 1.1A 54V DALI SR INT	1	DALI	SimpleSet	
LED	Xitanium 40W 1.1A 54V DALI SR INT	1.2	DALI	SimpleSet	
LED	Xitanium 40W 1.1A 54V DALI SR INT	1.3	DALI	SimpleSet	
LED	Xitanium 40W 1.1A 54V DALI SR INT	1.4	DALI	SimpleSet	
LED	Xitanium 40W 1.1A 54V DALI SR INT	1.5	DALI	SimpleSet	
LED	Xitanium 40W 1.1A 54V DALI SR INT	2	DALI	SimpleSet	
LED	Xitanium 40W 1.1A 54V DALI SR INT	2.1	DALI	SimpleSet	
LED	Xitanium 40W 1.1A 54V DALI SR JPN	2	DALI	SimpleSet	
LED	Xitanium 40W/t 0.3-1A 54V TD 230V PCBA	1	DALI	SimpleSet	
LED	Xitanium 43W/m 0.7-1.2A 54V 230V	1		SimpleSet	
LED	Xitanium 50/75W 0.3-1A 62V TD/TE 230V	1	DALI		
LED	Xitanium 50W 0.3-1A 62V TD/Is 230V	1.1	DALI		

LED	Xitanium 50W 0.3-1A 62V TD/Is 230V	1.2	DALI		
LED	Xitanium 50W 0.3-1A 62V TD/Is 230V	1.3	DALI		
LED	Xitanium 50W 0.3-1A 62V TD/TE 230V	1.1	DALI		
LED	Xitanium 50W 0.3-1A 62V TD/TE 230V	1.11	DALI		
LED	Xitanium 50W 0.3-1A 62V TD/TE 230V	1.16	DALI		
LED	Xitanium 50W 0.3-1A 62V TD/TE 230V	1.18	DALI		
LED	Xitanium 50W 0.3-1A 62V TD/TE 230V	1.8	DALI		
LED	Xitanium 50W LH 0.7-1.5A 48V 230V	1		SimpleSet	
LED	Xitanium 50W LH 0.7-1.5A 48V 230V	1.1		SimpleSet	
LED	Xitanium 50W LH 0.7-1.5A 48V TD/I 230V	1.1	DALI		
LED	Xitanium 50W WH 0.7-1.5A 54V Is	1		SimpleSet	
LED	Xitanium 50W WH 0.7-1.5A 54V S	1		SimpleSet	
LED	Xitanium 50W WH 0.7-1.5A 54V TD/Is 230V	1	DALI	SimpleSet	
LED	Xitanium 50W WH 0.7-1.5A 54V TD/Is CL	1	DALI	SimpleSet	
LED	Xitanium 50W/m 0.7-1.5A 54V 230V	1		SimpleSet	
LED	Xitanium 54W 0.1-1.5A 54V 0-10V 347V	1		SimpleSet	
LED	Xitanium 60W 0.08-0.35A 220V S 230V	1		SimpleSet	
LED	Xitanium 60W 0.08-0.35A 220V S/16 230V	1		SimpleSet	
LED	Xitanium 60W 0.08-0.35A 220V SR 230V	2	DALI	SimpleSet	
LED	Xitanium 60W 0.08-0.35A 220V SR 230V	2.1	DALI	SimpleSet	
LED	Xitanium 60W 0.08-0.35A 220V TD16 230V	2	DALI	SimpleSet	
LED	Xitanium 60W 0.08-0.35A 300V CL 230V	2	DALI	SimpleSet	
LED	Xitanium 60W 0.08-0.35A 300V S 230V	1		SimpleSet	
LED	Xitanium 60W 0.08-0.35A 300V S/16 230V	1		SimpleSet	
LED	Xitanium 60W 0.08-0.35A 300V SR 230V	2	DALI	SimpleSet	
LED	Xitanium 60W 0.08-0.35A 300V SR 230V	2.1	DALI	SimpleSet	
LED	Xitanium 60W 0.08-0.35A 300V TD 230V	2	DALI	SimpleSet	
LED	Xitanium 60W 0.08-0.35A 300V TD16 230V	2	DALI	SimpleSet	
LED	Xitanium 60W 0.08-0.35A 300V TD16 230V	2.1	DALI	SimpleSet	
LED	Xitanium 65W 0.5-1.4A 54V S 230V	1		SimpleSet	
LED	Xitanium 75W 0.1-2.0A 54V 0-10V 120-277V	1		SimpleSet	
LED	Xitanium 75W 0.1-2.0A 54V 0-10V 120-277V	1.1		SimpleSet	
LED	Xitanium 75W 0.12-0.4A 215V TD 230V	1.3	DALI		
LED	Xitanium 75W 0.12-0.4A 215V TD 230V	1.4	DALI		
LED	Xitanium 75W 0.12-0.4A 215V TD 230V	1.5	DALI		
LED	Xitanium 75W 0.12-0.4A 215V TD 230V	1.6	DALI		
LED	Xitanium 75W 0.12-0.4A 215V TD 230V	2	DALI		
LED	Xitanium 75W 0.12-0.4A 215V TD CL 230V	1.3	DALI		
LED	Xitanium 75W 0.7-2A 54V 0-10V 230V	1.3	DALI		
LED	Xitanium 75W 0.7-2A 54V 0-10V 230V	1.4	DALI		
LED	Xitanium 75W 0.7-2A 54V 0-10V 230V	1.5	DALI		
LED	Xitanium 75W 0.7-2A 54V 0-10V 230V	1.6	DALI		
LED	Xitanium 75W 0.7-2A 54V 0-10V 230V	1.7	DALI		
LED	Xitanium 75W 0.7-2A 54V 0-10V 230V	2	DALI		
LED	Xitanium 75W 0.7-2A 54V 0-10V 230V	2.1	DALI		
LED	Xitanium 75W 0.7-2A 54V SR 230V	4	DALI	SimpleSet	
LED	Xitanium 75W 0.7-2A 54V SR 230V	4.1	DALI	SimpleSet	
LED	Xitanium 75W 0.7-2A 54V TD 230V	1.3	DALI		
LED	Xitanium 75W 0.7-2A 54V TD 230V	1.4	DALI		

LED	Xitanium 75W 0.7-2A 54V TD 230V	1.5	DALI		
LED	Xitanium 75W 0.7-2A 54V TD 230V	1.6	DALI		
LED	Xitanium 75W 0.7-2A 54V TD 230V	2.2	DALI		
LED	Xitanium 75W 0.7-2A 54V TD 230V	2.4	DALI		
LED	Xitanium 75W 0.7-2A 54V TD 230V	3	DALI		
LED	Xitanium 75W 0.7-2A 54V TD 230V	3.1	DALI		
LED	Xitanium 75W 0.7-2A 54V TD 230V	3.2	DALI		
LED	Xitanium 75W 0.7-2A 54V TD 230V	4	DALI	SimpleSet	
LED	Xitanium 75W 0.7-2A 54V TD 230V	4.1	DALI	SimpleSet	
LED	Xitanium 75W 1.1A Prog+ GL-F sXt	1.1	DALI		
LED	Xitanium 75W 1.2A sProg 230V-F sXt	1.2	DALI		
LED	Xitanium 75W 1.2A sProg GL-F sXt	1.2	DALI		
LED	Xitanium 75W 2A 54V DALI INT	2	DALI	SimpleSet	
LED	Xitanium 75W 2A 54V DALI SR INT	1	DALI	SimpleSet	
LED	Xitanium 75W 2A 54V DALI SR INT	1.1	DALI	SimpleSet	
LED	Xitanium 75W 2A 54V DALI SR INT	1.2	DALI	SimpleSet	
LED	Xitanium 75W 2A 54V DALI SR INT	1.4	DALI	SimpleSet	
LED	Xitanium 75W 2A 54V DALI SR INT	1.5	DALI	SimpleSet	
LED	Xitanium 75W 2A 54V DALI SR INT	2	DALI	SimpleSet	
LED	Xitanium 75W 2A 54V DALI SR INT	2.1	DALI	SimpleSet	
LED	Xitanium 75W SH 0.3-1A 110V TD/I 230V	1.1	DALI		
LED	Xitanium 75W SH 0.3-1A 110V TD/I 230V	1.2	DALI		
LED	Xitanium 75W SH 0.3-1A 110V TD/I 230V	1.3	DALI		
LED	Xitanium 75W SH 0.3-1A 110V TD/I 230V	1.4	DALI		
LED	Xitanium 75W SH 0.3-1A 110V TD/I 230V	1.5	DALI		
LED	Xitanium 75W/0.15-0.4A 200V TD 230V	1.14	DALI		
LED	Xitanium 75W/0.15-0.4A 200V TD 230V	1.15	DALI		
LED	Xitanium 75W/0.15-0.4A 200V TD 230V	1.16	DALI		
LED	Xitanium 75W/0.15-0.4A 200V TD 230V	1.3	DALI		
LED	Xitanium 75W/0.2-0.4A 200V 1-10V 230V	1.3	DALI		
LED	Xitanium FULL PROG 110W1000 NL1 C150 Xt	1.3	DALI		
LED	Xitanium FULL PROG 110W1000 NLD C150 Xt	1.3	DALI		
LED	Xitanium FULL PROG 35W1000 NL1 C150 Xt	1.3	DALI		
LED	Xitanium FULL PROG 35W1000 NLD C150 Xt	1.3	DALI		
LED	Xitanium FULL PROG 70W1000 NL1 C150 Xt	1.3	DALI		
LED	Xitanium FULL PROG 70W1000 NLD C150 Xt	1.3	DALI		
LED	Xitanium LITE PROG 110W1000 NL C150 OD	1.3	DALI		
LED	Xitanium LITE PROG 70W1000 NL C150 OD	1.3	DALI		
LED	Xitanium Outdoor 100W .53 Prog+	V02E01	DALI		
LED	Xitanium Outdoor 100W .53 Prog+	V03E01	DALI		
LED	Xitanium Outdoor 100W .53 Prog+	V04E02	DALI		
LED	Xitanium Outdoor 100W 0.7 Prog+	V02E01	DALI		
LED	Xitanium Outdoor 100W 0.7 Prog+	V03E01	DALI		
LED	Xitanium Outdoor 100W 0.7 Prog+	V04E02	DALI		
LED	Xitanium Outdoor 125W JP Prog+	V01E01	DALI		
LED	Xitanium Outdoor 125W JP Prog+	V02E01	DALI		
LED	Xitanium Outdoor 125W JP Prog+	V03E02	DALI		
LED	Xitanium Outdoor 125W JP Prog+	V04E03	DALI		
LED	Xitanium Outdoor 125W JP Prog+	V05E03	DALI		

LED	Xitanium Outdoor 125W JP Prog+	V06E03	DALI		
LED	Xitanium Outdoor 150W .35 Prog+ H	V01E01	DALI		
LED	Xitanium Outdoor 150W .35 Prog+ H	V02E01	DALI		
LED	Xitanium Outdoor 150W .35 Prog+ H	V03E02	DALI		
LED	Xitanium Outdoor 150W .35 Prog+ H	V04E03	DALI		
LED	Xitanium Outdoor 150W .35 Prog+ H	V05E03	DALI		
LED	Xitanium Outdoor 150W .35 Prog+ H	V06E03	DALI		
LED	Xitanium Outdoor 150W 0.7 DD Prog+ 230V	V05E05	DALI		
LED	Xitanium Outdoor 150W 0.7 Prog+ 230V	V01E01	DALI		
LED	Xitanium Outdoor 150W 0.7 Prog+ 230V	V02E01	DALI		
LED	Xitanium Outdoor 150W 0.7 Prog+ 230V	V03E01	DALI		
LED	Xitanium Outdoor 150W 0.7 Prog+ H	V02E01	DALI		
LED	Xitanium Outdoor 150W 0.7 Prog+ H	V03E02	DALI		
LED	Xitanium Outdoor 150W 0.7 Prog+ H	V04E02	DALI		
LED	Xitanium Outdoor 150W 0.7 Prog+ H	V05E02	DALI		
LED	Xitanium Outdoor 150W 1.0 Prog+	V01E01	DALI		
LED	Xitanium Outdoor 150W 1.0 Prog+	V02E02	DALI		
LED	Xitanium Outdoor 150W 1.0 Prog+	V03E03	DALI		
LED	Xitanium Outdoor 150W 1.0 Prog+	V04E03	DALI		
LED	Xitanium Outdoor 150W 1.0 Prog+	V05E03	DALI		
LED	Xitanium Outdoor 150W Prog	V03E02	DALI		
LED	Xitanium Outdoor 150W Prog	V04E03	DALI		
LED	Xitanium Outdoor 150W Prog	V05E03	DALI		
LED	Xitanium Outdoor 150W Prog	V06E03	DALI		
LED	Xitanium Outdoor 150W Prog	V07E04	DALI		
LED	Xitanium Outdoor 150W Prog	V08E05	DALI		
LED	Xitanium Outdoor 150W Prog	V09E05	DALI		
LED	Xitanium Outdoor 150W Prog	V10E05	DALI		
LED	Xitanium Outdoor 150W Prog+	V01E01	DALI		
LED	Xitanium Outdoor 150W Prog+	V02E01	DALI		
LED	Xitanium Outdoor 150W Prog+	V03E01	DALI		
LED	Xitanium Outdoor 150W Prog+	V04E02	DALI		
LED	Xitanium Outdoor 150W Prog+	V05E03	DALI		
LED	Xitanium Outdoor 150W Prog+	V06E03	DALI		
LED	Xitanium Outdoor 150W Prog+	V07E03	DALI		
LED	Xitanium Outdoor 27W 1.0 Prog	V01E01	DALI		
LED	Xitanium Outdoor 27W 1.0 Prog	V02E01	DALI		
LED	Xitanium Outdoor 27W 1.0 Prog	V03E02	DALI		
LED	Xitanium Outdoor 40W .53 Prog+	V01E01	DALI		
LED	Xitanium Outdoor 40W .53 Prog+	V02E01	DALI		
LED	Xitanium Outdoor 40W .53 Prog+	V03E02	DALI		
LED	Xitanium Outdoor 40W 0.7 Prog 230V	V01E01	DALI		
LED	Xitanium Outdoor 40W 0.7 Prog 230V	V02E01	DALI		
LED	Xitanium Outdoor 40W 0.7 Prog 230V	V03E02	DALI		
LED	Xitanium Outdoor 40W 0.7 Prog+	V01E01	DALI		
LED	Xitanium Outdoor 40W 0.7 Prog+	V02E01	DALI		
LED	Xitanium Outdoor 40W 0.7 Prog+	V03E01	DALI		
LED	Xitanium Outdoor 40W 0.7 Prog+	V04E02	DALI		
LED	Xitanium Outdoor 75W 0.7 Prog+	V02E01	DALI		

LED	Xitanium Outdoor 75W 0.7 Prog+	V03E01	DALI		
LED	Xitanium Outdoor 75W 0.7 Prog+	V04E02	DALI		
LED	Xitanium Outdoor 75W 0.7 Prog+ 230V	V01E01	DALI		
LED	Xitanium Outdoor 75W 0.7 Prog+ 230V	V02E01	DALI		
LED	Xitanium Outdoor 75W 0.7 Prog+ 230V	V03E01	DALI		
LED	Xitanium Outdoor 75W 1.0 Prog+	V01E01	DALI		
LED	Xitanium Outdoor 75W 1.0 Prog+	V02E02	DALI		
LED	Xitanium Outdoor 75W 1.0 Prog+	V03E03	DALI		
LED	Xitanium Outdoor 75W 1.0 Prog+	V04E03	DALI		
LED	Xitanium Outdoor 75W 1.0 Prog+	V05E03	DALI		
LED	Xitanium Outdoor 75W JP Prog+	V01E01	DALI		
LED	Xitanium Outdoor 75W JP Prog+	V02E01	DALI		
LED	Xitanium Outdoor 75W JP Prog+	V03E02	DALI		
LED	Xitanium Outdoor 75W JP Prog+	V04E03	DALI		
LED	Xitanium Outdoor 75W JP Prog+	V05E03	DALI		
LED	Xitanium Outdoor 75W JP Prog+	V06E03	DALI		
LED	Xitanium Outdoor 75W Prog	V02E02	DALI		
LED	Xitanium Outdoor 75W Prog	V03E03	DALI		
LED	Xitanium Outdoor 75W Prog	V04E03	DALI		
LED	Xitanium Outdoor 75W Prog	V05E03	DALI		
LED	Xitanium Outdoor 75W Prog	V06E04	DALI		
LED	Xitanium Outdoor 75W Prog	V07E05	DALI		
LED	Xitanium Outdoor 75W Prog	V08E05	DALI		
LED	Xitanium Outdoor 75W Prog	V09E05	DALI		
LED	Xitanium Outdoor 75W Prog+	V01E01	DALI		
LED	Xitanium Outdoor 75W Prog+	V02E01	DALI		
LED	Xitanium Outdoor 75W Prog+	V03E01	DALI		
LED	Xitanium Outdoor 75W Prog+	V04E02	DALI		
LED	Xitanium Outdoor 75W Prog+	V05E03	DALI		
LED	Xitanium Outdoor 75W Prog+	V06E03	DALI		
LED	Xitanium Outdoor 75W Prog+	V07E03	DALI		
SwitchBox	CodedLightInjector	1		SimpleSet	
SwitchBox	LLC7730/00 Coded Mains Receiver	1	DALI		
SwitchBox	SR Bridge SRB-BS	1	DALI	SimpleSet	
SwitchBox	SR Bridge SRB-BS	1.1	DALI	SimpleSet	
SwitchBox	SR Bridge SRB-LD	1	DALI	SimpleSet	
SwitchBox	SR Bridge SRB-LD	1.1	DALI	SimpleSet	
SwitchBox	Xitanium SR Bridge built-in	1	DALI	SimpleSet	
SwitchBox	Xitanium SR Bridge built-in	1.1	DALI	SimpleSet	
SwitchBox	Xitanium SR Bridge independent	1	DALI	SimpleSet	
SwitchBox	Xitanium SR Bridge independent	1.1	DALI	SimpleSet	



Document: 11-11-2017
No: SDL3 2017
Author: L.Janssens

©2017 Philips Lighting Holding B.V. All rights reserved. This document contains information relating to the Philips Lighting portfolio, intended for companies who may be interested in developing their product offering. Note that the information provided is subject to change. Philips Lighting does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract.