





Metal Halide Lamp Ballast

Catalog Number 71A5493
For 150W M102/M142 (P.S.)
60 Hz SUPER-CWA
Status: Active

DIMENSIONS AND DATA




0.25" WIDE
2 SLOTS




INPUT VOLTS	120	208	240	277	
CIRCUIT TYPE	SUPER-CWA				
POWER FACTOR (min)	90%				
REGULATION					
Line Volts	±10%				
Lamp Watts	±10%				
LINE CURRENT (Amps)					
Operating.....	1.64	0.92	0.85	0.73	
Open Circuit.....	1.98	1.00	0.95	0.81	
Starting.....	0.70	0.39	0.37	0.31	
UL TEMPERATURE RATINGS					
Insulation Class	H(180°C)				
Coil Temperature Code	1029				
MIN. AMBIENT STARTING TEMP.	-20°F or -30°C				
NOM. OPEN CIRCUIT VOLTAGE	217				
INPUT VOLTAGE AT LAMP DROPOUT.....	60	110	120	140	
INPUT WATTS	190				
RECOMMENDED FUSE (Amps).....	5	2.5	2	2	
CORE and COIL					
Dimension (A)	2.40				
Dimension (B)	3.75				
Weight (lbs.)	7.5				
Lead Lengths	12"				
CAPACITOR REQUIREMENT					
Microfarads	16.0				
Volts (min.)	300				
Fault Current Withstand (amps)					
60 Hz TEST PROCEDURES (Refer to Advance Test Procedure for HID Ballasts - Form 1270)					
High Potential Test (Volts)					
1 minute	1500				
2 seconds	2500				
Open Circuit Voltage Test (Volts)	195-239				
Short-Circuit Current Test (Amps)					
Secondary Current	1.90-2.35				
Input Current.....	0.33-0.50	0.17-0.26	0.16-0.24	0.15-0.22	-

Capacitor: 7C160M30RA



Capacitance: 16
Dia/Oval Dim: 1.65
Height: 2.75
Temp Rating: 105°C

Wiring Diagram:



Ordering Information

Order Suffix	Description

Ignitor: LI501-J4



Ballast to Lamp Distance
(BTL) = 5 feet
Temp Rating: 105°C

Data is based upon tests performed by Advance Transformer in a controlled environment and representative of relative performance. Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.

ADVANCE TRANSFORMER CO.

O'HARE INTERNATIONAL CENTER · 10275 WEST HIGGINS ROAD · ROSEMONT, IL 60018
Customer Support/Technical Service: Phone: 800-372-3331 · Fax: 847-768-7768
Corporate Offices: Phone: 800-322-2086

08/31/09