





Metal Halide Lamp Ballast

Catalog Number 71A6553A
For 1000W M141 (Pulse Start)
60 Hz SUPER-CWA
Status: Active

DIMENSIONS AND DATA




Capacitor: MD2409-000



Capacitance: 24
Dia/Oval Dim: 1.75
Height: 3.9
Temp Rating: 90°C


Ignitor: LI572-H5



Ballast to Lamp Distance
(BTL) = 5 feet
Temp Rating: 105°C

INPUT VOLTS		120	208	240	277	480
CIRCUIT TYPE	SUPER-CWA					
POWER FACTOR (min)	90%					
REGULATION						
Line Volts	±10%					
Lamp Watts	±10%					
LINE CURRENT (Amps)						
Operating.....		9.20	5.80	4.80	4.10	2.40
Open Circuit.....		4.96	3.84	2.77	2.35	0.00
Starting.....		5.77	2.91	2.78	2.39	1.38
UL TEMPERATURE RATINGS						
Insulation Class	N(200°C)					
Coil Temperature Code	1029					
MIN. AMBIENT STARTING TEMP.	-30°F or -35°C					
NOM. OPEN CIRCUIT VOLTAGE	430					
INPUT VOLTAGE AT LAMP DROPOUT.....		80	130	160	190	320
INPUT WATTS	1090					
RECOMMENDED FUSE (Amps).....		25	15	12	10	6
CORE and COIL						
Dimension (A)	3.90					
Dimension (B)	5.60					
Weight (lbs.)	22					
Lead Lengths	12"					
CAPACITOR REQUIREMENT						
Microfarads	24.0					
Volts (min.)	480					
Fault Current Withstand (amps)						
60 Hz TEST PROCEDURES (Refer to Advance Test Procedure for HID Ballasts - Form 1270)						
High Potential Test (Volts)						
1 minute	2000					
2 seconds	2500					
Open Circuit Voltage Test (Volts)	473-468					
Short-Circuit Current Test (Amps)						
Secondary Current	5.22-6.38					
Input Current.....		4.36- 6.64	2.14- 3.20	2.10- 3.14	1.82- 2.74	1.04- 1.56

Wiring Diagram:



Ordering Information

Order Suffix	Description
500.	Ballast with Ignitor and Oil Filled Capacitor

Data is based upon tests performed by Advance Transformer in a controlled environment and representative of relative performance.
Actual performance can vary depending on operating conditions. Specifications are subject to change without notice.

ADVANCE TRANSFORMER CO.

O'HARE INTERNATIONAL CENTER · 10275 WEST HIGGINS ROAD · ROSEMONT, IL 60018
Customer Support/Technical Service: Phone: 800-372-3331 · Fax: 847-768-7768
Corporate Offices: Phone: 800-322-2086

07/05/11